BW2S-D






- Natural Nylon material for indoor use
- Weather Resistant material has greater resistance to damage caused by ultraviolet light indoor or outdoor use
- Combines cable tie, mount and fastener into a single part
- Used to attach bundles to another surface such as a flat panel
- Anchor is easily pressed into a pre-formed hole and locks in place
- Wings provide constant tension for a stable, secure and rattle-free installation
- Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

■ Part Number	BW2S-D
■ RoHS Compliancy Status	Compliant
■ Part Description	Wing Push Mount Cable Tie with metal barb, 8.5" Standard cross section
■ Product Type	Cable Tie
■ Material	Nylon 6.6
- Color	Natural
CSA Certified	Yes
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	8.5
■ Length (mm)	216
■ Width (In.)	.185
■ Width (mm)	4.7
■ CE Compliant	Yes
 Cross Section 	Standard
Head Height (In.)	.370
■ Head Height (mm)	9.4
■ Locking Style	Locking
 Material Flammability Rating 	UL 94V-2
■ Max. Bundle Diameter (In.)	2.00
■ Max. Bundle Diameter (mm)	51
 Max. Continuous Use Temperature 	e 185°F (85°C)
■ Max. Panel Thickness (In.)	.156
Max. Panel Thickness (mm)	4.0
Min. Loop Tensile Strength (Lbs.)	50
■ Min. Loop Tensile Strength (N)	222

■ Nominal Hole Diameter (In.)	.250
Nominal Hole Diameter (mm)	6.4
■ Pricing Description	Cable Tie, Wing Push Mount, 8.5"L (216mm), Intermediate, Nylon, Natural
■ Thickness (In.)	.052
■ Thickness (mm)	1.3
■ Tool	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
■ Min. Order UOM	PC
■ Min. Order Qty.	500
■ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE [MIN. in (mm)	DIAMETER MAX.	A in (mm)	B in (mm)	C	in (mm)	in (mm)	F in (mm)	G in (mm)	H in (mm)	j in (mm)	MAX. PANEL THICKNESS	MIN. LOOP TENSILE bs (n)	CROSS- SECTION	WEIGHT 100 pcs lbs (g)
BW2S	.06 (1.5)	2.00 (51)	.052 (1.3)	.185 (4.7)	.300 (7.6)	.370 (9.4)	.320 (8.1)	8.5 (216)	.330 (8.4)		.74 (18.8)	.156 (4.0)	50 (222)	STANDARD	.40 (181)
BW3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.185 (4.7)	.300 (7.6)	.370 (9.4)	.320 (8.1)	12 . 5 (318)		.250 (6.4)	.74 (18.8)	.156 (4.0)	50 (222)	STANDARD	.51 (231)
BW4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.185 (4.7)	.300 (7.6)	.370 (9.4)	.320 (8.1)	15.6 (396)	.330 (8.4)	.250 (6.4)	.74 (18.8)	.156 (4.0)	50 (222)	STANDARD	.62 (281)

										DIMENSIC	NS IN PARENTHESIS ARE	E IN METRIC UN	NITS		
										DOME-TOP Barb Ty LOCKING WING PUSH MOUNT TIE - BW SERIES					
										PUSH MUUNI IIE - BW SERIES					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN					
										(.X) ± .1(2.5)(.XXX) ± .020(.51) (.XX) ± .02(.5)ANGLES ±			ECTION.		
										DRAWN BY	MAT'L;	scale NONE			
6	12/2/04	ERW		REWORDED TITLE BLOCK	0278	6				DATE 1-19-99	NYLON 6.6	DRAWING NO.	DWG A		
REV	DATE	вү	снк	DESCRIPTION	ECN -	R	CUST	SUP		JVL JVL		BT-0278	SIZE		