## PANDUIT \*

## ABMM-AT-C



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

D (N)	ABMA AT C
■ Part Number	ABMM-AT-C
<ul> <li>RoHS Compliancy Status</li> </ul>	Compliant
■ Part Description	4-Way Adhesive Backed Cable Tie Mount
■ Product Type	Cable Tie Mounts - Adhesive Backed
■ Material	ABS
■ Color	White
■ UL Recognized	E136577
■ Height (In.)	.18
■ Height (mm)	4.6
■ Length (In.)	.75
■ Length (mm)	19.1
■ Width (In.)	.75
■ Width (mm)	19.1
■ Adhesive Type	Acrylic
■ CE Compliant	CT-ACC1 / 10.96
<ul><li>Environment</li></ul>	Indoors/High Temp
■ Max. Bundle Diameter (mm) 3.7	
■ Mounting Method	Adhesive Backed
■ Pricing Description	Cable Tie Mount, Hi Tmp. Adh., .75"x.75" (19.1mm x 19.1mm), WH
<ul> <li>Used With Cable Ties</li> </ul>	M, I
■ Min. Order UOM	PC
<ul><li>Min. Order Qty.</li><li>BOM Qty. (# of Pkgs.)</li></ul>	100

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 0.750 NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH [ 19.0] RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL. USE WITH THESE WEIGHT PANDUIT CABLE TIE lbs (g)/100 pcs PART NO. 0.750 CROSS SECTIONS [ 19.0 ] MINIATURE 0.113 ABMM - AT INTERMEDIATE (51.3)TO APPLY MOUNT 1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL. 2) REMOVE PROTECTIVE LINER. 3) PLACE IN DESIRED LOCATION. 4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS. NOTES:  $0.171 \pm 0.020$ [4.39±.508] \* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR. 2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR 0.180 EASY REMOVAL OF LINER. [4.6] 3) MOUNT HAS A CONTINUOUS OPERATING (REF) TEMPERATURE OF 180°F(82°C). ADHESIVE TAPE  $0.065 \pm .010$ PRESSURE SENSITIVE TAPE 0.040(1.0) [1.57±.254] THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.30 16s(136 g)
MAX. WEIGHT ON A CLEAN, DRY, SMOOTH, ACTUAL SIZE GREASE-FREE SURFACE. (DIMENSIONS IN PARENTHESES ARE IN METRIC.) CAD FILENAME/LAYERS G00239ER\_DC\_ABMM\_AT\_08 TINLEY PARK, ILLINOIS ABMM - AT ADHESIVE BACKED MOUNT UNLESS OTHERWISE SPECIFIED. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN  $(.X) \pm --- (.XXX) \pm .020(.51)$ IN INCHES, THIRD ANGLE PROJECTION. (.XX) ± .02(.5) ANGLES ± ----DRAWN BY MAT'L: NONE ABS DRAWING NO. DWG 8 (ACRYLONITRILE BUTADIENE STYRENE) l6/29/06 l JAD REMOVE ABM20B GB0239ER 12-23-96 CHK 'D GB0239ER DATE ВΥ СНК DESCRIPTION ECN - R CUST SUP SIZE