PANDUIT

ABMM-AT-C0



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

■ Part Number	ABMM-AT-C0
■ RoHS Compliancy Status	Compliant
■ Part Description	4-Way Adhesive Backed Cable Tie Mount
■ Product Type	Cable Tie Mounts - Adhesive Backed
■ Material	Weather Resistant ABS
- Color	Black
 UL Recognized 	E136577
■ Height (In.)	.18
■ Height (mm)	4.6
■ Length (In.)	.75
■ Length (mm)	19.1
■ Width (In.)	.75
■ Width (mm)	19.1
■ Adhesive Type	Acrylic
■ CE Compliant	CT-ACC1 / 10.96
Environment	Outdoors/High Temp
■ Max. Bundle Diameter (mm)	3.7
■ Mounting Method	Adhesive Backed
 Pricing Description 	Cable Tie Mount, Hi Tmp. Adh., .75"x.75" (19.1mm x 19.1mm), WR BL
 Used With Cable Ties 	M, I
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 0.750 NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH [19.0] RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL. USE WITH THESE WEIGHT PANDUIT CABLE TIE lbs (g)/100 pcs PART NO. 0.750 CROSS SECTIONS [19.0] MINIATURE 0.113 ABMM - AT INTERMEDIATE (51.3)TO APPLY MOUNT 1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL. 2) REMOVE PROTECTIVE LINER. 3) PLACE IN DESIRED LOCATION. 4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS. NOTES: 0.171 ± 0.020 [4.39±.508] * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR. 2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR 0.180 EASY REMOVAL OF LINER. [4.6] 3) MOUNT HAS A CONTINUOUS OPERATING (REF) TEMPERATURE OF 180°F(82°C). ADHESIVE TAPE $0.065 \pm .010$ PRESSURE SENSITIVE TAPE 0.040(1.0) [1.57±.254] THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.30 16s(136 g)
MAX. WEIGHT ON A CLEAN, DRY, SMOOTH, ACTUAL SIZE GREASE-FREE SURFACE. (DIMENSIONS IN PARENTHESES ARE IN METRIC.) CAD FILENAME/LAYERS G00239ER_DC_ABMM_AT_08 TINLEY PARK, ILLINOIS ABMM - AT ADHESIVE BACKED MOUNT UNLESS OTHERWISE SPECIFIED. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN $(.X) \pm --- (.XXX) \pm .020(.51)$ IN INCHES, THIRD ANGLE PROJECTION. (.XX) ± .02(.5) ANGLES ± ----DRAWN BY MAT'L: NONE ABS DRAWING NO. DWG 8 (ACRYLONITRILE BUTADIENE STYRENE) l6/29/06 l JAD REMOVE ABM20B GB0239ER 12-23-96 CHK 'D GB0239ER DATE ВΥ СНК DESCRIPTION ECN - R CUST SUP SIZE