## HLT2I-X2






- Broadest selection of sizes, styles, and colors to meet your application needs
- Adjustable, releasable, and reusable hundreds of times ideal for applications requiring frequent moves, adds, or changes
- Hook and loop material maintains network data integrity by protecting against over-tensioning of high performance copper and fiber cables
- Easy to use and operator safe with no sharp edges

Note: Minimum 2" overlap required to achieve loop tensile rating

■ Part Number	HLT2I-X2
■ RoHS Compliancy Status	Compliant
■ Part Description	Hook & Loop Cable Tie, Loop Tie, 8.0", Intermediate cross section
■ Product Type	Cable Ties
■ Material	Nylon Loop, Polyethylene Hook
- Color	Red
<ul> <li>CSA Certified</li> </ul>	No
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	No
■ Length (In.)	8.0
■ Length (mm)	203
■ Width (In.)	.500
■ Width (mm)	12.7
■ CE Compliant	Yes
<ul> <li>Cross Section</li> </ul>	Intermediate
<ul><li>Locking Style</li></ul>	Hook & Loop
■ Max. Bundle Diameter (In.)	1.91
<ul><li>Max. Bundle Diameter (mm)</li></ul>	49
Min. Loop Tensile Strength (Lbs.	) 40
<ul><li>Min. Loop Tensile Strength (N)</li></ul>	178
■ Pricing Description	Hook & Loop Tie, Loop Style, 8.0"L (203mm), .50"W (12.7mm), Red
■ Temperature Range	0°F to 220°F
■ Thickness (In.)	.10
<ul><li>Thickness (mm)</li></ul>	2.5
<ul><li>Min. Order UOM</li></ul>	PC
■ Min. Order Qty.	10

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	in	MAX. (mm)	A in (mm)	B in (mm)	in (mm)	in (mm)	in (mm)	MIN. LOOP * TENSILE lbs.	CROSS SECTION	APPROXIMATE WEIGHT   165/100 PIECES (9)
HLT2 I	.25	1.91	.100 (2.5)	.50 (12.7)	1.50	1.00	8.0 (203)	40 (178)	INTERMEDIATE	.48 (218)
HLT3I	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)		40 (178)	INTERMEDIATE	.65 (295)

## NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR. \* 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

CAD FILENAME/LAYERS

					DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS
					SS_26938_06.PRT
					CORP. TINLEY PARK, ILLINOIS
					TAK-TY™ HOOK & LOOP CABLE TIES
					HLT SERIES

									CORP. TINLEY PARK, ILLINOIS
									TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .030 (.XX) ± .125 ANGLES ± IN INCHES, THIRD ANGLE PROJECTION.
6	1/13/06	ERW		ADDED APPROX. WEIGHT PER 100 PIECES	26938	6			DRAWN BY MAT'L: SCALE NONE
5	5/3/05	ERW	JVL	REMOVED OVAL SLOT DIMENSION TO BE CONSISTENT WITH OTHER CUSTOMER DRAWINGS	26938	5	JVL		DATE POLYETHYLENE HOOK/ DRAWING NO. DWG
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP	SS - 26938 A