TA1S10-M







- Low profile and versatile these screw-installed mounts can be ideal for applications where space is limited. Designed for four-way cable tie insertion this mount can be mounted in-line or perpendicular to the wire bundle.
- 4-way cable tie entry makes part orientation fast and easy
 - Install with a screw or rivet for a strong, secure installation
 - Small overall size allows use where space is limited
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number	TA1S10-M
RoHS Compliancy Status	Compliant
Part Description	Cable Tie Mount - Screw Applied
Material	Nylon 6.6
Color	Natural
UL Recognized	E136577
Height (In.)	.20
Height (mm)	5.1
Length (In.)	.38
Length (mm)	19.1
Width (In.)	.75
Width (mm)	9.5
CE Compliant	CT-ACC4 / 10.96
Environment	Indoors
Flammability Rating	UL94 V-2
Hole Diameter (In.)	.20
Hole Diameter (mm)	5.1
Max. Bundle Diameter (mm)	4.8
Mounting Method	#10 (M5) Screw
Pricing Description	Tie Anchor Mount, #10 Screw (M
Screw Size	#10 (M5)
Screw Size Metric	M5
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	SUFFIX	MATERIAL	"D"	REC. FAST.	WEIGHT bs/100 pcs (g)/100 pcs	USE WITH THESE CABLE TIE CROSS-SECTIONS
TA1S8	NONE -0 -30 -69	NYLON 6/6 WEATHER RESISTANT NYLON HEAT STABILIZED NYLON FLAME RETARDANT NYLON	0.170 (4.3)	#8 (M4) SCREW	0.07 (32.0)	MINIATURE INTERMEDIATE STANDARD
TAIS10	NONE - 0	NYLON 6/6 WEATHER RESISTANT NYLON	0.200	#10 (M5) SCREW	0.07 (32.0)	MINIATURE INTERMEDIATE STANDARD





NOTES:

 SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS GB0239EP_PB_TA1_02

PANDUIT COR

TINLEY PARK, ILLINOIS

TA1 - TIE ANCHOR MOUNT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5*

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MAT'L: DATE 7/9/02 JAD UPDATED .195(4.95) DIMENSION LINE GB0239EP 2 12/17/96 CHK 'D REV DATE BY CHK DESCRIPTION ECN - R CUST SUP

SEE TABLE

SCALE NONE

DRAWING NO.

GB0239EP A
SIZE