World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click **x** to remove)

Search Tips 6

Your search criteria matched only one product, shown below.

- Designed to splice two solid or stranded wires together to repair or lengthen wires
- Butted configuration provides low profile for limited space applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal wire stop assures proper length of insertion into terminal barrel
- Maximum recommended operating temperature 302°F (150°C)
- Non-insulated barrel can be used to provide an economical termination when insulation is not required

‡UL and CSA approved tooling/product combinations.



Part Number: BS10-L **RoHS Compliancy** Compliant Status: Part Description: Butt Splice, non-insulated, 12 – 10 AWG wire range. Product Type: **Splices** CSA Certified: Yes UL Listed: Yes Length (In.): .63 Angle: straight Tool: CT-100A, CT-200, CT-600-A, CT-1570, CT-2500, CT-1701‡ Wire Range: 12 - 10 AWG 4.0 - 6.0Wire Range (mm²): PC Min. Order UOM: Min. Order Qty.: 50 BOM Qty. (# of Pkgs.)

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

View Content Details

Add to My Catalog

Evaluate Design a Solution Part Drawings: Butt Splice - Non-Insulated pdf **Design a Solution**

Part Drawings:



🔼 Butt Splice - Non-Insulated pdf

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUI PART NUME		WIRE	DIMENSIONS in.					
PREFIX	PK.	SIZE AWG	±.02 A	±.01 B DIA.	±.01 C			
BS18	-C -M	22-18	62 (15.7)	.14 (3.6)	.032 (0.81)			
BS14	-C -M	16-14	62 (15.7)	.16 (4.1)	.032 (0.81)			
BS10	-D	12-10	63 (16.0)	.22 (5.6)	.040 (1.02)			

NOTES:

- 1. UL LISTED AND CSA CERTIFIED FOR:
 A. SOLID OR STRANDED COPPER WIRE
 B. 302° F (150° C) MAX. TEMP. RATING
- 2. MATERIAL:
 A. STAMPING COPPER, TIN PLATED
- 3. PACKAGE QTY: STD. PKG.-L=50 BULK PKG.-D=500 -C=100 -M=1000
- 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 5. INSTALLATION TOOLS:
 - A. UL LISTED AND CSA CERTIFIED: CT-100, CT-200, CT-570, CT-1570
 - B. PANDUIT APPROVED: CT-160, CT-260
- 6. WIRE STRIP LENGTH: 9/32 *1/32 .0 (7.1 *.8 .0)



LISTED 587H E52164



A41338_05

REV	DATE	BY	СНК	DESCRIPTION	ECN #	CUST		DAW	CHKYD	NONE	A41338
2	9-88	DW		REDRAWN WITH REVISIONS				NON-INSOLATED BOTT SPLICE			
03	10/94	ТН	RLS	UPDATED NOTES AND DIMENSIONS	02547	LA	TKE	NON-INSULATED BUTT SPLICE			
04	8/98	DL		UPDATED BS10 A DIM. WAS .72 UPDATED NOTES & WIRE STOP CONFIGURATION	07119			CORP. TINLEY PARK, ILLINOIS		TINLEY PARK, ILLINOIS	
05	2/01	KMD		DRAWING NUMBER WAS 41338A				\mathbf{D}^{y}	משטטפב		