


High Reliability Slotted Optical Switch

OPB870, OPB871, OPB872 (TX, TXV)



Features:

- 0.125" (3.175 mm) slot width
- Choice of aperture (0.050" or 0.010" width)
- PCBoard mounting
- TX and TXV devices processed to MIL-PRF-19500
- S level processing available
- Hermetically sealed components



Description:

Each **OPB870**, **OPB871** and **OPB872 (TX, TXV)** phototransistor device provides the flexibility of a custom device from a standard product line. Building from a standard housing with a 0.125" (3.175 mm) wide slot and 0.425" (mm) leads for PCBoard mounting, a user can choose aperture width, opaque or IR transmissive housing shell material and mounting tab configuration.

Housings are made from an opaque grade of injection-molded plastic to minimize sensitivity to both visible and near-infrared light. Discrete shells exposed on the parallel faces inside each device's throat are made from either IR transmissive plastic (for applications where dust protection is needed) or from opaque plastic with aperture openings (for applications that require maximum protection against ambient light).

TX and TXV devices are processed to OPTEK's military screening program patterned after MIL-PRF-19500.

Please refer to Application Bulletins 208 and 210 for additional design information and reliability (degradation) data.

Contact your local representative or OPTEK for more information.

Applications:

- Non-contact object sensing
- Assembly line automation
- Machine automation
- Equipment safety
- Machine safety
- Military and harsh environments



RoHS

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

High Reliability Slotted Optical Switch

OPB870, OPB871, OPB872 (TX, TXV)



Part Number Guide — OPB870, OPB871, OPB872 (TX, TXV)

OPB 8 X X X X T X V

Optek Assembly
Phototransistor Output Family

Discrete Shell Material:
7 — Base mount opaque
Plastic discrete shell
PC mountable leads

TX and TXV processed to MIL-PRF-19500

Sensor Aperture:
1 — 0.010" (0.254 mm)
5 — 0.050" (1.270 mm)


Emitter Aperture:
1 — 0.010" (0.254 mm)
5 — 0.050" (1.270 mm)

Mounting Configurations:
N — No mounting tabs
L — Emitter side mounting tab only
T — Two mounting tabs
P — Phototransistor side mounting tab only



Electrical Specification Variations:

0 = Electrical Parameter A (lead spacing = 0.320")
1 = Electrical Parameter B (lead spacing = 0.320")
2 = Electrical Parameter C (lead spacing = 0.320")

Note: Assemblies with dual 0.010" apertures are currently available only with electrical



TOLERANCES ARE ± .010" [.25].



DIMENSIONS ARE IN: [MILLIMETERS]
INCHES

Pin #	Emitter	Pin #	Transistor/Diode
1	Anode	3	Collector / Anode
2	Cathode	4	Emitter / Cathode

CONTAINS POLYSULFONE

To avoid stress cracking, we suggest using ND Industries' **Vibra-Tite** for thread-locking. **Vibra-Tite** evaporates fast without causing structural failure in OPTEK's molded plastics.

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Absolute Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Storage Temperature ⁽¹⁾	-65° C to +150° C
Operating Temperature ⁽¹⁾	-65° C to +125° C
Lead Soldering Temperature ⁽³⁾	240° C

Input LED

Forward DC Current	50 mA
Peak Forward Current (1µs pulse width, 300 pps)	1.0 A
Reverse DC Voltage	2.0 V
Power Dissipation ⁽²⁾	100 mW

Output Phototransistor/Diode

Collector-Emitter Voltage	50 V
Emitter-Collector Voltage	7.0 V
Collector DC Current	30 mA
Power Dissipation	100 mW ⁽²⁾

Notes:

- (1) Derate linearly 1.00 mW/° C above 25° C.
- (2) Cleaning agents methanol and isopropanol are recommended. Spray or wipe; do not submerge.
- (3) RMA flux is recommended. Duration can be extended to 10 seconds maximum when flow soldering.
- (4) All parameters were tested using pulse technique.

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
--------	-----------	-----	-----	-----	-------	-----------------

Input Transistor/Diode

V_F	Forward Voltage	1.00 1.20 0.80	- - -	1.70 1.90 1.60	V	$I_F = 20.0\text{ mA}$ $I_F = 20.0\text{ mA}, T_A = -55^\circ\text{C}$ $I_F = 20.0\text{ mA}, T_A = -100^\circ\text{C}$
I_R	Reverse Current	-	-	10	μA	$V_R = 2.0\text{ VDC}$

Output Transistor


$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	50	-	-	V	$I_C = 1.0\text{ mA}, I_F = 0$
$V_{(BR)ECO}$	Emitter-Collector Breakdown Voltage	7.0	-	-	V	$I_E = 100\ \mu\text{A}, I_F = 0$
$I_{C(off)}$	Collector-Emitter Dark Current		- -	100 100	nA μA	$V_{CE} = 10.0\text{ V}, I_F = 0$ $V_{CE} = 10.0\text{ V}, I_F = 0, T_A = 100^\circ\text{C}$

Coupled


$I_{C(ON)}$	On-State Collector Current ⁽⁴⁾					
	Parameter A OPB870 OPB870 OPB870	500 200 200	- - -	- - -	μA	$V_{CE} = 10.0\text{ V}, I_F = 20.0\text{ mA}$ $V_{CE} = 10.0\text{ V}, I_F = 20.0\text{ mA}, T_A = -55^\circ\text{C}$ $V_{CE} = 10.0\text{ V}, I_F = 20.0\text{ mA}, T_A = 100^\circ\text{C}$
	Parameter B OPB871 OPB871 OPB871	1000 400 400	- - -	- - -	μA	$V_{CE} = 5.0\text{ V}, I_F = 10.0\text{ mA}$ $V_{CE} = 5.0\text{ V}, I_F = 10.0\text{ mA}, T_A = -55^\circ\text{C}$ $V_{CE} = 5.0\text{ V}, I_F = 10.0\text{ mA}, T_A = 100^\circ\text{C}$
	Parameter C OPB872 OPB872 OPB872	1800 800 800	- - -	- - -	μA	$V_{CE} = 0.4\text{ V}, I_F = 20.0\text{ mA}$ $V_{CE} = 0.4\text{ V}, I_F = 20.0\text{ mA}, T_A = -55^\circ\text{C}$ $V_{CE} = 0.4\text{ V}, I_F = 20.0\text{ mA}, T_A = 100^\circ\text{C}$
$V_{CE(SAT)}$	Collector-Emitter Saturation Voltage OPB870 OPB871 OPB872	- - -	- - -	0.30 0.30 0.30	V	$I_C = 400\ \mu\text{A}, I_F = 20.0\text{ mA}$ $I_C = 800\ \mu\text{A}, I_F = 10.0\text{ mA}$ $I_C = 1800\ \mu\text{A}, I_F = 20.0\text{ mA}$
t_r	Output Rise Time OPB870 OPB871 OPB872	- - -	- - -	15.0 20.0 20.0	μs	$V_{CC} = 10.0\text{ V}$ $I_F = 20.0\text{ mA}$ $R_L = 1000\Omega$
t_f	Output Fall Time OPB870 OPB871 OPB872	- - -	- - -	15.0 20.0 20.0	μs	$V_{CC} = 10.0\text{ V}$ $I_F = 20.0\text{ mA}$ $R_L = 1000\Omega$

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.



Aperture Configuration 51 - Flag Next to Emitter



Aperture Configuration 51 - Flag Next to Sensor




Aperture Configuration 51 - Flag in Middle of Slot




OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.



Aperture Configuration 55 - Flag Next to Emitter



Aperture Configuration 55 - Flag Next to Sensor



Aperture Configuration 55 - Flag in Middle of Slot



OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.