### **Non-Fusible Safety Switches**

Pass & Seymour

**D** legrand

## Non-Fusible Safety Switches UL Listed as "Suitable as Motor Disconnect."

Here's the first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as "Suitable as Motor Disconnect" per 2002 NEC® Article 430.109(A)(6).

P&S Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox® NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions. These rugged performers are available in capacities from 30 to 100 amps.

And when you take a closer look, you'll see even more to like. For example, the fits-anywhere compact design. The adjustable mounting feet that speed installation. Or the no-confusion, at-a-glance ON/OFF status indication.

See how P&S Non-Fusible Safety Switches work better for you.



## **Non-Fusible Safety Switches**

## Pass & Seymour

**Compact design** fits in most l-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.

Nonconductive, watertight, corrosion-, heat-, and impactresistant thermoplastic enclosure ensures NEMA 4X and 12 ratings. Withstands the harshest industrial environments. **meets OSHA Lockout/Tagout provisions** and provides plenty of grip for sure, easy operation. Black/red color coding and highvisibility ON/OFF markings clearly indicate status from a distance and at any visual angle. Switch entry into the enclosure is offset to the side and sealed to provide enhanced water resistance.

Heavy-duty, ergonomic switch handle

Durable, stainless steel cover-retaining chain makes installation and maintenance more convenient.

Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.



**Bottom and top wiring access options.** No unnecessary openings to compromise water resistance.

**Top mount auxiliary contact** enables additional control functions or signal lights. Adjustable mounting feet can be moved to

center of unit for instant strut- or pole-mounting without special brackets or harnesses.

K-21

**I**legrand

## Non-Fusible Safety Switches Ordering Information

	Maximum Horsepower	Non-Fusible Safety Switch	Non-Fusible Safety Switch with Auxiliary	Auxiliary	Replacement	Replacement Switch with	Replacement	
Voltage	Rating Catalog		Contact Catalog #	Contact Kit*			Cover	
30 Amps	600VAC				I	I		
120VAC	1 HP			AX30	RS30	PS30RSAX	PS30SSRC	
208VAC	2 HP							
240VAC	3 HP							
277VAC	3 HP		PS30SSAX					
480VAC	5 HP							
3ø 240VAC	5 HP	PS30SS						
3ø 480VAC	10 HP							
3ø 600VAC	10 HP							
3øY 120/208VAC	5 HP							
3øY 277/480VAC	10 HP							
3øY 347/600VAC	10 HP							
60 Amps	600VAC							
120VAC	3 HP		PS60SSAX		RS60	N/A		
208VAC	10 HP							
240VAC	10 HP						PS60SSRC	
277VAC	15 HP							
480VAC	20 HP							
3ø 240VAC	20 HP	PS60SS		AX60				
3ø 480VAC	40 HP							
3ø 600VAC	50 HP							
3øY 120/208VAC	20 HP							
3øY 277/480VAC	40 HP							
3øY 347/600VAC	50 HP							
100 Amps	600VAC							
120VAC	5 HP					N/A	PS100SSRC	
208VAC	10 HP							
240VAC	15 HP							
277VAC	15 HP							
480VAC	30 HP			AX60	RS100			
3ø 240VAC	25 HP	PS100SS	PS100SSAX					
3ø 480VAC	50 HP							
3ø 600VAC	50 HP							
3øY 120/208VAC	20 HP							
3øY 277/480VAC	50 HP							
3øY 347/600VAC	50 HP							

\*For replacement of side mount auxiliary contact on previous design.

#### **Mounting Feet Replacement Kit**

Catalog Number	Description
SSMF	Mounting Feet Replacement Kit for PS30SS and PS30SSAX







RS30

Ordering Information

## Non-Fusible Safety Switches Materials of Manufacture Typical/Sample Spec

## Pass & Seymour

**C**legrand

#### **Typical Specifications**

Manufacturer's Identification: Pass & Seymour PS60SS

Description: Non-Fusible Safety Switch

Rating: 60A, 600VAC maximum

Enclosure Type: NEMA 4X (watertight, hosedown), 12K (dusttight, falling dirt), IP67 suitability

Conduit Location: Top, bottom, or back feed. Units are shipped without holes for conduit. Spot drills for locating hole saw or knockouts are provided for top, bottom, or back feed. End user decides at installation whether top, bottom, or back feed is appropriate. No closure plug kits required. Units are not provided with conduit hubs.

#### **Materials**

Enclosure CoverValoEnclosure BaseValoEnclosure GasketNeopSwitch HandleValoSwitch Handle SealNeopSwitch Key10%Mounting FeetValoMounting Feet Screws300Enclosure Assembly Screws300Enclosure Assembly InsertsBrassGrounding PlateGalwCover Chain300

#### Valox 357° Valox 357° Neoprene Valox 357° Neoprene 10% Glass-Filled Nylon Valox 357° 300 Series Stainless Steel 300 Series Stainless Steel Brass (60 and 100 amp units only) Galvanized Steel 300 Series Stainless Steel

#### Performance

Electrical:	
Dielectric Voltage Withstand	3000V minimum
Maximum Working Voltage	600V RMS
Current Interrupting	Listed for current interrupting at full-rated current and voltage
Short Circuit Withstand Rating	For use on circuit capable of delivering not more than (see chart below) RMS amps at 600VAC
Operations	Mechanical: 15,000 cycles
	Electrical: 10,000 cycles
Auxiliary Contacts (optional)	10A @ 600VAC 1 N.O. & 1 N.C.

#### Interrupting Ratings — RMS Symmetrical Amperes

Suitable for use on circuits capable of delivering not more than (see chart below for cat. no. and application) RMS symmetrical amperes, 600VAC maximum.

Catalog Number	Manual Motor Controller	Motor Disconnect
PS30SS (AX)	10,000 AMP	10,000 AMP
PS60SS (AX) PS100SS (AX)	10,000 AMP	5,000 AMP

Mechanical:				
Impact Resistance	Per UL746C			
Terminal Identification	Per UL and CSA			
Product Identification	Identification and rating on external and internal labels			
Mounting External adjustable feet with five (5) positions Can be mounted directly to channel or strut (no washers required)				
Environmental:				
Moisture Resistance	Per UL50, section 35, NEMA Enclosure Type 4X (watertight, hosedown)			
	Per UL50, section 35, NEMA Enclosure Type 12K (dusttight, falling dirt) • IP67 suitability			
Flammability	UL94 5VA and VO Classification			
Operating Temperature	Maximum continuous: +60°C · Minimum continuous: -50°C without impact			
UV Resistance	All enclosure materials are UV stable			

**Materials of Manufacture** 

## Pass & Seymour

# Non-Fusible Safety Switches Dimensions


**C**legrand


## **Non-Fusible Safety Switches Dimensions**

ĎĖ

Amps	Α	В	С	D	E	F	G	н	I	J	К
30	5.75	7.38	4.88	7.19	9.69	3.75	5.75	6.56	6.13	8.06	8.88
60	7.19	9.13	6.31	9.63	12.38	4.75	7.19	8.13	8.00	10.38	11.38
100	7.19	9.13	6.31	9.63	12.38	4.75	7.19	8.13	8.00	10.38	11.38

All measurements shown in inches.





(See dimensions above.)

K-24