
Six-Element SMD Photodiode Array OPR2100, OPR2100T, OPR2100HS, OPR2100HST



Features:

- Six-PIN photodiode array
- High-temperature chip carrier
- Closely matched responsivity between elements
- · Choice of low or high speed
- Easily mountable in any configuration
- Suitable for harsh industrial operating conditions



Description:

Each **OPR2100** device is a six-element photodiode that is designed to meet the needs of motor encoder applications. Designed specifically for *industrial* encoder applications, the **OPR2100** features a high temperature SMD chip carrier, a temperature range and a low leakage current that can withstand extreme operating conditions.

These devices have an opaque chip carrier that encloses six individual chips, which are mounted on isolated cathode contacts to allow external connection in any desired configuration. The opaque polyimide package shields the photodiodes from stray light and can withstand multiple exposures to the most demanding soldering conditions, while the gold-plated wraparound solder pads provide exceptional storage and wetting characteristics.

See Application Bulletin 237 for handling instructions.

Applications:

- Motor encoder applications
- Industrial encoder applications

Ordering Information											
Part Number	Sensor	# of Elements	Responsivity (mA/mW) Min	Reverse Voltage Breakdown	Active Area mm²(each)	Bandwidth	Packaging				
OPR2100	Photodiode Array	6	0.45	50	3.45	55kHz	Tube				
OPR2100T	Photodiode Array	6	0.45	50	3.45	55kHz	Tape & Reel				
OPR2100HS	Photodiode Array	6	0.45	50	3.45	200kHz	Tube				
OPR2100HST	Photodiode Array	6	0.45	50	3.45	200kHz	Tape & Reel				



(Human Body Model)






OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Six-Element SMD Photodiode Array OPR2100, OPR2100T, OPR2100HS, OPR2100HST





Absolute Maximum Ratings (T_A = 25° C unless otherwise noted)


Storage and Operating Temperature	-55° C to +125° C
Reverse Breakdown Voltage	50 V / minute
Solder reflow time within 5°C of peak temperature is 20 to 40 seconds ⁽¹⁾	250° C

Electrical Characteristics (T_A = 25° C unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS	
R	Responsivity		-	-	A/W	E_e = 10 μ W, λ = 890 nm, V = 0 V	
V_{BR}	Reverse Breakdown Voltage		-	-	V	I _R = 10 μA	
I_D	Reverse Dark Current	-	-	10	nA	$V_R = 10 \text{ V}, E_e = 0$	
B_W	Bandwidth	-	-	200	kHz	T _A ≤ 125°C	
Ст	Capacitance	-	10	-	pF	V _R = 10 V	
Lx W	Active Area (per diode)	-	3.45	-	mm ²	2.73 mm x 1.34 mm	

Notes:

- 1. Solder time less than 5 seconds at temperature extreme.
- 2. Package thermal resistance is 142° C / W



OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.