• Efficiency up to 97%,Non isolated, Features no need for heatsinks Pin-out compatible with LM78XX Linears • Very low profile(L*W*H=11.5*7.5*10.2) • Wide input range.(4.75V ~ 34V) Short circuit protection, Thermal shutdown Non standard outputs available as specials Low ripple and noise • UL94V-O Package Material EMC Certified See Positive-to Negative Converter Application Note for use as a voltage inverter (alternative to LM79xx Linear) Rev.1

Description

The R-78xx-Series high efficiency switching regulators are ideally suited to replace 78xx linear regulators and are pin compatible. The efficiency of up to 97% means that very little energy is wasted as heat so there is no need for any heat sinks with their additional space and mounting costs. Low ripple and noise figures and short circuit , overload and over-temperature protection round off the specifications of this versatile converter series.


This R-78xx-0.5 is fully certified to EN 60601-1-2 (Medical Equipment), EN 55022 (Emissions), and EN55024 (Immunity) EMC Standards.

Selection Guide

Part	Input	Output	Output	Efficiency	
Number SIP3	Range (1) (V)	Voltage (V)	Current (A)	Min. Vin (%)	Max. Vin (%)
R-781.5-0.5	4.75 - 30	1.5	0.5	73	63
R-781.8-0.5	4.75 – 34	1.8	0.5	82	71
R-782.5-0.5	4.75 – 34	2.5	0.5	87	77
R-783.3-0.5	4.75 – 34	3.3	0.5	91	81
R-785.0-0.5	6.5 – 34	5.0	0.5	94	86
R-786.5-0.5	8.0 - 34	6.5	0.5	95	88
R-789.0-0.5	11 – 34	9.0	0.5	96	92
R-7812-0.5	15 – 34	12	0.5	97	94
R-7815-0.5	18 – 34	15	0.5	97	95

Note 1:1.5V Output can be unstable with Vin>30VDC

Standard Application Circuit



Input capacitor needed only if Vin>26VDC.

INNOLINE DC/DC-Converter

R-78xx-0.5 Series

0.5 AMP SIP3 Single Output




EN-55022 Certified EN-55024 Certified EN-60601-1-2 Certified



Derating-Graph

(Ambient Temperature)



INNOLINE DC/DC-Converter

R-78xx-0.5 Series

Specifications (typical at 25°C, 10% minimum load, unless otherwise specified)

nput Voltage Range Dutput Voltage Range (for customized parts) Dutput Current (see note) Dutput Current Limit Short Circuit Input Current (Vin = 24V) Internal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load) Line Voltage Regulation (Vin = min. to max. at full load)	1.5V 1.8V to 15.5V All Series All Series All Series All Series All Series 1.5V to 6.5V	4.75 4.75 1.25 0*		30.0V 34.0V 15.5V 500mA 2000mA 60mA 0.4W
Dutput Current (see note) Dutput Current Limit Short Circuit Input Current (Vin = 24V) Internal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)	All Series All Series All Series All Series All Series All Series	1.25		15.5V 500mA 2000mA 60mA
Dutput Current (see note) Dutput Current Limit Short Circuit Input Current (Vin = 24V) Internal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)	All Series All Series All Series All Series			500mA 2000mA 60mA
Dutput Current Limit Short Circuit Input Current (Vin = 24V) Internal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)	All Series All Series All Series All Series	0*		2000mA 60mA
Short Circuit Input Current (Vin = 24V) Internal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)	All Series All Series			60mA
nternal Power Dissipation Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)	All Series			
Short Circuit Protection Dutput Voltage Accuracy (At 100% Load)			0	0.4\\/
Dutput Voltage Accuracy (At 100% Load)			0 "	0.4W
			Continuo	us, automatic recovery
ine Voltage Regulation (Vin = min_to max_at full load)	1 5\/ to 6 5\/		±2	±3%
in voltago hogulation (vin – min. to max. at run load)	1.37 10 0.37		0.2	0.4%
	9V to 15.5V		0.1	0.2%
oad Regulation (10 to 100% full load)	1.5V to 6.5V		0.4	0.6%
	9V to 15.5V		0.25	0.4%
Dynamic Load Stability	100% <-> 50% load		±75mV	
	100% <-> 10% load			±100mV
Ripple & Noise (without Output Capacitor)	1.5V to 6.5V		20mVp-p	З0mVp-р
	9V to 15.5V		30mVp-p	40mVp-р
Ripple & Noise (with Output Capacitor=100µF)	1.5V to 6.5V		15mVp-р	20mVp-p
	9V to 15.5V		25mVp-p	35mVp-p
emperature Coefficient	-40°C ~ +85°C ambient			0.015%/°C
Max capacitance Load				220µF
Switching Frequency		280	330	380kHz
Quiescent Current	Vin = min. to max. at 0% load		5	7mA
Operating Temperature Range		-40°C		+85°C
Operating Case Temperature				+100°C
Storage Temperature Range		-55°C		+125°C
Case Thermal Impendance				70°C/W
hermal Shutdown	Internal IC junction			+160°C
Conducted Emissions	EN55022			Class B
Radiated Emissions	EN55022			Class B
SD	EN61000-4-2			Class A
Radiated Immunity	EN61000-4-3			Class A
Fast Transient Conducted Immunity	EN61000-4-4 EN61000-4-6			Class A Class A
Agnetic Field Immunity	EN61000-4-8			Class A Class A
Package Weiught				1.9g
MTBF (+25°C) Detailed Information see	using MIL-HDBK 217F			21098 x 10 ³ hours
(+71°C) S Default information See (+71°C) Application Notes chapter "MTBF"	using MIL-HDBK 217F			4212 x 10 ³ hours


*Note: Operation under no load will not damage these devices, however they may not meet all specifications. A minimum load of 6mA is recommended




R-78xx-0.5 Series

Application Examples

High efficiency, isolated, dual unregulated outputs



Isolated (up to 6KV), wide Input range regulated output



Package Style and Pinning (mm)

