

Product Details

DC Gearmotor GM8224S010

Note: Product photo is for illustrative purposes. Please refer to Engineering Drawing for specifics.



Motor Series	Series GM8000 LO-COG Brush Commutated DC Gearmotors
Price (USD)	
Frame Size (Mounting Face) (in)	1.37
Motor Frame Size (in)	1.175
Gear Frame Size (in)	1.370
Overall Body Length (in)	3.285
Supply Voltage (V)	24
Continuous Output Torque (oz-in)	16
Output Speed @ Cont. Torque (RPM)	319
Current @ Cont. Torque (A)	0.61
Continuous Output Power (W)	3.7
No Load Current (A)	0.14
No Load Output Speed (RPM)	739
Peak Current (A)	1.4
Peak Output Torque (oz-in)	47
Motor Constant (oz-in/ \sqrt{W})	1.5
Motor Torque Constant (oz-in/A)	6.18
Motor Voltage Constant (V/krpm)	4.57
Terminal Resistance (Ohms)	17
Inductance (mH)	9.4
Coulomb Friction Torque (oz-in)	0.35
Viscous Damping Factor (oz-in/krpm)	0.02
Electrical Time Constant (ms)	0.55
Mechanical Time Constant (ms)	14
Thermal Time Constant (min)	11
Thermal Resistance ($^{\circ}C/Watt$)	21
Maximum Winding Temperature ($^{\circ}C$)	155
Rotor Inertia (oz-in-s ²)	0.00023
Output Bearing	Ball
Gear Series	G35A-WF
Gear Ratio (xx.x:1)	6.3
Gear Type	wide face spur
Gear Efficiency	0.95
Gear Maximum Torque (oz-in)	100
Encoder Series	n/a
Encoder Resolution (CPR)	n/a
Encoder Output Channels	n/a
Weight (Mass) (oz)	8.2
Voltage Note	Note: rated voltage of PittmanExpress item is different than catalog reference voltage of base motor.
Torque Warning	n/a