


### Pass & Seymour

### Turnlok<sup>®</sup> Locking Devices Heavy-Duty Flanged Inlets & Outlets 15, 20 & 30A; 125 & 250V, 277VAC

4716SS, 4715SS, 615, 614, L0715, L0714, L520, L620, L720, L530, L630, L730

# Turnlok performance and durability for fixed-mounting applications.

or permanent mounting, these rugged inlets and outlets provide a generous, predrilled flange that features clearly visible NEMA configurations and ratings. Their solid brass blades and contacts provide both durability and excellent conductivity. Thick, impact-resistant thermoplastic housings help ensure long-term durability.



#### **Features & Benefits**

**Interior components constructed of high-grade brass** material for physical and electrical integrity.



#### Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional

Retail

Office

- Hospitality/Lodging
- SF1703R1 Updated January 2004 For latest specs visit www.legrand.us/passandseymour




### Turnlok<sup>®</sup> Locking Devices Heavy-Duty Flanged Inlets & Outlets 15, 20 & 30A; 125 & 250V, 277VAC

### **Ordering Information**

Catalog Number	Rating A. V.	Description/Color	NEMA Config. No.
Flanged	Inlets &	Outlets	
4716-SS	15 125	Flanged Inlet, Gray	L5-15P
4715-SS	15 125	Flanged Outlet, Gray	L5-15R
615	15 250	Flanged Inlet, Gray	L6-15P
614	15 250	Flanged Outlet, Gray	L6-15R
L0715	15 277*	Flanged Inlet, Gray	L7-15P
L0714	15 277*	Flanged Outlet, Gray	L7-15R
L520-FI	20 125	Flanged Inlet, Gray	L5-20P
L520-FO	20 125	Flanged Outlet, Gray	L5-20R
L620-FI	20 250	Flanged Inlet, Gray	L6-20P
L620-FO	20 250	Flanged Outlet, Gray	L6-20R
L720-FI	20 277*	Flanged Inlet, Gray	L7-20P
L720-FO	20 277*	Flanged Outlet, Gray	L7-20R
L530-FI	30 125	Flanged Inlet, Gray	L5-30P
L530-FO	30 125	Flanged Outlet, Gray	L5-30R
L630-FI	30 250	Flanged Inlet, Gray	L6-30P
L630-FO	30 250	Flanged Outlet, Gray	L6-30R
L730-FI	30 277*	Flanged Inlet, Gray	L7-30P
L730-FO	30 277*	Flanged Outlet, Gray	L7-30R

\*AC only.



For more information on these and other P&S products refer to our Product Guide or visit our web site.

### Turnlok<sup>®</sup> Locking Devices Heavy-Duty Flanged Inlets & Outlets 15, 20 & 30A; 125 & 250V, 277VAC



Pass & Seymour

1.655

### **Technical Specifications**


#### **3rd Party Compliance**

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596.

CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs. Conforms to NEMA WD-1.

Performance				
Electrical				
Dielectric Withstand Voltage	15A = 2000V minimum, 20 & 30A = 3000V minimum			
Maximum Working Voltage	15A = 277VAC, 20 & 30A = 600VAC			
Current Interrupting	Certified for current interrupting at full-rated current			
Temperature Rise	30°C max. after 50 cycles at 150% rated current			
Mechanical				
Terminal Identification	15A = Green = Ground, White = Neutral, Brass = Hot; 20 & 30A = Green = Ground, "W" and White = Neutral, "X", "Y", "Z" = Hot			
Terminal Accommodation	15A = #18 AWG min #10 AWG max. 20A = #12 AWG min #8 AWG max. 30A = #12 AWG min #6 AWG max.			
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration			
Environmental				
Flammability	UL94 V2			
Operating Temperature	15 & 20A = Maximum continuous +115°C, minimum -40°C without impact; 30A = Maximum continuous +75°C, minimum -40°C without impact			

ithout	
el	
el	
-	
	ı



Dimensions for 15 Amp Flanged Inlet

Dimensions for 15 Amp Flanged Outlet


### 1.650" 2.875" 2.093" 1.25"

Dimensions for 20 Amp Flanged Inlet


#### **Materials** Inlet Outlet Flanged Casing Polycarbonate Polycarbonate Contact Carrier 15 & 20A = Polycarbonate 30A = NylonContacts 15 & 20A = Brass 30A = Tin-Plated Brass Blade Holder 15 & 20A = Polycarbonate 30A = Nylon15A = Nickel-Plated Brass Blades 20A = Brass 30A = Tin-Plated Stresscon Terminal Clamp 15 & 20A = Zinc-Plated Steel 15 & 20A = Zinc-Plated Steel 30A = Brass- or Nickel-Plated Stee 30A = BrassTerminal Screws 15 & 20A = Zinc- or 15 & 20A = Zinc- or Brass-Plated Steel 30A = Brass30A = Brass- or Nickel-Plated Ste **Ground Screws** 15 & 20A = Zinc-Plated Steel 15 & 20A = Zinc-Plated Steel 30A = Nickel-Plated Brass 30A = BrassZinc-Plated Steel Zinc-Plated Steel Assembly Screws

#### Warranty


1 Year



Dimensions for 30 Amp Flanged Inlet



Dimensions for 30 Amp Flanged Outlet



Dimensions for 20 Amp Flanged Outlet

#### **Complementary Devices & Accessories**



### TURNLOK® LOCKING DEVICES

- Heavy-Duty Receptacles
- Extra-Hard Use Plugs & Connectors



#### GROUND CONTINUITY MONITORING (GCM)

- Extra-Hard Use Straight Blade
- Heavy-Duty Turnlok®



## STRAIGHT BLADE PLUGS & CONNECTORS

- Extra-Hard Use
- Heavy-Duty MaxGrip® II



### TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS



### IEC 309 INDUSTRIAL PRODUCTS

- Fusible & Non-Fusible Mechanical Interlocks
- Fusible & Non-Fusible Safety Switches
- Pin & Sleeve Devices

#### Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail<sup>™</sup> Devices
- Switches
- Straight Blade Receptacles
- GFCIs
- Weatherproof Boxes & Covers
- Wall Plates
- Flexcor<sup>®</sup> Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour P.O. Box 4822

Syracuse, NY 13221-4822 800-223-4185 North America Headquarters 60 Woodlawn Street West Hartford, CT 06110

West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721 www.legrand.ca