


## TECHNICAL SPECIFICATIONS

[Home](#) » [Products & Services](#) » [Technical Specifications: MB-09-201-S\(F\)](#)

### AudioLarm II

MB-09-201-S(F)





## Specifications

Medium Loud Beep Tone; Fast Rate; Panel Mount Case and Quick Connect Blades with Screws Termination

<b>Mounting:</b>	Panel Mount
<b>Operating Mode:</b>	Medium Loud Fast Beep Tone
<b>Operating Voltage:</b>	30-120 Vac
<b>Operating Frequency:</b>	2900 $\pm$ 250 Hz
<b>Typical Operating Current:</b>	5 mA at 30 Vac 20 mA at 120 Vac
<b>Typical Sound Pressure:</b>	85 $\pm$ 5 dB(A), at 30 Vac, at 24 inches (61 cm), at 25°C 95 $\pm$ 5 dB(A), at 120 Vac, at 24 inches (61 cm), at 25°C
<b>Termination:</b>	Quick Connect Blades with Screws
<b>Termination Strength:</b>	Pull test with a maximum of 22 pounds (10 kg) load
<b>Operating Temperature:</b>	-20°C to +65°C
<b>Storage Temperature:</b>	-40°C to +85°C
<b>Surge Voltage:</b>	20% over maximum rated voltage for less than 5 minutes
<b>Reverse Voltage Protection:</b>	To the maximum operating voltage
<b>Construction Materials:</b>	Case- Plastic "NORYL® N-190", Flame Retardant UL 94-VO, Black Internal Circuit- Audio-oscillator and piezoelectric driver Potting- 2 parts epoxy resin or silicone, black Diaphragm- Stainless Steel 304
<b>Gasket:</b>	Gasket (Sold Separately)– 0.062" Thick, 60 Durometer Neoprene
<b>Environmental Durability:</b>	ASTM B117 Certified - Withstands exposure to salt spray for 300 hours IP 68 Certified - Withstands water submergence and dust exposure Humidity- 95% relative humidity at +40°C continuously for 100 hours. Vibration- Withstands vibration between 0 and 55 Hz. on all axes.
<b>Life Expectancy:</b>	10 years under normal operating conditions.
<b>Warranty:</b>	For a period of two years from the date of manufacture under normal operating conditions.

## Dimensions

