

Slimline Power Supply

User Configurable 1U size



PLUG & PLAY POWER next generation power source

FEATURES

- · Slimmest 750W configurable power
- Extra low profile: 1U height (40mm)
- · Up to 800W peak power
- Ultra high efficiency, up to 89%
- Plug & Play Power
 - allows fast custom configuration
 - allow easy logistics
- FLEXIMOUNT Flexible mounting system
- Few electrolytic capacitors (all long life)
- · Visual LED indicators
- Series / Parallel of multiple outputs
- 5V bias standby voltage provided
- · Individual output control signals

APPLICATIONS INCLUDE

- Industrial machines
- · Test and measurement
- Automation equipment
- Printing
- Telecommunications
- For Medical applications see Xmite

The XLD is the latest addition to the Xitte family of power supplies and provides an unprecedented 750W in a slimline 1U x 268 x 89mm package. Providing up to 8 isolated outputs, the Xitte family is the most flexible power supply in its class and brings affordable configurable power to the 750W market.

With 800W peak power capability the slimline product boasts unrivalled power density saving valuable system space. Combine with ultra high efficiencies, the Xiite family provides system designers with flexible instant solutions that significantly shorten and simplify system design-in time.

The XLD 750W *powerPac* model may be populated with up to 4 *powerMods* selected from the table of *powerMods* shown below.

All configurations carry full safety agency approvals, UL60950, EN60950 and are CE marked. For alternative power interfaces contact support@excelsys.com

powerMods

MODEL	Vr	nin(4)	Vnom	Vmax(4	Imax	Watts
	Vtrim	Vpot				
Xg1	1.0	1.5	2.5	3.6	50A	125W
Xg2	1.5	3.2	5.0	6.0	40A	200W
Xg3	4.0	6.0	12.0	15.0	20A	240W
Xg4	8.0	12.0	24.0	30.0	10A	240W
Xg5	8.0	24.0	48.0	58.0	6A	288W
Xg7	5.0	5.0	24.0	28.0	5A	120W
Xg8 v1	5.0 5.0	5.0 5.0	24.0 24.0	28.0 28.0	3A 3A	72W 72W

powerPacs


MODEL	Watts
XLD	750W

EFFICIENCY (typical)

93 92 91 8 90 8 88 8 87 86 84 70 85 100 115 130 145 160 175 190 205 220 235 260 Line Voltage VAC



MECHANICAL SPECIFICATIONS



1

750W Slimline Plug & Play Power Supply Series

SPECIFICATION applies to configured units consisting of powerMods modules plugged into the appropriate powerPac

INPUT					
Parameter	Conditions/Description	Min	Nom	Max	Units
Input Voltage Range	Universal Input	85		264	VAC
	'	120		380	VDC
nput Frequency Range		47		63	Hz
Power Rating XLD	Derate linearly from 750W at 140VAC to 525W at 85VAC. Note 5	1		750(800)	W
nput Current XLD	85VAC in 525W out		7.5	700(000)	A
nrush Current	230VAC @ 25°C		7.0	50	A
Indervoltage Lockout	Shutdown	65		74	VAC
<u> </u>		65	FOA LIDO	74	VAC
Fusing XLD	250V 5 x 20mm		F8A HRC		
ОИТРИТ					
Parameter	Conditions/Description	Min	Nom	Max	Units
powerMod Power	As per <i>powerMod</i> table	IVIIII	Nom	WILL	Units
Output Adjustment Range	Manual: Multi-turn potentiometer. As per <i>powerMod</i> table				
output Aujustilient hange					
Minimum Lood	Electronic: See Xgen Designers' Manual		0		Δ.
Minimum Load	F 1400/ 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		0	.0.4	A
ine Regulation	For ±10% change from nominal line			±0.1	%
_oad Regulation	For 25% to 75% load change			±0.2	%
Cross Regulation				±0.2	%
Transient Response	For 25% to 75% load change Voltage Deviation			10	%
	Settling Time			250	μs
Ripple and Noise	20MHz Bandwidth			1.0	% pk
Overvoltage Protection	Two-level. 1st level: Vset Tracking. 2nd level: Vmax (Latching)	110		125	%
Overcurrent Protection	Straight line with hiccup activation at <30% of Vnom	110		120	%
	See Designer's Manual for full details	<u> </u>			
Remote Sense	Max. line drop compensation. (except Xg7, Xg8)			0.5	VDC
Overshoot				2	%
Turn-on Delay	From AC In / Enable signal			1000/30	ms
Rise Time	Monotonic			5	ms
Hold-up Time	For nominal output voltages at full load	15		-	ms
Output Isolation	Output to Output / Output to Chassis	500 / 500			VDC
•	Super to Sup	0007 000			
GENERAL					
Parameter	Conditions/Description	Min		Max	Units
Isolation Voltage	Input to Output	3000			VAC
**	Input to Chassis	1500			VAC
Efficiency	230VAC, 750W @ 24V		89		%
Safety Agency Approvals	EN60950, UL60950, CSA22.2 No.950 UL File No. E181875				
Leakage Current	250VAC, 60Hz, 25°C			1.5	mA
Signals	See Xgen Series datasheet				
Bias Supply	Always ON. Current 250mA	4.8	5.0	5.2	VDC
Reliability	Failures per million hours at 25°C and full load powerMod	7.0	0.0	0.98	fpmh
ionability	See Designers' Manual. powerPac excludes fans powerPac			0.98	
	oce Designers Manual. powerPac excludes lans powerPac			0.82	fpmh
EMC					
Parameter	Standard		Level		Units
Emissions					
			Level B		
Conducted	FN55011 FN55022 FCC				
	EN55011, EN55022, FCC EN55011, EN55022, FCC		Level R		
Radiated	EN55011, EN55022, FCC		Level B		
Radiated Harmonic Distortion	EN55011, EN55022, FCC EN61000-3-2		Compliant		
Radiated Harmonic Distortion Flicker and Fluctuation	EN55011, EN55022, FCC				
Radiated Harmonic Distortion Flicker and Fluctuation Immunity	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3		Compliant Compliant		
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2		Compliant Compliant Level 4		
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3		Compliant Compliant Level 4 Level 3		
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4		Compliant Compliant Level 4 Level 3 Level 4		
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5		Compliant Compliant Level 4 Level 3 Level 4 Class 4		
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges Conducted RFI	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6		Compliant Compliant Level 4 Level 3 Level 4 Class 4		V/m
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst nput Line Surges Conducted RFI	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5		Compliant Compliant Level 4 Level 3 Level 4 Class 4		V/m ms
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst nput Line Surges Conducted RFI Voltage Dips	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6		Compliant Compliant Level 4 Level 3 Level 4 Class 4		
Conducted Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL	EN55011, EN55022, FCC EN61000-3-2 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024)	Min	Compliant Compliant Level 4 Level 3 Level 4 Class 4 10	Max	ms
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6	Min	Compliant Compliant Level 4 Level 3 Level 4 Class 4	Max	ms Units
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter Operating Temperature	EN55011, EN55022, FCC EN61000-3-2 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024)	-20	Compliant Compliant Level 4 Level 3 Level 4 Class 4 10	+70	ms Units ℃
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst nput Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter Operating Temperature Storage Temperature	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024) Conditions/Description		Compliant Compliant Level 4 Level 3 Level 4 Class 4 10		ms Units
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst nput Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter Operating Temperature Derating	EN55011, EN55022, FCC EN61000-3-2 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024)	-20	Compliant Compliant Level 4 Level 3 Level 4 Class 4 10	+70	ms Units ℃
Radiated Harmonic Distortion Flicker and Fluctuation Immunity Electrostatic Discharge Radiated RFI Fast Transients - burst Input Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024) Conditions/Description	-20	Compliant Compliant Level 4 Level 3 Level 4 Class 4 10	+70	ms Units ℃ ℃
Radiated Harmonic Distortion Flicker and Fluctuation mmunity Electrostatic Discharge Radiated RFI Fast Transients - burst nput Line Surges Conducted RFI Voltage Dips ENVIRONMENTAL Parameter Operating Temperature Derating	EN55011, EN55022, FCC EN61000-3-2 EN61000-3-3 EN61000-4-2 EN61000-4-3 EN61000-4-5 EN61000-4-6 EN61000-4-11 (EN55024) Conditions/Description 0.667% per °C 40-60°C.; 1.33% per per °C 60-70°C	-20 -40	Compliant Compliant Level 4 Level 3 Level 4 Class 4 10	+70 +85	ms Units ℃

NOTES

- 1. This product is not intended for use as a stand alone unit and must be installed by qualified personnel.
- 2. The specifications contained herein are believed to be correct at time of publication and are subject to change without notice.
- 3. All specifications at nominal input, full load, 25°C unless otherwise stated.
- 4. Vmin and Vmax voltages achieved when using Vtrim function on powerMod or the on board potentiometer. Vtrim is the lowest voltage that can be achieved using Vtrim pin on powerMod. Vpot is the minimum voltage that can be achieved using the on-baord potentiometer. See Xgen series Designers' Manual for full details on Vtrim and adjustment ranges.
- 5. 800W peak for 1s; Duty cycle 7%. powerMod output power must not exceed normal ratings.
- 6. When powering inductive or capacitive loads, it is recommended to use a blocking diode on the output.



t: +353 21 4354716 f: +353 21 4354864 e: sales@excelsys.com

North America Excelsys Technologies 519 Interstate 30, #309 Rockwall, TX 75087

USA

t: (972) 771 4544 f: (972) 421 1805 e: salesusa@excelsys.com

Doc. XLD Rev02 11/09

The multi-turn potentiometer that adjusts each output within the specified range may be accessed via the output panel of the power supply. Clockwise rotation increases output voltage. Resolution is approximately 5% of nominal voltage (Vnom) per turn.


Voltage Adjustment - Remote (resistive / electronic)

The output voltage may be adjusted or trimmed by means of an external resistor or potentiometer network connected to the Vtrim pin. Linear Electronic programming is also possible and may be implemented according to the formula Vout = K Vcontrol. See Xgen series Designers' Manual for full details.

Paralleling

To achieve increased current capacity, simply parallel outputs using the standard parallel links. Excelsys 'wireless' sharing ensures that current hogging is not possible. To parallel connect outputs:


- 1. Switch on IShare switch to ON on powerMods.
- 2. Connect Negative parallel link.
- 3. Adjust output voltages of powerMods to within 5mV of eachother.
- 4. Connect Positive Parallel Link.



Parallel Links available to order. Part Number XP1

Seriesing

To achieve increased output voltages, simply series outputs using standard series links, paying attention to the requirements to maintain SELV levels if required in your system.



Series Links available. Part Number XS1

Remote Sensing

When the load is remote from the power supply, the remote sense pins may be used to compensate for drops in the power leads. Where the power cabling contributes significant dynamic impedance, see Xgen series Designers' Manual.

Bias Voltage

A SELV isolated 5V (always on) bias voltage rated at 250mA is provided on J2 to facilitate miscellaneous control functions.

Current Limit Adjustment


The output current limit setting may be adjusted (downwards only) by means of an external resistor connection to the I trim pin.

Inhibit/Enable

Inhibiting may be implemented either globally or on a per module basis (powerPac or powerMod inhibiting). Reverse logic (Enabling) may also be implemented, see Xgen series Designers' Manual.

AC Fail

Open collector signal indicating that the input voltage has failed or is less than 80Vac. This signal changes state giving 5mS of warning before loss of output regulation. See Xgen series Designers' Manual for full specifications.




Temperature Alarm (Option 01)

Open collector signal indicating excessive powerPac temperatures due to fan failure or operation beyond ratings. This signal is activated at least 10ms prior to system shutdown.


Fan Fail (Option 01)

Open collector signal indicating that at least one of the system fans have failed. This does not cause system shutdown.



Power Good

Opto-isolated output signal indicates that the powerMod is operating correctly and output voltage is within normal band. Opto transistor ON = Good.



Indication LEDs

Each powerMod has a visual indicator to identify that it is operating within normal ratings. Very useful for system diagnosis.


Signal Connector Pinout

Pin	J2 (powerPac)	J3 (powerMod)	J3 (powerMod)	
		Type A	Type B)	
1	common	+sense	+pg (V2)	
2	+5V bias	-sense	-pg (V2)	
3		V trim	inhibit (V2)	
4	ac fail	I trim	common (V2)	
5	fan fail*	+inhibit/enable	+pg (V1)	
6	global enable	-inhibit/enable	-pg (V1)	
7	temp alarm*	+power good	inhibit (V1)	
8	global inhibit	-power good	common (V1)	

*Option 01 only

Signal Connector Pinout


TYPE A Xg1-Xg7



J4 Connector : M4 Screw

J3 Connector Mating Connector Housing: Locking Molex 51110-0860 Non Locking Molex 51110-0850

TYPE B: Xg8



J4Connector : Camden 9200/4A


J3 Connector Mating Connector Housing: Locking Molex 51110-0860
Non Locking Molex 51110-0850
Crimo Terrmal: Molex n/n 50394

See Xgen series Designers' Manual for full signal connector details.

3









			Family	MODEL	Watts
			Xmite	XMA	200W
	Med			XMB	400W
ž			XMC		600W
				XMD	750W
	m.		Xrite	XRA	200W
Low	Low	Med		XRB	400W
				XRC	600W


powerPacs (6slot package, 127mm wide)

	Family	MODEL	Watts
	Xcite	XCA	400W
ard		XCB	700W
Standard		XCC	1000W
ά		XCD	1200W
		XCE	1340W
High Temp	Xhite	XHA	400W
三中		XHB	600W
Low Noise	Xqite	XQA	400W
		XQB	900W
		XQC	1200W

		Family	MODEL	Watts
		Xvite	XVA	400W
	-		XVB	700W
	Med		XVC	1000W
			XVD	1200W
			XVE	1340W
	- 0 -	Xzite	XZA	400W
Low	Noise		XZB	900W
	_		XZC	1200W

powerMods (for use with all powerPac models)


poncin	power ac models)						
MODEL	Vmin(4)		Vnom Vmax(4) Imax		Watts		
	Vtrim	Vpot					
Xg1	1.0	1.5	2.5	3.6	50A	125W	
Xg2	1.5	3.2	5.0	6.0	40A	200W	
Xg3	4.0	6.0	12.0	15.0	20A	240W	
Xg4	8.0	12.0	24.0	30.0	10A	240W	
Xg5	8.0	24.0	48.0	58.0	6A	288W	
Xg7	5.0	5.0	24.0	28.0	5A	120W	
Xg8 v1	5.0	5.0	24.0	28.0	3A	72W	
V2	5.0	5.0	24.0	28.0	3A	72W	



Part Numbering

Configured Units may be specified and ordered using the part numbering system shown opposite. For example, part number XVC123400-00 specifies the following 1000W medical power supply.

XVC-00 powerPac 1000W medically approved powerPac



Accessories .

PowerMods can be parallel connected for higher current and series connected for higher voltages. Configured units will have parallel and series links fitted as required.



Europe/Asia

Excelsys Technologies Ltd 27 Eastgate Drive Eastgate Business Park Little Island, Cork, Ireland IRELAND t: +353 21 4354716 f: +353 21 4354864 e: sales@excelsys.com North America Excelsys Technologies 519 Interstate 30, #309 Rockwall, TX 75087

USA

t: (972) 771 4544 f: (972) 421 1805 e: salesusa@excelsys.com