## Hirschmann Automation and Control GmbH





## BAT54-Rail Client - FCC

Industrial Networking:Industrial Ethernet:Wireless LAN:Chassis

Delivery informations	
Availability	available
Document created at	22.05.2009
Product description	
Description	Dualband industrial Wireless LAN access point/client with two independent radio modules with IEEE 802.11a/b/g/h/i. With FCC-approval for USA and Canada.
Port type and quantity	1 x WLAN interface, up to 8 SSIDs, 1 x LAN port 10/100 BASE-TX, autosensing, Power over Ethernet according to IEEE 802.3af
Туре	BAT54-Rail Client - FCC
Order No.	943 926-502
Radio technology	
Antenna connector	2 x RP-SMA jack antenna connectors
Range	Up to 20 km with external antenna (depending on type of antenna, frequency range and data rate)
Transmission rate	54 Mbps according to IEEE 802.11g (Fallback to 48, 36, 24, 18, 12, 9, 6 Mbps, Automatic Rate Selection), compatible to IEEE 802.11b (11, 5,5, 2, 1 Mbps, Automatic Rate Selection), 802.11 b/g compatability mode or pure g or pure b selectable. 54 Mbps according to IEEE 802.11a/h (fallback to 48, 36, 24, 18, 12, 9, 6 Mbpss, Automatic Rate Selection), Super A/G with Turbo Mode (108 MBps), Bursting, Compression, fully compliant to ETSI requirements with TPC and DFS
Encryption	IEEE 802.11i / WPA2 with passphrase or 802.1x and hardware-accelerated AES, user authentication by 802.1x/EAP, IEEE 802.1x supplicant in client mode, WPA/TKIP, WEP, access-control lists, WLAN port and protocol filter, RADIUS client, built-in firewall with QoS, port filter, protocol filter, PMK caching and preauthentication for fast roaming with IEEE 802.1x
Operating system	LAN interface usable for NAT/Reverse NAT (IP-Masquerading) DHCP server, DHCP client, DHCP relay server, DNS server, PPPoE client (incl. Multi-PPPoE), PPTP client and server, NetBIOSProxy, DynDNS client, NTP, Port-Mapping, policy-based routing on basis of routing-tags, tagging according to firewall rules, dynamic routing RIPv2, VRRP, Rapid Spanning Tree Protocol (IEEE 802.1w), ARP, Proxy ARP, BOOTP, DHCP, DNS, HTTP, HTTPS, IP, ICMP, NTP/SNTP, NetBIOS, PPPoE (server), RADIUS, RIP-1, RIP-2, RTP, SIP, SNMP, TCP, TFTP, UDP, VRRP, VLAN with up to 4094 VLAN IDs for WLAN connections, 32 usable simultaneously, dynamic VLAN-tags for 802.1x-clients, integrated RADIUS server with IEEE 802.1x/EAP authentication
Frequency band	1 x radio module, 2.4 GHz and 5 GHz: 2400-2483.5 MHz (ISM) and 5170-5810 MHz
Modulation	22M0F7D(DSSS/OFDM) @ 2.4 GHz 20M0G7D (OFDM) @ 5 GHz
Receiver sensitivity	2.4 GHz 802.11b: -87 dBm @ 11 Mbps, -94 dBm @ 1 Mbps; 2.4 GHz 802.11g: -87 dBm @ 6 Mbps, -70 dBm @ 54 Mbps; 5 GHz 802.11a/h: -87 dBm @ 6 Mbps, -67 dBm @ 54 Mbps
Radio topology	WLAN access client-, client-bridge-modus, fixed mesh with RSTP

Roaming	Soft Roaming, seamless handover between radio cells, IAPP support, IEEE 802.11d support, background scanning for rogue AP detection and fast roaming, support of IEEE 802.11e (WME), preauthentication and PMK caching with IEEE 802.1x
Radio Power	2.4 GHz 802.11b: +19 dBm @1 and 2 Mbps, +19 dBm @ 5.5 and 11 Mbps, 2,4 GHz 802.11g: +19 dBm @ 6 Mbps, +14 dBm @ 54 Mbps, 5 GHz 802.11a/h: +18 dBm @ 6 Mbps, +12 dBm @ 54 Mbps with TPC and DFS, Power Reduction in 1dB steps down to 0.5 dBm minimum
Power requirements	
Operating voltage	2 x DC 24 V; DC 12 Vexternal power supply (230 V) 1 x Power over Ethernet according to IEEE802.3af; all power supllies redundant to each other
Current consumption at 24 V DC	417 mA
Current consumption	DC 12 V: 625 mA; DC 24 V: 417 mA; PoE (48 V DC): 167 mA
Service	
Diagnostics	Extensive LOG and TRACE options, PING and TRACEROUTE for checking connections, LANmonitor status display, internal logging buffer for SYSLOG and firewall events, monitor mode for Ethernet ports, WLANmonitor for WLAN network overview and Rogue AP detection
Management	SNMP management via SNMP V2, private MIB exportable by WEBconfig, MIB II; Remote configuration with Telnet/SSL, SSH, browser (HTTP/HTTPS), TFTP or SNMP, firmware upload via HTTP/HTTPS or TFTP; Support of up to 4094 VLAN IDs for WLAN connections, 256 simultaneously usable VLAN tags for 802.11 clients
Other services	[Änderungsvorschlag]
Ambient conditions	
Operation temperature	-30 °C to +50 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	max. 95%
MTBF	43.3 years
Mechanical construction	
Dimensions (W x H x D)	80 mm x 100 mm x 135 mm
Mounting	for wall and Din Rail mounting
Protection class	IP 40
Approvals	
Safety of information technology equipment	
Radio	FCC IDENTIFIER: U99BAT54RAIL IC certification number: 4019A-BAT54R For other notifications or certifications please refer to INET-Sales@hirschmann.de
Environmental	EN 61000-6-2, EN 61131 for operation in automation environment EMC approval for E1 certification (cars and vehicles) available
Scope of delivery and accessories	
Scope of delivery	Device, CD, serial cable, Ethernet cable (3 m), 2 x 3-dBi-Dipol - Dualband antennas, Rail mount material, 1 x 50 Ohm terminator
Accessories to order separately	External antennas for 802.11b/g and 802.11a/h operation; adapter cable and surge arrestor