



## Product information RS2-5TX/FX

Name	
RS2-5TX/FX	
	
Unmanaged Industrial ETHERNET Rail-Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)	
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	Unmanaged Industrial ETHERNET Rail-Switch, store and forward switching mode, Ethernet (10 Mbit/s) and Fast-Ethernet (100 Mbit/s)
Port type and quantity	4 x 10/100BASE-TX, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity, 1 x 100BASE-FX, MM cable, MTRJ socket
Type	RS2-5TX/FX
Order No.	943 732-103
<b>More interfaces</b>	
Power supply/signaling contact	1 plug-in terminal block, 5-pin / no signal contact
<b>Network size - length of cable</b>	
Twisted pair (TP)	0 - 100 m
Multimode fiber (MM) 50/125 µm	0 - 5000 m, 8 dB link budget at 1300 nm, A = 1 dB/km, 3 dB reserve, B = 800 MHz x km
Multimode fiber (MM) 62.5/125 µm	0 - 4000 m, 11 dB link budget at 1300 nm, A = 1 dB/km, 3 dB reserve, B = 500 MHz x km
<b>Network size - cascading</b>	
Line - / star topology	any
<b>Power requirements</b>	
Operating voltage	24 V DC (-25% to +30%)
Current consumption at 24 V DC	max. 180 mA
Power consumption	max. 4,0 W at 24 V DC
<b>Service</b>	
Diagnostics	LEDs (power, link status, data, error)
<b>Redundancy</b>	
Redundancy functions	redundant 24 V power supply
<b>Ambient conditions</b>	
Operating temperature	0 °C to +60 °C
Storage/transport temperature	-25 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
MTBF	74,4 years; MIL-HDBK 217F: Gb 25 °C
<b>Mechanical construction</b>	
Dimensions (W x H x D)	40 mm x 145 mm x 80 mm
Mounting	DIN Rail 35 mm
Weight	520 g
Protection class	IP 20
<b>Mechanical stability</b>	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	3.5 mm, 3 Hz - 9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz - 150 Hz, 10 cycles, 1 octave/min.
<b>EMC interference immunity</b>	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 1 kV (line/earth), 0.5 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz - 80 MHz)
<b>EMC emitted immunity</b>	
FCC CFR47 Part 15	FCC CFR47 Part 15 Class A



<b>EN 55022</b>	EN 55022 Class A
<b>Approvals</b>	
<b>Safety of industrial control equipment</b>	cUL 508
<b>Hazardous locations</b>	ISA 12.12.01 Class 1 Div. 2
<b>Scope of delivery and accessories</b>	
<b>Scope of delivery</b>	device, terminal block, operating manual
<b>Accessories to order separately</b>	rail power supply RPS 30, RPS 80 EEC or RPS 120 EEC, 19" installation frame

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.