SM Series Photoelectric Sensors

Contents

Overview	1
Model Selection, Sensors	3
Model Selection, Compatible	
Connector Cables	4
Model Selection, Accessories	4
Wiring Diagrams	4
Specifications	5
Dimensions	5

The Cutler-Hammer® SM Series from Eaton's electrical business provides high performance and ease of use in an economical, compact package.

Lock In on Great Performance with TargetLock™

A sensor can have the greatest performance in the world, but if it is slightly misaligned or the target is positioned at the wrong range, you will have reliability problems sooner or later. TargetLock™ not only simplifies sensor setup but visually confirms your sensor is positioned to operate with the highest possible reliability. In addition, TargetLock™ provides diagnostic information during use to inform you of impending problems before they result in equipment downtime.

No Sensor Is Easier to Use

The SM Series includes many other features that simplify use. Visible sensing beams on all models show you exactly where the sensors are pointing. The durable housing features multiple mounting options to easily fit on your equipment in the tightest of spaces. Full protection from overvoltage, reverse polarity and short circuits reduces the chance of damage. Bright 360° LED indicators clearly show sensor status.

Approvals


- UL Listed
- C-UL Listed

CE



Unless otherwise noted, the products contained in this document are not designed or intended for use in human safety applications.

SM Series™ with TargetLock™ The Easiest Photoelectric Sensor to Set Up and Use



Product Features

- Highly visible LED indicators for power, output and TargetLock[™]
- TargetLock[™] simplifies setup and ensures the sensor operates at the highest level of reliability possible
- Perfect Prox® models sense different colored targets at the same range and ignore objects in the background
- AC/DC models operate on either 18 264V AC or 18 50V DC
- DC-only models feature both NPN and PNP outputs
- Visible beam on all models let you see exactly where the sensor is pointing
- Compact size to fit in tight spaces
- Multiple mounting options including industry standard 18 mm threads
- Reverse polarity, overload and short circuit protection
- Full family includes thru-beam, polarized reflex, diffuse reflective and Perfect Prox® background rejection

Typical Applications

- Packaging Machines
- Conveyors and Other Material Handling Equipment
- Food Processing Equipment
- Assembly Machines
- Pharmaceutical Machines

For Customer Service in the U.S. call **1-877-ETN CARE (386-2273)**, in Canada call **1-800-268-3578**.

For Application Assistance in the U.S. and Canada call **1-800-426-9184**.

August 2007

Unparalleled Optical Performance — Perfect Prox®

Exceptional background rejection sets Perfect Prox® apart from all other sensors. Just point the sensor's visible beam at the target and get reliable detection regardless of color, reflectance, contrast or surface shape, while ignoring background objects just a fraction of an inch away.

Fast and Easy Setup

The SM Series features an advanced 3-LED indicator display to provide valuable information at a glance. The bright display is clearly visible from 360°. In addition to LEDs for power and output status indication, the SM features a third LED that is part of the TargetLock™ system.

TargetLock™ is a microprocessorcontrolled system that enables you to quickly and easily align the sensor and ensure it is operating most reliably.

- Alignment: The TargetLock[™] LED provides a quick and easy way to set up the sensor for optimum operation. On initial setup, when you have achieved the minimum signal required for the sensor to operate, the TargetLock™ LED will blink in a short flash pattern. As you improve the setup and approach the best alignment and range, the LED changes from short flash to long flash to a solid ON condition. This means that even after you reach a point where the sensor will operate in the application, you are able to further fine tune the setup for highest reliability.
- Maintenance: Another valuable feature of the TargetLock™ LED is to indicate the need for maintenance prior to loss of sensor operation. Observing a change from the normal operation of the LED (for example, from solid ON to a long flash) indicates the gain has been reduced. Possible causes include bumping or vibrating out of alignment or contamination buildup on the lens. With the TargetLock™ LED, you are made aware of this condition before the sensor stops working, allowing you ample time to address the problem before your machine goes down.

The following chart details the function of each of the SM Series LED indicators.

LED	State	LED Condition				
		(Thru-Beam/ Reflex)	(Diffuse/ Perfect Prox®)			
Power	ON	Power is applie	er is applied to sensor			
(Green)	OFF	No power				
Output	ON	Output is ON				
(Red)	OFF	Output is OFF				
	Flashing	Output is short circuited or overloaded				
Target- Lock™ (Orange)	ON	Excellent alignment; sensor is operating within optimum range	Target present — excellent gain; sensor is operating within optimum range			
	Long Flash	Good alignment ①	Target present — good gain			
	Short Flash	Poor alignment ①	Target present — poor gain			
	OFF	Target is present; If no target present: sensor is out of alignment or beyond range	No target, or sensor is beyond range			


① A target that doesn't fully block the effective sensing beam or is translucent may cause a flashing indication and unreliable performance.

Gain Adjustment


Thru-beam and diffuse reflective sensors include an adjustment control for optimizing the amount of gain for the application. The 3/4-turn pot provides a 10:1 adjustment of gain. A mechanical stop eliminates the possibility of sensor damage. Adjustment of the control does not require any special tools.

Mounting

The SM sensor features two mounting holes in the rectangular section of the body for mounting to a surface with #6 or smaller hardware. The threaded barrel and jam nut allows mounting into any 0.75 inch (19 mm) hole or a selection of accessory mounting brackets available from Eaton and detailed in **PG.05.03.T.E.**



Mounting sensor using #6 hardware.



Mounting sensor using a jam nut.



Mounted SM sensor in 18 mm Ball Swivel Bracket, as seen in **PG.05.03.T.E**.

Photoelectric Sensors SM Series

August 2007

Model Selection

	Operating Voltage	Sensing Range	Optimum Range	Cutoff Range	Field of View	Thru-Beam Component	Connection Type	Catalog Number	Dark Operate		
Wire and 4-Wire Sensors	Tomage	nunge	nunge	nunge	21044	Joinponent	.урс	Light Operate	Dark Operate		
Thru-Beam	10 – 30V DC	50 feet	0.1 to 25	_	10 inch	Source	2-meter	F65-SI	MTS15-HA		
IIIIu-Dealii	10 001 20	(15m)	feet	_	(254 mm)	Jource	Cable	200 01			
			(30 mm to 7.5m)		diameter at 10 feet						
			10 7.5111)		(3m)		4-pin	E65-SM1	rs15-had :::		
					(0111)		Micro DC	255 511110 15 11112 (6)			
							Connector				
						Detector	2-meter	E65-SMTD15-HL	E65-SMTD15-HD		
Source Detector							Cable				
For a complete system, order one Source and							4-pin	E65-SMTD15-HLD 3	E65-SMTD15-HDD 3		
one Detector							Micro DC Connector				
olarized Reflex	18 – 264V AC 50/60 Hz or	10 feet	0.1 to 5 feet	-	1 inch (25 mm)	-	2-meter Cable	E65-SMPR3-GL	E65-SMPR3-GD		
	18 – 50V DC	(3m)	(30 mm		diameter at		Cable				
	1		to 1.5m)		50 inches						
					(1.3m)		4-pin	E65-SMPR3-GLD 🕄	E65-SMPR3-GDD 3		
	l e						Micro AC Connector				
							Oomicotor				
	10 – 30V DC	10 feet	0.1 to 5	_	1 inch	_	2-meter	E65-SMPR3-HL	E65-SMPR3-HD		
Retroreflector		(3m)	feet (30 mm		(25 mm)		Cable				
(Not Included) Sensor			to 1.5m)		diameter at 50 inches						
			,		(1.3m)		4-pin	E65-SMPR3-HLD (3)	E65-SMPR3-HDD (3)		
For Complete System,							Micro DC				
Order Sensor and Retrore- flector (See PG.05E.17.T.E)							Connector				
Diffuse Reflective	18 – 264V AC	8 inches	0.25 to	_	2 inch	_	2-meter	E65-SMSD200-GL	E65-SMSD200-GD		
and to notice to	50/60 Hz or	(200 mm)		_	(50 mm) diameter at 5 inches (127 mm)	_	Cable	ESS SINOSESS GE	Los omoscos ds		
	18 – 50V DC										
							4-pin Micro AC	E65-SMSD200-GLD (3)	E65-SMSD200-GDD 3		
							Connector				
	10 – 30V DC	8 inches (200 mm)		_	2 inch (50 mm) diameter at	_	2-meter	E65-SMSD200-HL	E65-SMSD200-HD		
							Cable				
T							5 inches	5 inches		es	4-pin
					(127 mm)		Micro DC				
Perfect Prox®	18 – 264V AC	2 inches	0.4+0	2.2 in abox	0.2E inch		Connector 2-meter	E65-SMPP050-GL	E65-SMPP050-GD		
reflect Flox®	50/60 Hz or	(50 mm) 1.8 (58 mm) (6 mm) diameter at		2.3 inches (58 mm)		-	Cable	E03-SIVIPPU3U-GL	E03-3IVIFFU3U-GD		
	18 – 50V DC			4-pin	E65-SMPP050-GLD (#)	E65-SMPP050-GDD (#)					
			(10 mm to 45 mm)	beyond @	2.25 inches (57 mm)		Micro AC				
_		4 in a bas	0.54-	Final an	0.05 :		Connector	FCF CMDD400 CI	FCF CMADD400 CD		
		4 inches (100 mm)		5 inches (127 mm) and beyond 2	0.35 inch (9 mm)		2-meter Cable	E65-SMPP100-GL	E65-SMPP100-GD		
		(**************************************			diameter at		4-pin	E65-SMPP100-GLD (3)	E65-SMPP100-GDD (#)		
1					5 inches (127 mm)		Micro AC				
	10 001/00	1		0.0 : 1			Connector	FOR OBJEDUCES !!!	FOR OMADDOSO UD		
	10 – 30V DC	2 inches (50 mm)	0.4 to 1.8 inches (10 mm to 45 mm)	2.3 inches (58 mm)	0.25 inch (6 mm)	-	2-meter Cable	E65-SMPP050-HL	E65-SMPP050-HD		
7				and	diameter at		4-pin	E65-SMPP050-HLD (#)	E65-SMPP050-HDD (#)		
					2.25 inches (57 mm)		Micro DC	FOO-SIMIL LOOD-UFD (8)			
			·				Connector				
		4 inches	0.5 to	5 inches	0.35 inch (9 mm) diameter at	at	2-meter	E65-SMPP100-HL	E65-SMPP100-HD		
		(100 mm)	3 inches (13 mm to	(127 mm) and			Cable				
			76 mm)	beyond ②	5 inches		4-pin Micro DC	E65-SMPP100-HLD :	E65-SMPP100-HDD ::		
	1	1	1	1	(127 mm)	1	Connector				

Nominal range — sensor will detect a 90% reflectance white card at this range.
 Sensor will ignore a 90% reflectance white card at this range.

Fast turn product with typical one business day lead-time to shipment.

[😩] See listing of compatible connector cables on Page 4.


Model Selection — Compatible Connector Cables ①

	Voltage	Number	Gauge	Length	Catalog Number			Pin Configuration/Wire Colors
	Style	of Pins			PVC Jacket	PUR Jacket	IRR PUR Jacket	(Face View Female Shown)
Standard Cables — Micro Style)							
Micro Style Straight Female	AC	4-pin 4-wire	22 AWG	6.0 feet (2m)	CSAS4F4CY2202	CSAS4F4RY2202	CSAS4F4I02202	1-Red/Black 2-Red/White 3-Red 4-Green
	DC	4-pin 4-wire	22 AWG	6.0 feet (2m)	CSDS4A4CY2202	CSDS4A4RY2202	CSDS4A4I02202	1-Brown 2-White 3-Blue 4-Black


① For a full selection of connector cables, see PG.05.05.T.E.

Stocked product, typical order quantities guaranteed in stock.


Excess Gain



- 1. Thru-Beam
- Polarized Reflex (Based on a 3-Inch Diameter Retroreflector)



- 1.50 mm Perfect Prox®
- 2. 100 mm Perfect Prox®



Diffuse Reflective (Based on a 90% Reflectance White Card)

Model Selection — Accessories

Description	Reference
Retroreflectors and Retroreflective Tape	See PG.05E.17.T.E
Mounting Brackets	See PG.05.03.T.E
Replacement Mounting Nuts and Other Accessories	See PG.05.04.T.E
Connector Cables	See PG.05.05.T.E

Wiring Diagrams (Pin numbers are for reference only, rely on pin location when wiring)

Operating Voltage	Mode	Cable Models	Micro-Connector Models (Face View Male Shown)
B-Wire Sensors	3		
18 – 264V AC, 50/60 Hz or 18 – 50V DC	All Sensors	BN L1 or (-) WH No Connection BU L2 or +V	L2 or +V 2 L1 No Connection 4 or (-)
-Wire Sensors	; ;		•
10 – 30V DC	Thru-Beam Source	BN +V BU (-)	(-) (2) (1) +V
	All Others	BN +V WH Load BK Load BU (-)	(-) Load +V

August 2007

Specifications

	AC/DC Models	AC/DC Models					
	AC Operation	DC Operation					
Input Voltage	18 – 264V AC, 50/60 Hz	18 – 50V DC	10 – 30V DC				
Power Dissipation	4 VA maximum	4 VA maximum	2W maximum				
Output Type	VMOS (bi-directional)	NPN (sink)	NPN and PNP (dual outputs)				
Current Switching	200 mA maximum	200 mA maximum	100 mA maximum				
Voltage Switching	264V AC	50V DC	30V DC maximum				
OFF-State Leakage	500 μA maximum	500 μA maximum	10 μA maximum				
Surge Current	2A maximum	2A maximum	1A maximum				
ON-State Voltage Drop	3.5V maximum	3.5V maximum	2.5V maximum				
Response Time	16 mS	1 mS	1 mS				
Protection	Revers	Short circuit and overload protection (Output Indicator LED will flash). Reverse polarity protection (Sensor will reset automatically once fault is removed). IMPORTANT: During installation, correct power connections must be made first to ensure fail-safe short circuit protection of the outputs					
Light/Dark Operation		By model					
Temperature Range	Ор	Operating: -13° to 131°F (-25° to 55°C); Storage: -13° to 158°F (-25° to 70°C)					
Material of Construction		Lens: Polycarbonate; Cable Jacket: PVC; Body: Cycoloy					
Cable/Connector	Connector N	Cable Models: 6.5 foot (2m) 4-wire cable; Connector Models: 4-pin, micro-connector (AC-key on AC/DC models; DC-key on DC models)					
Vibration and Shock	Vib	Vibration: 30g over 10 Hz to 2 kHz; Shock: 50g for 10 mS 1/2 sinewave pulse					
Indicator LEDs		Green LED: Power; Red LED: Output; Orange LED: TargetLock™					
Source Light		Visible Red, 660 nm					
Gain Adjustment	3/4-turn pot, 1	3/4-turn pot, 10:1 adjustment of gain (provided on thru-beam and diffuse reflective sensors only)					
Sunlight Immunity		Perfect Prox®: 5,000 foot-candles; All others: 10,000 foot-candles					
Enclosure Ratings		NEMA 1, 3, 4, 4X, 6, 6P, 12 and 13; IP68 ①					

① NOTE: Our products conform to NEMA tests as indicated, however, some severe washdown applications can exceed these NEMA test specifications. If you have questions about a specific application, contact our Applications Department.

Approximate Dimensions in Inches (mm)

