70 Series Modular Photoelectric Sensors

Contents

Overview	1
Model Selection,	
Sensor Heads	2
Model Selection,	
Control Units	4
Model Selection,	
Logic Modules	6
Model Selection,	
Output Devices	7
Model Selection,	
Accessories	8
Wiring Diagrams	10
Dimensions	11

The Cutler-Hammer® 70 Series by Eaton's electrical business offers a wide choice of sensor heads, control units, output devices, logic modules, and accessories to solve virtually any problem.

Sensor Heads are connected by cables to the control unit, and can be mounted up to 1000 ft. away. They are available in thru-beam, reflex, diffuse reflective, fiber optic, Curtain-of-Light and slot-style optical modes.


Self-Contained Control Units are available in 4 circuitry types and work with all sensor heads unless noted. Output devices (required for all but Analog) and optional logic modules are contained in a sealed enclosure.

- Standard: General purpose control.
- High Power: 3 times the power of the standard control unit in normal gain mode and 27 times in high gain mode. Gain modes are switch selectable.
- Differential: Compares the signal from 2 separate sensor heads via direct analog signal subtraction. The output is activated when sensor "A" receives more signal than "B." Cannot be used with the 1471A-6501 Curtain-of-Light sensor head.
- Analog: Provides a voltage level output proportional to the amount of light received. Most commonly used with the 1471A-6501 Curtain-of-Light sensor head.



Unless otherwise noted, the products contained in this document are not designed or intended for use in human safety applications.

High Performance Modular Sensors to Solve the Toughest Sensing Problems



Product Features

- Modular design allows you to customize a sensor to solve any application problem
- Control units feature a variety of capabilities and housings
- Logic modules provide added functions including time delays, one-shot outputs and stopped motion detection
- A variety of output devices available for switching AC or DC loads from a few milliamps to 10 Amps
- Unique Curtain-of-Light Sensor Head is ideal for web loop control (when used with the analog control unit) and detection of small parts (when used with 8171B control unit and low contrast module)
- Slot Sensor Head combined with the DIN Rail Mount Control Unit is an easy solution for web guiding or centering applications
- Standard: General Purpose Control Unit
- Enhanced: Time-delay and one shot functions available

Modular Control Units are compact, plug-replaceable units designed for dry locations or mounting within a separate enclosure. An LED indicator provides alignment and beam status. Optional output devices and logic modules are available as separate modular units.

- Standard: General purpose control unit
- Enhanced: Time-delay and oneshot functions available

The **DIN Rail Mount Control Unit** is an analog control unit that provides a voltage output signal which varies proportional to target movement, position or translucence. It is ideal for use with the 1372A-6501 slot sensor head for web guiding or centering.

For Customer Service in the U.S. call 1-877-ETN CARE (386-2273), in Canada call 1-800-268-3578. For Application Assistance in the U.S. and Canada call 1-800-426-9184.

Model Selection — 70 Series Sensor Heads (Connection is by 9-foot cable) ①

Cutler-Hammer

	Sensing Ran	ge by Control	Unit ②③		Field of	Material of	Operating	Infrared	Catalog Number
	A 8171B in High Gain Mode	B 8171B in Normal Gain Mode	C 8170A, 8771A or 8772A	D 8172A or 8173A Analog	View	Construction	Temperature; Enclosure Rating	Sensing Beam Wavelength	
Thru-Beam Right-Angle Viewing Threaded Housing	15 feet (4.5m)	5.5 feet (1.6m)	3 feet (0.9m)	_	Source: 25° Detector: 45° Effective Beam: 0.10 inch (3 mm)	Housing: Stainless Steel Lens: Plastic	-40° to 176°F (-40° to 80°C) NEMA 4,13	925 nm	Source: 1179A-6501 Detector: 1279A-6501
Thru-Beam Forward Viewing Smooth Housing	32 feet (9.7m)	10.2 feet (3.1m)	6 feet (1.8m)	_	Source: 10° Detector: 25° Effective Beam: 0.15 inch (4 mm)	Housing: Aluminum Lens: Glass	-40° to 212°F (-40° to 100°C) NEMA 1	880 nm	Source: 1170A-300 Detector: 1270A-300
Thru-Beam Forward Viewing Threaded Housing Short Range	31.2 feet (9.5m)	10.2 feet (3.1m)	6 feet (1.8m)	_	Source: 10° Detector: 25° Effective Beam: 0.15 inch (4 mm)	Housing: Stainless Steel Lens: Lexan (Acrylic)	-40° to 176°F (-40° to 80°C) NEMA 3, 4, 6, 12, 13	940 nm	Source: 1173A-300 Detector: 1273A-300
Thru-Beam Forward Viewing Threaded Housing Medium Range	369 feet (112m)	123 feet (37.5m)	71 feet (21.6m)	_	Source: 2° Detector: 2° Effective Beam: 0.55 inch (14 mm)	Housing: Aluminum Lens: Glass	-40° to 176°F (-40° to 80°C) NEMA 4, 6, 13	880 nm	Source: 1173A-100 Detector: 1273A-100
Thru-Beam ® Forward Viewing Threaded Housing Long Range	743 feet (226m)	248 feet (75.6m)	143 feet (43.6m)	_	Source: 1° Detector: 1° Effective Beam: 0.88 inch (22.4 mm)	Housing: Aluminum Lens: Glass	-40° to 176°F (-40° to 80°C) NEMA 4, 6, 13	880 nm	Source: 1173A-200 Detector: 1273A-200
Reflex (Includes Retroreflector)	Do not use in this mode	23 feet (7m)	15 feet (4.5m)	_	0.75 inch (19 mm) diameter at 24 inches (610 mm)	Housing: Cast Zinc Lens: Acrylic	-40° to 176°F (-40° to 80°C) NEMA 1	940 nm	1470A-6501

① See Control Unit specification Page 6 on for restrictions on longer length cables, see Accessories for extension cable.

② Sensing ranges are based on a 3-inch retroreflector for reflex; 90% reflectance white card for diffuse reflective.

 $[\]ensuremath{^{\circlearrowleft}}$ For gain graphs and additional specifications, see Page 6.

Precise alignment must be maintained for this model. Catalog Number 6142A or 6168A mounting brackets shown on Page 9 are recommended.

Fast turn product with typical one business day lead-time to shipment.

Model Selection — 70 Series Sensor Heads (Connection is by 9-foot cable) (Continued)

	Sensing Range by Control Unit ②③				Field of	Material of	Operating	Operating Infrared	
	A 8171B in High Gain Mode	B 8171B in Normal Gain Mode	C 8170A, 8771A or 8772A	D 8172A or 8173A Analog	View	Construction	Temperature; Enclosure Ratings	Sensing Beam Wavelength	
Reflex Curtain-of-Light (Retroreflector sold separately)	_	6 feet (1.8m) (Requires 8215A Low Contrast module)	_	6 feet (1.8m)	6° by 60° fan- shaped sensing zone	Housing: Aluminum Lens: Acrylic	-5° to 158°F (-20° to 70°C) NEMA 1, 3, 4, 6, 12, 13	940 nm	Sensor Head: 1471A-6501
									Retroreflector: 6210A-6501
Diffuse Reflective	36 inches (914 mm)	_	7 inches (177 mm)	_	2 inch (50 mm) diameter at 7 inches (177 mm)	Housing: Cast Zinc Lens: Glass	-40° to 212°F (-40° to 100°C) NEMA 1	940 nm	1370A-6501
Diffuse Reflective Fixed Focus	2.5 ± 0.25 inches (63.5 ± 6 mm)	_	_	_	0.12 inch (3 mm) diameter at 2.5 inches (63.5 mm)	Housing: Delrin Lens: Glass	-40° to 212°F (-40° to 100°C) NEMA 1, 3, 4, 12, 13	940 nm	9082A-6501
Slot Sensor Head	_	_	_	2 inch (50 m) slot	Fan-shaped zone 2.75 inches (70 mm) wide at base	Housing: Aluminum Lens: Acrylic	-32° to 140°F (-0° to 60°C) NEMA 1	880 nm	1372A-6501
Glass Fiber Optic For diffuse reflective sensing (order both parts for a complete system)	Do not use in this mode	1.5 inches (38 mm)	1 inch (25 mm)	_	30°	Sensor: Anodized Aluminum Glass fiber: ABS, Brass	-40° to 212°F (-40° to 100°C) NEMA 1	940 nm	Source: 1571A-6501 Fiber: 6276A-6501
Glass Fiber Optic Adapter	PG.05E.15.	T.E) for thru-b	eam or diffu	se reflective	l sensor heads for us sensing. To use orc er optic cable(s).				6221A-7501

- ① See Control Unit specification on Page 6 for restrictions on longer length cables, see Accessories on Page 9 for extension cable.
- ② Sensing ranges are based on a 3-inch retroreflector for reflex; 90% reflectance white card for diffuse reflective.
- $\ensuremath{^{\circlearrowleft}}$ For gain graphs and additional specifications, see Page 6.
- Fast turn product with typical one business day lead-time to shipment.
- Stocked product, typical order quantities guaranteed in stock.

Model Selection — Control Units (See Page 7 and Page 8 for logic modules and output devices) 102

	Maximum (Cable Length	Response Time		Output	Operating Temp.	Power Input	Catalog Number
	Source	Detector	Light-to-Dark	Dark-to-Light		Enclosure Rating		
Control Unit Self-Contained	1000 feet (304m)	75 feet (22m)	3 mS (5 mS maximum)	0.5 mS (1.5 mS maximum)	Requires Output Module	32° to 158°F (0° to 70°C) NEMA 3, 4, 6, 12, 13	115V AC, 50/60 Hz 230V AC, 50/60 Hz	8170A-6501 8170A-6502
	1000 (
Self-Contained Control Unit without Enclosure (circuit board only) ® 4	1000 feet (304m)	75 feet (22m)	3 mS (5 mS maximum)	0.5 mS (1.5 mS maximum)	Requires Output Module	32° to 158°F (0° to 70°C)	115V AC, 50/60 Hz 230V AC,	8170A-6504 8170A-6505
Control Unit	1000 feet	High Gain:	High Gain:	High Gain:	Requires	4° to 131°F	50/60 Hz 95 – 130 V _{RMS}	8171B-6501
Self-Contained High Power	(304m)	36 feet (11m) Normal Gain: 250 feet	14 mS Normal Gain: 3 mS	4.5 mS Normal Gain: 1.5 mS	Output Module	(-20° to 55°C) NEMA 3, 4, 6,	50/60 Hz	
		(76m)				12, 13	190 – 260 V _{RMS} , 50/60 Hz	8171B-6502
Control Unit Self-Contained Differential 4	1000 feet (304m)	150 feet (45m)	3 mS — Sensor A 5 mS — Sensor B		Requires Output Module	32° to 158°F (0° to 70°C)	115V AC, 50/60 Hz	9072A-6501
Differential						NEMA 3, 4, 6, 12, 13		
Control Unit Self-Contained Analog ①	250 feet (76m)	100 feet (30m)	Difference between actual output and equilibrium value is halved every 12 mS ± 3 mS for a step input change. 5% setting time is 40 mS ± 15 mS		Output voltage is field adjustable from -15V to +10V DC. Can be isolated with analog	14° to 131°F (-10° to 55°C) NEMA 3, 4, 6, 12, 13	90 – 130V AC, 60 Hz or 100 – 125V AC, 50 Hz 190 –260V AC,	8172A-6501 8172A-6502
c c					isolation module accessory		60 Hz or 200 – 250V AC, 50 Hz	
Control Unit Modular ® (Requires 11-pin panel mount socket 8905A-6501 for installation, See Page 10)	1000 feet (304m)	150 feet (45m)	3 mS maximum	0.5 mS maximum	Complementary open collector transistor outputs Sink: 150 mA (ON) or standoff 30V DC (OFF) ®	-5° to 122°F (-15° to 50°C) NEMA 1	9 – 18V DC, 135 mA max. (see PG.05.06.T.E for regulated DC power supply)	8771A-6501
Control Unit ® Modular Enhanced With time delay or one-shot function (adjustable from 0.02 to 15 seconds) (Requires an 11-pin panel mount socket 8905A-6501	1000 feet (304m)	150 feet (45m)	3 mS maximum	0.5 mS maximum	Complementary open collector transistor outputs Sink: 150 mA (0N) or standoff 30V DC (0FF) (5)	-5° to 122°F (-15° to 50°C) NEMA 1	9 – 18V DC, 170 mA max. (see PG.05.06.T.E for regulated DC power supply)	8772A-6501
for installation, See Page 10) Control Unit® DIN Rail Mount Analog	250 feet (76m)	100 feet (30m)	20 mS for 10 – 90% of signal range at ±10V output		15 mA sourcing and sinking maximum	32° to 131°F (0° to 55°C)	+15V DC 0.1A max. and -15V DC 0.05A max.	8173A-6507

① An output device is required for Self-Contained Control Units (except Analog), and when using Modular Control Units to switch AC loads. Logic modules are optional and not used with Analog Control Units. 8272X-6501 Isolated Output option available for 8172A Analog Control.

² For additional specifications, see Page 6.

⁽⁹⁾ For mounting in existing enclosure, or for use when multiple units are installed in a central location. Mount 2 inches apart minimum to avoid crosstalk.


⁽⁴⁾ Cannot be used with Curtain-of-Light Sensor Head, Catalog Number 1471A-6501.

⑤ Optional output devices can be used for switching AC loads.

[®] Requires user supplied linear regulated power supply. Control unit rise time is 20 mS for 10 - 90% of signal range at ±10V output.


Fast turn product with typical one business day lead-time to shipment.

Excess Gain




Reflex (3 Inch diameter Retroreflector)

- 1. 1470A Sensor Head with 8171B Control Unit
- 2. 1470A Sensor Head with 8170A, 8771A or 8772A Control Unit




Diffuse Reflectance (90% Reflective White Card)

- 1. 1370A with 8171B Control Unit in High Gain Mode
- 2. 1370A with 8171B Control Unit in Normal Gain Mode
- 3. 1370A with 8170A, 8771A or 8772A Control Unit



Fixed Focus (90% Reflectance White Card)

- 1.9082A-6501 with 8171B Control Unit in High Gain Mode
- 2. 9082A-6501 with 8171B in Normal Gain Mode, 8170A, 8771A or 8772A Control Unit



Fiber Optic Diffuse Reflective (90% Reflectance White Card)

- 1. 1571A/6276A with 8171B Control Unit in Normal Gain Mode
- 2. 1571A/6276A with 8170A, 8771A or 8772A Control Unit

Specifications — **Sensor Heads and Control Units**

	Sensor Heads	Control Units		
		Self-Contained	Modular	DIN Rail Analog
Power Dissipation	_	Analog: 18 VA max. All others: 12 VA max.	2.5 Watts max.	2 Watts max.
Sensitivity Adjustment	_	20:1 ratio	20:1 ratio	_
Sunlight Immunity	Depends upon control unit used (Curtain-of-Light: 7,500 foot-candles when used with 8171B control unit)	10,000 foot-candles	6,000 foot- candles	10,000 foot- candles
Relative Humidity (non-condensing)	Thru-beam, fiber optic: 98% Reflex, diffuse reflective: 95%	98%	90%	90%
Vibration	10g or 0.06 inch displacement, whichever is less, over 10 Hz (20 Hz for slot sensor) to 2 kHz	5g up to 1 kHz	5g up to 4 kHz	_
Shock	15g minimum for 1 mS		15g min. for 1 mS	_
Case Material	See Model Selection Table	Aluminum	Lexan® and phenolic	_

Model Selection — Logic Modules (Optional, not used with analog control units)

	Description	For			t Voltage	Input Power	Output Type and	Catalog
		Control Units	Ranges	Н	LO		Ratings	Number
Logic Modules for Self- Contained Control Units 8171B & 8170A (Modules mount to circuit board within control unit enclosure)	Time Delay ON and OFF time delays from 0.01 to 35 seconds. Independent adjustment of ON-delay and OFF-delay.	8170A 8171B 9072A	Timing Ranges: ① 0.01 to 0.2 seconds 0.1 to 2.0 seconds 1.0 to 15.0 seconds 2.0 to 35.0 seconds	_	_	Provided by Control Unit	See Specifications for Selected Output Device	8212B-6501
	One-Shot Produces a pulse of preset time when triggered. Switch- select to trigger on leading or trailing edge of object.	8170A 8171B 9072A	Pulse Width: ① 0.02 to 0.5 seconds 0.3 to 2.0 seconds 1.0 to 18.0 seconds 10.0 to 30.0 seconds	_	_	Provided by Control Unit	See Specifications for Selected Output Device	8213B-6501
	Stopped Motion Retriggerable one-shot. Start-up delay adjusts from 0.1 to 11 seconds to allow machine to come up to speed. Control can be reset from remote location.	8170A 8171B 9072A	Retrigger Interval: ① 30 to 430 RPM 430 to 5,000 RPM	_	_	Provided by Control Unit	See Specifications for Selected Output Device	8216A-6501
	Low Contrast Responds to slight but abrupt signal variation while ignoring slower changes. Response Time: 0.1 mS.	8171B	Output one-shot time: 20 mS to 2.5 seconds (After this point it becomes a latch function.)	_	_	Provided by Control Unit	See Specifications for Selected Output Device	8215A-6501
Logic Modules for Modular Control Units (Lexan® cover with phenolic base,	Time Delay Provides ON and OFF delay timing, with independent adjustment of ON-delay and OFF-delay.	8771A 8772A	Timing Range: 0.5 to 15 seconds	V supply 4V min.	0.4V max.	9 – 18V DC, 13.3 mA max.	Open Collector, 110 mA sink, 30V DC maximum protected for load spikes above 35V	8712A-6501
(Requires 11-pin panel mount socket 8905A-6501 for installation, See Page 10)	One-Shot ③ Produces a pulse of preset time when triggered. Jumper-selected retriggerable mode for stopped motion detection.	8771A 8772A	Pulse Width: ① 0.02 to 0.325 seconds 0.2 to 6.5 seconds	V supply 3.5V min.	3V max.	11 – 15.5V DC, 40 mA max.	Open Collector, 110 mA sink, 30V DC maximum protected for load spikes above 35V	8713A-6501
	Shift Register ③ ④ Delays the response to a beam break (or beam completion) by a preset number of clock pulses, usually generated by a pulse generator on a conveyor.	8771A 8772A	Register Length: 1 to 64 clock pulses		_	10 – 15.5V DC, 60 mA max.	Complementary open collector NPN transistor; On-state: 150 mA max. with 1V max. drop Off-state: 1 µA max. leakage at 30V DC	8730A-6501

- ① Once range is selected, exact value is adjusted via potentiometer.
- $\ensuremath{^{\circ}}$ Driving device must be capable of sinking 1.6 mA maximum to ground.
- ③ Clear pin input (allows outputs to be cleared or held, in untriggered state, independent of input). One-Shot — Voltage HI: 1.0V minimum; Voltage LO: 0.4V maximum. Shift Register — Voltage HI: 2/3 input voltage minimum; Voltage LO: 1/3 input voltage maximum.
- Pulse width: 20 mS (voltage must not exceed input voltage).

 4 Clock and date inputs
- Shift Register Rate: 600 Hz maximum fast mode, 30 Hz maximum slow mode; Pulse Width (data): 0.75 mS minimum fast mode, 15 mS minimum slow mode (voltage must not exceed input voltage); Logic level 1 (HI): 2/3 input voltage minimum; Logic level 0 (LO): 1/3 input voltage maximum.
- Fast turn product with typical one business day lead-time to shipment.

Model Selection — **Output Devices** (Required for Self-Contained Control Units [except analog] and when switching AC loads with Modular Control Units)

<u> </u>	Description	Input		Output					Catalog Numbe
		Operating Voltage	Current	Туре	ON-State Current	OFF-State Leakage	ON-State V Drop	One Cycle Surge A	
Output Devices for 8170A and 9072A Control Units	DPDT Relay For low frequency general purpose switching of control power loads	Supplied — by Control Unit		DPDT Contact Ratings: AC Load: 5A at 115V AC or 230V AC DC Load: 5A at 30V DC Contact Life: 100,000 operations at rated load					8526A-6501
	Isolated Triac For high rate switching of resistive or inductive AC loads	Supplied by Control Unit		SPST Normally open triac	2 A _{RMS} continuous	5 mA at 100V AC	1.7 V _{RMS} or less	20A peak	8570A-6501
-	Triac, PC Compatible Optically isolated solid- state relay for switching non-capacitive AC loads. Response is 100,000 operations/hour	Supplied by Control Unit		SPST Normally open triac	5-500 mA _{RMS} at 70°C	1.5 mA at 120V AC	1.7V maximum	6A peak	8574A-6501
	Optical Isolator Driver Drives a user supplied remote optical isolator for a solid-state interface. Isolator can then be used to switch DTL, TTL, CMOS, etc.	Supplied by Control Unit		PNP output drive to a remote optical isolator	20 mA	_	_		8580A-6501
	Isolated NPN Transistor Optically isolated NPN SPST transistor switch	Supplied by Control Unit	_	Optically isolated NPN transistor switch	20 mA at V _{SAT} less than 0.2V	0.01 mA maximum at 30V DC	_	_	8582A-6501
Output Device for 8172A Control Unit (optional)	Analog Isolation Module Eliminates ground loop problems and induced noise between the control unit and other system components	Supplied by Control Unit	_	allowing the controllers v Bi-directions	e 8172A's outpu control unit to vith control cir al output: 30 m 75V DC ± 1.0V r	interface with cuitry at the A A from E2 to E	n solid-state A .C line potentia	دC motor al.	8272A-6501
Output Devices for 8171B, 8771A and 8772A Control Units	DPDT Relay Plug-in industrial control relay	12V DC nominal. Supplied by Control Unit	75 mA at 75°F 12V DC	DPDT Contact Ratings: Resistive Load: 10A, 1/4 hp maximum at 110/220V AC 10A maximum at 28V DC Inductive Load: 7A maximum at 110/220V AC, 7A maximum at 28V DC Contact Life: 500,000 operations at rated load			IV AC,	8530A-6501	
	Isolated Triac Optically isolated, solid-state relay for switching non- capacitive AC loads. Response is 100,000 operations/hour	3 – 20V DC Supplied by Control Unit	_	SPST Normally open triac	2 A _{RMS} at 25°C, 1 A _{RMS} at 65°C	5 mA at 100V AC, 9 mA at 200V	1.7 V _{RMS} or less	60A peak	8572A-6501
Polycarbonate Housing (requires an 8-pin panel mount socket Catalog Number 8907A-6501 for installation when used	Triac, PC Compatible Optically isolated, solid-state relay for switching non- capacitive AC loads. Response is 100,000 operations/hour	8 – 20V DC Supplied by Control Unit	9.5 – 20 mA	SPST Normally open triac	5 – 500 mA _{RMS} at 70°C	1.5 mA at 120V AC	1.7V maximum	6A peak	8573A-6501
	Isolated NPN Transistor Optically isolated, NPN SPST transistor switch	12V DC nominal	20 mA typical	Optically isolated NPN transistor switch	20 mA at V _{SAT} less than 0.2V, 500 mA at V _{SAT} less than 1V ①	10 µA maximum at 30V DC	_	_	8586A-6501

- ① For 3-wire connection. For 2-wire connection, 100mA at V_{SAT} less than 1.2V.
- $\, @ \,$ For 3-wire connection. For 2-wire connection, 0.1 μA maximum at 30V DC.
- Fast turn product with typical one business day lead-time to shipment.
- Stocked product, typical order quantities guaranteed in stock.

Specifications — Output Devices

	DPDT Relays		Triacs	Others	
	8526A-6501	8530A-6501	Isolated	PC Compatible	
Operating Temperature	-40° to 140°F (-40 to 60°C)	-4° to 131°F (-20° to 55°C)	-4° to 149°F (-20° to 65°C)	-4° to 149°F (-20° to 65°C)	-4° to 149°F (-20° to 65°C)
Response Time	15 mS	25 mS maximum	1 mS maximum		Instantaneous
Off-to-On (pull-in) On-to-Off (drop-out)	5 mS	25 mS maximum	1/2 cycle of line voltage		Instantaneous
Pull-In Voltage	8 – 9.6V	8 – 9.6V	3V minimum	8 – 20V	_
Drop-Out Voltage	1.2 – 2V	1.2 – 2V	0.8V maximum	_	_

8

August 2007

Model Selection — Accessories

Cutler-Hammer

	Description	Catalog Number	Approximate Dimensions in Inches (mm) Except Where Noted
	For a selection of mounting brackets for use with tubular sensor heads	See PG.05.03.T.E	
L-Shaped Mounting Bracket	For horizontal or vertical mounting of Catalog Number 1370A and 1470A reflex sensor heads	6177A-6501	0.325 (8.2) 0.563 (14.3) 0.563 (14.3) 0.564 (14.3) 0.564 (14.3) 0.564 (14.3) 0.565 (14.3) 0.
Mounting Clip	Stainless steel, for Catalog Number 1170A and 1270A sensor heads, two per package	6170A-6501	NOTE: Dimensions in Inches
6° Mounting Block	Converts 70 Series 3/4 inch thru-beam heads to high gain diffuse reflective sensor. Chromate finished aluminum	6162A-6501	0.625 (15.9) Diameter x 0.75 (19) Deep C Bore 2.50 3 1.10 (28) (31.8) 0.40 (10.2) 1.30 (2 Places) 2.60 (63.5) 1.00 (12.7) (25.4) (25
Metal Ball Swivel Mount	Allows 5.5° rotation with screw lock to fix final position. Extremely rugged, made from zinc plated steel/Celenex [®] . Electrically isolates the sensor to prevent noise pick-up caused by poor grounding.	6168A-6501	0.75 (19.1) Diameter Hole 1.0 (53) 2.1 1.0 (53) 2.5 (12.7) 1.1 (28) 0.5 (12.7) 1.1 (28) 0.3 (7.5) Diameter Slot
Plastic Ball Swivel Mount	Allows 10° rotation on X and Y axes with a clamping action to hold adjustment. Noryl — avoid exposing to chlorinated halogenated or aromatic hydrocarbons. Operating temperature: -40° to 160° F. 18 mm (3/4 inch) 8 mm (3/8 inch) (11/1273A-300)	6143A-6501	Clamping Gap This Side Size A B C D E F G 8 mm 1.96 1.56 0.20 0.40 0.80 1.05 0.375 (49.8) (39.6) (5.1) (10.2) (20.3) (26.7) (9.5) 18 mm 2.80 2.25 0.275 0.50 1.00 1.64 0.75 (71.1) (57.2) (7.0) (12.7) (25.4) (41.7) (19.1)

Stocked product, typical order quantities guaranteed in stock.


Model Selection — **Accessories** (Continued)


	Description	Catalog Number	Approximate Dimensions in Inches (mm)
Retroreflectors	Retroreflectors and retroreflective tape	See PG.05E.17.T.E	
Sensor Head Extension Cables	Source extension cable Order quantity = Length in feet i.e. Qty. 20 of model 6503-xxx = One 20 foot length extension cable	6503A-XXX	
(see control unit specifications for maximum extended cable length)	Detector extension cable Order quantity = Length in feet i.e. Qty. 20 of model 6503-xxx = One 20 foot length extension cable	6507A-XXX	
Conduit Coupling	Brass compression fitting for connecting Catalog Number 8903A-6501 flexible conduit to control unit	8904A-6501	
Thru-Beam Sensor Head Apertures	With 0.04 inch hole for small parts detection. Used with Catalog Number 1173A-300 and 1273A-300 sensor heads.	6271A-6501	0.040 (1.02) 0.50 (12.7) Diameter Thru-Hole
	With 0.025 inch slot for small parts detection. Used with Catalog Number 1173A-300 and 1273A-300 sensor heads.	6271A-6502	0.095 (2.4)
Fiber Optic Cables	Glass fiber optic cables (for use with 6221A-7501 fiber optic adapters)	See PG.05E.15.T.E	
Module Panel Mount Sockets	11-pin panel mount socket for Catalog Number 8712, 8713 and 8730 Logic Modules, and 8771 and 8772 Modular Control Units	8905A-6501	2.99 (75.8) — 1.70 (43.2) (50.0) (36.3) (60.0) (36.3) (60.0) (60.
	8-pin panel mount socket for Catalog Number 8530, 8572, 8573 and 8586 Output Devices	8907A-6501	1.63 (41.3) 1.33 0.88


Stocked product, typical order quantities guaranteed in stock.

Wiring Diagrams — Self-Contained Control Units


Standard: 8170A-6501, -6502, -6504 and -6505













⊕







Wiring Diagrams — Modular Control Units

Standard: 8771A-6501

Optical Isolator Driver Model 8580A




Enhanced with Time Delay or One-Shot: 8772A-6501




Wiring Diagram — DIN Rain Mount Analog Control Unit

8173A-6507




Wiring Diagrams — Logic Modules


Time Delay: 8712A-6501



One-Shot: 8713A-6501




Shift Register: 8730A-6501




When connecting to relay contacts for clock and data signals, clock and data inputs have 15 mS of debounce filtering. Clock speed and data speed bypass the debounce filter but a jumper from clock speed to clock is required if a pull-up resistor is desired. The same applies to data speed and data inputs.

Approximate Dimensions in Inches — Thru-Beam Sensor Heads


Right-Angle Viewing: 1179A-6501 and 1279A-6501




Forward Viewing: 1170A-300 and 1270A-300




Forward Viewing: 1173A-300 and 1273A-300



Forward Viewing: 1173A-100 and 1273A-100




Forward Viewing: 1173A-200 and 1273A-200




Approximate Dimensions in Inches — Reflex Sensor Heads


Standard: 1370A-6501



Curtain-of-Light: 1471A-6501




For Retroreflector Curtain-of-Light: 6210-6501




Approximate Dimensions in Inches — Diffuse Reflective Sensor Heads

Standard: 1470A-6501




Fixed Focus: 9082A-6501



Approximate Dimensions in Inches (mm) — Slot Sensor Heads


1372A-6501



Approximate Dimensions in Inches (mm) Except Where Noted — Fiber Optic Sensor Heads


Glass Fiber Optic: 1571A-6501 and 6276A-6501

NOTE: Dimensions in Inches




Approximate Dimensions Shown in Inches — Self-Contained Control Units


Standard: 8170A-6501 and -6502




High Power and Analog: 8171B-6501 and -6502;



Standard without Enclosure: 8170A-6504 and -6505




Differential: 9072A-6501




Approximate Dimensions in Inches — Modular Control Units

8771A-6501 and 8772A-6501



Approximate Dimensions in Inches (mm) Except Where Noted — DIN Rain Mount Analog Control Unit

8173A-6507



Approximate Dimensions in Inches — **Logic Modules**

8712A-6501, 8713A-6501 and 8730A-6501

