## **ZVC45 Series**

### Single output 20W to 45W AC/DC External Adapters

So small it's hardly there. Packing 8 watts per cu. inch the EOS ZVC45 "Micro Z model' adapters range in power from 20 watts to 45 watts and are available in popular voltage outputs from 5 volts to 24 volts.

Applications include low power LAN/WAN routers, hubs and switches, industrial products, computing equipment, multimedia gear and many general electronics applications. Millions are in operation with leading product brands. These small package, big power adapters provide greater than 90% efficiency converting AC power to DC. The cell phone size Micro Z measures a mere 3.50" x1.76" x 0.967" and weighs under 6 ounces. The ZVC45 Micro Z adapters feature auto ranging AC input from 90v to 264v, operating temperature of 0 to 40 degrees C and have worldwide safety and agency certifications and are RoHs compliant. Our factory also is ISO140001 environmentally approved.



#### Features:

- High power density up to 8W/in<sup>3</sup>
- > Efficiency to 90%
- **Smallest 45W adapter**
- EN55022-B, FCC Part 15 Level B Noise safety approvals
- Class 2 safety approvals

Model Number	Case Type	Voltage	Current	Min Current Limit Point
ZVC20FS05E	FS	5V	4.00A	5.00A
ZVC25FS09E	FS	9V	2.77A	3.50A
ZVC36FS12E	FS	12V	3.00A	3.35A
ZVC36FS15E	FS	15V	2.40A	2.60A
ZVC36FS19E	FS	19V	1.90A	2.05A
ZVC36FS24E	FS	24V	1.50A	1.62A
ZVC45FS19E	FS	19V	2.36A	2.52A
ZVC45FS24E	FS	24V	1.87A	2.00A

INPUT SPECIFICATIONS				
AC Input	Auto - Ranging	90 to 132V 180 to 264V		
Efficiency	5V Other Models	82% >90%		
Input Frequency		47-63 Hz		
Input Current	Full Load at low line	1.1Arms, max		
Inrush Current	High Line, cold start	40A, Max		
Leakage Current		<250 μA		

OUTPUT SPECIFICATIONS				
Output Power		20 to 45W		
Minimum Load	5V output models 9V output models Other models	0.5A 0.2A 0.0A		
Hold-Up Time		10ms		
Set Point Accuracy		±5%		
Line Regulation	Low line to high line	± 0.5%		
Load Regulation	Min to Full Load	± 5%		
Transient Response	2.5% Load Change from mid level Voltage Deviation Recovery Time ZVC20 & 25FS ZVC36 & 45FS	<3% <1ms <3ms		
OVP		YES		
Overload Protection		Yes, 125%		
Short Circuit Protection	Auto Recovery <3s	Short Term		
Ripple and Noise	5V Other voltages	60mV 1%		
Output Rise Time		<10ms		

All Red Rocket, Inc. EOS power supplies have UL, CSA and Nemko safety compliance and medical versions meet UL60601-1 standards. All our products are RoHs compliant. Visit us at www.redrocketpower.com and contact us at: sales@redrocketpower.com or by calling +1 805-409-0909 today. © 2008, Red Rocket, Inc. EOS brand power supplies and patents are owned exclusively by Red Rocket, Inc. All Rights Reserved. 39-DE60-43153-002/A1



# **ZVC45 Series**



## Single output 20W to 45W AC/DC External Adapters

MECHANICAL SPECIFICATIONS				
Input Connector	IEC320 C8			
Output Connector	Right angle, hollow coax plug 0.10" (2.54mm) inside and 0.216" (5.49mm) outside diameter. Center positive polarity			
Size	3.5 x1.76 x 0.967 " (88.9 x 44.7 x 24.57 mm)			
Weight	5oz (150g)			

EMC AND SAFETY SPECIFICATIONS				
CE Mark	Complies with low voltage and EMC Directives			
EMC	EN5022-B,CISPR22-B, FCC Part 15 Class B, EN50082-1			
Agency Approvals	NEMKO, UL, c-UL,GOST,CCIB, MITI, PCBC, MEEI			
Safety Standards	IEC60950, CSA C22.2 No. 60950, EN60950, UL1950 Class 2 SELV			
Safety file numbers	NEMKO: P06206737 UL : E150565			

<u>'</u>					
ENVIRONMENTAL SPECIFICATIONS					
Operating Temperature		0 to 40° C			
Storage Temperature		-40 to 85° C			
Cooling		Convection			
Relative humidity	Non condensing	95%, max			
MTBF	MIL-HDBK 217F	> 100,000 hrs			



