



MACH102-8TP-R

Industrial Networking:Industrial Ethernet:MACH100:Switches

Delivery informations	
Availability	available
Document created at	22.05.2009
Product description	
Description	26 port Fast Ethernet/Gigabit Ethernet Industrial Workgroup Switch (fix installed: 2 x GE, 8 x FE; via Media Modules 16 x FE), managed, Software Layer 2 Professional, Store-and-Forward-Switching, fanless Design, redundant power supply
Port type and quantity	Up to 26 Ethernet ports, thereof up to 16 Fast-Ethernet ports via media modules realisable; 8x TP (10/100 BASE-TX, RJ45) Fast Ethernet ports and 2 Gigabit Combo ports fix installed
Type	MACH102-8TP-R
Order No.	943 969-101
More Interfaces	
Power supply/signaling contact	1 x plug-in terminal block, 2-pin, output manual or automatic switchable (max. 1 A, 24 V DC bzw. 24 V AC)
V.24 interface	1 x RJ11 socket, serial interface for device configuration
USB interface	1 x to connect auto-configuration adapter ACA21-USB
Network size - length of cable	
Twisted pair (TP)	0 - 100m
Multimode fiber (MM) 50/125 µm	Fast Ethernet: cf. SFP LWL module M-FAST SFP-MM/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
Multimode fiber (MM) 62.5/125 µm	Fast Ethernet: cf. SFP LWL module M-FAST SFP-MM/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
Single mode fiber (SM)9/125 µm	Fast Ethernet: cf. SFP LWL module M-FAST SFP-SM/LC and M-FAST SFP-SM+/LC; Gigabit Ethernet: cf. SFP LWL module M-SFP-LX/LC
Single mode fiber (LH)9/125 µm (long haul transceiver)	Fast Ethernet: cf. SFP LWL modul M-FAST SFP-LH/LC; Gigabit Ethernet: cf. SFP LWL modul M-SFP-LH/LC and M-SFP-LH+/LC
Network size - cascadiability	
Line - / star topology	any
Ring structure (HIPER-Ring) quantity switches	50 (reconfiguration time < 0,3 sec.)
Power requirements	
Operating voltage	100 - 240 VAC, 47 - 63 Hz
Power output in Btu (IT) h	44 (without media modules)
Rated current	0.4 - 0.2 A
Power consumption	13 W (without media modules)
Software	
Management	serial Interface, web interface, SNMP V1/V2, HiVision file transfer SW HTTP/TFTP
Diagnostics	LEDs, log-file, syslog, signal contact, RMON (statistic, history, alarms, events), port mirroring, topology discovery 802.1AB, cable diagnostic
Configuration	Comand line interface (CLI), TELNET, BootP, DHCP, DHCP option 82, HiDiscovery, auto-configuration adapter (ACD11, ACA21-USB), Watchdog configuration; integrated DHCP server
Security	Port security (IP and MAC), SNMP V3, SSH, authentication (802.1x)

Redundancy functions	HIPER-ring (ring structure), MRP (IEC-ring functionality), RSTP 802.1D-2004, redundant network/ring coupling, dual homing, link aggregation, redundant 100 - 240 VAC power supply
Filter	QoS 4 Klassen, Portpriorisierung (IEEE 802.1D/p), VLAN (IEEE 802.1Q), shared VLAN learning, Multicast (IGMP Snooping/Querier), Multicast Detection unknown Multicast, Broadcastlimiter, Fast Aging, Multicast GMRP IEEE 802.1D
Industrial Profiles	EtherNet/IP, PROFINET, configuration and diagnostic via automation software tools like e.g. STEP7, or Control Logix
Realtime	SNTP server, realtime clock with energy buffer
Flow control	Flow Control 802.3x, Port Priority 802.1D/p, Priority (TOS/DIFFSERV), Prio (MAC/IP), Prio Mapping (TOS Layer2), Traffic Shaping (Unicast, Multicast, Broadcast) Ingress / Egress
Ambient conditions	
Operating temperature	0° - +50°C
Storage/transport temperature	-20° - +85°C
Relative humidity (non-condensing)	10% to 95%
MTBF	18.06 years (MIL-HDBK-217F Gb 25°C) (without media modules)
Mechanical construction	
Dimensions (W x H x D)	448 x 310 x 44 (without fixing bracket)
Mounting	19" control cabinet
Weight	3.85 kg
Protection class	IP20
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80 - 2700 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 4 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz - 80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	cUL 508 (pending)
Scope of delivery and accessories	
Scope of delivery	MACH100 device, terminal block for signal contact, 2 brackets with fasteningscrews (pre-assembled), housing feet - stick-on, non-heating appliance cable - Euro model, CD-ROM with user manual, installation user manual
Accessories to order separately	Fast Ethernet SFP modules, Gigabit Ethernet SFP modules, autoConfiguration Adapter ACA21-USB, terminal cable, Industrial Hivision Network Management software