

www.circuitprotection.com

308 Constitution Drive Menlo Park, CA 94025-1164 Phone: 800-227-4856

# PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: microSMD035F

DOCUMENT: SCD25265

**REV LETTER: H** 

**REV DATE: MAY 13, 2011** 

PAGE NO.: 1 OF 1

# **Specification Status: Released**

# **Maximum Electrical Rating**


Voltage: 6.0V<sub>DC</sub>


**Short Circuit Current: 40A** 

#### Notes:

- 1. All terminations are tin plated.
- 2. Drawing not to scale

# Marking:





### **TABLE I. DIMENSIONS:**

	Α		В		С		D		Е
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
mm:	3.00	3.43	0.38	0.62	2.35	2.80	0.25	0.75	0.076
in:	(0.118)	(0.135)	(0.015)	(0.025)	(0.092)	(0.110)	(0.010)	(0.030)	(0.003)

### TABLE II. PERFORMANCE RATINGS:

CUI	RRENT F	RATING	SS**		TIME TO TRIP**	RESISTANCE VALUES		TRIPPED-STATE POWER DISSIPATION**			
AMPERES			AMPERES		SECONDS	OHMS		WATTS AT			
AT 0°C	AT 20°C		AT 60°C		AT 20°C, 8A	AT 20°C		20°C, 6V			
HOLD TRIP	HOLD	TRIP	HOLD	TRIP	MAX	MIN	MAX*	MAX			
0.40 0.85	0.35	0.75	0.24	0.51	0.2	0.32	1.30	0.8			

- \* Maximum resistance is measured 1 hour after reflow.
- \*\* Values specified were determined using PCB's with 0.030"X1.5 ounce copper traces.

Agency Recognition: UL, CSA, TÜV

Reference Documents: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

## **Materials Information**

**ROHS Compliant** 

Directive 2002/95/EC Compliant **ELV Compliant** 

Directive 2000/53/EC Compliant Pb-Free



**Halogen Free\*** 



© 2006, 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All rights reserved.

<sup>\*</sup> Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm