**E·T**•**N** Cutler-Hammer

## Photoelectric Sensors Comet Series

## Comet Series Photoelectric Sensors

## **Contents**

Overview Model Selection, Sensors Model Selection, Compatible	
Connector Cables	5-36
Wiring Diagrams	5-36
Specifications	5-37
Model Selection,	
Accessories	5-38
Dimensions	5-39

The Cutler-Hammer<sup>®</sup> Comet Series from Eaton's electrical business is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.

The sensors are available in thrubeam, reflex, polarized reflex, diffuse reflective, focused diffuse reflective, wide angle diffuse reflective, Perfect Prox®, fine spot Perfect Prox® and fiber optic sensing. Perfect Prox® is one of the most powerful problem-solving sensors available. These sensors can reliably detect targets of different color, reflectance, contrast or surface shape at the same range, while ignoring background objects just a fraction of an inch away.

The Comet Series includes AC/DC and DC-only models with 2-, 3- and 4-wire circuitry. Choose from cable or microconnector. Mini-connectors are available on 2-wire models for easy retrofit. Each sensor features a Light/ Dark Operation switch and a gain control to provide for quick adjustment to peak optical performance.

The unique threaded body with flat sides allows quick mounting in a 3/4 inch hole or against any flat surface. Internal components are rigidly sealed in a solid encapsulated package for excellent performance in highvibration and high-shock applications.


## Approvals

- UL Recognized
- C-UL Recognized

**(** except 2-wire DC models)

For the most current information on this product, visit our web site: www.EatonElectrical.com






# **Product Features**

- Industry standard 18 mm diameter threaded body has flat sides allowing it to be mounted like a tubular sensor or against any flat surface
- Right-angle viewing models mount in a depth of only 6/10th of an inch
- Perfect Prox<sup>®</sup> technology provides exceptional background rejection and application problem-solving
- Visible sensing beams let you see where the beam is aimed for quick setup and alignment
- Solid polyurethane housing completely encapsulates internal circuits for high resistance to shock and vibration
- Adaptable modulation circuit provides immunity to crosstalk from other closely mounted sensors
- The industry's only background rejection sensors with a 2-wire circuit design
- Models available with both AC and DC operation in a single unit up to 264 volts AC!
- 4-wire DC sensors offer both NPN and PNP outputs
- Output status indicator visible from a wide 270° angle

## **Product Comparison**

Eaton's cost-effective Prism Series, OEM Prism and premium Comet Series all share the same 18 mm flatsided housing. This results in the largest interchangeable sensor family available, allowing you to select from well over 250 different models to solve the widest variety of sensing applications.



പ

# **F·T**•**N** Cutler-Hammer

August 2007

# Sensing Modes

## Thru-Beam

This sensing mode is available with ranges of 20 and 80 feet (6 and 24m). The 20 foot (6m) range is available in forward and right-angle viewing, and can be intermixed in any combination for the best fit in your application. Long range models feature a visible sensing beam to help simplify installation and alignment.

## **Reflex and Polarized Reflex**

In reflex sensing, the sensing beam is reflected from a retroreflector back to the sensor. The Comet Series includes standard and polarized models with 2-wire, 3-wire and 4-wire circuits. Right-angle models are also available. Polarized models feature a polarizing filter built into the sensor to ensure that only light reflected from a corner-cube retroreflector is recognized by the sensor. This allows reliable detection of shiny targets that could reflect light and be missed by a non-polarized sensor. Most models include a visible sensing beam for easy installation and alignment.

# Diffuse Reflective, Focused Diffuse and Wide Angle Diffuse

A wide variety of diffuse reflective models are available with ranges of 8 inches (200 mm) and 24 inches (610 mm). Forward and right-angle viewing configurations offer identical optical performance in this series. Focused diffuse reflective models feature a light beam that is focused at a point 1.6 inches (40 mm) in front of the sensor lens for applications where you need to avoid sensing objects in front of or behind the target. Wide angle diffuse models provide a large spot and wide detection area.

#### **Perfect Prox®**

This is a unique type of diffuse reflective sensor that combines extremely high sensing power (called "excess gain") with a sharp optical cutoff to ignore backgrounds. This allows the sensor to reliably detect targets regardless of variations in color, reflectance, contrast or surface shape, while ignoring objects that are just slightly outside the target range. This gives the Perfect Prox® an outstanding ability to solve sensing applications that would be difficult or impossible to manage with other types of sensors. It also makes Perfect Prox® one of the easiest photoelectric sensors to set up and use.


Eaton's Comet Series includes more background rejection models than any other family on the market. Choose from forward or right-angle viewing, 2-, 3- or 4-wire circuits, cable, micro or mini-connector terminations and a variety of sensing ranges. A visible sensing beam on most models lets you quickly confirm that the sensor is aligned correctly with the target. Fine spot models provide an extremely small 0.05 inch (1.3 mm) light spot for accurately detecting tiny targets such as fine strands of wire or targets that are in or behind small diameter holes.

#### **Fiber Optic**

The Comet Series also includes sensors that utilize fiber optic cables to sense objects where space is restricted, temperatures are high, or tight viewing angles are required. Choose from models that accept low cost plastic fiber optic cables, or use our patented glass fiber optic adapter that inexpensively converts our standard diffuse reflective sensors for use with durable glass fiber optic cables.

## Mounting

Comet Series sensors feature a threaded housing and include two jam nuts and washers for mounting into any 0.75 inch (19 mm) hole or a selection of accessory mounting brackets available from Eaton. The flat sides of the sensor feature two mounting holes for easily attaching the sensor to any flat surface with #4 hardware.



See **Page 5-38** at the back of this section, and **Section 8** for a full list of mounting brackets compatible with the Comet Series.

С

#### Model Selection — Reflex Sensors

	Operating Voltage	Sensing Range ①	Optimum Range <sup>(1)</sup>	Field of View	Sensing Beam	Connection Type	Catalog Number
2-Wire Sensors			•				1
Standard Reflex Forward Viewing	90 – 132V AC 50/60 Hz or 18 – 50V DC	25 feet (7.6m)	0.1 to 15 feet (0.03 – 4.5m)	1 inch (25 mm) Diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14102AS6515
Sensor Retroreflector (Not Included)						3-pin Micro AC Connector	14102ASQD05 @
Polarized Reflex Forward Viewing ③	90 – 132V AC 50/60 Hz or 18 – 50V DC	15 feet (4.5m)	0.1 to 10 feet (0.03 – 3m)	1 inch (25 mm) Diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14101AS6515
						3-pin Micro AC Connector	14101ASQD05 🕃
-Wire and 4-Wire Sensors							
Standard Reflex	20-264V AC	25 feet	0.1 to 15 feet	1 inch (25 mm)	Visible Red	6-foot Cable	14102A6513
Forward Viewing ④	50/60 Hz or	(7.6m)	(0.03 – 4.5m)	diameter at	Beam	4-pin Micro AC Connector	14102AQD03 🕃
	15-30V DC (NPN)			50 inches (1.3m)	Infrared Beam	6-foot Cable	14100A6513
Sensor	(,					4-pin Micro AC Connector	14100AQD03 🕮
Retroreflector	10 – 30V DC (NPN and PNP)	25 feet	0.1 to 15 feet	1 inch (25 mm)	Visible Red	6-foot Cable	14102A6517
(Not Included)		(7.6m)	(0.03 – 4.5m)	diameter at 50 inches (1.3m)	Beam	4-pin Micro DC Connector	14102AQD07 🕃
					Infrared Beam	6-foot Cable	14100A6517
						4-pin Micro DC Connector	14100AQD07 🕃
Standard Reflex Right-Angle Viewing <sup>®</sup> Sensor Retroreflector (Not Included)		15 feet (4.5m)	0.1 to 10 feet (0.03 – 3m)	1 inch (25 mm) diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14102R6513
						4-pin Micro AC Connector	14102RQD03 🕄
		15 feet (4.5m)	0.1 to 10 feet (0.03 – 3m)	1 inch (25 mm) diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14102R6517
						4-pin Micro DC Connector	14102RQD07 🏵
Polarized Reflex Forward Viewing 3 (a)	20 – 264V AC 50/60 Hz or 15 – 30V DC (NPN)	15 feet (4.5m)	0.1 to 10 feet (0.03 – 3m)	1 inch (25 mm) diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14101A6513
						4-pin Micro AC Connector	14101AQD03 🏽
		15 feet (4.5m)	0.1 to 10 feet (0.03 – 3m)	1 inch (25 mm) diameter at	Visible Red Beam	6-foot Cable	14101A6517
	PNP)			50 inches (1.3m)		4-pin Micro DC Connector	14101AQD07 🕄
Polarized Reflex Right-Angle Viewing <sup>(2)</sup> <sup>(3)</sup> <sup>(4)</sup> Sensor Retroreflector (Not Included)		10 feet (3m)	0.1 to 5 feet (0.03 – 1.5m)	1 inch (25 mm) diameter at 50 inches (1.3m)	Visible Red Beam	6-foot Cable	14101R6513
						4-pin Micro AC Connector	14101RQD03 🏵
	15-30V DC	- 30V DC 10 feet 0.1 to 5 (3m) (0.03 – 1			Visible Red Beam	6-foot Cable	14101R6517
		,		50 inches (1.3m)		4-pin Micro DC Connector	14101RQD07 🏶

① Ranges based on a 3-inch diameter retroreflector.

② Right-angle viewing polarized reflex models are rated NEMA 1 only. See Prism Series Page 5-40 for a right-angle viewing polarized reflex sensor rated NEMA 4X and 6.

<sup>③</sup> Polarized Reflex Sensors may not operate with retroreflective tape. Test selected tape prior to installation.

 $\circledast\,$  For complete system, order sensor and retroreflector, see Section 8.

Fast turn product with typical one business day lead-time to shipment.

Stocked product, typical order quantities guaranteed in stock.

See listing of compatible connector cables on Page 5-36.

#### Model Selection — Compatible Connector Cables ①

	Voltage		Gauge	Length		Catalog Number	Pin Configuration/Wire Colors			
	Style	of Pins			Γ	PVC Jacket	PUR Jacket	IRR PUR Jacket	(Face View Female Shown)	
Standard Cables — Micro Styl	e									
Micro Style Straight Female	AC	3-pin 22 3-wire		G 6.0 feet (2m)		CSAS3F3CY2202	CSAS3F3RY2202	-	(2) (3) 1-Green 2-Red/Black 3-Red/White	
		4-pin 4-wire	22 AWG	6.0 fee	et (2m)	CSAS4F4CY2202	CSAS4F4RY2202	CSAS4F4I02202	1-Red/Black 2-Red/White 3-Red 4-Green	
	DC	4-pin 4-wire	22 AWG	6.0 fee	et (2m)	CSDS4A4CY2202	CSDS4A4RY2202	CSDS4A4102202	(1)(2) (4)(3) (4)(3) (4)(3) (2)(4)(4)(4)(4)(4)(4)(4)(4)(4)(4)(4)(4)(4)	
		VoltageNumber0Styleof Pins		Gauge Length		Catalog Number	Pin Configuration/Wire Colors (Face View Female Shown)			
Standard Cables — Mini Style										
Mini Style Straight Female		_	3-pin		16 AWG	6 feet (2m)	CSMS3F3CY1602		1-Green 2-Black 3-White	
Current Rating @ 600V										


3-pin: 13A

① For a full selection of connector cables, see Section 10.


Stocked product, typical order quantities guaranteed in stock.

#### Wiring Diagrams


## AC/DC Models (AC Connection)




#### AC/DC Models (DC Connection)




#### **DC Models (DC Connection)**







#### **DC Models (DC Connection)**



CAUTION: AC/DC connector version sensors use an ACtype connector. Use of DC power with AC-type connectors may not conform with established standards.

**NOTE:** For connector versions, the pin numbering and color codes shown are typical of several manufacturers. However, variations are possible. In case of discrepancies, rely on function indicated and pin location rather than pin number or color code.

C1

# F:T•N

# Photoelectric Sensors Comet Series

#### **Specifications**

	3-Wire and 4-Wire Sensors		2-Wire Sensors							
	AC/DC Models (AC Operation)	AC/DC Models (DC Operation)	DC-Only Models	AC Models	DC Models					
Input Voltage	20 to 264V AC, 50/60 Hz	15 to 30V DC (15 to 24V DC above 131°F/55°C)	10 to 30V DC, (10 to 24V DC above 131°F/55°C)	90 to 132V AC, 50/60 Hz	18 to 50V DC					
Power Dissipation	1.5W maximum	1.5W maximum	1W maximum	2W maximum	2W maximum					
Output Type	VMOS (bi-directional)	NPN (sink)	NPN and PNP (dual outputs)	DMOS	DMOS					
Current Switching	300 mA maximum	300 mA maximum	PNP: 100 mA maximum; NPN: 250 mA maximum (NPN: 120 mA maximum above 131°F/55°C)	300 mA	300 mA					
Voltage Switching	375V peak maximum	375V peak maximum	30V DC maximum	132V AC maximum	50V DC maximum					
Off-State Leakage	250 μA typical; 500μA maximum	250 μA typical; 500 μA maximum	10 µA maximum	1.7 mA maximum	1.5 mA maximum					
Surge Current	2A maximum	2A maximum	1A maximum	1A maximum	1A maximum					
On-State Voltage Drop	_	1.8V at 10 mA; 3.5V at 300 mA	NPN: 400 mV at 10 mA, 1.5V at 250 mA; PNP: 2.4V at 100 mA	10V AC	8V DC					
Response Time	10 mS		1 mS; 3.5 mS (thru-beam)	32 mS	32 mS					
Time Delay		Models with Fixed Time Delay Available — Contact Factory								
Short Circuit Protection	detected (Indicator LED flas reset. IMPORTANT: During	ately when short or overload is shes). Turn power OFF and back ON to installation, correct power first to ensure fail-safe short circuit	Sensor will turn off immediately when short or overload is detected (indicator LED flashes). Sensor will reset when short is removed.	Auto reset	Auto reset					
Temperature Range	Thru-Beam Source: -4	Thru-Beam Source: -4° to +158°F (-20° to +70°C); All others: -40° to +158°F (-40° to +70°C) -13° to +131°F (-25° to +55°C)								
Light/Dark Operation	Switch selectable									
Enclosure Material	Lens: polycarbonate; Cable jacket: PVC; Body: structural polyurethane foam (do not expose to concentrated acids, alcohols or ketones)									
Cable/Connector	Cable versions: 6-foot cable; Connector versions: male mini and micro connectors (refer to wiring diagrams for number of pins per model) on nominal 8″ pigtails									
Vibration and Shock		Vibration: 30g over 10 Hz to 2 kHz; Shock: 100g for 3 mS 1/2 sine wave pulse								
Indicator LED	Lights steady when output is ON; flashes when short circuit protection is in latch condition (except 2-wire models)									
Sunlight Immunity	Perfect Prox: 5,000 foot-candles; All others: 10,000 foot-candles									
Enclosure Ratings		NEMA 1, 2, 3, 4, 4X, 6, 12 and 13 <sup>①</sup> NEMA 6P Models Available — Contact Factory								
Approvals		UL and C-UL Recognized (all mo	dels), CE Compliant (except 2-wire	e DC models)						


O NOTE: These products conform to NEMA tests as indicated, however, some severe washdown applications can exceed these NEMA test specifications. For questions about a specific application, contact Eaton's Cutler-Hammer Sensor Applications Department at 1-800-426-9184. ഹ

F^T•N

**Cutler-Hammer** 

## Photoelectric Sensors Comet Series

#### Approximate Dimensions in Inches (mm) Except Where Noted



PHOTOELECTRIC SENSORS

ß