


## Specification Status: Released

### Maximum Electrical Rating

**Voltage: 13.2V<sub>DC</sub>**
**Short Circuit Current: 40A**
**Notes:**

1. All terminations are tin plated.
2. Drawing not to scale

**Marking:**

**PART IDENTIFICATION**
**MANUFACTURER'S MARK**

**TABLE I. DIMENSIONS:**

	A		B		C		D		E
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
mm:	3.00	3.43	0.38	0.62	2.35	2.80	0.25	0.75	0.076
in:	(0.118)	(0.135)	(0.015)	(0.025)	(0.092)	(0.110)	(0.010)	(0.030)	(0.003)

**TABLE II. PERFORMANCE RATINGS:**

CURRENT RATINGS**						TIME TO TRIP**	RESISTANCE VALUES		TRIPPED-STATE POWER DISSIPATION**
AMPERES AT 0°C		AMPERES AT 20°C		AMPERES AT 60°C		SECONDS AT 20°C, 8A MAX	OHMS AT 20°C		WATTS AT 20°C, 13.2V MAX
HOLD	TRIP	HOLD	TRIP	HOLD	TRIP		MIN	MAX*	
0.58	1.16	0.50	1.00	0.35	0.70	0.05	0.25	0.90	0.8

\*Maximum resistance is measured 1 hour after reflow.

\*\* Values specified were determined using PCB's with 0.030"X1.5 ounce copper traces.

Agency Recognition: UL, CSA, TÜV

Reference Documents: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

### Materials Information

**ROHS Compliant**

 Directive 2002/95/EC  
Compliant

**ELV Compliant**

 Directive 2000/53/EC  
Compliant

**Pb-Free**

**Halogen Free\***


\* Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm