P158 Refrigeration Pressure Transducers

Description

The model P158 is based on Kavlico's ceramic capacitive technology with a custom ASIC. The Brass housing surrounds a pressure transducer designed specifically for refrigeration applications. It can endure the high vibration, broad temperature ranges and humidity conditions found in refrigeration systems while withstanding high over- pressures and pressure pulsations without damage or degradation.

The P158 package has a built-in Metri-Pack 150, electrical connector and supports male and female process connections. The P158 is offered with seal materials that are suitable for many of the latest refrigerants such as R134a, R22, R123, R12, including many of the proprietary blends, and assocated lubricants.

Features

- SAE female Process Connection with Built-in Schrader Deflator
- Linear Amplified Output
- Temperature Compensated
- Superior Long Term Stability
- Excellent Repeatability/Hysteresis
- EMI/RFI Rejection
- Low Power Consumption
- Ten Million Cycle Life Expectancy
- Outstanding Shock & Vibration Performance
- Over Voltage, Reverse Polarity and Short Circuit Protection

Applications

- High and Low Side Pressure Measurements in **Refrigeration Systems**
- Product Refrigeration
- Refrigerant Recovery
- Transport Refrigeration
- Environmental Test Equipment

Standard Full Scale **Pressure Ranges**

0-100, 150, 300, 400, 500 and 750 PSIA, PSIS

Technical Specifications

Note: Performance Specifications with $5v \pm 0.002$ Vdc supply at 25° C

Pressure Ranges:

0 - 100 PSI through 0 - 1,000 PSI Absolute or Sealed Gage

Proof Pressure: 3x (FSO) (100 through 300 PSI) 2x (FSO) (400 through 750 PSI) **Burst Pressure:** 5x (100 through 300 PSI)

2250 PSI (400 through 750 PSI)

Supply Voltage: $5.0 \pm .5 \text{ V}$ **Supply Current:** 5 mA (Max)

Linearity Error: ±0.5% of Full Span Max.

Response Time: 15ms Max to 63% of F.S. Pressure

with Step Change on Input

Output Voltage:

Zero/Null Pressure: 0.50 ±0.08 Vdc Full Pressure: 4.50 ±0.08 Vdc Ratiometricity: ±0.51% of Span

≤ 2.0% of Span (-20°C to 100°C) **Total Error Band:**

Output Impedance: Operating Temperature: Storage Temperature: Service Life:

Vibration: Shock: Stability: Weight:

Electrical Termination: Pressure Connection: Recommended Interface

Impedance:

Over-Voltage Protection: Reverse Polarity Protection: Material - Main Housing:

 $< 100 \Omega$

-30°C to + 100°C

-40°C to + 135°C

10 Million Full Pressure Cycles

10G's P-P Sinusoidal, from 10-2000 Hz

75 G's 1/2 Sine Wave

±0.5% of Full Span over 1-Year

100 grams (Max)


Packard Electric Metri-Pack 150 Series See "How to Order"

Min. Load 25 kΩ

16 Vdc -5 Vdc CA3600 Brass



P158Refrigeration Pressure Transducers



How to Order

P158 Pressure Transducer

Pressure Ranges

100 0 - 100 PSI 150 0 - 150 PSI 300 0 - 300 PSI 400 0 - 400 PSI 500 0 - 500 PSI 750 0 - 750 PSI

Reference

A AbsoluteS Sealed Gage

Seal Material

C Neoprene -40 to 125°C F Ethylene Propylene -40 to 121°C H HNBR -30 to 135°C

Pressure Connection


- 1 1/4-18 NPT (External Threads)
- 2 1/4 SAE Female Flare w/ Schrader Deflator (7/16-20 UNF internal threads)
- 4 1/8-27 NPT

Electrical Connection

A With mating connector, w/12", 18 AWG leads
C Without mating connector

P158 500 S F 1 A Example: P158-500S-FIA

Contact Kavlico for accuracy options, custom packaging, alternative pressure ranges, pressure connections or other OEM or application specific requirements.



Although possible applications for our product(s) and other statements are presented herein, Kavlico is not expert in the user's technical field and therefore does not warrant the suitability of its product(s) for the user's applications. Therefore, Kavlico will not accept any liability and provides no guarantee, responsibility, or warranties of any kind concerning the suitability or related to the use of its product(s) for the user's applications.

Additionally, Kavlico will not be liable and provides no guarantee, responsibility, or warranties of any kind concerning the suitability or related to the use of its product(s) for the life support market or to be used in life support systems, safety or emergery systems, critical care applications, human implantation, aviation, nuclear facilities or systems or any other applications where product failure could lead to injury to persons, loss of life, harm to the environment, or catastrophic property damage.

Kavlico warrants that its products will be free from defective materials and workmanship for a period of one (1) year from date of delivery to the original purchaser and that its products will conform to Kavlico's specifications or standards. Any product found to be defective will be replaced or repaired at the sole option of Kavlico.

Note: Kavlico reserves the right to change its specifications at any time without notice. Kavlico is not an expert in the customer's technical field and therefore does not warrant the suitability of its product for the application selected by the customer.

Kavlico products are manufactured or covered by one or more of the following patents: 1,799,995, 4,735,908, 4,924,702, 4967.071, 4,974,117, 5,020,377, 5,233,875, 5,275,054, 5,315,877, 5,329,819, 5,349,864, 5,349,865, 5,349,867, 5,369,989, 5,415,036, 5,528,930, 5,540,086, 5,553,502, 5,576,251, 5,578,843, 5,656,780, 5,824,889, 5,907,278, 5,923,989, 5,929,794, 5,935,189, 6,008,113, 6,041,658, 6,148,674, 6,178,829, 621,1558, 81, 6,279,407, 6,297,733, 6,311,566, 6,351,132, 81, 6,404,184, 81, 6,495388, 81, 6,505,398, 82, 6,553,812, 82, 6,564,642, 82, 6,581,468, 82, 6,583,631,82, 6,584,853, 82, 6,605,904, 81, 6,683,464, 812, with the U.S> and foreign patents pending.



14501 Princeton Avenue | Moorpark, CA 93021 Tel (805) 523-2000 | Fax (805) 523-7125 Web: www.kavlico.com | E-Mail: sales@kavlico.com