


## TELUX™



19232

### FEATURES

- High luminous flux
- Supreme heat dissipation:  $R_{thJP} = 90 \text{ K/W}$
- High operating temperature:  
 $T_{amb} = -40 \text{ °C to } +110 \text{ °C}$
- Packed in tubes for automatic insertion
- Luminous flux, forward voltage and color categorized for each tube
- Small mechanical tolerances allow precise usage of external reflectors or light guides
- Lead (Pb)-free device - RoHS-COMPLIANT
- ESD-withstand voltage: up to 1 kV according to JESD22-A114-B
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC
- Compatible with wave solder processes according to CECC 00802 and J-STD-020C
- Automotive qualified



### DESCRIPTION

The VLWTG9900 is a clear, non diffused LED for applications where high luminous flux is required.

It is designed in an industry standard 7.62 mm square package utilizing highly developed InGaN technology.

The supreme heat dissipation of VLWTG9900 allows applications at high ambient temperatures.

All packing units are binned for luminous flux, forward voltage and color to achieve the most homogenous light appearance in application.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: TELUX™
- Product series: power
- Angle of half intensity:  $\pm 45^\circ$

### APPLICATIONS

- Exterior lighting
- Replacement of small incandescent lamps
- Traffic signals and signs

### PARTS TABLE

PART	COLOR, LUMINOUS FLUX	TECHNOLOGY
VLWTG9900	True green, $\phi_V = 2500 \text{ mlm (typ.)}$	InGaN on SiC

**ABSOLUTE MAXIMUM RATINGS<sup>1)</sup> VLWTG9900**

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage	$I_R = 10 \mu A$	$V_R$	5	V
DC Forward current	$T_{amb} \leq 50^\circ C$	$I_F$	50	mA
Surge forward current	$t_p \leq 10 \mu s$	$I_{FSM}$	0.1	A
Power dissipation		$P_V$	230	mW
Junction temperature		$T_j$	100	$^\circ C$
Operating temperature range		$T_{amb}$	- 40 to + 100	$^\circ C$
Storage temperature range		$T_{stg}$	- 55 to + 100	$^\circ C$
Soldering temperature	$t \leq 5 s$ , 1.5 mm from body preheat temperature 100 $^\circ C$ / 30 s	$T_{sd}$	260	$^\circ C$
Thermal resistance junction/ambient	with cathode heatsink of 70 mm <sup>2</sup>	$R_{thJA}$	200	K/W
Thermal resistance junction/pin		$R_{thJP}$	90	K/W

Note:

<sup>1)</sup>  $T_{amb} = 25^\circ C$ , unless otherwise specified**OPTICAL AND ELECTRICAL CHARACTERISTICS<sup>1)</sup> VLWTG9900, TRUE GREEN**

PARAMETER	TEST CONDITION	SYMBOL	MIN	TYP.	MAX	UNIT
Total flux	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$\phi_V$	2000	2500		mlm
Luminous intensity/Total flux	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$I_V/\phi_V$		0.7		mcd/mlm
Dominant wavelength	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$\lambda_d$	509	523	535	nm
Peak wavelength	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$\lambda_p$		518		nm
Angle of half intensity	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$\varphi$		$\pm 45$		deg
Total included angle	90 % of Total Flux Captured	$\varphi$		100		deg
Forward voltage	$I_F = 50 mA$ , $R_{thJA} = 200^\circ K/W$	$V_F$		3.9	4.7	V
Reverse voltage	$I_R = 10 \mu A$	$V_R$	5	10		V
Junction capacitance	$V_R = 0$ , $f = 1 MHz$	$C_j$		50		pF
Temperature coefficient of $\lambda_{dom}$	$I_F = 30 mA$	$TC\lambda_{dom}$		0.02		nm/K

Note:

<sup>1)</sup>  $T_{amb} = 25^\circ C$ , unless otherwise specified**LUMINOUS FLUX CLASSIFICATION**

GROUP	TRUE GREEN	
	LUMINOUS FLUX (MLM)	
	MIN.	MAX.
D	2000	3000
E	2500	3600
F	3000	4200

Note:

Luminous flux is tested at a current pulse duration of 25 ms and an accuracy of  $\pm 11\%$ .

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped in one tube (there will be no mixing of two groups on each tube).

In order to ensure availability, single brightness groups will not be orderable. In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped in any one tube.

In order to ensure availability, single wavelength groups will not be orderable.

**COLOR CLASSIFICATION**

GROUP	TRUE GREEN	
	DOM. WAVELENGTH (NM)	
	MIN.	MAX.
2	509	517
3	515	523
4	521	529
5	527	535

Note:

Wavelengths are tested at a current pulse duration of 25 ms and an accuracy of  $\pm 1 nm$ .

Technical drawing of a cathode marking component, showing three views: top, front, and side.

**Top View:**

- Central feature: Cathode marking (A)
- Area not plane (B)
- Dimensions: 7.62±0.3 (width), 7.62±0.3 (height), 6.55 (inner width), 1.6 (radius), 1.45 (height), 1.32 (height), 5.08±0.3 (width), 0.4±0.1 (width), 5.08±0.3 (width), 7.62±0.3 (width), 7.62±0.3 (height)

**Front View:**

- Dimensions: 1.45 (height), 1.6 (radius), 1.32 (height), 5.08±0.3 (width), 0.4±0.1 (width), 5.08±0.3 (width), 7.62±0.3 (width), 7.62±0.3 (height)

**Side View:**

- Dimensions: 1.2±0.1 (height), 0.6 max. (height), 5.08±0.2 (width), 1.55±0.2 (width), 0.75<sup>+0.2</sup>/<sub>-0.1</sub> (width), 4.8±0.3 (width), 7.8±0.3 (width), 2.85±0.3 (width), SR1.65 (radius), 6° (angle)

**Legend:**

- Technical drawings according to DIN specifications

Technical drawing of a rectangular box and a separate long, thin rectangular piece. The box has dimensions 45 (height), 110 (width), and 600 (length). A label is indicated on the front face. The separate piece is also labeled 'Label'.

**TUBE WITH BAR CODE LABEL** Dimensions in millimeters




Figure 9. Drawing Proportions not Scaled