


Small Signal Fast Switching Diode

Features

- · These diodes are also available in other case styles including the DO35 case with the type designation 1N4148, MiniMELF case with the type designation LL4148, and the SOT23 case with the type designation IMBD4148-V.





- · Fast switching diodes
- · Lead (Pb)-free component
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

Mechanical Data

Case: SOD123 plastic case Weight: approx. 10.3 mg **Packaging Codes/Options:**

GS18/10 k per 13" reel (8 mm tape), 10 k/box GS08/3 k per 7" reel (8 mm tape), 15 k/box

Parts Table

Part	Ordering code	Marking	Remarks	
1N4148W-V	1N4148W-V-GS18 or 1N4148W-V-GS08	A2	Tape and Reel	

Absolute Maximum Ratings

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit	
Reverse voltage		V _R	75	V	
Repetitive peak reverse voltage		V _{RRM}	100	V	
Average rectified current half wave rectification with resistive load	f ≥ 50 Hz	I _{F(AV)}	150 ¹⁾	mA	
Surge forward current	t < 1 s and T _j = 25 °C	I _{FSM}	500	mA	
Power dissipation		P _{tot}	350 ¹⁾	mW	

Thermal Characteristics

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit	
Thermal resistance junction to ambient air		R _{thJA}	357 ¹⁾	K/W	
Junction temperature		Tj	150	°C	
Storage temperature		T _{stg}	- 65 to + 150	°C	

Document Number 85748 www.vishay.com Rev. 1.4, 14-Sep-07

¹⁾ Valid provided that electrodes are kept at ambient temperature.

¹⁾ Valid provided that electrodes are kept at ambient temperature.




Electrical Characteristics

 T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Min	Тур.	Max	Unit
Forward voltage	I _F = 10 mA	V_{F}			1000	mV
	I _F = 100 mA	V _F			1200	mV
Leakage current	V _R = 20 V	I _R			25	nA
	V _R = 75 V	I _R			5	μΑ
	V _R = 100 V	I _R			100	μΑ
	V _R = 20 V, T _J = 150 °C	I _R			50	μΑ
Diode capacitance	$V_F = V_R = 0 V$	C _D			4	pF
Voltage rise when switching ON (tested with 50 mA pulses)	tested with 50 mA pulses, t_p = 0.1 μ s, rise time < 30 ns, f_p = (5 to 100) kHz	V _{fr}			2.5	V
Reverse recovery time	$I_F = 10 \text{ mA}, I_R = 1 \text{ mA}, V_R = 6 \text{ V},$ $R_L = 100 \Omega$	t _{rr}			4	ns
Rectification efficiency	f = 100 MHz, V _{RF} = 2 V	ην	0.45			

Rectification Efficiency Measurement Circuit





Typical Characteristics

T_{amb} = 25 °C, unless otherwise specified




Figure 1. Forward characteristics




Figure 2. Dynamic Forward Resistance vs. Forward Current




Figure 4. Relative Capacitance vs. Reverse Voltage




Figure 5. Leakage Current vs. Junction Temperature




Figure 3. Admissible Power Dissipation vs. Ambient Temperature

www.vishay.com Rev. 1.4, 14-Sep-07









Figure 6. Admissible Repetitive Peak Forward Current vs. Pulse Duration

Package Dimensions in millimeters (inches): SOD123





foot print recommendation:



Rev. 03 - Date: 08.November.2004 Document no.:S8-V-3910.01-001 (4) 17432



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany

Document Number 85748 www.vishay.com



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com