

EV200ADANA Product Details



EV200ADANA

TE Internal Number: 1-1618002-1

 Active

High Voltage Relays

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Contact - Arrangement = 1 Form A, SPST-NO, 1 N/O
- Power Switching = Make Only, Yes, No
- Contact - Rated Current = 0 - 500 A
- Not RF Rated
- Coil - Rated Voltage = 32 - 95 VDC

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Style](#) = Stud Terminal

Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 0 - 500
- [RF Rated](#) = No
- [Coil - Rated Voltage \(VDC\)](#) = 32 - 95
- [Voltage, Max. \(VDC\)](#) = 0 - 2200

Termination Features:

- [High Voltage Connection \(Power\)](#) = Screw Terminals
- [High Voltage Connection \(Coil\)](#) = Flying Leads

Body Features:

- [Mount Style](#) = Panel

Contact Features:

- [Auxiliary Contacts](#) = Without

Configuration Features:

- [Contact - Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Internal

Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Hand solderable with lead free solder
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Other:

- [Brand](#) = Kilovac