

Vishay Semiconductors

Small Signal Schottky Diodes, Single and Dual

Features

- These diodes feature very low turn-on voltage and fast switching
- These devices are protected by a PN junction guard ring against excessive voltage, such as electrostatic discharges






 Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

Mechanical Data

Case: SOT23 plastic case Weight: approx. 8.8 mg Packaging codes/options:

GS18/10k per 13" reel (8 mm tape), 10k/box GS08/3k per 7" reel (8 mm tape), 15k/box



Parts Table

Part	Ordering code	Type marking	Remarks	
BAT54-V	BAT54-V-GS18 or BAT54-V-GS08	L4	Tape and reel	
BAT54A-V	BAT54A-V-GS18 or BAT54A-V-GS08	L42	Tape and reel	
BAT54C-V	BAT54C-V-GS18 or BAT54C-V-GS08	L43	Tape and reel	
BAT54S-V	BAT54S-V-GS18 or BAT54S-V-GS08	L44	Tape and reel	

Absolute Maximum Ratings

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit	
Repetitive peak reverse voltage		V _{RRM}	30	V	
Forward continuous current		I _F	200 ¹⁾	mA	
Repetitive peak forward current		I _{FRM}	300 ¹⁾	mA	
Surge forward current current	t _p < 1 s	I _{FSM}	600 ¹⁾	mA	
Power dissipation		P _{tot}	230	mW	

Note

¹⁾ Device on fiberglass substrate, see layout on next page.

BAT54-V, BAT 54A-V, BAT 54C-V, BAT 54S-V

Vishay Semiconductors



Thermal Characteristics

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit	
Thermal resistance junction to ambiant air		R_{thJA}	430 ¹⁾	K/W	
Junction temperature		Tj	125	°C	
Storage temperature range		T _{stg}	- 65 to + 150	°C	

Note

Electrical Characteristics


 T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Symbol	Min.	Тур.	Max.	Unit
Reverse Breakdown voltage	I _R = 100 μA (pulsed)	$V_{(BR)}$	30			V
Leakage current	Pulse test t_p < 300 μ s, δ < 2 % at V_R = 25 V	I _R			2	μΑ
Forward voltage	I_F = 0.1 mA, t_p < 300 μ s, δ < 2 %	V _F			240	mV
	I_F = 1 mA, t_p < 300 μs, δ < 2 %	V _F			320	mV
	I_F = 10 mA, t_p < 300 μ s, δ < 2 %	V_{F}			400	mV
	I_F = 30 mA, t_p < 300 μ s, δ < 2 %	V _F			500	mV
	I_F = 100 mA, t_p < 300 μs, δ < 2 %	V_{F}			800	mV
Diode capacitance	V _R = 1 V, f = 1 MHz	C_D			10	pF
Reverse recovery time	I_F = 10 mA to I_R = 10 mA, I_R = 1 mA, R_L = 100 Ω	t _{rr}			5	ns

Layout for R_{thJA} test

Thickness:

Fiberglass 1.5 mm (0.059 in.) Copper leads 0.3 mm (0.012 in.)



¹⁾ Device on fiberglass substrate, see layout on next page.

Vishay Semiconductors

Typical Characteristics

T_{amb} = 25 °C, unless otherwise specified




Figure 1. Typical Forward Voltage Forward Current vs. Various Temperatures




Figure 2. Diode Capacitance vs. Reverse Voltage V_{R}





Figure 3. Typical Variation of Reverse Current vs. Various Temperatures


BAT54-V, BAT 54A-V, BAT 54C-V, BAT 54S-V


Vishay Semiconductors



Package Dimensions in millimeters (inches): SOT23








Document no.:6.541-5014.01-4 Rev. 7 - Date: 08.July.2004 17418

|-

Foot print recommendation:



0.7 (0.028)

BAT54-V, BAT 54A-V, BAT 54C-V, BAT 54S-V



Vishay Semiconductors

Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively.
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA.
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany

Document Number 85508 Rev. 1.7, 19-Jan-09



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com