


## GELCAP-1(B5) Product Details



**GELCAP-1(B5)**

TE Internal Number: 566376-000



### Power Cable Splices, Repair Sleeves and End Seals

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Cable Splice
  - Splice Type = Stub Splice
  - Splice Style = Cap
  - GelCap Series
  - Direct Burial Application, Motor Connections Application, Street Lights Application, Submersible Application
- [View all Features](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Cable Splice
- Splice Type = Stub Splice
- Splice Style = Cap
- Cable Type = Polymeric
- Jacketed Cable = With

#### Mechanical Attachment:

- Retention Type = Clamp

#### Body Related Features:

- Series = GelCap

#### Configuration Related Features:

- Conductor (Wire) Size = #16 - #10
- Cable Shielding = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Printer/Label Features:

- Voltage Rating (kV) = 0.6

#### Operation/Application:

- Application = Direct Burial, Motor Connections, Street Lights, Submersible
- Armored Cable = No

#### Other:

- Installation Type = Cold Applied
- Brand = Raychem
- Comment = Kits include connectors; Clear cap to allow visual inspection.