

- Greater than 1 Watt rating for 2512 pad design
 Zero ohm jumper available, OARSZ
- Zero onin jumper available, O.
 Economical low value SMT
- Resistance values $2m\Omega$ to $50m\Omega$
- ±1% or ±5% tolerance
- Open air design provides cooler operation

Electrical Data

IRC Туре	Power Rating (watts)	Available Resistance (ohms)		
OARS-1	1W @ 70°C	.002, .003, .004, .005, .010, .015 .020, .022, .025, .030, .040, .050		
*Contact factory for unlisted resistance values between 0.002 & 0.050 ohms.				


Features:

- Superior thermal expansion cycling
- Flameproof
- Inductance less than 10 nanohenries
- · Lead flexible for thermal expansion

Physical Data

Applications:

- · Current sensing
- Feedback
- · Low inductance
- Surge and pulse
- · AC applications (please contact the factory)



Dimensions (Inches and (mm))					
IRC Type	L	н	т	D	W
OARS-1	0.440 ±0.015	0.120 ±0.030	0.093 ±0.010	0.190 ±0.030	0.125 ±0.015
UANS-1	(11.18 ±0.381)	(3.05 ±0.762)	(2.36 ±0.254)	(4.83 ±0.762)	(3.175 ±0.381)
OARS-1	0.455 ±.015	0.150 ±0.030	0.093 ±0.010	0.185 ±0.030	0.140 ±0.015
0.002 Ω	(11.56 ±.381)	(3.51 ±0.762)	(2.36 ±0.254)	(4.70 ±0.762)	(3.56 ±0.381)
OARS-1	0.440 ±.015	0.138 ±0.030	0.093 ±0.010	0.190 ±0.030	0.125 ±0.015
0.003 Ω	(11.18 ±.381)	(3.51 ±0.762)	(2.36 ±0.254)	(4.83 ±0.762)	(3.175 ±0.381)

General Note

IRC reserves the right to make changes in product specification without notice or liability. All information is subject to IRC's own data and is considered accurate at time of going to print.

Wire and Film Technologies Division • 4222 South Staples Street • Corpus Christi Texas 78411 USA Telephone: 361 992 7900 • Facsimile: 361 992 3377 • Website: www.irctt.com







Environmental Data

Test Spec: AEC Q200	2m - 3m	4m - 15m	> 15m		
TCR +125 to -55°C	240ppm	40ppm	40ppm		
Thermal Shock	< 0.75%	< 0.75%	< 0.75%		
High Temperature Exposure 125°C	< 1.75%	< 0.5%	< 1.0%		
Temperature Cycling: -40 to +125°C	< 1.0%	< 1.0%	< 0.75%		
Operational Life	< 2.0%	< 1.0%	< 1.0%		
Baised Humidity	< 0.75%	< 0.5%	< 0.5%		
Mechanical Shock	< 1.5%	< 1.5% < 1.0% < 1.0%			
Vibration	< 1.0%	< 1.0%	< 1.0%		
Moisture Resistance	< 1.0	< 2.5%	< 2.0		
Terminal Strength	Meets JIS-C-6429				
Solvent Resistance	N	Meets MIL-STD-202 Method 215			
Solderability	Meets J-STD-002 Method B				

Reference Documents: MIL-STD-202

Power Derating Curve







Note:


The power derating curve is a guidance based on a conservative design model. The OARS is a solid metal alloy construction that can withstand significantly greater operating temperatures than conservative design models permit. The resistive alloys can withstand temperatures in exess of 350°C. Therefore, the system thermal design is a more significant design parameter due to the heat limitations of solder joints and/or circuit board substrate materials. Refer to additional information below.

The thermal image (not a simulation) to the left is of an OARS 10 m Ω running at 2 Watts, which exceeds the 1 Watt conservative model. Notice the hotpsot is nearly 200°C, but the solder joint is approximately 65°C (FR4 is rated for 130°C). The unique construction of the OARS isolates the hotspot from the circuit board material preventing damage. Additionally, the thermal energy is dissipated to the air instead of being conducted into the circuit board potentially causing a nearby power component to exceed its rating.

The standard test circuit board consists of a four layer FR4 material with 2 ounce outer layers and 1 ounce inner layers, which is typical of many industry designs. Contact IRC for more details or for other thermal image test data for specific resistance values and power levels.



Pulse/Surge Chart




Note:

The high pulse surge capability of the OARS parts is attributed to the solid metal alloy construction. In many applications the cross-section of the OARS is greater than the cross-section of the board traces connecting the parts to the circuit board.

Cross-Sectional area ranges from approximately 650 mils to 3600 mils.






Dimensions (Inches and (mm))							
IRC A B C D E F G							G
OARS	0.17 ±0.003	0.461 ±0.003	0.945 ±0.010	0.453 ±0.004	0.069 ±0.004	0.315 ±0.004	0.157 ±0.004
UARS	(4.32 ±0.08)	(11.7 ±0.08)	(24.0 ±0.30)	(11.5 ±0.10)	(1.75 ±0.10)	(8.0 ±0.10)	(4.0 ±0.1)

Ordering Data

Sample Part No	OA	RS1	F	005	J][.F
IRC Type · · · · · · · · · · · · · · · · · · ·		•		•	:		:
Power Rating in Watts •• •• •• •• •• •• •• •• •• •• •• •• ••	•••						•
Resistance Range (ohms) · · · · · · · · · · · · · · · · · · ·	•••	•••	•••				•
Tolerance $F = \pm 1\%, G = \pm 2\%, J = \pm 5\%$	•••	•••	•••	•••			•
RoHS Indicator	•••	•••	•••	••••	• • • •		-



IRC Solder Reflow Recommendations



* Based on Industry	/ Standards and IPC recommendations
Duscu on mausu	

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average Ramp-up rate $(T_{smax} \text{ to } T_p)$	3°C / second max.	3°C / second max.
Preheat - Temperature Min (T _{smin}) - Temperature Max (T _{smax}) - Time (T _{smin} to T _{smax}) (ts)	100°C 150°C 60 -120 seconds	150°C 200°C 60 -180 seconds
Time maintained above - Temperature (T _L) - Time (t _L)	183°C 60 - 150 seconds	217°C 60 - 150 seconds
Peak Temperature (T _P)	See Table 1	See Table 2
Time within 5°C of actual Peak Temperature (tp) ²	10 - 30 seconds	20 - 40 seconds
Ramp-down Rate	6°C / second max.	6°C / second max.
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.

Note 1: All temperatures refer to topside of the package, measured on the package body surface.

Note 2: Time within 5 °C of actual peak temperature (tp) specified for the reflow profiles is a "supplier" minimum and a "user" maximum.

Tabel 1: SnPb Eutectic Process - Package Peak Reflow Temperatures				
Package Thickness	Volume mm ³ < 350 Volume mm ³ \ge			
< 2.5 mm	240 +0/-5°C	225 +0/-5°C		
≥ 2.5 mm	225 +0/-5°C	225 +0/-5°C		

Tabel 2: Pb-free Process - Package Peak Reflow Temperatures						
Package Volume mm ³ Volume mm ³ Volume mm ³ Thickness < 350 350 - 2000 > 2000						
< 1.6 mm	260°C *	260°C *	260°C *			
1.6 mm - 2.5 mm	260°C *	250°C *	245°C *			
≥ 2.5 mm	250°C *	245°C *	245°C *			

* Tolerance: The device manufacturer/supplier shall assure process compatibility up to and including the stated classification temperature at the rated MSL level. **Note 1**: Package volume excludes external terminals (balls, bumps, lands, leads) and/or non-integral heat sinks.

Note 2: The maximum component temperature reached during reflow depends on package thickness and volume. The use of convection reflow processess reduces the thermal gradients between packages. However, thermal gradients due to differences in thermal mass of SMD packages may still exist.

Note 3: Components intended for use in "lead-free" assembly process shall be evaluated using the "lead-free" peak temperature and profiles defined in Table 1, 2 and reflow profile whether or not lead-free.