



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

TMS-SCE-1K-1/2-2.0-4 Product Details

[Share](#) [Print](#) [Email](#)



Heat Shrink Sleeve

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- TMS-SCE Series
- Military Grade
- Radiation Cross-Linked Polyolefin Material
- Shrink Ratio = 3:1
- Operating Temperature = -55 - 135 °C

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TMS-SCE-1K-1/2-2.0-4

TE Internal Number: 8988010001

Active

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • Wire and Harness ID Products (PDF, English) • IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX (PDF, English) • TMS-SCE Military grade heat-shrinkable sleeves (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Grade = Military • Color = Yellow <p>Dimensions:</p> <ul style="list-style-type: none"> • Expanded ID, Min. (mm [in]) = 12.70 [0.500] • Sleeve Length, Nominal (in [mm]) = 2 [50.8] • Recovered ID, Max. (mm [in]) = 4.22 [0.166] • Recommended Wire/Cable OD Use Range (mm [in]) = 4.64 - 10.79 [0.183 - 0.425] <p>Body Features:</p> <ul style="list-style-type: none"> • Material = Radiation Cross-Linked Polyolefin • Shrink Ratio = 3:1 • Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.61 [0.024] 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (°C [°F]) = -55 - +135 [-67 - +275] <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Quantity = 1,000 <p>Other:</p> <ul style="list-style-type: none"> • Series = TMS-SCE • Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)