
# **Compact Pressure Sensor for Pneumatics** CE Series **PSE540**

Connector for PSE300

ZS-28-C

1 pc.

How to Order



### Specifications


			Conforms to CE marking and UL (CSA) standards.				
	Model	PSE541	PSE543				
Rat	ed pressure range	0 to –101 kPa	-100 to 100 kPa				
Pro	of pressure	500 kPa					
Flu	id	Air, No-corrosive gas, Non-flammable gas					
Ρο	wer supply voltage	12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection)					
Cui	rrent consumption	15 mA	15 mA or less				
Out	tput specification	Analog output 1 to 5 V (within rated pressu	Analog output 1 to 5 V (within rated pressure range), Output impedance: Approx. 1 k $\Omega$				
Aco	curacy (ambient temperature of 25°C)	±2%F.S. or less					
Lin	earity	±0.4%F.S. or less					
Rep	peatability	±0.2%F.S. or less					
Ροι	wer supply voltage effect	±0.8%F.S. or less					
	Enclosure	IP40					
	Operating temperature range	Operating: 0 to 50°C, Stored: -20 to 70°	C (with no condensation and no freezing)				
e	Operating humidity range	Operating/Stored: 35 to 85%RH (with no condensation)					
Resistance	Withstand voltage	1000 VAC, 50/60 Hz for 1 minu	ute between live parts and case				
sis	Insulation resistance	50 M $\Omega$ between live part	s and case (at 500 VDC)				
Å	Vibration resistance	10 to 500 Hz at whichever is smaller of 1.5 mm amplitude or 98 m/s <sup>2</sup> acceleration,					
		in X, Y, Z directions, for 2 hours each (de-energized)					
	Impact resistance	980 m/s <sup>2</sup> in X, Y, Z directions	s, 3 times each (de-energized)				
Ten	nperature characteristics	±2%F.S. or less	±2%F.S. or less (based on 25°C)				

#### **Piping specification**

	Model	M3	M5	01	N01	R04	R06	IM5	IM5H
Port size		M3 x 0.5	M5 x 0.8	R1/8	NPT1/8	ø4	ø6	M5 female thread,	M5 female thread, through type
FUIT SIZE		IVI3 X 0.5	IVIS X 0.0	M5 x 0.8	M5 x 0.8	plug-in reducer	plug-in reducer	through type	(with mounting hole)
	Case	Resin case: PBT		Resin case: PBT		PBT		Resin case: PBT	
Material		Fitting: SUS303		Fitting: C3604BD				Fitting: A	6063S-T5
	Pressure sensing section	Pressure sensor: Silicon, O-ring: NBR							
Sensor o	able	3 wire oval cable (0.15 mm <sup>2</sup> )							
Weight	With sensor cable	42.4 g	42.7 g	49.	3 g	41.4 g	41.6 g	43.3 g	44.1 g
weight	Without sensor cable	2.9 g	3.2 g	9.	8 g	1.9 g	2.1 g	3.8 g	4.6 g




# Pressure Sensor Controller ( € Series PSE300 CAL



**SMC** 

## **Options/Part No.**

Description	Part no.	Note
Power supply/Output connection cable	ZS-28-A	
Bracket	ZS-28-B	With M3 x 5L (2 pcs.)
Sensor connector	ZS-28-C	1 pc.
Panel mount adapter	ZS-27-C	With M3 x 8L (2 pcs.)
Panel mount adapter + Front protective cover	ZS-27-D	With M3 x 8L (2 pcs.)



### **Specifications**

	Conforms to CE marking and UL (CSA) standa								
	Model	PSE30							
Rate	ed pressure range	-101 to 101 kPa	10 to –101 kPa	-10 to 100 kPa	-0.1 to 1 MPa	-50 to 500 kPa	–0.2 to 2.00 kPa		
Pow	ver supply voltage	12 to 24 VDC $\pm$ 10%, Ripple (p-p) 10% or less (with power supply polarity protection)							
Cur	rent consumption	50 mA or less (Current consumption for sensor is not included.)							
Sensor input		1 to 5 VDC (Input impedance: 1 MΩ)							
	No. of inputs	1 input							
	Input protection With excess voltage protection (up to 26.4 V)								
Hys	teresis	Hysterisis mode: Variable, Window comparator mode: Variable							
Swi	tch output	NPN or PNP open collector output: Two outputs							
	Maximum load current			80	mA				
	Maximum load voltage			30 VDC (at	NPN output)				
	Residual voltage			1 V or less (with loa	ad current of 80 mA)				
	Output protection			With short cir	cuit protection				
Res	ponse time			1 ms	or less				
	Anti-chattering function	Re	esponse time setting	gs for anti-chattering	function: 20 ms, 160	0 ms, 640 ms, 1280	ns		
Rep	eatability			±0.1%F.	S. or less				
	Voltage output Note 1)	Output voltage: 1 to 5 V (within rated pressure range), Output impedance: Approx. 1 k $\Omega$							
t	Voltage Output and a	Linearity: ±0.2%F.S. (not including sensor accuracy), Response speed: 150 ms or less							
dt	Accuracy (to display value) (25°C)		±0.6%F	S. or less		±1.0%F.S. or less	±1.5%F.S. or less		
0 Go		Output current: 4 to 20 mA (within rated pressure range)							
Analog output	Current output Note 1)	Maximum load impedance: 300 $\Omega$ (at 12 VDC), 600 $\Omega$ (at 24 VDC), Minimum load impedance							
Ā		Linearity: ±0.2%F.S. (not including sensor accuracy), Response time: 150 ms or less							
	Accuracy (to display value) (25°C)	±1.0%F.S. or less ±2.0%F.S. or less							
	olay accuracy	±0.5%F.S.	$\pm 0.5\%$ F S $\pm 1.$ digit or less						
(am	bient temperature of 25°C)	±2 digits or less	2 digits or less						
Disp	olay	3 + 1/2-digit, 7-segment indicator, 2-color display (Red/Green), Sampling frequency: 5 times/sec							
Indi	cation light	OUT1: Lights up when ON (Green), OUT2: Lights up when ON (Red)							
Aut	o shift input Note 1)	Non-voltage input (reed or solid state), Low level input: 5 ms or more, Low level: 0.4 V or less							
-	Enclosure	IP40							
ø	Operating temperature range	Operating: 0 to 50°C, Stored: -10 to 60°C (with no condensation and no freezing)							
Resistance	Operating humidity range	Operating/Stored: 35 to 85%RH (with no condensation)							
sist	Withstand voltage	1000 VAC for 1 minute between live parts and case							
Bes	Insulation resistance	50 M $\!\Omega$ between live parts and case (at 500 VDC)							
-	Vibration resistance	10 to 150 Hz at whichever is smaller of 1.5 mm amplitude or 98 m/s <sup>2</sup> acceleration, in X, Y, Z directions, for 2 hours each (de-energized)							
	Impact resistance	100 m/s <sup>2</sup> in X, Y, Z directions, 3 times each (de-energized)							
	perature characteristics	±0.5%F.S. or less (based on 25°C)							
	nection	Power supply/Output connection: 5 P connector, Sensor connection: 4 P connector							
	erial	Front case: PBT, Rear case: PBT							
Weight	With power supply/output connection cable				5 g				
۶.	Without power supply/output connection cable			30	) g				

Note 1) Auto shift function is not available when analog output option is selected. Also, analog output option is not available when auto shift function is selected.

Note 2) The following units can be selected with unit conversion function:

For vacuum & compound pressure: kPa·kgf/cm<sup>2</sup>·bar·psi·mmHg·inHg For positive pressure & low pressure: MPa·kgf/cm<sup>2</sup>·bar·psi For low differential pressure: kPa·mmH<sub>2</sub>O

Applicable pressure sensor	For compound pressure	For vacuum	For low pressure	For positive pressure		For differential pressure
	PSE533Note 4)	PSE531 Note 4)	Note 4)		PSE530	
Applicable pressure sensor	PSE543	PSE541	PSE532	PSE564	PSE560	-
	PSE563	PSE561				
Regulating pressure range	-101 to 101 kPa	10 to –101 kPa	–10 to 100 kPa	–50 to 500 kPa	-0.1 to 1 MPa	–0.2 to 2.00 kPa
Regulating pressure resolution	0.2 kPa	0.1 kPa	0.1 kPa	1 kPa	0.001 MPa	0.01 kPa

Note 4) Series PSE530 pressure sensors are also applicable.

Contact SMC for more information.