# **5 Port Solenoid Valve**

# Series SY3000/5000/7000/9000

Rubber Seal









#### Improved pilot valve

Pilot valve cover is stronger using stainless steel. Mounting thread is also reinforced from size M1.7 to M2.


#### Flow Characteristics

Series	Flow char	acteristics	
Series	C [dm³/(s·bar)]	b	Cv
SY3000	1.1	0.28	0.29
SY5000	2.8	0.37	0.90
SY7000	4.5	0.28	1.4
SY9000	10	0.29	2.5


# **Cylinder Speed Chart**

**Body Ported** 

Use as a guide for selection.
Please confirm the actual conditions with SMC Sizing Program.



#### **Base Mounted**



- \* Cylinder is in extending. Speed controller is meter-out, which is directly connected with cylinder and its needle is fully opened
- Average speed of cylinder is obtained by dividing the full stroke time by the stroke Load factor: ( (Load mass x 9.8) /Theoretical force) x 100%
- The histograms with ★ marked are the case when piping is done by using steel

#### Conditions

	-				
Body	/ ported	Series CJ2	Series CM2	Series MB, CA2	Series CS1
	Tubing bore x Length	T	0604 x 1 r	n	
SY3120-C6	Speed controller	Α	S2052F-0	6	
	Silencer		AN120-M5	5	
	Tubing bore x Length	T0604 x 1 m	T0806	x1m	
SY5120-01	Speed controller	AS3002F-06	AS300	02F-08	
	Silencer		AN101-01		
	Tubing bore x Length		T1075	x 1 m	
SY7120-02	Speed controller	AS3002F-06	AS400	02F-10	-
	Silencer		AN110-01		
	Tubing bore x Length			T1209	x 1 m
SY9120-03	Speed controller	AS3002F-06	AS4002F-10	AS400	)2F-12
	Silencer		AN20-02		AN202-02

#### Conditions [When using SGP (steel pipe)]

Body	/ ported	Series CS1
	Tubing bore x Length	SGP10A x 1 m
SY9120-03	Speed controller	AS420-03
	Silencer	AN20-02

#### Conditions

Base	mounted	Series CJ2	Series CM2	Series MB, CA2	Series CS1
	Tubing bore x Length	T	0604 x 1 i	n	_
SY3140-01	Speed controller	Α	S3002F-0	6	_
	Silencer		AN110-01		-
	Tubing bore x Length	T0604 x 1 m	T0806	x 1 m	-
SY5140-02	Speed controller	AS3002F-06	AS30	02F-08	-
	Silencer		AN101-01		-
	Tubing bore x Length		T1075 x 1 m	T1209 x 1 m	-
SY7140-03	Speed controller	AS3002F-06	AS40	02F-10	-
	Silencer		AN20-02		-
	Tubing bore x Length		T1075 x 1 m	T1209	x 1 m
SY9140-04	Speed controller	AS3002F-06	AS4002F-10	AS400	2F-12
	Silencer		AN2	0-02	

Conditions [When using SGP (steel pipe)]

Base	mounted	Series CS1
	Tubing bore x Length	SGP10A x 1 m
SY7140-03	Speed controller	AS420-03
	Silencer	AN30-03
	Tubing bore x Length	SGP15A x 1 m
SY9140-04	Speed controller	AS420-04
	Silencer	AN40-04

## **Valve Variations**

														_	_					. ,									N	ote 1
															ctu				+	$\overline{}$	oltaç			EI	ect	rıca	l en	try		pressor
	Serie	S				ſ	C [d	ndı dm <sup>3</sup> 4/2	³/(s →5	anc s-ba	r)] [		Single	Double	Closed center	Ť	Exhaust center   so	Pressure center 3	5	٧	A 100 50/6 110 50/6 200 50/6 220 50/6	O V 0 Hz O V 0 Hz O V 0 Hz	- Crommor		L plug connector	M plug connector	DIN terminal	M8 connector		Light/surge voltage suppressor을
þ	P.290	S	Υ3		20			0	.65	5		ŀ	•	•			•	•							•	•	•			•
porte		S	<b>Y</b> 5		20			2	2.4			ľ	•	•	•		•	•	•				•		•	•	•	•		
Body ported		S	Υ7	<u>'</u>	20			;	3.3			ľ	•	•			•	•	•				•		•	•	•			•
		S	Υ9		20			8	3.6			ľ	•	•	•		•	•	•				•		•	•	•	•		•
pa	P.306	S	Υ3	;	40				1.1			1	•	•	•		•	•					•	•	•	•	•	•		•
Base mounted		S	<b>Y</b> 5	<u> </u>	40			2	2.8			ľ	•	•	•		•	•	•				•	•	•	•	•			•
ase m		S	<b>Y7</b>	<u>'</u>	40			4	4.5			1	•	•			•	•	•				•	•	•	•	•	•		•
m		S	Υ9		40				10			•		•	•		•	•	•				•		•	•	•			•
			anu:					EA rt si		3					Α	, B	ро	rt s	ize						\	/alv	e op	otio	n	
	Series	Non-locking push type	Push-turn locking slotted type	Push-tum locking lever type		M5				1/2	M5	1/6	1/4	3/6	1/6		C	)ne-	tou	ch	fitti	ng		rottle	Oil resistant (Other than designated turbine oil)	specifications	Low pressure specifications	sure	Note 3)	egulator
		Non-locking	Push-tum lock	Push-tum loc	Bracket	IVIO	70	74	70	72	IVIO	70	74	70		C4	C6	C8	C10 C	12	N3 N	7 N	9 N1	Exhaust throttle	Oil resistant (Other the	Vacuum sp	Low pressure	Dual pressure	Enclosure IP65	Interface regulator
5	SY3□20	•	•	•	•	•			_		•			_	-	•	•	_	-	-			-							
oorte	SY5□20	•	•	•	•	_		_	_	_	_				-	•	•	•	- -	-										ı_
Body ported	SY7□20	•	•	•	•	_	(EA EB)	(P)	_	_	_	_	•	_	-	_			•		-[	-				External Pilot (Note 2)	External B Pilot B (Note 2)	External C Pilot In Note 2) N	ON eminal	
n	SY9□20	•	•	•	_	_	_		_	_	_	_		•	_	_		•		•	_	-				(vw/00 Z)	(resol E)	2) 10	connection	
ted	SY3□40	•	•	•	_	_	•	_	_		_	•	_		_	_		_	1	1	1	-	-							
Base mounted	SY5□40	•	•	•	_	_	_	•	_	-	_	_	•	_	-	_		-	-	- -	-	-	-							•
ase n	SY7□40	•	•	•	_	_	_	•	•	_	_	_	•	•	-	_				- -	-	-	-	Sub-pie		External pilot	External is	External C	ON eminal	
m		I .	١.	١.	1									_	_		1								1	1		l.	no nonector	

Note 1) All AC voltage models have built-in surge voltage suppressor.

SY9 □ 40

SJ SY

SYJ
SZ
VF
VP4
S0700
VQ
VQ4
VQ5
VQC4
VQC4
VQC8
VFS
VFR

Note 2) Body ported external pilot style (made to order) is not available for DIN terminal.

Note 3) Only available for DIN terminal and M8 connector.

Note 4) SY3000 does not have a DIN terminal which can be connected to a manifold.

									Wir					
	Manifold Va	ariations		Valve Series	Individual wiring	Flat ribbon cable (26 pins)		Plug-in type D-sub	ype flat ribbon , 20, 10 pins)	ype terminal 18 pins)	PC wiring	Serial transmission unit	Positive common session	Negative common
				5 port	Indiv	Flat r (26 p	Flat rib	Plug- conn	Plug-i	Plug-in t block (9,	PC	Seria unit	Posit	Nega
	Bar stock type		Type 20	SY3□20										
	Individual wiring  Direct piping to the main unit of a valve. Combination of		P. 324	SY5□20		_	_	_	_	_	_	_	_	_
	different fittings is possible.			SY7□20										
	Bar stock type		<sub>Туре</sub> 20P	SY3□20										Note)
	■ A 26 pins MIL connector		P. 334	SY5□20	-	•	_	_	-	_	_	_		
	permits One-touch wiring of external cables in a bundle.	o de la constantina della cons		SY7□20									In con	nmon
rted	Stacking type Individual wiring  Manifold stations can be increased or decre	eased.	Type <b>23</b> P. 330	SY9□20	•	_	_	_	_		_	_	1	_
Body ported	Stacking type Flat ribbon cable  Manifold stations can be increased or decre	eased.	Type <b>23P</b> P. 340	SY9□20	_	•	_	_	_	_	_	_	In con	Note)
000	Bar stock type EX510 gateway type		Type 20SA	SY3□20										
11	Can be used with a serial transmission system.		P. 344	SY5□20	_	—	_	_	-	_	_	•	_	-
	transmission system.	The same of the sa		SY7□20										
	Stacking type EX510 gateway type Can be used with a serial transmission system.		Type <b>23SA</b> P. 350	SY9□20	_	_	_	_	_	_	_	•	_	_
	Cassette type		туре 60	SY3□60	•	_	_	_	_	_	_	_	_	_
	Size and weight reduced by eliminating the manifold base		P. 358	SY5□60	•	_	_	_	_	_	_	_	_	_
	eminating the manifold base	765	<b>≯</b>	SY7□60	•	_	_	_	_	_	_	_	_	_

Standard ○ Option ▲ Made to order (Refer to page "Made to Order".) Note) When there are polarities, the positive common specifications are used.

		Ma	anifo	old	opti	ion							A	, B <sub> </sub>	port	siz	e								,	Valv	e op	otior	1			
Blanking plate	Individual SUP spacer	Individual EXH spacer	SUP block disk	EXH block disk	Label for block disk	Silencer for One-touch fitting	Built-in silencer	Connector	M5	1/8	1/4	3/8			On	e-tc	uch	n fitt	ing			Mixed mounting	stant (Other than ted turbine oil)	Vacuum specifications	Low pressure specifications	Different pressure	Dual pressure	Exhaust throttle	Bundle wiring	Mixed fitting sizes	IP65 enclosure	Interface regulator
Blank	Individ	Individ	SUP	EXH	Label	Silencer	Built-	Conn					C4	C6	C8	C10	C12	N3	N7	N9	N11	SY3000 SY5000	Oil resignates	Vacuur	Low pres	Differ	Dual	Exha	Bund	Mixed	IP65	Interfa
									•	_	_	_	•	•	_	_	_		•	_	_										Note) Note)	
			_	_	_	_	_	_	_	•	_	_	•	•	•	_	_	•	_	•	_	-	•	_	-	Individual SUP	_	Individual EXH	_	_	Note)	-
									•	_	_	_	•	•	_	_	_	•	•	_	_					interface		interface				$\dashv$
			_	_	_	_	_	_	_	•	_	_	•	•	•	_	_	•	•	•		_	▲	_	-	Individual	_	Individual	•	_	$\left  - \right $	-
									_	_	•	_	_	_	•	•	_	_	_	•	•					SUP interface		EXH interface				
						_	_	_	_	_	•	•	_	_	•	•	•	_	_	•	•	_	•	External pilot	External pilot	Individual SUP block disk	External pilot	Individual EXH	_	_	Note)	
•		•			•	_	_	_	_	_	•	•	_	_	•	•	•	_	_	•	•	_	•	External pilot	External pilot	Individual SUP block disk	External pilot	Individual EXH	•	_	-	
									•	_	_	_	•	•	_	_	_	•	•	_	_			F					•			
•			_	_	-	_	-	•	_	•	_	_	•	•	•	_	_	•	•	•	_	-	•	_	-	Individual SUP	_	Individual EXH	•	-	-	-
									_	_	•	_	_	_	•	•	_	_	_	•	•					interface		interface	•		$\vdash$	$\dashv$
			_	_	_	_	-		_	_	•	•	_	-	•	•	•	_	_	•	•	-	•	External pilot	External pilot	Individual SUP block disk	External pilot	Individual EXH	•	-	-	-
	_	_	•	•	•	•	_	_	•	_	_	_	•	•	_	_	_	•	•	_	_	_	▲	External pilot	External pilot	Individual SUF block disk		_	_	_	Note)	
	_	_					_	_	_	•	_	_	•	•	•	_	_	•	•	•	_	_	<b>A</b>	External pilot	External pilot	Individual SUF block disk	Individual SUP black disk	_	_	_	Note)	
		-					-		_	-		-	-	-			_	-	-			—		External pilot	External	Individual SUP block disk	Individual SUP block disk	-	-	-	1000	-

Note) When using DIN terminal or M8 connector. SY3000 does not have a DIN terminal which can be connected to a manifold.

287

SJ SY

SYJ
SZ
VF
VP4
S0700
VQ
VQ4
VQ5
VQC4
VQC4
SQ

VFS VFR VQ7

							Conne	Wir				C	and and an
	Manifold Variations		Valve Series	Individual wiring	t ribbon cable pins)	Flat ribbon cable (20 pins)	dns)	n type flat ribbon 26, 20, 10 pins)	n type terminal (9, 18 pins)	iring	Serial transmission unit	Positive common	Negative common
			5 port	Indiv	Flat ri (26 pi	Flat ribt	Plug-	Plug-ii cable (	Plug-ii block	PC wiring	Serial	Positi	Nega
	Compact bar stock type Individual wiring	туре 41	SY3□40		_		_	_	_	_	_	_	
	The base mounting facilitates maintenance after valves are changed.	P. 376	SY5□40										
	Compact bar stock type Flat ribbon cable  A 26 pins MIL connector permits one-touch	1ype 41P P. 392	SY3□40	_	•	_	_	_	_	_	_		Note)
	wiring of external cables in a bundle.		SY5□40									In con	nmon
	Bar stock type/Common external EXH Individual wiring	Туре 42	SY3□40										
	■ The base mounting facilitates maintenance after valves are changed.  ■ Vacuum/low pressure combination	P. 376	SY5□40		_	_	_	_	-	_	_	_	_
	system is possible.	49D	SY7□40										
	Flat Hubbell Cable	Type <b>42P</b> P. 392	SY3□40										Note)
	A 26 pins MIL connector permits one-touch wiring of external cables in a bundle.  Vacuum/low pressure combination system	F. 392	SY5□40	-	•	_	_	_	_	_	_	In cor	nmon
	is possible.	Type 43	SY7□40										
70	Individual wiring ■ Manifold stations can be increased or decreased.	P. 386	SY9□40					_					
Base mounted	Stacking type Flat ribbon cable  Manifold stations can be increased or decreased.	Type 43P P. 400	SY9□40	_	•	_	_	_	_	_	_	In cor	Note)
υu	Bar stock type	Type 42SA	SY3□40										
e l	an be used with a serial	P. 406	SY5□40	—	_	_	_	_	_	_		_	_
as	transmission system.		SY7□40										
11	Stacking type EX510 gateway type Can be used with a serial transmission system.	Type <b>43SA</b> P. 411	SY9□40	_	_	_	_	_	_	_	•	_	_
	Stacking type/DIN rail mounted Individual wiring	туре 45	SY3□40										
	■ Stations can be increased on the DIN rail. Integral mounting of other electric parts is possible, too.	P. 422	SY5□40										
	Stacking type/DIN rail mounted Connector box	Type <b>45</b> A NA P. 434	SY3□40	_	_	•	_	_	_	•	_	•	•
	connector box permits one-touch connection of electric cables.		SY5□40										
	Stacking type/DIN rail mounted  EX510 gateway type  Can be used with a serial	<sub>™</sub> 4586A P. 442	SY3□40 SY5□40	-	_	_	_	_	_	_	•	_	_
	Stacking type/DIN rail mounted	<sub>Type</sub> 45	SY3□40										
	■ A variety of centralized wiring methods are possible. It is a variety of centralized wiring methods are possible.	P. 450	SY5□40	-	_	_							
	Stacking type/DIN rail mounted Plug-in	13pe 45S6B	SY3□40	_	_	_	_	_	_	_	•	_	
	EX510 gateway type  Can be used with a serial transmission system.  Standard Option Made to order (Refer to page "N	P. 490	SY5□40										

<sup>●</sup> Standard ● Option ▲ Made to order (Refer to page "Made to Order".)

Note) When there are polarities, the positive common specifications are used.

		Ma	anif	old	opti	on					A, B port size Valve option											1										
Blanking plate	Individual SUP spacer	Individual EXH spacer	SUP block disk	EXH block disk	Label for block disk	Silencer for One-touch fitting	Built-in silencer	Connector	M5	1/8	1/4	3/8			On	e-to	ouch	n fitt	ing			Mixed mounting	Oil resistant (Other than designated turbine oil)	Vacuum specifications	ow pressure specifications	Different pressure	Dual pressure	Exhaust throttle	Bundle wiring	Mixed fitting sizes	P65 enclosure	Interface regulator
Blan	Individ	Individ	SUP	EXH	Label	Silencer	Built	Con					C4	C6	C8	C10	C12	N3	N7	N9	N11	SY3000 SY5000	Oil res design	Vacuu	Low pre	Diffe	Dual	Exp	Bunc	Mixe	IP65	Interf
			_	_	_	_	_	_	•	_	_	_	•	•	_	_	_	•	•	_	_	_	•	_	_	Individual	_	_	_	_	Note)	
									_		_	_	_	•	•	_	_	_	•	•	_					SUP interface						
			_	_	_	_	_	_	•	_	_	-	•	•	_	_	_	•	•	_	_	_	<b>A</b>	_	-	Individual	_	_	•	_	_	
									_		_	_	-	•				_	•							SUP interface					Note)	
									_		_	E	_		_		_	•		•	_	_									Note)	
						_			_	_		E				_	_	_			_	-		External pilot	External pilot	Individual SUP	External pilot				Note)	
									_		_	_				_	_				_					interface					•	
			_	_	_	_	_	_	_	_	•	_	_	•	•	_	_	_	•	•	_	_	<b>A</b>	•	•		•	_	•	_	_	
									_	_	•	-	_	_	_	•	_	_	_	_	•			External pilot	External pilot	Individual SUP interface	External pilot					
		•	•	•			•	_	_	_	•	•	_	_	•	•	•	_	_	•	•	_	<b>A</b>	External	External	Individual SUP	External	Individual	_	•	Note)	
																								pilot	pilot	block disk	pilot	EXH				_
								_	_	-	•	•	_	-	•	•	•	_	-	•	•	-	<b>A</b>	External pilot	External pilot	Individual SUP block disk	External pilot	Individual EXH	•	•	_	
									_		_	_		•	_	_	_			_	_											
			-	_	_	-	-		_	_	•	_	_	•	•	_	_	—	•	•	_	-	<b>A</b>	External	External	Individual	External	_	_	-	_	
									_	_	•	_	_	_	_	•	_	_	_	_	•			pilot	pilot	SUP	pilot					
						•	_		_	_	•	•	_	_	•	•	•	_	_	•	•	_	•	External pilot	External pilot	Individual SUP	External pilot	Individual EXH	_	•	_	_
									_	_	_	_	•	•	_	_	_	•	•	_	_	_				Infividual					Note)	
									_	_	_	_	•	•	•	_	_	•	•	•	_			External pilot	External pilot	SUP spacer or block disk					Note)	
								_	_	_	_	_	•	•	_	_	_	•	•	_	_			_		Individual SUP	_	_			_	
									_	_	_	_	•	•	•	_	_	•	•	•	_			External pilot	External pilot	spacer or block disk						
	_	_	_	_	_	_	•		_	_	_	_	•	•	_	_	_	•	•	_	_	_		•	•	Individual SUP spacer or	_	_	•	•	_	
									_	_	_	_	•	•	•	_	_	•	•		_			External pilot	External pilot	block disk						
								_	_	_	_	_	•		_	_	_		•		_	-	<b>A</b>	External	External	Individual SUP spacer or	_	_	•	•	_	_
											_				_				•					pilot	pilot	block disk						
_	-	_	_	_	_	_	•	_	_						_		_			-		-		External	External	Individual SUP spacer or block disk	_	-	•	•	-	-
Noto				<u> </u>							L		•			\ tor					conn			pilot	pilot	JOSK USK						

Note) When using DIN terminal or M8 connector. SY3000 does not have a DIN terminal which can be connected to a manifold.

**SMC** 

SJ

SY

sv

SYJ SZ

VF

**VP4** S0700

VQ VQ4

VQ5 VQC

VQC4


SQ

VFS VFR

# 5 Port Solenoid Valve **Body Ported/Single Unit**

Note) AC-type models that are CE-compliant

# Series SY3000/5000/7000/9000



Ì	Electri	cal entry for G, H, L, M, W	Electr	ical entry for D, Y
i	Nil	Without light/surge voltage suppressor	Nil	Without light/surge voltage suppressor
ļ	S	With surge voltage suppressor	S	With surge voltage suppressor
Ĺ	Z	With light/surge voltage suppressor	Z	With light/surge voltage suppressor
ŀ	R	With surge voltage suppressor (Non-polar type)	* DOZ	and YOZ are not available.
	U	With light/surge voltage suppressor (Non-polar type)		C voltage valves there is no
İ	It is a	C voltage valves there is no "S" option. ready built-in to the rectifier circuit. "and "U", DC voltage is only available.		ption. It is already built-in to ectifier circuit.

\* Power saving circuit is only available in the "Z" type.

Note) When placing an order for body ported solenoid valve as a single unit, mounting screw for manifold and gasket are not attached. Order them separately, if necessary. (For details, refer to page 353.)

EN-175301-803C (former DIN43650C). For details,

\* For connector cable of M8 connector, refer to page

\* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.

\* Refer to page 519 for the lead wire length of L and M

Refer to page 520 for the connector assembly with cover for L and M plug connectors. Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523.

refer to page 519.

plug connectors.



#### Made to Order (For details, refer to pages 502 to 510.)

#### **Specifications**

Series		SY3000	SY5000	SY7000	SY9000
Fluid			A	ir	
Internal pilot	2 position single		0.15	to 0.7	
Operating pressure	2 position double		0.1 t	o 0.7	
range (MPa)	3 position		0.2 t	o 0.7	
Ambient and fluid t	temperature (°C)		-10 to 50 (I	No freezing)	
Max. operating	2 position single, double	10	5	5	5
frequency (Hz)	3 position	3	3	3	3
Manual override (M	lanual aparation)		Non-locking	push type,	
wanuai overnue (iv	ianuai operation)	Push-turn lock	ing slotted type	e, Push-turn loc	king lever type
Pilot exhaust meth	od	Common	exhaust type	for main and	pilot valve
Lubrication			Not re	quired	
Mounting orientation	on		Unres	tricted	
Impact/Vibration re	sistance (m/s²) Note)		150	0/30	
Enclosure		Dust proof (	* DIN termina	l and M8 con	nector: IP65)

Based on IEC60529

Note) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

#### Solenoid Specifications

			Grommet (G), (H)	DIN terminal (D), (Y)			
Electrical entry			L plug connector (L) M plug connector (M)	M8 connector (W)			
			G, H, L, M, W	D, Y			
Coil rated		DC	24, 12, 6, 5, 3	24, 12			
voltage (V)		AC 50/60 Hz	100, 110,	200, 220			
Allowable voltage f	fluct	uation	±10% of rate	ed voltage *			
Power	DC	Standard	0.35 (With indicator light: 0.4 DIN terminal with indicator light: 0.45)				
consumption (W)	ьс	With power saving circuit	0.1 (With indicator light only)				
		100 V	0.78 (With indicator light: 0.81)	0.78 (With indicator light: 0.87)			
		110 V	0.86 (With indicator light: 0.89)	0.86 (With indicator light: 0.97)			
Apparent power	• •	[115 V]	[0.94 (With indicator light: 0.97)]	[0.94 (With indicator light: 1.07)]			
(VA) *	AC	200 V	1.18 (With indicator light: 1.22)	1.15 (With indicator light: 1.30)			
		220 V	1.30 (With indicator light: 1.34)	1.27 (With indicator light: 1.46)			
		[230 V]	[1.42 (With indicator light: 1.46)]	[1.39 (With indicator light: 1.60)]			
Surge voltage supp	pres	sor	Diode (Varistor is for DIN terminal and Non-polar type.)				
Indicator light			LED (AC of DIN connector is neon light.)				

- \* In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.
- For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.
- \* S, Z and T type (with power saving circuit) should be used within the following allowable voltage S, Z and Type from power samp directly should be used within the fluctuation range due to a voltage drop caused by the internal circuit. S and Z type: 24 VDC: -7% to +10%

  T type: 24 VDC: -8% to +10%

12 VDC: -6% to +10%

\* DIN terminal and M8 connector with power saving circuit are not available.

#### **Response Time**

Note) Based on dynamic performance test, JIS B 8375-1981. (Coil temperature: 20°C, at rated voltage)

#### SY3000

	Response time (ms) (at the pressure of 0.5 MPa)							
Type of actuation	Without light/surge	With light/surge voltage suppressor						
actuation	voltage suppressor	Type S, Z	Type R, U					
2 position single	12 or less	15 or less	12 or less					
2 position double	10 or less	13 or less	10 or less					
3 position	15 or less	20 or less	16 or less					

#### SY5000

	Response time (ms) (at the pressure of 0.5 MPa)							
Type of actuation	Without light/surge	With light/surge voltage suppressor						
actuation	voltage suppressor	Type S, Z	Type R, U					
2 position single	19 or less	26 or less	19 or less					
2 position double	18 or less	22 or less	18 or less					
3 position	32 or less	38 or less	32 or less					

#### SY7000

<b>-</b> ,	Response time (ms) (at the pressure of 0.5 MPa)							
Type of	Without light/surge	With light/surge voltage suppressor						
actuation	voltage suppressor	Type S, Z	Type R, U					
2 position single	31 or less	38 or less	33 or less					
2 position double	27 or less	30 or less	28 or less					
3 position	50 or less	56 or less	50 or less					

#### SY9000

<b>-</b> ,	Response time (ms) (at the pressure of 0.5 MPa)							
Type of actuation	Without light/surge	With light/surge voltage suppresso						
actuation	voltage suppressor	Type S, Z	Type R, U					
2 position single	35 or less	41 or less	35 or less					
2 position double	35 or less	41 or less	35 or less					
3 position	62 or less	64 or less	62 or less					



SJ

SYJ

SZ

VP4

S0700

VO V04 V05 voc VOC4 VOZ SO VFS

**VFR** 

#### Flow Characteristics/Weight

#### Series SY3000

			Por	t size		Flow	char	acter	istics	6	We	eight	(g)
Valve		e of	1, 5, 3	4, 2		2 (P→	A/B)		3 (A/B-	EA/EB)	Gro-	L/M	W
model	actu	ation		(A, B)	C (kdm <sup>3</sup> / (s-bar))	b	Cv	C (kdm <sup>3</sup> / (s-bar))	b	Cv	mmet	plug cornector	M8
	2	Single			(2-1/41))			(5-041))			51	53	57
		Double	1		0.61	0.44	0.16	0.64	0.45	0.18	68	74	82
SY3□20		Closed center		ME 0.0	0.48	0.46	0.13	0.47	0.43	0.13			
-□-M5	3 position	Exhaust center		M5 x 0.8	0.47	0.42	0.13	0.47 (0.44)	0.41 (0.37)	0.13 (0.12)	71	76	84
		Pressure center			0.50 (0.41)	0.48 (0.35)	0.15 (0.11)	0.47	0.43	0.13		-	
	2	Single		x0.8 C4 One-touch fitting for ø4	0.72 0.29 0	0.00	0.18	0.64	0.34	0.17	60	63	67
	position	Double				0.10	0.04	0.34	0.17	78	83	91	
SY3□20		Closed center			0.59	0.28	0.15	0.59	0.30	0.15		86	94
-□-C4	3 position	Exhaust center	Mo X U.8		0.63	0.35	0.16	0.42 (0.41)	0.34 (0.37)	0.11 (0.11)	81		
		Pressure center		(101547	0.76 (0.46)	0.42 (0.34)	0.21 (0.12)	0.59	0.29	0.15			
	2	Single			0.70	0.00	0.10	0.05	0.00	0.17	56	59	63
	position	Double			0.76	0.30	0.19	0.65	0.39	U.17	74	79	87
SY3□20		Closed center		C6 / One- \	0.76	0.55	0.24	0.60	0.33	0.16			
-□-C6	3 position	Exhaust center		touch fitting for ø6	0.65	0.32	0.16	0.64 (0.42)	0.31 (0.36)	0.17 (0.11)	77	82 90	90
		Pressure center			0.77 (0.49)	0.34 (0.43)	0.21 (0.15)	0.61	0.34	0.16			

Note) []: denotes normal position.

#### Series SY7000

			Por	t size		Flow	char	acter	istics	3		Weig	ht (g)	
Valve model		e of ation	1, 5, 3 (P, EA, EB)	4, 2 (A, B)	1→4) C (dm³/ (s-bar))	2 (P b	Cv	4/2→5 C (dm <sup>3</sup> / (s-bar))	3 (A/B-	Cv	Gro- mmet	L/M plug connector	DIN terminal	W M8 cornector
	2 position	Single Double			4.1	0.23	0.93	3.3	0.33	0.81	101 120	104 125	125 167	108 133
SY7□20		Closed center		1/	2.9	0.31	0.70	2.4	0.38	0.63				
-□-02	3 position	Exhaust center		1/4	2.5	0.39	0.65	3.4 (2.1)	0.35 (0.38)	0.82 (0.54)	128	133	175	141
		Pressure center			4.3 (2.4)	0.23 (0.32)	0.97 (0.61)	2.2	0.39	0.58				
	2 position	Single Double	1 (P) Port		3.2	0.26	0.77	3.2	0.37	0.82	107 126	110 132	131 174	114 140
SY7□20		Closed center	1/4	C8 / One- \	2.6	0.24	0.63	2.4	0.31	0.62	134	140	182	148
-□-C8	3 position	Exhaust center	5, 3 (EA, EB)	touch fitting for ø8	2.4	0.25	0.57	2.6 (1.9)	0.42 (0.46)	0.70 (0.56)				
		Pressure center	port 1/6	( 10. 50 )	3.3 (2.4)	0.28 (0.22)	0.78 (0.57)	2.2	0.34	0.60				
	2 position	Single Double			3.8	0.26	0.86	3.2	0.34	0.82	103 122	105 127	126 169	109 135
SY7□20		Closed center		C10 / One- \	2.8	0.27	0.67	2.4	0.21	0.59				
-□-C10	3 position	Exhaust center		touch fitting for ø10	2.5	0.25	0.59	2.7 (2.0)	0.38	0.70 (0.56)	130	135	177	143
		Pressure center		( 510)	3.8 (2.4)	0.25 (0.31)	0.89 (0.61)	2.3	0.38	0.61				

Note) []: denotes normal position.

#### Series SY5000

			Port size			Flow			istics		Weight (g)			
Valve		e of	1, 5, 3			2 (P→	A/B)		/3 (A/B-	EA/EB)	Gro-	L/M	DIN	W
model	actu	ation	(P, EA, EB)		C (dm <sup>3</sup> / (s-bar))	b	Cv	C (dm% (s-bar))	b	Cv	mmet	plug conrector	terminal	M8 connector
	2 position	Single Double			1.9	0.35	0.49	2.4	0.39	0.61	70 88	72 93	93 135	76 101
SY5□20		Closed center		1/8	1.7	0.43	0.45	1.8	0.35	0.46				
-□-01	3 position	Exhaust center		1/8	1.5	0.44	0.41	2.5 (1.5)	0.32 (0.43)	0.59 (0.40)	93	98 1	140	106
		Pressure center			2.2 (0.91)	0.46 (0.58)	0.61 (0.28)	1.8	0.38	0.46				
	2	Single			0.75	0.43	0.20	0.85	0.64	0.30	94	96	117	100
	position	Double			0.73	0.40	0.20	0.00	0.04	0.00	111	117	159	125
SY5□20		Closed center		C4 / One- \	0.74	0.40	0.19	0.84	0.57	0.28				
-□-C4	3 position	Exhaust center		touch fitting for #4	0.75	0.36	0.19	0.84 (0.84)	(0.53)	0.30	117	122	164	130
		Pressure center	1/8	(10157)	0.78 (0.71)	0.44 (0.37)	0.21 (0.18)	0.84	0.57	0.27				
	2 position	Single Double	78		1.5	0.33	0.33	2.0	0.37	0.52	88 106	91 111	112 153	95 119
SY5□20		Closed center		C6 / One- \	1.3	0.31	0.33	1.6	0.32	0.39				
-□-C6	3 position	Exhaust center		touch fitting for ø6	1.3	0.33	0.33	1.8 (1.4)	0.35 (0.37)	0.44 (0.35)	111	116	158	124
		Pressure center		(10150 )	1.7 (0.80)	0.31 (0.47)	0.42 (0.23)	1.7	0.33	0.44				
	2	Single			1.9	0.21	0.45	2.3	0.29	0.57	80	82	103	86
	position	Double			1.9	0.21	0.40	2.0	0.23	0.57	98	103	145	111
SY5□20		Closed center		C8 / One- \	1.6	0.29	0.39	1.7	0.38	0.46				
-□-C8	3 position	Exhaust center		touch fitting for ø8	1.4	0.38	0.39	2.0 (1.5)	0.37 (0.41)	0.52 (0.43)	103	3 108 1	150	116
		Pressure center		( 50 )	2.2 (1.6)	0.32 (0.44)	0.56 (0.44)	1.8	0.41	0.50				

Note) []: denotes normal position.

#### Series SY9000

			Por	t size				acter			Weight (g)			
Valve	Type o		1. 5. 3	4. 2		2 (P→	A/B)	4/2→5/	/3 (A/B-	EA/EB)	Gro-	L/M	DIM	W
model	actuati	on		(A, B)	C (dm³/ (s-bar))	b	Cv	C (dm <sup>9</sup> / (s-bar))	b	Cv	mmet	plug cornector	DIN terminal	
	2 Sin position Dou	gle ible			7.0	0.33	1.7	7.6	0.35	2.0	241 260	244 266	265 308	248 274
SY9□20	Clos	ed		1/4	6.7	0.37	1.7	6.4	0.34	1.6				
-□-02	3 Exha position cer			1/4	6.4	0.36	1.6	8.3 (4.1)	0.41 (0.27)	2.2 (0.91)	284		298	
	Pres				8.0 (3.2)	0.27 (0.34)	1.8 (0.76)	6.5	0.22	1.4				
	2 Sin position Dou				8.0	0.29	1.9	8.0	0.33	2.0	236 255	239 261	260 303	
SY9□20	Clos			3/8	7.9	0.33	1.9	6.6	0.27	1.6				
-□-03	3 Exha position cer			9/8	8.0	0.33	1.9	8.7 (8.3)	0.34 (0.40)	2.2 (2.3)	279	285	327	293
	Pres				8.9	0.34 (0.40)	2.2 (0.82)	6.5	0.25	1.5				
	2 Sin position Dou				4.3	0.28	0.96	7.1	0.32	1.7	293 312	296 318	317 360	300
SY9□20	Clos		1/4	C8 / One- \	4.3	0.31	0.99	6.1	0.28	1.4				
-□-C8	3 Exh position cer		1/4	touch fitting	4.3	0.3	0.99	7.4 (3.8)	0.36 (0.29)	1.9 (0.86)	336	342	342 384	350
	Pres cer			\ 10F86 /	4.4 (3.2)	0.35 (0.26)	1.0 (0.71)	2.1	0.41	0.53				
	2 Sin				6.1	0.28	1.4	7.9	0.33	1.9	279		303	
	Clos	ed		C10	5.9	0.30	1.4	6.5	0.26	1.5	298	304	346	312
SY9□20 -□-C10	g Exha	aust		/ One- \ touch fitting	5.8	0.25	1.3	8.4	0.33	2.0	322	328	370	336
	position cer Pres	sure		\ for ø10 7	6.3	0.29	1.5	6.4	0.25	1.5				
	2 Sin				(3.2)	10 -7	(0.72)				265	268	289	272
	position Dou				7.0	0.25	1.6	8.6	0.41	2.2	284	290		
SY9□20	Clos	ed		C12	6.9	0.24	1.6	7.0	0.33	1.7				
-□-C12	3 Exh position cer			(One- )- touch fitting	6.6	0.23	1.4	9.4 (4.5)	0.48 (0.32)	2.6 (1.0)	308	314	356	322
	Pressure center		\for ø12/	7.4 (3.2)	0.25 (0.34)	1.7 (0.74)	6.6	0.23	1.5					

Note) []: denotes normal position.





#### Construction

#### Series SY


#### Symbol 2 position single

(A)4 2(B) (EA)5 1 3(EB) (P)

# 2 position single 2 (EA)

#### Symbol 2 position double

(A)4 2(B) (EA)5 1 3(EB)



#### 3 position closed center / exhaust center / pressure center

#### Symbol 3 position closed center







#### 3 position pressure center



(This figure shows a closed center type.)

(EA)

(P) (EB)

#### Component Parts

No.	Description	Material	Note
1	Body	Aluminum die-casted (SY3000: Zinc die-casted)	White
2	Adapter plate	Resin	White (SY9000: Gray)
3	End plate	Resin	White
4	Piston	Resin	-
5	Spool valve assembly	Aluminum, H-NBR	_

Replacement Parts

No.	Description	Part no.
6	Pilot valve assembly	Refer to "How to Order Pilot Valve Assembly" on page 511.
7	M5 port block assembly	Refer to "How to Order Port Block Assembly" on page 511.

#### Bracket Assembly No.


Description	Part no.
Bracket (For F1)	SX <sub>9</sub> 000-16-2A (with mounting screw)
Bracket (For F2)	SX <sub>9</sub> 000-16-1A (with mounting screw)

<sup>\*</sup> SY9000 has no bracket

### How to Change Port Block Assembly

5

If using body port type, both A and B port sizes can be changed by replacing the port block assembly mounted on the body. When changing this block assembly, the correct screw torque must be achieved to avoid possible air leakage.



Mounting screw tightening torques

SY3000 (M2): 0.12 N·m SY 7000 (M3): 0.6 N·m SY9000 (M4): 1.4 N·m

\*Referto "How to Order Port Block Assembly" on page 511 for part no.



SJ

SY

SV

SYJ

SZ

۷F VP4 S0700

VO

V04

V05

VQC

VQC4

VOZ


SQ

VFS


VFR

#### **Dimensions: Series SY3000**

[ ]: AC




# 





M8 connector (WO):


# L plug connector (L): SY3120-□L□- C4, N3 (-F1) 28.5 [35.5] 13.1 000 xouddy 16.9 18.5 C6: 33.6 N7: 37.4 (3.2)





M plug connector (M):












Note) Refer to page 523 for dimensions of connector types


295


#### **Dimensions: Series SY3000**


[ ]: AC

3 position closed center / exhaust center / pressure center Grommet (G), (H): SY3 $\frac{3}{4}$ 20- $\Box_H^G\Box\Box$ - $C_{6}^{4}$ ,  $N_7^3$ (-F2)
















M plug connector (M): SY3<sup>3</sup>/<sub>4</sub>20-□M□□-<sup>C4</sup>/<sub>C6</sub>, N<sub>7</sub>(-F2)



M8 connector (WO): SY3<sup>3</sup>/<sub>2</sub>20-□WO□□-<sup>C4, N3</sup><sub>C-F2</sub>(-F2)



Note) Refer to page 523 for dimensions of connector types.



**Dimensions: Series SY5000** [ ]: AC 2 position single Foot bracket SY5120-□G□□-C6, N7□-F1 Grommet (G), (H): SY5120-□H□□-C6, N7□(-F2) 38 SJ 2 x M3 x 0.5 depth 3.5 12.7 (For mounting bracket) SY 9 9.91 SY 2 x ø3.2 28.1 [35.1] SV (For mounting) One-touch fitting G: Approx. 300 A, B port 85.9 [88.1] H: Approx. 600 SYJ Applicable tubing O.D.: ø4, ø5/32" (Lead wire length) 63.7 ø6, ø1/4" ø8. ø5/16 SZ φ 88.6 [90.8] ۷F (\*) 2 x ø3.2 Manual override 14.5 (For manifold mounting) VP4 36 (\*) (45)mounting) S0700 (4.9) (37)2 x ø3.2 (Light/surge voltage suppressor) VO (4.9)40.4 10.5 V04 Q (36.7)6 6 28.1 23 SY5120-010(-F1) 20. VQ5 32.3 VOC 0.8 ဖျ (A, B port) VQC4 (50) 35. VQZ 1/8 20.5 (P, EA, EB port) 32. ន 2 x ø2.2 die-cast hole SQ For manifold gasket positioning VFS L plug connector (L): M plug connector (M): DIN terminal (D, Y): M8 connector (WO): VFR SY5120-□L□□-C4, N3 C6, N7 C8, N9 VQ7 60.9 Applicable cable O.D. Lead wire length 53.4 ø3.5 to ø7 28.1 [35.1] 9 42.1 Approx. 12.7 27 M8 x 1 32.6 15.1 39.2 [46.2] Approx. 300 Pg7 (Lead wire length) 105.8 98 88.2 94.9 87.5 95.8 8 86 65 32.3 33

40.4

20.5

23

(4.9)

20.5

23

40 4

(4.9)

20.5

23

40.4

(4.9)

20.5

23

40.4

(4.9)

#### **Dimensions: Series SY5000** [ ]: AC 2 position double Grommet (G), (H): SY5220-□ GR □ □ - C6, N7 □ (-F2) SY5220-□G□□-01□(-F2) 2 x M3 x 0.5 depth 3.5 B port) (For mounting bracket) [35] 32 g One-touch fitting (A. B port) G: Approx. 300 Applicable tubing O.D.: ø4, ø5/32" H: Approx. 600 107.2 [111.6] : ø6, ø1/4" (Lead wire length) 62.8 : ø8. ø5/16" Manual override 2 x ø3.2 14.5 (For manifold mounting) (45)(37)2 x ø3.2 (Light/surge voltage suppressor) 4 (For mounting)




40.

0.8 ø. 2

20.5

1/8

27.2 /2 x ø2.2 die-cast hole (P, EA, EB port)



(40.2)(36.7)

28.1

**Dimensions: Series SY5000** 

[ ]: AC

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VQ VO4

VQ5


voc


VQC4


VQZ


SQ


VQ7






L plug connector (L): M plug connector (M): DIN terminal (D, Y): M8 connector (WO): SY5 \( \frac{4}{5} \)20-□L□□-\( \frac{C4}{C8}, \)N3 □(-F2) \( \frac{C4}{5}, 










Note) Refer to page 523 for dimensions of connector types.




#### **Dimensions: Series SY7000**


[ ]: AC







**Dimensions: Series SY7000** [ ]: AC 2 position double Grommet (G), (H): SY7220- $\square_H^G\square\square$ -C8, N9  $\square$ (-F2) SY7220-□G□□-02□(-F2) 1/4 2 x M4 x 0.7 depth 6.5 (A, B port) (For mounting bracket) [38.5] 5 3 One-touch fitting (A, B port) G: Approx. 300 Applicable tubing O.D.: Ø8, Ø5/16" H: Approx. 600 121.4 [125.8] ø10, ø3/8" (Lead wire length) 3.6 19 2 x ø4.2 Manual override 42 (For manifold mounting) (For mounting) 2 x Ø4.2 (66)(Light/surge voltage suppressor) (52)(5.5)(49.5)(42.5)31.5 1/4 (P port) 6 2 x Ø2.2 die-cast hole 1/8 For manifold gasket positioning (EA, EB port)









Note) Refer to page 523 for dimensions of connector types.

SJ

SY

SV

SYJ

SZ VF

VP4

S0700

VO

V04

VQ5 VQC


VQC4


SQ VFS


VFR

#### **Dimensions: Series SY7000**

[ ]: AC









2 x ø2.2 die-cast hole


For manifold gasket positioning



1/8

(EA, EB port)





Note) Refer to page 523 for dimensions of connector types.

**Dimensions: Series SY9000** [ ] AC 2 position single 2 position single C8, N9 Grommet (G), (H): SY9120- $\square_H^G \square \square$ -C10, N11 $\square$  C12 SY9120-04 00-03 G: Approx. 300 H: Approx. 600 130.2 [132.4] (Lead wire length) 108 3/8. 1/4 Manual 6.5 56.3 [4(A), 2(B) port)] override 18.4 One-touch fitting 3 x ø3.2 33.6 [4(A), 2(B) port] (For manifold mounting) 64.2 Applicable tubing O.D.: ø8, ø5/16 ø10, ø3/8" (Light/surge voltage suppressor) (5.5)ø12 ф œ 33 Ф 56.3 [47.9] 6 39.1 25.5 9 36. 9 36.6 2 x ø4.4 24.9 (For mounting) 39.1 51.5 1/4 [1(P), 5(EA), 3(EB) port] 0 33 0.5 49.8

L plug connector (L): SY9120-□L□□-C10, N11□ C12 M plug connector (M): SY9120-□M□□-Çi0, N11□ DIN terminal (D, Y): SY9120-□D□□-C10,N11□ C12

M8 connector (WO):

SY9120-□WO□□-C10, N11□
C12

M8 x 1

8

(5.5)

(tjbus sum pear)

40.9 [47.9]

25.5

40.9 [47.9]

(47.9)

(47.9)

(47.9)


(47.9)

(47.9)

(47.9)

(47.9)

(5.5)



Note) Refer to page 523 for dimensions of connector types.

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

vo

V04

VQ5

voc

VQC4

SQ


VFS

**VFR** 




**Dimensions: Series SY9000** 


[ ]:AC




L plug connector (L): SY9220-□L□□-C10, N11□ C12 M plug connector (M): SY9220-□M□□-C10, N11□ C12 DIN terminal (D, Y): SY9220-□<sup>D</sup><sub>Y</sub>□□-C10, N11□ C12

M8 connector (WO): SY9220-□WO□□-C10, N11□ C12







Note) Refer to page 523 for dimensions of connector types.

**Dimensions: Series SY9000** 

[ ]: AC

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO


V04

VQ5

VOC

VQC4

VQZ



L plug connector (L):

C8, N9

SY9

420-□L□□-C10, N11□

C12

M plug connector (M):

C8, N9

SY9<sup>4</sup>/<sub>5</sub>20-□M□□-C10, N11□
C12


DIN terminal (D, Y):


C8, N9
SY9420-□7□□-c10, N11□
C12

M8 connector (WO):

SY9<sup>3</sup>/<sub>5</sub>20-□WO□□-c10, N11□

c12





**SMC** 


Note) Refer to page 523 for dimensions of connector types.

# 5 Port Solenoid Valve Base Mounted/Single Unit Note) AC-type models that are CE-compliant have DIN terminals

(Details → P.513)

# Series SY3000/5000/7000/9000

#### How to Order



- 100 VAC 2 200 VAC 3 110 VAC [115 VAC 4 220 VAC [230 VAC]
- \* DC specifications of type D, Y, DO and YO is only available with 12 and 24 VDC
- ∗ For type W□, DC voltage is only available.
- \* The DIN terminal of series SY3000 cannot be mounted on the standard sub-plate. For details, refer to page 520.
- "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C). For details, refer to page 519.
- \* For connector cable of M8 connector, refer to page 522.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.
- \* Refer to page 519 for the lead wire length of L and M plug connectors. \* Refer to page 520 for the connector assembly with cover for L and M plug connectors.
- Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523. Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

# Base Mounted Series SY3000/5000/7000/9000





#### **Response Time**

Note) Based on dynamic performance test, JIS B 8375-1981. (Coil temperature: 20°C, at rated voltage)

#### SY3000

Type of	Response time (ms) (at the pressure of 0.5 MPa)								
		Without light/surge   With light/surge voltage suppre							
	voltage suppressor	Type S, Z	Type R, U						
2 position single	12 or less	15 or less	12 or less						
2 position double	10 or less	13 or less	10 or less						
3 position	15 or less	20 or less	16 or less						

#### SY5000

Type of		onse time ( ressure of 0	
actuation	Without light/surge	With light/surge v	oltage suppressor
	voltage suppressor	Type S, Z	Type R, U
2 position single	19 or less	26 or less	19 or less
2 position double	18 or less	22 or less	18 or less
3 position	32 or less	38 or less	32 or less

#### SY7000

Type of	Response time (ms) (at the pressure of 0.5 MPa)								
actuation	Without light/surge	With light/surge voltage suppresso							
	voltage suppressor	Type S, Z	Type R, U						
2 position single	31 or less	38 or less	33 or less						
2 position double	27 or less		28 or less						
3 position	50 or less	56 or less	50 or less						

#### SY9000

Type of	Response time (ms) (at the pressure of 0.5 MPa)									
actuation	Without light/surge	With light/surge v	oltage suppressor							
	voltage suppressor	Type S, Z	Type R, U							
2 position single	35 or less	41 or less	35 or less							
2 position double	35 or less	41 or less	35 or less							
3 position	62 or less	64 or less	62 or less							

#### **Specifications**

Series			SY3000 SY5000 SY7000 SY9000					
Fluid			Air					
Internal pilot 2 position single				0.15	to 0.7			
Operating pressure	2 position double			0.1 t	o 0.7			
range (MPa)	3 position			0.2 t	o 0.7			
	Operating pressure range			-100 kF	Pa to 0.7			
External pilot	Pilot	2 position single		0.25	to 0.7			
Operating pressure range (MPa)	pressure	2 position double		0.25	to 0.7			
range (wra)	range	3 position		0.25	to 0.7			
Ambient and fluid t	emperati	ıre (°C)	-10 to 50 (No freezing.)					
Max. operating	2 positio	n single, double	10 5 5 5					
frequency (Hz)	3 positio	on	3	3	3	3		
Manual override				Non-locking	push type,			
(Manual operation)			Push-turn lock	ing slotted type	e, Push-turn loc	king lever type		
Pilot exhaust	Internal	pilot	Common	exhaust type	for main and	pilot valve		
method	Externa	pilot	F	Pilot valve indi	ividual exhaus	st		
Lubrication				Not re	quired			
Mounting orientation	on			Unres	tricted			
Impact/Vibration re	Impact/Vibration resistance (m/s²) Note)			150/30				
Enclosure			Dust proof (* DIN terminal and M8 connector: IP65)					
* Based on IEC60520								

Based on IEC60529

Note) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

#### **Solenoid Specifications**

Electrical entry			Grommet (G), (H) L plug connector (L) M plug connector (M)	DIN terminal (D), (Y) M8 connector (W)			
			G, H, L, M, W	D, Y			
Coil rated		DC	24, 12, 6, 5, 3	24, 12			
voltage (V)		AC 50/60 Hz		200, 220			
Allowable voltage	fluct	uation	±10% of rate				
Power	DC	Standard	0.35 (With indicator light: 0.4 DIN	terminal with indicator light: 0.45)			
consumption (W)	ьс	With power saving circuit	0.1 (With in	dicator light only)			
		100 V	0.78 (With indicator light: 0.81)	0.78 (With indicator light: 0.87)			
		110 V	0.86 (With indicator light: 0.89)				
Apparent power		[115 V]	[0.94 (With indicator light: 0.97)]	[0.94 (With indicator light: 1.07)]			
(VA) *	AC	200 V	1.18 (With indicator light: 1.22)	1.15 (With indicator light: 1.30)			
		220 V	1.30 (With indicator light: 1.34)	1.27 (With indicator light: 1.46)			
		[230 V]	[1.42 (With indicator light: 1.46)]	[1.39 (With indicator light: 1.60)]			
Surge voltage sup	pres	sor	Diode (Varistor is for DIN terminal and Non-polar type.)				
Indicator light			LED (AC of DIN connector is neon light.)				
<ul> <li>In common between</li> </ul>	110	VAC and 115 VAC,	and between 220 VAC and 230	VAC.			

- For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.
- S, Z and T type (with power saving circuit) should be used within the following allowable voltage fluctuation
- range due to a voltage drop caused by the internal circuit. S and Z type: 24 VDC: -7% to +10%

12 VDC: -4% to +10% T type: 24 VDC: -8% to +10% 12 VDC: -6% to +10%

\* DIN terminal and M8 connector with power saving circuit are not available.

SJ

SYJ SZ

۷F

VP4

S0700

VO

VQ4 VQ5

VQC

VOC4

VOZ

SO VFS

**VFR** 

#### Flow Characteristics/Weight

#### Series SY3000

	т.	Type of			Flow	charact	eristics N	ote 1)		Weight (g) Note 2)		
Valve model	actuation		Port size	1 → 4	I/2 (P →	$\rightarrow$ A/B) 4/2 $\rightarrow$ 5/3 (A/B $\rightarrow$		EA/EB) Grommet		L plug connector,	W	
	uoi	actuation		C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	Groninic	M plug connector	M8 connector
	2	Single		1.0	0.30	0.24		0.00	0.00	84 (50)	85 (53)	89 (57)
	position	Double			0.30	0.24	1.1	0.30	0.26	102 (68)	107 (73)	115 (81)
		Closed center	1/8	0.77	0.28	0.18	0.85	0.30	0.19			
SY3□40-□-01	١. ا	Exhaust		0.73	0.31	0.18	1.1	0.26	0.24			
	3 position	center		0.73	0.31	0.16	[0.55]	[0.52]	[0.16]	104 (69)	109 (74)	117 (82)
		Pressure		1.2	0.24	0.29	0.89	0.47 0.24	0.24			
		center		[0.51]	[0.45]	[0.14]	0.69	0.47	0.24			

Note 1) [ ]: denotes the normal position. Note 2) ( ): denotes without sub-plate.

#### Series SY5000

	Tv	Type of			Flow	charact	eristics N	ote 1)		Weight (g) Note 2)			
Valve model	actuation		Port size	1 → 4	l/2 (P →	A/B)	4/2 → 5/3 (A/B → EA/EB)		Grommet	L plug connector,	DIM terminal	W	
	aoi	actuation		C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	Grommet	L plug connector, M plug connector DIN terminal	M8 connector	
	2	2 Single		2.4	0.41	0.64	2.8	0.29	0.66	121 (58)	123 (61)	154 (92)	127 (65)
	position	Double		2.4	0.41	0.04	2.0	0.29	0.00	139 (76)	144 (81)	186 (123)	152 (89)
		Closed center	1/4	1.8	0.47	0.50	1.8	0.40	0.47	144 (82)	150 (87) 192 (129		158 (95)
SY5□40-□-02	3 position	Exhaust center		1.4	0.55	0.44	3.0 [1.2]	0.33 [0.48]	0.72 [0.37]			192 (129)	
	position	Pressure center		3.3 [0.84]	0.36 [0.60]	0.85 [0.28]	1.8	0.40	0.48				

Note 1) [ ]: denotes the normal position. Note 2) ( ): denotes without sub-plate.

#### Series SY7000

	т.		Port		Flow	charact	eristics N	ote 1)			Weight	(g) Note 2)	
Valve model		Type of actuation		1 → 4	1/2 (P →	A/B)	4/2 → 5/	/3 (A/B →	EA/EB)	Grommet	L plug connector, DIAL to remine	DIM terminal	W
	ac			C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	Grommer	M plug connector	DIN terminal	W M8 connector
	2	Single		4.1	0.41	1.1	4.1	0.29	1.0	218 (89)	221 (92)	242 (113)	225 (96)
	position	Double		4.1	0.41	1.1	4.1	0.29	1.0	237 (108)	242 (113)	284 (155)	250 (121)
		Closed center		3.0	0.43	0.80	2.6	0.41	0.72				
SY7□40-□-02		Exhaust	1/4	2.6	0.42	0.71	4.7	0.35	1.1				
	3 position	center		2.0 0.42	0.42	0.71	[1.7]	[0.48]	[0.49]	239 (110)	245 (116)	287 (158)	253 (124)
		Pressure		5.3	0.39	1.3	2.2	0.49	0.63				
		center		[2.3]	[0.49]	[0.65]	2.2	0.49	0.03				
	2	Single		4.9	0.29	1.2	4.5	0.27	1.1	218 (89)	221 (92)	242 (113)	225 (96)
	position	Double		4.9	0.29	1.2	4.5	0.27	1.1	237 (108)	242 (113)	284 (155)	250 (121)
		Closed center		3.0	0.40	0.80	2.6	0.45	0.73				
SY7□40-□-03		Exhaust	3/8	2.6	0.42	0.71	4.8	0.35	1.1				
	3 position	center		2.0	0.42	0.71	[1.7]	[0.48]	[0.49]	239 (110)	245 (116)	287 (158)	253 (124)
	position	Pressure		5.3	0.31	1.3		0.45	0.66				
		center		[2.3]	[0.51]	[0.64]	2.3	2.3 0.45 0	0.00				

Note 1) [ ]: denotes the normal position. Note 2) ( ): denotes without sub-plate.

#### Series SY9000

	Type of		Port		Flov	v charac	teristics 1	Note1)			Weight	(g) Note 2)			
Valve model		actuation			l/2 (P →			/3 (A/B →		Grommet	L plug connector,	DIN terminal	W M8 connector		
	_ uo.			C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv		M plug connector	Bir to i i i i i i	M8 connector		
	2	Single		7.9	0.34	2.0	9.6	0.43	2.6	469(172)	472(175)	493(196)	476(179)		
	position	Double		1.5	0.54	2.0	3.0	0.43	2.0	488(191)	494(197)	535(239)	502(205)		
		Closed center		7.5	0.33	1.8	7.3	0.30	1.7						
SY9□40-□-03	١.	Exhaust	3/8	3/8	3/8	7.2	0.34	1.7	13	0.23	2.8				
	3 position	center		'.2	0.34	1.7	[4.0]	[0.41]	[0.95]	512(215)	518(221)	560(263)	526(229)		
		Pressure		12	0.26	2.8	6.7	0.40	1.9						
		center		[3.3]	[0.41]	[0.84]	6.7	0.40	1.9						
	2	Single			0.40	0.0	40	0.00	0.5	448 (172)	453 (175)	472	457(179)		
	position	Double		8.0	0.48	2.2	10	0.29	2.5	467 (191)	473 (197)	515	481(205)		
		Closed center		7.6	0.32	1.8	7.3	0.32	1.8						
SY9 40- 0-04		Exhaust	1/2	7.3	0.42	2.0	13	0.32	3.6						
pi	3 position	center		7.3	0.42	2.0	[4.7]	[0.54]	[1.5]	491 (215)	497 (221)	539	505(229)		
	Position	Pressure	ecure 12 0.33 3.3	7.4	0.33	1.9	1 ' '	` ′		,					
		center		[3.3]	[0.51]	[0.94]	7.4	0.33	1.9						

Note 1) [ ]: denotes the normal position. Note 2) ( ): denotes without sub-plate.




# Base Mounted Series SY3000/5000/7000/9000

#### Construction

#### **Series SY**


Symbol 2 position single

(A)4 2(B) (EA)5 1 3(EB) (P)



Symbol 2 position double

(A)4 2(B) (EA)5 1 3(EB) (P)



Symbol 3 position closed center

3 position exhaust cen
(A)4 2(B)
(EA)5 1 3(EB)
(P)


(A)4 2(B) (R1)5 1 3(R2) (P) (SY9000)

3 position pressure center

(A)4 2(B) (EA)5 1 3(EB) (P)



3 position closed center / exhaust center / pressure center



(This figure shows a closed center type.)

#### Component Parts

00.	iipoiiciit i ui to		
No.	Description	Material	Note
1	Body	Aluminum die-casted (SY3000: Zinc die-casted)	White
2	Adapter plate	Resin	White (SY9000: Gray)
3	End plate	Resin	White
4	Piston	Resin	_
5	Spool valve assembly	Aluminum, H-NBR	_

Renlacement Parts

Rep	Replacement Parts												
No.	Deser	intion		Part No.									
INO.	No. Description		SY3□40	SY5□40	SY7□40	SY9□40	Note						
6	Sub-plate Note)		SY3000-27-1®	SY5000-27-1®	1/4: SY7000-27-1 * 3/8: SY7000-27-2 *	3/8: SY9000-27-1 1/2: SY9000-27-2 ■	Aluminum die-casted						
7	Pilot valve	assembly		Refer to "How to Order Pilot Valve Assembly" on page 511.									
8	Gasket	Standard	SY3000-11-25	SY5000-11-15	SY7000-11-11	SY9000-11-2	H-NBB						
۰	CE-compliant		SY3000-11-25	SY5000-11-18	SY7000-11-14	SY9000-11-2	n-INDN						
	Reference screw size		SY3000-23-4	AC00077	AC00296	SY9000-18-2	For valve mounting						
-			Reference screw size		(M2 x 21)	(M3 x 26)	(M4 x 31)	(M3 x 42)	(Matt nickel plated)				

<sup>\*</sup> Thread type



Mounting screw tightening torques M2: 0.16 N·m

M3: 0.8 N·m M4: 1.4 N·m



SJ

SY

SV

SYJ SZ

۷F

VP4 80700 VO

VQ4 VQ5

VOC

VQC4


VQZ


SQ

**VFS** 

VFR

#### **How to Order Interface Regulator**





Note) ARBY is not CE-compliant.

Accessory

Series	Round head combination screw Reference screw size	Gasket
ARBY3000	SY3000-23-10	SX3000-57-4
	(M2 x 36)	
ARBY5000	AC00283 (M3 x 48.5)	SX5000-57-6
ARBY7000	AC00282	SX7000-57-5
	(M4 x 58)	

Caution

Mounting screw tightening torques


M2: 0.16 N·m M3: 0.8 N·m M4: 1.4 N·m

# Base Mounted Series SY3000/5000/7000/9000


2 position single

**Dimensions: Series SY3000** 


Grommet (G), (H): SY3140(R)-□ G □ □ -01 □




With interface regulator




L plug connector (L): SY3140(R)-□L□□-01□



M plug connector (M): SY3140(R)-□M□□-01□



M8 connector (WO): SY3140(R)-□WO□□-01□



Note) Refer to page 523 for dimensions of connector types.

311

[ ]: AC

SJ SY

SV

SYJ

SZ

۷F

VP4

SQ


VFS VFR




**Dimensions: Series SY3000** [ ]: AC




Grommet (G), (H): SY3240(R)-□H□□-01□




#### L plug connector (L): SY3240(R)-□L□□-01□



#### M plug connector (M): SY3240(R)-□M□□-01□



#### M8 connector (WO): SY3240(R)-□WO□□-01□




Note) Refer to page 523 for dimensions of connector types.


# Base Mounted Series SY3000/5000/7000/9000


**Dimensions: Series SY3000** 


[ ]: AC


3 position closed center / exhaust center / pressure center Grommet (G), (H): SY3 <sup>3</sup>/<sub>4</sub>40(R)-□ <sup>G</sup><sub>H</sub>□□-01□













50


42

L plug connector (L):



SY3<sup>3</sup>/<sub>4</sub>40(R)-□M□□-01□





Note) Refer to page 523 for dimensions of connector types.

**SMC** 

313

SJ

SY

SV

SYJ

SZ

۷F

VP4 S0700

VO

VQ4

V05 VOC

VQC4


VOZ

SO

VFS VFR

#### **Dimensions: Series SY5000**


[ ]: AC



L plug connector (L): SY5140(R)-□L□□-02□

M plug connector (M): SY5140(R)-□M□□-02□ DIN terminal (D, Y): SY5140(R)-□<sup>D</sup>□□-02□

M8 connector (WO): SY5140(R)-□WO□□-02□



Note) Refer to page 523 for dimensions of connector types.

# Base Mounted Series SY3000/5000/7000/9000

**Dimensions: Series SY5000** [ ]: AC 2 position double Grommet (G), (H): SY5240(R)-□ G□ -02□ 1/4 (A, B port) SJ SY SV (Light/surge voltage suppressor) 35.2 SYJ 17 17 2 x ø4.3 15.5 15.5 (For mounting) M5 x 0.8 (External pilot port) SZ Manual override ۷F VP4 M5 x 0.8 G: Approx. 300 62.8 (Pilot EXH port) H: Approx. 600 107.2 [111.6] S0700 <In the case of external (Lead wire length) pilot type> With interface regulator VO V04 VQ5 57. 73.6 [80.6] ผ VOC 18 18 8 VQC4 22 28 1/4 56 (P, EA, EB port) With plug VQZ 56 (59) (16.5)SQ L plug connector (L): M plug connector (M): DIN terminal (D, Y): M8 connector (WO): SY5240(R)-□♥□□-02□ VFS SY5240(R)-□L□□-02□ SY5240(R)-□M□□-02□ SY5240(R)-□WO□□-02□ Applicable cable O.D. ø3.5 to ø7 VFR Lead wire length 300 83.4 75.9 9 VQ7 50.6 [57.6] Approx. 64.6 Max. 35.2 49.5 55.1 M8 x 1 (Lead wire length) 37.6 61.7 [68.7] Approx. 300 Pg7 107.4 [111.8] 27 [131.4] 65.4 145.2 25.2 10.4 47 97.




9.5


Note) Refer to page 523 for dimensions of connector types.


# Dimensions: Series SY5000

[ ]: AC


3 position closed center / exhaust center / pressure center Grommet (G), (H): SY5  $\frac{4}{5}40(R)-\Box \frac{G}{1}\Box\Box$ -02 $\Box$ 








# 18 18 9



L plug connector (L): SY5<sup>3</sup>/<sub>4</sub>40(R)-□L□□-02□ M plug connector (M): SY5<sup>3</sup>/<sub>4</sub>40(R)-□M□□-02□ DIN terminal (D, Y): SY5<sup>3</sup>/<sub>4</sub>40(R)-□<sup>D</sup>/<sub>Y</sub>□□-02□ M8 connector (WO): SY5 <sup>3</sup>/<sub>5</sub>40(R)-□WO□□-02□



(P. EA, EB port)

# Base Mounted Series SY3000/5000/7000/9000

**Dimensions: Series SY7000** [ ]: AC 2 position single Grommet (G), (H): SY7140(R)-□G□□-03□ 3/8.1/4 (A, B port) SJ SY SV (Light/surge voltage suppressor) SYJ 43.1 61 10.4 21.5 2 x ø4.3 (For mounting) SZ ۷F ·8 8 働 VP4 21.5 21 6.4 G: Approx. 300 77.9 M5 x 0.8 M5 x 0.8 S0700 H: Approx. 600 100.1 [102.3] (Pilot EXH port) (External pilot port) <In the case of external (Lead wire length) With interface regulator pilot type> VO VQ4 VQ5 58.5 [65. [93.7] 83.2 VQC हु। हु 41.2 20.5 20.5 VQC4 26.5 3/8.1/4 (P. EA, EB port) VQZ With plug (17) 69 (73)SQ L plug connector (L): SY7140(R)- $\Box$ L $\Box$ - $^{02}_{03}$ M plug connector (M): SY7140(R)- $\square$ M $\square$ - $_{03}^{02}\square$ DIN terminal\_(D, Y): M8 connector (WO): SY7140(R)-\(\bigcap\)\(\bigcap\)\(\bigcap\)\(\bigcap\)\(\bigcap\)\(\bigcap\) SY7140(R)-□WÒ□□-02□ VFS VFR Lead wire length Applicable cable O.D. Approx. 300 ø3.5 to ø7 VQ7 85.5 58.5 [65.5] 74.2 59.1 43.1 63 45.5 (Lead wire length) M8 x 1 69.6 [76.6] Approx. 300 95.2 100.2 [102.4] 110 [112.2] 120 9. 101.7 60 79.2 8 4 11.5 9 13.5 9 13.5 11.5 26.5


Note) Refer to page 523 for dimensions of connector types.


#### **Dimensions: Series SY7000**

[ ]: AC

#### 2 position double

Grommet (G), (H): SY7240(R)-□ G□□-02□





### Base Mounted Series SY3000/5000/7000/9000

**Dimensions: Series SY7000** [ ]: AC 3 position closed center / exhaust center / pressure center Grommet (G), (H): SY7<sup>3</sup>/<sub>4</sub>40(R)-□<sup>G</sup><sub>H</sub>□□-<sup>02</sup>/<sub>03</sub>□ 3/8,1/4 (A, B port) SJ 13.5 SY SY (Light/surge voltage suppressor SV 43.1 2 x ø4.3 21.5 (For mounting) SYJ Manual override SZ ۷F 21 71.5 18.5 21.5 VP4 40.7 [42.9] **G:** Approx. 300 M5 x 0.8 M5 x 0.8 134.4 [138.8] H: Approx. 600 (External pilot port) (Pilot EXH port) S0700 <In the case of external (Lead wire length) pilot type> With interface regulator VO 92 58.5 V04 VQ5 20.5 20.5 3/8.1/4 VOC 69 (P. EA. EB port) 41.2 VQC4 26.5 VQZ (73)With plug (17) 69 SQ L plug connector (L): M plug connector (M): DIN terminal (D, Y): M8 connector (WO): **VFS** SY7<sup>3</sup>/<sub>4</sub>40(R)-□M□□-<sup>02</sup>/<sub>03</sub>□ SY7 40(R)- DD - 02 02 SY7<sup>3</sup>/<sub>4</sub>40(R)-\(\sum WO \subseteq \cdot \frac{02}{03} \subseteq SY7<sup>3</sup>/<sub>4</sub>40(R)-□L□□-<sup>02</sup>/<sub>03</sub>□ VFR Applicable cable O.D. Lead wire length Approx. 300 ø3.5 to ø7 85.5 VQ7 74.2 58.5 [65.5] 59.1 43.1 M8 x 1 (Lead wire length) 45.5 69.6 [76.6] Approx. 300 95.3 154.2 [158.6] 88.8 134.6 [139] 72.8 172.4 152.4 19.8 [52.8] 11.5 35.8 .8 [43] 13.5 13 핛 26.5 50.6 9.09 29 Note) Refer to page 523 for


dimensions of connector types.


### Series SY3000/5000/7000/9000


Dimensions: Series SY9000


2 position single


Grommet (G), (H): SY9140(R)-□ G□□- 03 □














### Base Mounted Series SY3000/5000/7000/9000

**Dimensions: Series SY9000** 

[ ]: AC

SJ SY

SV

SYJ

SZ

۷F

VP4

S0700


VO


VQ4

VQ5 VQC VQC4

VQZ

2 position double Grommet (G), (H): SY9240(R)-□<sup>G</sup><sub>H</sub>□□-<sup>03</sup><sub>04</sub>□







### Series SY3000/5000/7000/9000

#### **Dimensions: Series SY9000**

[ ]: AC


3 position closed center / exhaust center / pressure center






# 5 Port Solenoid Valve Body Ported Manifold Bar Stock Type/Individual Wiring Series SY3000/5000/7000

#### **How to Order Manifold**



#### **How to Order Manifold Assembly (Example)**




# Body Ported Series SY3000/5000/7000 IVE 20



How to Order Valve

Note) AC-type models that are CE-compliant have DIN terminals only.





**Electrical entry** 

24. 12 VDC/ 24, 12, 6, 5, 3 VDC/ 100, 110, 200, 24, 12, 6, 5, 3 VDC 100, 110, 200, 220 VAC 220 VAC **DIN** terminal Grommet | L plug connector | M plug connector M8 connector G: Lead wire L: With lead wire M: With lead wire (SY5000/7000 only) WO: Without (Length 300 mm) length 300 mm (Length 300 mm) connector cable D: With connector MN: Without lead wire H: Lead wire LN: Without lead wire DO: Without connector W□: With connector cable Note length 600 mm LO: Without connector MO: Without connector Y: With connector YO: Without connector

\* LN, MN type: with 2 sockets.

page 523.

DC

CF. mpliant AC

"Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C).

- For details, refer to page 519.
- \* For connector cable of M8 connector, refer to page 522.

- \* M8 thread conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.
- Refer to page 519 for the lead wire length of L and M plug connectors
- \* Refer to page 520 for the connector assembly with cover for L and M plug connectors. Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to

them separately, if necessary

#### Note) When placing an order for body ported solenoid valve as a single unit, mounting screw for manifold and gasket are not attached. Order

#### ■Gasket assembly part no.



**									
Series	Gasket assembly part no.								
SY3000	SY3000-GS-1								
SY5000	SY5000-GS-1								
SY7000	SY7000-GS-1								

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.





#### **Manifold Specifications**

Model		SS5Y3-20(-Q)	SS5Y5-20(-Q)	SS5Y7-20(-Q)					
	al re	SY3□20	SY5□20	SY7□20					
Applicable v		513⊔2U		S17⊔20					
Manifold ty	pe	Single base/B mount							
P (SUP)/R (	EXH)	Common SUP, Common EXH							
Valve static	ns	2 to 20 stations Note1)							
A, B port lo	cation	Valve							
	P, EA, EB port	1/8	1/4						
Port size A, B port		M5 x 0.8 C4(One-touch fitting for ø4) C6 (One-touch fitting for ø6)	1/8 C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)	1/4 C8 (One-touch fitting for ø8) C10 (One-touch fitting for ø10)					
Manifold basen: Stations	e weight W (g)	W = 13n + 24	W = 36n + 64	W = 43n + 35					

Note 1) For more than 10 stations (more than 5 stations in case of SS5Y7), supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

#### Flow Characteristics

	Port si	ze		Flow characteristics								
Model	1, 5, 3	4, 2	1 →	4/2 (P → A	VB)	4/2 → 5/3 (A/B → EA/EB)						
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv				
SS5Y3-20(-Q)	1/8	C6	0.72	0.29	0.18	0.80	0.36	0.21				
SS5Y5-20(-Q)	1/4	C8	1.9	0.28	0.48	2.2	0.20	0.53				
SS5Y7-20(-Q)	SS5Y7-20(-Q) 1/ <sub>4</sub> C10 3.6		3.6	0.31	0.93	3.6	0.27	0.88				

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

Note 2) Refer to "Manifold Option" on page 353.

# Body Ported Series SY3000/5000/7000 Type 20

20

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

VQ4

VQ5

VQC

VQC4

VQZ

SQ **VFS** VFR VQ7

20

9 82

46

0.5

SY3000: SS5Y3-20-Stations -[ ]: AC Grommet (G) One-touch fitting 4.75 (A, B port) Applicable tubing O.D Manual : ø4, ø5/32' : ø6, ø1/4" (P, EA, EB port) 30.7 97.3 [101.7] 23.5 23.5 22.2 16.5 [93.2] 6 8 2 9 88 16 46 12.5 4 x ø4.5 (Pitch) (For mounting) (M5 port) P = 10.5 M5 x 0.5 Approx. 300 (Lead wire length) (A, B port) Dimensions when mounting Dimensions when mounting (Station n) ----- (Station 1) individual EXH spacer individual SUP spacer (3.2)/ SUP port is at the end plate of (3.2)single solenoid. 3.2) (Light/surge voltage suppressor) SUP port C6:45.1 N7:48.9 EXH port 40 [47] C6:45.1 N7:48.9 M5 x 0.8 M5 x 0.8 C6:54.1 N7:57.9 (Both sides) [26] 33.6 49


0.5

L plug connector (L) M plug connector (M) M8 connector (WO) 117.1 [121.5] 97.5 [101.9] 108.6 [113] 89 [93.4] 106.8 44.5 [46.7] [56.5] 53, 54.3 60.1 [67.1] Approx. 300 (Lead wire length) Approx. 300 (Lead wire length) 53.5 33.6 49 [56] Note) Refer to page 523 for dimensions of connector types.

2

Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	40	50.5	61	71.5	82	92.5	103	113.5	124	134.5	145	155.5	166	176.5	187	197.5	208	218.5	229
L2	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5


# Series SY3000/5000/7000



Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	60	76	92	108	124	140	156	172	188	204	220	236	252	268	284	300	316	332	348
L2	40	56	72	88	104	120	136	152	168	184	200	216	232	248	264	280	296	312	328

# Body Ported Series SY3000/5000/7000 Type 20





**SMC** 


# <sub>1...</sub>23

## 5 Port Solenoid Valve Body Ported Manifold Stacking Type/Individual Wiring


# Series SY9000



#### **How to Order Manifold**



#### **How to Order Manifold Assembly (Example)**



CE-compliant

Q CE-compliant


Note) AC-type models that are CE-compliant have DIN terminals

Nil

How to Order Valve

Note) AC-type models that are CE-compliant have DIN terminals only





option. It is already built-in to the rectifier


					Ele	ectrical entry
			4, 12, 6, 5, 3 VDC 00, 110, 200, 220	24, 12 VDC/ 100, 110, 200, 220 VAC	24, 12, 6, 5, 3 VDC	
		Grommet	L plug connector	M plug connector	DIN terminal	M8 connector
		G: Lead wire length 300 mm H: Lead wire length 600 mm	L: With lead wire (Length 300 mm) LN: Without lead wire LO: Without connector	M: With lead wire (Length 300 mm) MN: Without lead wire MO: Without connector	D: With connector DO: Without connector Y: With connector YO: Without connector	WO: Without connector cable W□: With connector cable Note)
CE-	DC	•	•	•	•	•
compliant	AC	_	_	_	•	_

- \* LN, MN type: with 2 sockets.
- \* "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C). For details, refer to page 519
- \* For connector cable of M8 connector, refer to page 522.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details
- Refer to page 519 for the lead wire length of L and M plug connectors.
- \* Refer to page 520 for the connector assembly with cover for L and M plug connectors.

Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523.

Note) When placing an order for body ported solenoid valve as a single unit, mounting screw for manifold and gasket are not attached. Order them separately, if necessary.

#### ■Gasket assembly part no.



Series	Gasket assembly part no.
SY9000	SY9000-GS-1

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.



**VQ7** 



#### **Manifold Specifications**

Model		SS5Y9-23(-Q)					
Applicable	valve	SY9□20					
Manifold to	ype	Stacking type					
P (SUP)/R (EXH)		Common SUP, Common EXH					
Valve stati	ons	2 to 20 stations Note1)					
A, B port location		Valve					
. , _ <b> </b>	P, EA, EB port	3/8					
		1/4					
Port size	A, B port	3/8 C8 (One-touch fitting for ø8)					
	· · · · ·	C10 (One-touch fitting for ø10)					
		C12 (One-touch fitting for ø12)					
Manifold bas	se weight W (g)	W = 66n + 246					

Note 1) For more than 10 stations, supply pressure to P port on both sides and exhaust from EA/EB port on both sides.


#### **Flow Characteristics**

	Port si	ze		Flow characteristics								
Model	1, 5, 3	4, 2	1 →	$4/2 (P \rightarrow A)$	VB)	4/2 → 5/3 (A/B → EA/EB)						
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv				
SS5Y9-23(-Q)	3/8	C12	6.3	0.20	1.5	8.2	0.28	1.9				

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

Note 2) Refer to "Manifold Option" on page 353.

# Body Ported Series SY9000 Type 23



Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	123	148	173	198	223	248	273	298	323	335.5	360.5	385.5	410.5	435.5	460.5	485.5	510.5	535.5	560.5
L2	112.5	137.5	162.5	187.5	212.5	237.5	262.5	287.5	312.5	325	350	375	400	425	450	475	500	525	550
L3	96	120	144	168	192	216	240	264	288	312	336	360	384	408	432	456	480	504	528
L4	13.5	14	14.5	15	15.5	16	16.5	17	17.5	12	12.5	13	13.5	14	14.5	15	15.5	16	16.5
L5	66	90	114	138	162	186	210	234	258	282	306	330	354	378	402	426	450	474	498

Note) In the case of direct mounting without DIN rail, total width of manifold is L3.



# Type **20P**


# 5 Port Solenoid Valve Body Ported Manifold Bar Stock Type/Flat Ribbon Cable


# Series SY3000/5000/7000

#### **How to Order Manifold**



#### How to Order Manifold Assembly (Example)





Note) Please indicate the connector assembly part no. below that connects the valve and the manifold.

#### **Connector Assembly**

#### For 12, 24 VDC

Specifications	For SY3000	For SY5000/7000
For single solenoid	SY3000-37-3A	SY5000-37-3A
Double solenoid, 3 position type	SY3000-37-4A	SY5000-37-4A
Single with spacer assembly	SY5000-37-3A	SY5000-37-5A
Double, 3 position with spacer assembly	SY3000-37-6A	SY5000-37-6A

Note) Spacer assembly indicates Individual SUP/EXH

#### For 100 VAC

Specifications	For SY3000	For SY5000/7000
For single solenoid	SY3000-37-32A	SY5000-37-15A
Double solenoid, 3 position type	SY3000-37-33A	SY5000-37-16A
Single with spacer assembly	SY5000-37-15A	SY5000-37-17A
Double, 3 position with spacer assembly	SY3000-37-34A	SY5000-37-18A

#### For 100 VAC (115 VAC)

Specifications	For SY3000	For SY5000/7000
For single solenoid	SY3000-37-35A	SY5000-37-19A
Double solenoid, 3 position type	SY3000-37-36A	SY5000-37-20A
Single with spacer assembly	SY5000-37-19A	SY5000-37-21A
Double, 3 position with spacer assembly	SY3000-37-37A	SY5000-37-22A

#### **∧**Caution

• For non-polar (U) valves, the electrical DC connections can be used with either positive and negative COM. For type (Z), only use with positive COM as the valve does not operate correctly when used with negative COM.

# Body Ported Series SY3000/5000/7000 1120



How to Order Valve

Nil


Non-locking push type

Push-turn locking slotted type

Push-turn locking lever type

Note) CE-compliant: For DC only.





C8 One-touch fitting for ø8

C8 One-touch fitting for ø8

C10 One-touch fitting for ø10

SY7000

"U" and "Z" types are for DC specifications and "Z" type is for AC specifications. "Z" for DC is positive common specifications only. For the other combination, please contact SMC.

SY

LYS

SZ ۷F

VP4

S0700

VO V04

V05

VQC

VQC4 VQZ

SO VFS

**VFR VQ7** 

■Gasket assembly part no.


if necessary.

valve as a single unit, mounting screw for manifold

and gasket are not attached. Order them separately.

assembly part no. from those stated on page 334.

Note) Since the electrical entry is "LO", select a connector



Series	Gasket assembly part no.
SY3000	SY3000-GS-1
SY5000	SY5000-GS-1
SY7000	SY7000-GS-1

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.

 Multiple valve wiring is simplified through the use of the flat cable connector

#### Clean appearance

In the case of a flat ribbon cable type, each valve is wired on the print board of manifold base to allow the external wiring to be piped all together with 26 pins MIL connector.



#### **Manifold Specifications**

Model		SS5Y3-20P(-Q)	SS5Y5-20P(-Q)	SS5Y7-20P(-Q)		
Applicable v	valve	SY3□20	SY7□20			
Manifold ty	/pe		Single base/B mount			
P (SUP)/R (	(EXH)	Co	mmon SUP, Common E.	XH		
Valve static	ons	4 to 12 stations(1)	3 to 12 sta	ations Note 1)		
A, B port lo	ocation		Valve			
	P, EA, EB port	1/8	1/4	1/4		
Port size	A, B port	M5 x 0.8, C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6)	1/8 C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)	1/4 C8 (One-touch fitting for Ø8) C10 (One-touch fitting for Ø10)		
Manifold bas n: Stations	se weight W (g)	W = 19n + 45	W = 43n + 77	W = 51n + 81		
Applicable flat ribbon cable connector		Flat ribbon cable connector, Socket: 26 pins MIL type with strain relief, Conforming to MIL-C-83503				
Internal wir	ring	In common between +COM and -COM (Z type: +COM only).				
Rated volta	d voltage Note 4) 12, 24 VDC 100, 110 VAC					


Note 1) For more than 10 stations (more than 5 stations in case of SS5Y7), supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

#### Flow Characteristics

	Port size		Flow characteristics						
Model	1, 5, 3	4, 2	1 →	4/2 (P → A	$P \rightarrow A/B$ ) 4/2 $\rightarrow$ 5/3 (			$(A/B \rightarrow EA/EB)$	
	(P, EA, EB)	(A, B)	C [dm3/(s-bar)]	b	Cv	C [dm3/(s-bar)]	b	Cv	
SS5Y3-20P	1/8	C6	0.72	0.29	0.18	0.80	0.36	0.21	
SS5Y5-20P	1/4	C8	1.9	0.28	0.48	2.2	0.20	0.53	
SS5Y7-20P	1/4	C10	3.6	0.31	0.93	3.6	0.27	0.88	

Note) The value is for manifold base with 5 stations and individually operated 2 position type.


#### **Internal Wiring of Manifold**





 For non-polar (U) valves, the electrical DC connections can be used with either positive and negative COM. For type (Z), only use with positive COM as the valve does not operate correctly when used with negative COM.  For more than 10 stations, both poles of the common should be wired.
 For single solenoid, connect to the solenoid A side

 The maximum number of stations that can be accommodated is 12. For more stations, please contact SMC.




Note 2) The withstand voltage specification for the wiring unit section is JIS C 0704, Grade 1 or its equivalent. Note 3) Refer to "Manifold Option" on page 353.


Note 4) CE-compliant: For DC only.

# Body Ported Series SY3000/5000/7000

SY3000: SS5Y3-20P-Stations

[ ]: AC





Stations n	4	5	6	7	8	9	10	11	12
L1	72.5	85	97.5	110	122.5	135	147.5	160	172.5
L2	64.5	77	89.5	102	114.5	127	139.5	152	164.5

SJ

SY

SV SYJ

SZ

۷F

VP4

S0700 VO

VQ4


VQ5 vqc

VQC4

VQZ SQ

VFS

VFR VQ7 SY5000: SS5Y5-20P-Stations




Stations n	3	4	5	6	7	8	9	10	11	12
L1	77	94.5	112	129.5	147	164.5	182	199.5	217	234.5
12	67	84.5	102	1105	137	1545	172	180.5	207	224 5

# Body Ported Series SY3000/5000/7000 20P



SY7000: SS5Y7-20P-Stations [ ]: AC



Stations n	3	4	5	6	7	8	9	10	11	12
L1	88	108.5	129	149.5	170	190.5	211	231.5	252	272.5
12	68	88.5	100	120.5	150	170.5	101	211 5	232	252.5

SJ

SY

SV

SYJ

SZ

۷F VP4

S0700

VQ

VQ4

VQ5 vqc

VQC4

VQZ

SQ

VFS


VFR VQ7

## 5 Port Solenoid Valve Body Ported Manifold Stacking Type/Flat Ribbon Cable


# Series SY9000




#### **How to Order Manifold**



#### How to Order Manifold Assembly (Example)



Note) Please indicate the connector assembly part no. (page 341) that connects the valve and the manifold



#### Multiple valve wiring is simplified through the use of the flat cable connector.

#### Clean appearance

In the case of a flat ribbon cable type, each valve is wired on the print board of manifold base to allow the external wiring to be piped all together with 26 pins MIL connector.



#### **Connector Assembly**

#### For 12, 24 VDC

,	
Specifications	For SY9000
For single solenoid	SY9000-37-1A
Double solenoid 3 position	SY9000-37-2A
Single with spacer assembly	SY9000-37-3A
Double, 3 position with spacer assembly	SY9000-37-4A

#### For 100 VAC

Specifications	For SY9000
For single solenoid	SY9000-37-1B
Double solenoid 3 position	SY9000-37-2B
Single with spacer assembly	SY9000-37-3B
Double, 3 position with spacer assembly	SY9000-37-4B

#### For 110 VAC (115 VAC)

Specifications	For SY9000
For single solenoid	SY9000-37-1C
Double solenoid 3 position	SY9000-37-2C
Single with spacer assembly	SY9000-37-3C
Double, 3 position with spacer assembly	SY9000-37-4C

Note) Spacer assembly indicates Individual SUP/EXH.

#### **.** Caution

 For non-polar (U) valves, the electrical DC connections can be used with either positive and negative COM. For type (Z), only use with positive COM as the valve does not operate correctly when used with negative COM.

#### **Manifold Specifications**

Model		SS5Y9-23P(-Q)			
Applicable valve		SY9□20			
Manifold typ	е	Stacking type			
P (SUP)/R (	EXH)	Common SUP, Common EXH			
Valve stations		4 to 12 stations Note1)			
A, B port location		Valve			
	P, EA, EB port	3/8			
		1/4			
Port size		3/8			
1 011 3120	A, B port	C8 (One-touch fitting for ø8)			
		C10 (One-touch fitting for ø10)			
		C12 (One-touch fitting for ø12)			
Manifold base	e weight W (g)	W = 73n + 259			
n: Stations		VV = 7311 + 239			
Applicable flat ribb	on cable connector	Flat ribbon cable connector, Socket: 26 pins MIL with strain relief, Conforming to MIL-C-83503			
Internal wir	ing	In common between +COM and -COM (Z type: +COM only)			
Rated volta	ge Note4)	12, 24 VDC, 100, 110 VAC			

Note 1) For more than 10 stations, supply pressure to P port on both sides and exhaust from EA/EB port on both sides. Note 2) The withstand voltage specification for the wiring unit section is JIS C 0704, Grade 1 or its equivalent. Note 3) Refer to "Manifold Option" on page 35:


Note 4) CE-compliant: For DC only.

#### Flow Characteristics

	Port si	ze		Flow characteristics					
Model	1, 5, 3	4, 2	1 → 4/2 (P → A/B)			4/2 → 5/3 (A/B → EA/EB)			
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	
SS5Y9-23P(-Q)	3/8	C12	6.3	0.20	1.5	8.2	0.28	1.9	

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

#### **Internal Wiring of Manifold**




- . For more than 10 stations, both poles of the common should be wired.
- For single solenoid, connect to the solenoid A side.

connector, as shown in the reference, means a correlation of 1, 2, 3,...,26 from the triangle mark side on

The maximum number of stations that can be accommodated is 12. For more stations, please contact SMC.

Reference figure



the flat ribbon cable of connector.

SMC

SJ

01

SV

SYJ

SZ

VP4

S0700

VQ

VQ4

VQ5

VQC

VQC4

VQZ

SQ VFS


VFR


VQ7



#### SY9000: SS5Y9-23P-Stations -(D)

[ ]: AC






Stations n	4 stations	5	6	7	8	9	10	11	12 stations
L1	173	198	223	248	273	298	323	335.5	360.5
L2	162.5	187.5	212.5	237.5	262.5	287.5	312.5	325	350
L3	144	168	192	216	240	264	288	312	336
L4	14.5	15	15.5	16	16.5	17	17.5	12	12.5
L5	114	138	162	186	210	234	258	282	306

Note) In the case of direct mounting without DIN rail, total width of manifold is L3.


# **EX510 Gateway-type Serial Transmission System Body Ported Manifold/Integrated Base**

# Series SY3000/5000/7000

#### **How to Order Manifold**



#### How to Order Manifold Assembly (Example)



assembly is shipped with the valves (including blanking plates) and connector assembly mounted on it, as the standard specification. Be sure to specify the part

nos. of the solenoid valves to be mounted

- . SS5Y3 can be set from 4 stations.
- . The number of the blanking plate assembly is also included.
- Note 1) Double wiring: Use of a single solenoid will result in an unu control signal. If this is not desired, order with a specified
- Note 2) Specified layout: Indicate wiring specifications on the manifold specification sheet. (Note that double and 3 position valves cannot be used where single solenoid wiring has been specified.)

# Body Ported Manifold Series SY3000/5000/7000 Type 20SA



#### **How to Order Valves**



SJ

SYJ

SZ

۷F

VP4

S0700

VO

V04

V05

VQC

VOC4


VOZ

SO

VFS

**VFR** 

**VQ7** 



Manual override Non-locking push type

Push-turn locking

Push-turn locking

slotted type

lever type

Nil


ם

Ε

0	don many (mon oize)	
N3	One-touch fitting for ø5/32"	SY3000
N7	One-touch fitting for ø1/4"	313000
N3	One-touch fitting for ø5/32"	
N7	One-touch fitting for ø1/4"	SY5000
N9	One-touch fitting for ø5/16"	
N9	One-touch fitting for ø5/16"	SY7000
N11	One-touch fitting for ø3/8"	317000

Note) When placing an order for body ported solenoid valve as a single unit, mounting screw for manifold and gasket are not attached. Order them separately, if necessary.

#### ■Gasket assembly part no.





Series	Gasket assembly part no.
SY3000	SY3000-GS-1
SY5000	SY5000-GS-1
SY7000	SY7000-GS-1

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.


# 20SA Series SY3000/5000/7000

SY3000: SS5Y3-20SA - Stations -





(Station n) - - - - - (Station 1)





Statio	ns n 4 stations	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	72.5	85	97.5	110	122.5	135	147.5	160	172.5	185	197.5	210	222.5
L2	64.5	77	89.5	102	114.5	127	139.5	152	164.5	177	189.5	202	214.5

346

# Body Ported Manifold *Series* **SY3000/5000/7000** 100 **Series SY3000/5000/7000**

SY5000: SS5Y5-20SA - Stations -





Stations n	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	77	94.5	112	129.5	147	164.5	182	199.5	217	234.5	252	269.5	287	304.5
L2	67	84.5	102	119.5	137	154.5	172	189.5	207	224.5	242	259.5	277	294.5

**SMC** 

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

VQ4 VQ5

voc

VQC4

VQZ


SQ


VFS

VFR VQ7

# 20SA Series SY3000/5000/7000

SY7000: SS5Y7-20SA - Stations -





Sta	ations n	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
	L1	88	108.5	129	149.5	170	190.5	211	231.5	252	272.5	293	313.5	334	354.5
	L2	68	88.5	109	129.5	150	170.5	191	211.5	232	252.5	273	293.5	314	334.5

348


# Type 23SA

## EX510 Gateway-type Serial Transmission System Body Ported Manifold/Stacking Type


# Series SY9000



#### **How to Order Manifold**



#### **How to Order Manifold Assembly (Example)**



#### SI unit part no.

Symbol	SI unit specifications	SI unit part no.	Page
Nil	NPN output (+COM.)	EX510-S001	P.2143
N	PNP output (-COM.)	EX510-S101	F.2143

Refer to page 2124 and the Operation Manual for the details of EX510 Gateway-type Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

nos. of the solenoid valves to be mounted.



#### **How to Order Valves**



SJ

SYJ

SZ

۷F

VP4

S0700

VO

V04

V05

VOC


VOC4

VOZ SO

VFS

VFR

**VQ7** 



Push-turn locking

Push-turn locking

slotted type


lever type

D

Ε

Note) When placing an order for body ported solenoid valve as a single unit, mounting screw for manifold and gasket are not attached. Order them separately,

#### ■Gasket assembly part no.




Series	Gasket assembly part no.						
SY9000	SY9000-GS-1						

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.



SY9000: SS5Y9-23SA - Stations - (-D)



Stations n	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	148	173	198	223	248	273	298	323	335.5	360.5	385.5	410.5	435.5	460.5
L2	137.5	162.5	187.5	212.5	237.5	262.5	287.5	312.5	325	350	375	400	425	450
L3	120	144	168	192	216	240	264	288	312	336	360	384	408	432
L4	14	14.5	15	15.5	16	16.5	17	17.5	12	12.5	13	13.5	14	14.5
L5	90	114	138	162	186	210	234	258	282	306	330	354	378	402

Note) In the case of direct mounting without DIN rail, total width of manifold is L3.

352





#### **Manifold Option**


#### ■ Type 20, 23, 20SA, 23SA Blanking plate assembly



•	Stariuaru>	
	Series	Assembly part no.
	SY3000	SY3000-26-9A
	SY5000	SY5000-26-20A
	SY7000	SY7000-26-22A
	SY9000	SY9000-26-1A

<ce-compliant></ce-compliant>	:CE-compliant>						
Series	Assembly part no.						
SY3000	SY3000-26-19A-Q						
SY5000	SY5000-26-1A-Q						
SY7000	SY7000-26-1A-Q						
SY9000	SY9000-26-1A						

#### ■ Individual SUP spacer assembly



Series	Assembly part no.	Port size	t
SY3000	SY3000-38-20A(-Q)	M5 x 0.8	10.5
SY5000	SY5000-38-1*A(-Q)	1/8	15
SY7000	SY7000-38-1*A(-Q)	1/4	18
SY9000	SY9000-38-1*A	1/4	20

Note) • The SUP port of SY3000/5000/7000 may be either on the lead wire side or on the end plate side. (An assembly is shipped under

the conditions shown in the figure.) . The end plate side is only available to SY9000.


#### ■ Type 20P, 23P Blanking plate assembly



	<3tanuaru>						
	Series	Assembly part no.					
	SY3000	SY3000-26-10A					
	SY5000	SY5000-26-21A					
	SY7000	SY7000-26-23A					
	SY9000	SY9000-26-3A					

•	<ce-compliant></ce-compliant>					
	Series	Assembly part no.				
	SY3000	SY3000-26-20A-Q				
	SY5000	SY5000-26-3A-Q				
	SY7000	SY7000-26-3A-Q				
	SY9000	SY9000-26-3A				

#### ■ Individual EXH spacer assembly



	\$4°		
Series	Assembly part no.	Port size	t
SY3000	SY3000-39-20A(-Q)	M5 x 0.8	10.5
SY5000	SY5000-39-1*A(-Q)	1/8	15
SY7000	SY7000-39-1*A(-Q)	1/4	18
SY9000	SY9000-39-1*A	1/4	20

Note) In case of 20P and 23P, for protection of the wiring unit section from drainage, piping at the EA port should be arranged so that it will not be directly exposed to exhaust from the valve

\* Thread type


NPTF

Nil Ro

F G

N NPT


#### ■ Gasket assembly part no.




Series	Gasket assembly part no.
SY3000	SY3000-GS-1
SY5000	SY5000-GS-1
SY7000	SY7000-GS-1
SY9000	SY9000-GS-1

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.

#### ■ Individual SUP spacer assembly + Individual EXH spacer assembly



(Double spacer)



#### ∕!\ Caution

#### Mounting screw tightening torques

M2: 0.16 N·m M3: 0.8 N·m M4: 1.4 N·m

#### /!\Warning

When mounting a valve or spacer on the manifold base or sub-plate, etc., those mounting directions are determined. If mounted in the wrong direction, the equipment to be connected may cause malfunction. Refer to external dimensions, and then mount it.

#### [ : Available X: Not available]

		1			
	Individual SUP +		Applicable manifold types		
Series	Individual EXH Assemble part no.	Port size	20	20P	
SY3000	SY3000-120-1A(-Q)	M5 x 0.8	•	×	
SY5000	SY5000-75-2*A(-Q)	1/8	•	×	
SY7000	SY7000-73-3*A(-Q)	1/4	•	×	

Note) The SUP spacer's port does not have an orientation. As for the EXH ports, adjust the symbol "5" to the pilot valve side. Also, please make sure to connect the individual ports to protect the wiring section of the pilot valve from drainage, etc.

The individual SUP spacer and EXH spacer can be mounted either on the upper side or lower side. (The above illustration shows the condition when the product is shipped out from a factory.)

SJ SY

SV

SYJ SZ

۷F

VP4 S0700

VO

VQ4

V05 VQC

VOC4

VOZ SO

VFS


**VFR VQ7** 




### Series SY3000/5000/7000/9000

#### **Manifold Option**

#### ■ Connector assembly For single solenoid (SY3000-37-81A-□-N)





Connector assembly order no. (Can be used for the manifold without a specified layout (8 stations or less))

miegrated type					
Model	Part no.	Connector mounting position			
	SY3000-37-81A-3-N	Single : For 1 to 4 stations			
SS5Y3-20SA	SY3000-37-81A-3-6	Double/3 position: For 1 to 4 stations			
33313-203A	SY3000-37-81A-2-N	Single : For 5 to 8 stations			
	SY3000-37-81A-2-4	Double/3 position: For 5 to 8 stations			
SS5Y5-20SA	SY3000-37-81A-3-N	Single : For 1 to 8 stations			
33313-203A	SY3000-37-81A-3-6	Double/3 position: For 1 to 8 stations			
	SY3000-37-81A-3-N	Single : For 1 to 4 stations			
SS5Y7-20SA	SY3000-37-81A-3-6	Double/3 position: For 1 to 4 stations			
33317-203A	SY3000-37-81A-4-N	Single : For 5 to 8 stations			
	SY3000-37-81A-4-7	Double/3 position: For 5 to 8 stations			

Note) The above is for the station addition or maintenance. When ordering a connector assembly separately, a number would not be printed on the connector.

#### ■ Connector assembly SY3000-37-80A-



#### ■ Housing (8 pcs./set) SY3000-44-3A



onnector assembly order no. (Can be used for the manifold with a specified layout)

Connector assembly order no. (Can be used for the manifold with a specified layout)							
Model	Part no. Connector mounting position						
	SY3000-37-80A-3	For A side	For 1 to 8 stations				
CCEVA AACA	SY3000-37-80A-6	For B side	FOR 1 to 8 Stations				
SS5Y3-20SA	SY3000-37-80A-4	For A side	For 9 to 16 stations				
	SY3000-37-80A-7	For B side	For 9 to 16 stations				
	SY3000-37-80A-3	For A side	For 4 to 0 stations				
CCEVE OOCA	SY3000-37-80A-6	For B side	For 1 to 8 stations				
SS5Y5-20SA	SY3000-37-80A-7	For A side	Fan O to 40 ataliana				
	SY3000-37-80A-9	For B side	For 9 to 16 stations				
	SY3000-37-80A-4	For A side	For 1 to 8 stations				
SS5Y7-20SA	SY3000-37-80A-7	For B side	FOR 1 to 8 Stations				
55517-205A	SY3000-37-80A-8	For A side	Fan O to 40 ataliana				
	SY3000-37-80A-11	For B side	For 9 to 16 stations				
	SY3000-37-80A-6	For A side	For the Ortokions				
	SY3000-37-80A-11	For B side	For 1 to 8 stations				
00570 0004	SY3000-37-80A-9	For A side	Fan O to 40 atotions				
SS5Y9-23SA	SY3000-37-80A-14	For B side	For 9 to 12 stations				
	SY3000-37-80A-13	For A side	F 40 t 40 -tti				
	SY3000-37-80A-18	For B side	For 13 to 16 stations				

Note 1) The above is for station addition or maintenance. When ordering a connector assembly separately, a number will not be printed on

the connector.

Note 2) After inserting the connector assembly into the housing, be sure to confirm that the lead wire will not come off by lightly pulling the wire. Furthermore, do not reuse the lead wire after it has been inserted and removed.

Note 3) Wiring is set longer than the actual wiring distance.



## Body Ported Manifold Series SY9000 Type 20



#### **Manifold Option**

#### SUP blocking disk (For SY9000)

By installing a SUP blocking disk in the pressure supply passage of a manifold valve, it is possible to supply two or more different high and low pressures to one manifold.



o.
31-2A

#### ■ EXH blocking disk (For SY9000)

By installing an EXH blocking disk in the exhaust passage of a manifold valve, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to divide both exhausts.)



Series	Part no.
SY9000	SY9000-61-2A
010000	010000 01 21

#### Label for blocking disk (For SY9000)

The labels shown below are used on manifold stations containing SUP/EXH blocking disk(s) to show their location. (3 pcs. each)

#### VZ3000-123-1A

Label for SUP block disk Label for EXH block disk Label for SUP/EXH block disk








 When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block disk is mounted.

#### ■ DIN Rail Dimensions/Weight for SY9000

#### VZ1000-11-4-

#### Refer to L dimensions

\* Fill in □ with an appropriate no. listed on the table of DIN rail dimensions shown below.



No.	0	1	2	3	4	5	6	7	8	9
L Dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5
Weight (g)	24.8	28	31.1	34.3	37.4	40.6	43.8	46.9	50.1	53.3
No.	10	11	12	13	14	15	16	17	18	19
L Dimension	223	235.5	248	260.5	273	285.5	298	310.5	323	335.5
Weight (g)	56.4	59.6	62.7	65.9	69.1	72.2	75.4	78.6	81.7	84.9
No.	20	21	22	23	24	25	26	27	28	29
L Dimension	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5
Weight (g)	88	912	94.4	97.5	100.7	103.9	107	110 2	1133	1165

Note) · For DIN rail, refer to page 521.

Refer to L1 dimension on pages 314, 342 and 352 for lengths that correspond to the number of manifold stations.

#### Cable assembly (For 20P, 23P)

AXT100-FC26-to 3

#### Connector Assembly for Flat Ribbon Cables

Cable length (L)	Assembly part no.	Note
1.5 m	AXT100-FC26-1	
3 m	AXT100-FC26-2	Cable 26 core x 28 AWG
5 m	AXT100-FC26-3	

 For other commercial connectors, use a 26 pins with strain relief conforming to MIL-C-83503.

#### Connector manufacturers' example

- Hirose Electric Company
- Japan Aviation Electronics Industry, Ltd.
- Sumitomo 3M Limited
- · J.S.T. Mfg. Co., Ltd.
- Fujitsu Limited

#### ■ Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports. Purchasing order is available in units of 10 pieces.



#### **Dimensions**

Applicable fittings size ød	Model	Α	L	D
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12
12	KQ2P-12	24	44.5	14
1/8"	KQ2P-01	16	31.5	5
5/32"	KQ2P-03	16	32	6
1/4"	KQ2P-07	18	35	8.5
5/16"	KQ2P-09	20.5	39	10
3/8"	KQ2P-11	22	43	11.5

SJ

SY

SV

SYJ SZ

VF

VP4

S0700 VQ

VQ4 V05

VQC

VQC4

VQZ

SQ VFS

VFR

VQ7



#### How to Increase Manifold Bases (Series SY9000 only) Manifold case can be added at any location.

When a type 23 manifold base is added, tension bolts as well as manifold block assembly will be required. Order the tension bolt suitable for the stations after a station was increased (decreased), since the length of a tension bolt differs by the number of stations. (For changing the number of stations for a type 23P manifold, wingo unit for the stations and lead assembly will be required.)

Loosen the tension bolts 5 connecting the manifold base, and pull out both of 2 tension bolts.

(When equipped with a DIN rail, loosen one DIN rail holding screw on either U side or D side.)

Separate the blocks at the location where station expansion is desired.

3 Mount additional manifold block assembly.

Press block-to-block so that there's no gap. After connection, insert a tension bold for desired stations and then tighten it.

**^Caution** (Tightening torque: 2.9 N⋅m)

(When equipped with a DIN rail, be sure to tighten the DIN rail holding screws after tightening the tension bolts. Tightening torque: 1.4 N·m)


#### 

increase the manifold

- 1. Be sure to shut off the power and air supplies before disassembly. Furthermore, since air may remain inside the actuator, piping and manifold, confirm that the air is completely exhausted before performing any work.
- When disassembly and assembly are performed, air leakage may result if connections between blocks and tightening of the end block's holding screw, is inadequate.
- 3. By adding wiring unit assembly to type 23 manifold, it can be changed to type 23P manifold, too.

#### Body Ported Manifold Exploded View, 23/23P Common

As for body ported manifold, it is available only for Series SY9000 to disassemble or



# **Body Ported Manifold Cassette Type**

5 Port Solenoid Valve

Note) AC-type models that are CE-compliant have DIN




# Series SY3000/5000/7



manifold part no. Be sure to order solenoid valves for mounting at the same time while referring to the ordering example.






SUP/EXH block assembly mounting position

Symbol	Mounting position	Applicable stations
U	U side	2 to 10 stations
D	D side	≥ to 10 stations
В	Both sides	2 to 20 stations
M°	Special location	

<sup>\*</sup> For special specifications, indicate separately by the manifold specification sheet.

#### How to Order Manifold Assembly (Example)



## Body Ported Series SY3000/5000/7000 Type 60

### **Manifold Specifications**

Model		SS5Y3-60(-Q)	SS5Y5-60(-Q)	SS5Y7-60(-Q)		
Applicable valve		SY3□60	SY5□60	SY7□60		
Manifold type			Stacking type/DIN rail mounted			
P (SUP)/R (EXH) Common SUP/Common EXH						
Valve stations			2 to 20 stations Note 1)			
A, B port location		Valve				
	P, R port	C8 (One-touch fitting for ø8)	C10 (One-touch fitting for ø10)	C12 (One-touch fitting for ø12)		
Port size	A, B port	M5 x 0.8 C4(One-touch fitting for ø4) C6 (One-touch fitting for ø6)	1/8 C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)	1/4 C8 (One-touch fitting for Ø8) C10 (One-touch fitting for Ø10)		
Manifold base weight W (g) Note 2) (n: Number of SUP/EXH blocks, m: Weight of DIN rail)		W = 13n + m + 36	W = 41.2n + m + 77.6	W = 65.4n + m + 128.2		

Note 1) In cases such as those where many valves are operated simultaneously, use "-<u>station</u>B (SUP/EXH block on both sides)", applying pressure to the P ports on both sides and exhausting from the R ports on both sides.

Note 2) For DIN rail weight, refer to page 364.

#### Flow Characteristics

	Port size		Flow characteristics						
Model	1,5/3	4,2	1	$1 \rightarrow 4/2(P \rightarrow A/B)$			$4/2 \rightarrow 5/3(A/B \rightarrow R)$		
	(P,R)	(A,B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	
		M5	0.55	0.29	0.14	0.72	0.24	0.18	
SS5Y3-60(-Q)	C8	C4	0.57	0.24	0.14	0.71	0.20	0.17	
		C6	0.68	0.28	0.17	0.77	0.24	0.19	
		1/8	1.8	0.24	0.44	2.1	0.17	0.47	
SS5Y5-60(-Q)	C10	C6	1.5	0.30	0.37	2.0	0.16	0.46	
		C8	1.8	0.20	0.45	2.2	0.17	0.50	
		1/4	3.7	0.25	0.96	3.8	0.19	0.94	
SS5Y7-60(-Q)	C12	C8	3.2	0.26	0.81	4.0	0.18	0.96	
		C10	3.7	0.28	0.98	4.1	0.19	1.0	

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

SJ

SY

SV

SYJ

SZ

VF

VP4

S0700

VQ VQ4

VQ5

VQC

VQC4

....

VQZ


SQ VFS

VFR VQ7

#### How to Order Valve

Note) AC-type models that are CE-compliant have DIN terminals only.





For D	C
5	24 VDC
6	12 VDC
٧	6 VDC
S	5 VDC
R	3 VDC

#### For AC (50/60Hz)

1	100 VAC
2	200 VAC
3	110 VAC [115 VAC]

- 4 220 VAC [230 VAC] \* DC specifications of type D. Y. DO and YO is only available with 12 and 24 VDC
- \* D. Y. DO and YO only available for SY5000, SY7000
- \* For type W□, DC voltage is only available.
- Note) AC-type models that are CE-compliant have DIN terminals only.

Electrical entry								
24,	12, 6, 5, 3 VDC/1	00, 110, 200, 22	0 VAC	24, 12 VDC/ 100, 110, 200, 220 VAC	24, 12, 6, 5, 3 VDC			
Grommet	L plug connector	M plug	connector	DIN terminal	M8 connector			
G: Lead wire length 300 mm	L: With lead wire (Length 300 mm)	M: With lead wire (Length 300 mm	MN: Without lead wire	(SY5000, 7000) D, Y: With connector	WO: Without connector cable			
H: Lead wire length 600 mm	LN: Without lead wire	LO: Without connector	MO: Without connector	DO, YO: Connector	W□: With connector cable Note)			
•	•		•	•	•			
_	_		_	•	_			

\* LN, MN type: with 2 sockets.

CE. DO

- \* "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C). For details, refer to page 519,
- \* For connector cable of M8 connector, refer to page 522.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.
- \* Refer to page 519 for the lead wire length of L and M plug connectors.
- \* Refer to page 520 for the connector assembly with cover for L and M plug connectors.

Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523. Note) When ordering single unit of the cassette type solenoid valve, the bushing assembly is included.



## Body Ported Series SY3000/5000/7000 Type 60

### **Specifications**

Series		SY3000	SY5000	SY7000		
Fluid			Air			
Internal pilot	2 position single		0.15 to 0.7			
Operating pressure	2 position double		0.1 to 0.7			
range (MPa)	3 position	0.2 to 0.7				
Ambient and flu	uid temperature (°C)		Max. 50			
Max. operating	2 position double	10	5	5		
frequency (Hz)	3 position	3	3	3		
Manual override (Manual operation)		Non-locking push type, Push-turn locking slotted type, Push-turn locking lever type				
Pilot exhaus	t method	Common exhaust type for main and pilot valve				
Lubrication		Not required				
Mounting po	Mounting position		Unrestricted			
Impact/Vibratio	Impact/Vibration resistance Note)		150/30			
Enclosure		Dust proof (* DIN terminal, M8 connector: IP65)				

Note) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition.

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz.

Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values in the initial stage)

\* Based on IEC60529

#### **Solenoid Specifications**

Electrical entry			Grommet (G), (H) L plug connector (L) M plug connector (M) DIN terminal (D), (Y) M8 connector (W)		
			G, H, L, M, W	D, Y	
Coil rated	DO	2	24, 12, 6, 5, 3	24, 12	
voltage (V)	A	C <sup>50</sup> ∕60 Hz	100, 110,	200, 220	
Allowable voltage fluctuation			±10% of rat	ed voltage *	
Power consumption	DC	Standard	0.35 [With indicator light: 0.4 (DIN terminal with indicator light: 0.45)]		
(W)		With power saving circuit	0.1 (With indicator light only)		
	AC	100 V	0.78 (With indicator light: 0.81)	0.78 (With indicator light: 0.87)	
Apparent		110 V [115 V]	0.86 (With indicator light: 0.89) [0.94 (With indicator light: 0.97)]	0.86 (With indicator light: 0.97) [0.94 (With indicator light: 1.07)]	
(VA) *	AC	200 V	1.18 (With indicator light: 1.22)	1.15 (With indicator light: 1.30)	
		220 V [230 V]	1.30 (With indicator light: 1.34) [1.42 (With indicator light: 1.46)]	1.27 (With indicator light: 1.46) [1.39 (With indicator light: 1.60)]	
Surge voltage suppressor		Diode (Varistor is for DIN terminal and non-polar)			
Indicator light			LED (AC of DIN connector is neon light.)		

<sup>\*</sup> In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC

S and Z type: 24 VDC: -7% to +10% 12 VDC: -4% to +10% 12 VDC: -4% to +10% T type: 24 VDC: -8% to +10% 12 VDC: -6% to +10%

#### Response Time

Note) Based on dynamic performance test, JIS B 8375-1981. (Coil temperature: 20°C, at rated voltage)

#### SY3000

_ ,	Response time (ms) (at the pressure of 0.5 MPa)				
Type of actuation	Without surge voltage	With surge voltage suppressor			
	suppressor	S, Z type	R, U type		
2 position single	12 or less	15 or less	12 or less		
2 position double	10 or less	13 or less	10 or less		
3 position	15 or less	20 or less	16 or less		

#### SY5000

	Response time (ms) (at the pressure of 0.5 MPa)				
Type of actuation	Without surge voltage	With surge voltage suppressor			
actuation	suppressor	S, Z type	R, U type		
2 position single	19 or less	26 or less	19 or less		
2 position double	18 or less	22 or less	18 or less		
3 position	32 or less	38 or less	32 or less		

#### SY7000

<b>-</b> ,	Response time (ms) (at the pressure of 0.5 MPa)				
Type of actuation	Without light/surge	With light/surge voltage suppressor			
actuation	voltage suppressor	S, Z type	R, U type		
2 position single	31 or less	38 or less	33 or less		
2 position double	27 or less	30 or less	28 or less		
3 position	50 or less	56 or less	50 or less		

SJ

SY

SYJ

SZ

VP4

S0700 VO

V04 V05

VQC

VOC4

VOZ SO

VFS

VFR VQ7

<sup>\*</sup> For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.

<sup>\*</sup> S, Z and T type (with power saving circuit) should be used within the following allowable voltage fluctuation range due to a voltage drop caused by the internal circuit.

### Weight

#### Series SY3000

			Port size	Weight (g)		
Valve model	Тур	e of actuation	A, B	Gro- mmet	L/M plug connector	M8 Connector
	2	Single		49	51	55
	position	Double		70	73	81
SY3□60-□-M5		Closed center	M5 x 0.8			
	3 position	Exhaust center		73	76	84
	position	Pressure center				
	2 position	Single	C4 (One-touch)	62	61	65
		Double		80	83	91
SY3□60-□-C4		Closed center				
	3 position	Exhaust center (fitting for ø4) 8	82	86	94	
	pusition	Pressure center				
	2	Single		55	57	61
	position	Double	C6	76	79	87
SY3□60-□-C6		Closed center	/ One-touch \			
	3	Exhaust center	fitting for ø6	78	82	90
	position	Pressure center				

Note) [ ]: denotes normal position.

#### Series SY5000

	Type of actuation		Port size		Weigh	nt (g)	
Valve model			A, B	Gro- mmet	L/M plug connector	DIN terminal	M8 Conne- ctor
	2	Single		67	69	90	71
	position	Double		91	94	136	102
SY5□60-□-01		Closed center	1/8				
	position	Exhaust center		97	100	142	108
	p = =	Pressure center				1 1	
	2	Single	C4 (One-touch (fitting for ø4)	91	93	114	97
	position	Double		113	116	158	124
SY5□60-□-C4	3 position	Closed center					
		Exhaust center		119	122	164	130
		Pressure center					
	2	Single		86	88	109	92
	position	Double	C6	108	111	153	119
SY5□60-□-C6		Closed center	One-touch				
	3 position	Exhaust center	fitting for ø6	114	117	159	125
	position	Pressure center					
	2	Single		78	80	101	84
	position	Double	C8	100	103	145	111
SY5□60-□-C8	,	Closed center	/ One-touch \				
	3 position	Exhaust center	fitting for ø8	106	109	151	117
	Position	Pressure center					


#### Series SY7000

3eries 3 1 / 000									
			Port size		Weigh	eight (g)			
Valve model	Туре	e of actuation	A, B	Gro- mmet	L/M plug connector	DIN terminal	M8 Conne- ctor		
	2	Single		103	105	126	109		
	position	Double		125	128	170	136		
SY7□60-□-02		Closed center	1/4						
	3 position	Exhaust center		133	136	178	144		
	position	Pressure center							
	2 position 3 position	Single		138	139	160	143		
		Double	C8	160	163	205	171		
SY7□60-□-C8		Closed center	(One-touch)		171	213	179		
		Exhaust center	fitting for ø8	168					
		Pressure center							
	2	Single		123	125	146	129		
	position	Double	C10	145	149	191	157		
SY7□60-□-C10		Closed center	/ One-touch \						
	3 position	Exhaust center	fitting for ø10	153	157	199	165		
	position	Pressure center							

## Body Ported Series SY3000/5000/7000 Type 60

#### **Manifold Option**

#### ■ Individual SUP block assembly




Port size	Assembly part no.	
One-touch fitting for ø6	SY3000-54-2C(-Q)	0)/0000
One-touch fitting for ø8	SY3000-54-1C(-Q)	513000
One-touch fitting for ø10	SY5000-54-1C(-Q)	SY5000
One-touch fitting for ø12	SY7000-54-1C(-Q)	SY7000

#### One-touch fitting (Inch size)

Port size	Assembly part no.	Applicable series
One-touch fitting for ø5/16"	SY3000-54-3C(-Q)	SY3000
One-touch fitting for ø3/8"	SY5000-54-2C(-Q)	SY5000
One-touch fitting for ø3/8"	SY7000-54-3C(-Q)	SY7000

#### ■ Individual EXH block assembly




#### One-touch fitting (Inch size)


Port size	Assembly part no.	
One-touch fitting for ø5/16"		
	SY5000-55-2B(-Q)	
One-touch fitting for ø3/8"	SY7000-55-3B(-Q)	SY7000

Port size	Assembly part no.	
One-touch fitting for ø5/16"	SY3000-55-2B(-Q)	SY3000
	SY5000-55-2B(-Q)	
One-touch fitting for ø3/8"	SY7000-55-3B(-Q)	SY7000

### [When supplying the manifold with 2 different supply pressures.]

Specify arrangement of individual SUP block assembly on the manifold specification sheet. (When using SS5Y $\square$ -60- $\square$ D, blocking disk is assembled on D side.) <Manifold model no.: SS5Y<sub>5</sub>-60-□□ U<sub>D</sub>>






### [When a different supply pressure is required for only a middle valve.]

Specify arrangement of individual SUP block assembly and SUP blocking disk on the manifold specification sheet


(Applicable manifold model no.: SS5Y□-60-□□B)



#### [When 2 different EXH passages are required.]

Specify arrangement of individual EXH block assembly on the manifold specification sheet. (When using SS5Y = -60- = D, blocking disk is assembled on D side.)


<Manifold model no.: SS5Y<sub>5</sub>-60-□□ U<sub>D</sub>>



### [When a separate exhaust passage is needed on only a middle valve.]

Specify arrangement of individual EXH block assembly and EXH blocking disk on the manifold specification sheet.

(Applicable manifold model no.: SS5Y□-60-□□B)



SJ

SV

SYJ SZ

۷F

VP4 S0700

VO

V04

V05 VQC

VOC4

VQZ SQ

VFS VFR

**VQ7** 

## Type 60 Series SY3000/5000/7000

#### **Manifold Option**

#### ■ SUP blocking disk

By installing a SUP blocking disk in the pressure supply passage of a manifold valve, it is possible to supply two or more different high and low pressures to one manifold. (This is the same block disk used with the individual SUP block assembly.)



Series	Part no.
SY3000	SY3000-52-6A
SY5000	SY5000-52-4A
SY7000	SY7000-70-2A

#### ■ EXH blocking disk

By installing an EXH blocking disk in the exhaust passage of a manifold valve, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to separate both EXH passages. It is the same block disk that is used in the individual EXH block assembly.)



Series	Part no.
SY3000	SY3000-52-6A
SY5000	SY5000-52-4A
SY7000	SY7000-70-2A

#### ■ Label for block disk

The labels shown below are used on manifold stations containing SUP/EXH blocking disk(s) to show their location. (3 pcs. each)

#### VZ3000-123-1A


Label for SUP block disk Label for EXH block disk Label for SUP/EXH block disk








\* When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block disk is mounted.



#### ■ Silencer with One-touch fitting


The silencer plugs directly into the One-touch fittings of the manifold.



Series	Model	Effective area mm <sup>2</sup>	Α	В	С
SY3000 (for ø8)	AN15-C08	20	ø13	20	45
SY5000 (for ø10)	AN20-C10	30	ø16.5	30.5	57.5
SY7000 (for ø12)	AN30-C12	41	ø20	43.5	71.5

#### ■ Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports.



Dimensions


Applicable fittings size ød	Model	Α	L	D
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12
12	KQ2P-12	24	45.5	14
5/32"	KQ2P-03	16	32	6
1/4"	KQ2P-07	18	35	8.5
5/16"	KQ2P-09	20.5	39	10
3/8"	KQ2P-11	22	43	11.5

#### ■ DIN Rail Dimensions/Weight for SY3000/5000

#### VZ1000-11-1-

#### Refer to the L dimension tables

\* Enter a number from the DIN rail dimension table below in them.



No.	0	1	2	3	4	5	6	7	8	9	
L dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	
Weight (g)	17.6	19.9	22.1	24.4	26.6	28.9	31.1	33.4	35.6	37.9	
No.	10	11	12	13	14	15	16	17	18	19	
L dimension	223	235.5	248	260.5	273	285.5	298	310.5	323	335.5	
Weight (g)	40.1	42.4	44.6	46.9	49.1	51.4	53.6	55.9	58.1	60.4	
No.	20	21	22	23	24	25	26	27	28	29	
L dimension	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	


#### ■ DIN Rail Dimensions/Weight for SY7000

#### VZ1000-11-4-

#### Refer to the L dimension tables

Weight (g) 62.6 64.9 67.1 69.4 71.6 73.9 76.1 78.4 80.6

\* Enter a number from the DIN rail dimension table below in them.



No.	0	1	2	3	4	5	6	7	8	9
L dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5
Weight (g)	24.8	28	31.1	34.3	37.4	40.6	43.8	46.9	50.1	53.3
No.	10	11	12	13	14	15	16	17	18	19
L dimension	223	235.5	248	260.5	273	285.5	298	310.5	323	335.5
Weight (g)	56.4	59.6	62.7	65.9	69.1	72.2	75.4	78.6	81.7	84.9
NI-	00	01	00	00	0.4	0.5	-00	0.7	00	- 00

No.	20	21	22	23	24	25	26	27	28	29
L dimension	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5
Weight (g)	88	91.2	94.4	97.5	100.7	103.9	107	110.2	113.3	116.5

Note) For DIN rail mounting, refer to page 521.

#### Construction

#### Series SY

Symbol 2 position single (A)4 2(B) (EA)5 1 3(EB)

Symbol 2 position double (A)4 2(B) (EA)5 1 3(EB)


#### Symbol 3 position closed center (A)4 2(B)




3 position pressure center (A)4 2(B)




#### 2 position single





3 position closed center / exhaust center / pressure center



(This figure shows a closed center type.)

#### Component Parte

COII	iponent Parts	•		
No.	Description	Material	Note	
1	Body	Aluminum die-casted SY3000: Zinc die-casted	White	
2	Adapter plate	Resin	White	
3	End plate	Resin	White	
4	Piston	Resin	_	
5	Spool valve assembly	Aluminum/H-NBR	_	

#### Replacement Parts

No	. Description	No.					
6	Pilot valve assembly	Refer to "How to Order Pilot Valve Assembly" on page 51					
7	Port block assembly	Refer to "How to Order Port Block Assembly" on page 511.					
8	Bottom cover	SY3000-41-2A (with screw, gasket)					
0	assembly Note)	SY5000-41-2A (with screw, gasket)					

Note) There is no bottom cover assembly available for SY7000.



SJ

SY

SV SYJ SZ ۷F

VP4

S0700 VO

VQ4 VQ5 VQC VQC4 VQZ

SQ


**VFS** 

VFR


VQ7

Dimensions [ ]: AC

#### SS5Y3-60- Stations U








tations	2 stations	3	4	5	6	7	8	9	10 stations
L1	98	110.5	123	135.5	135.5	148	160.5	173	185.5
L2	87.5	100	112.5	125	125	137.5	150	162.5	175
L3	69.5	80	90.5	101	111.5	122	132.5	143	153.5
L4	14	15	16	17	12	13	14	15	16

S

#### SS5Y3-60-Stations D





		One-touch fitting	
		(P, R port)	
(3.2)	(Light/surge voltage suppressor)	Applicable tubing O.D.: Ø8, Ø	5/16"
(9)			
		/ ®	
ω <del>.</del>	N THE STATE OF THE	7	Stations
C6:43. N7:47.		10. 40 4	11
925	[√] ∞ Beloga eta eta eta eta eta eta eta eta eta et		
02			L2
	1.2.1		L3

Stations	2 stations	3	4	5	6	7	8	9	10 stations
L1	98	110.5	123	135.5	135.5	148	160.5	173	185.5
L2	87.5	100	112.5	125	125	137.5	150	162.5	175
L3	69.5	80	90.5	101	111.5	122	132.5	143	153.5
L4	14	15	16	17	12	13	14	15	16

[ ]: AC

SS5Y3-60- Stations B







D.D.: ø8, ø5/16"											
	Stations	2 stations	3	4	5	6	7	8	9	10 stations	
	L1	110.5	123	135.5	148	160.5	173	173	185.5	198	
	L2	100	112.5	125	137.5	150	162.5	162.5	175	187.5	
	L3	86	96.5	107	117.5	128	138.5	149	159.5	170	
	L4	12	13	14	15	16	17	12	13	14	


Stations	11 stations	12	13	14	15	16	17	18	19	20 stations
			_	_		_	_		-	
L1	210.5	223	235.5	235.5	248	260.5	273	285.5	298	310.5
L2	200	212.5	225	225	237.5	250	262.5	275	287.5	300
L3	180.5	191	201.5	212	222.5	233	243.5	254	264.5	275
L4	15	16	17	11.5	12.5	13.5	14.5	15.5	16.5	17.5

### M8 connector (WO)





M plug connector (M)



Note) Refer to page 523 for dimensions of connector types. SJ SY

SV

SYJ

SZ

۷F VP4

S0700

vo VQ4

VQ5

vqc

VQC4


VQZ

SQ VFS

VFR VQ7

**Dimensions** [ ]: AC


#### SS5Y5-60-Stations U



207 25.9	39.6 [46.6]
288 34.9	44
(DIN:30.1)	(1/8 port)

Stations	2 stations	3	4	5	6	7	8	9	10 stations
L1	123	135.5	148	160.5	185.5	198	210.5	235.5	248
L2	112.5	125	137.5	150	175	187.5	200	225	237.5
L3	88	104	120	136	152	168	184	200	216
L4	17.5	15.5	14	12	16.5	15	13	17.5	16

#### SS5Y5-60- Stations D



	One-touch fitting
பெ	(P, R port)
(Light/surge voltage suppressor)	Applicable tubing O.D.: ø10, ø3/8" û
	(3)
ol	h h \
	₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩ ₩
[4]	<u> </u>
	-

(Station n) ----- (Station 1)

Stations	2 stations	3	4	5	6	7	8	9	10 stations
L1	123	135.5	148	160.5	185.5	198	210.5	235.5	248
L2	112.5	125	137.5	150	175	187.5	200	225	237.5
L3	88	104	120	136	152	168	184	200	216
L4	17.5	15.5	14	12	16.5	15	13	17.5	16

SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

VQ4

VQ5

VQC

VQC4


VQZ


SQ

VFS

**VFR** 

VQ7






**ØSMC** 

[1(P), 3/5(R) port Applicable tubing O.D.: ø12, ø3/8"

**Dimensions** [ ]: AC

#### SS5Y7-60-Stations U (Lead wire length) Approx. 300 U side D side One-touch fitting [4(A), 2(B) port] Applicable tubing O.D.: Ø8, Ø5/16" Manual override ø10, ø3/8" DIN rail holding screw DIN rail 51.5 (DIN: 52.8) 38.5 134.4 [138.8] 89 121.4 [125.8] 39. 39 [62.9] ß 88 60.7 5.4) [4 (A), 2 (B) port] (Pitch) P = 19 42.5 [49.5] 29.5 (L4) 51 \_5 (1/4 port) (Rail mounting hole pitch: 12.5) (Station n)-----(Station 1) 2 (Light/surge voltage suppressor (5, (5.4)Stations 2 stations 3 6 10 stations 11 135.5 260.5 285 5 148 173 185.5 210.5 223 248 L2 125 137.5 162.5 175 200 212.5 237.5 250 275 28 49 68 L3 103 141 160 179 198 217 236 255 25. 16 13 16 12.5 15.5 12.5 15.5 12 15 One-touch fitting





Applicable tubing O.D.: Ø12, Ø3/8"



SJ

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

VQ4


VQ5

VQC VQC4

VQZ SQ VFS

**VFR** 

VQ7




5 49. 99 25.4 [1(P), 3/5(R) port] Applicable tubing O.D.: Ø12, Ø3/8"

SS5Y7-60- Stations B

Stations	2 stations	3	4	5	6	7	8 stations
L1	160.5	173	198	210.5	235.5	248	273
L2	150	162.5	187.5	200	225	237.5	262.5
L3	128	147	166	185	204	223	242
L4	16	13	16	12.5	15.5	12.5	15.5
Stations	9 stations	10	11	12	13	14	15 stations
L1	285.5	310.5	323	348	360.5	385.5	410.5
L2	275	300	312.5	337.5	350	375	400
L3	261	280	299	318	337	356	375
L4	12	15	12	15	11.5	14.5	17.5
Stations	16 stations	17	18	19	20 stations		

Stations	16 stations	17	18	19	20 stations	
L1	L1 423		460.5	485.5	498	
L2	412.5	437.5	450	475	487.5	
L3	394	413	432	451	470	
L4	14.5	17.5	14	17	14	

L plug connector (L) M plug connector (M) DIN terminal (D, Y) M8 connector (WO) 42.5 [49.5] 27.1 (Lead wire length) Approx. 300 53.6 [60.6] M8 x 1




**SMC** 

## Type 60 Series SY3000/5000/7000

### **DIN Rail Manifold Exploded View**

#### SY3000 Type 60




Replacement Parts

nep	iacement Parts							
No.	Description	Description Part no. Note						
1	Valve	SY3□60-□□-□(-Q)	☐ at the end of part number denotes A. B port size: M5, C4, C6, N3, N7. Includes bushing assembly (SY3000-52-5A) 3 pcs.					
2	SUP/EXH block assembly	SY3000-55-1A(-Q)	P, R port (1: One-touch fitting for ø8, 2: One-touch fitting for ø5/16") Includes bushing assembly (SY3000-52-5A) 3 pcs.					
3	End block assembly	SY3000-56-1A(-Q)	For D side (Bushing assembly: Not available for SY3000-52-5A)					
4	End block assembly	SY3000-56-1B(-Q)	For U side (Bushing assembly: Not available for SY3000-52-5A)					
5	Bushing assembly	SY3000-52-5A						
6	DIN rail	VZ1000-11-1-□	Refer to page 364.					

## Body Ported Series SY3000/5000/7000 Type 60





нер	lacement Parts							
No.	Description	Part no.	Note					
1	Valve	SY5□60-□□-□(-Q)	$\Box$ at the end of part number denotes A. B port size: 01, C4, C6, C8, N3, N7, N9. Includes bushing assembly (SY5000-52-3A) 3 pcs.					
2	SUP/EXH block assembly	SY5000-55-1A(-Q)	P, R port (1: One-touch fitting for ø10, 2: One-touch fitting for ø3/8") Includes bushing assembly (SY5000-52-3A) 3 pcs.					
3	End block assembly	SY5000-56-1A(-Q)	For D side (Bushing assembly: Not available for SY5000-52-3A)					
4	End block assembly	SY5000-56-1B(-Q)	For U side (Bushing assembly: Not available for SY5000-52-3A)					
5	Bushing assembly	SY5000-52-3A						
6	DIN rail	VZ1000-11-1-□	Refer to page 364.					

#### How to Add Additional Valves to the DIN Rail Valves can be added at any station on the rail.



#### **⚠** Caution


Tightening torque SY3000: 1 N·m SY5000: 1.4 N·m

(While lightly holding the blocks after fixing an end block on one side, tighten the other end block for better sealing after no gap between valves is confirmed.)

- . Bushing assembly must be seated properly to each valve block in order to prevent air leaks from occurring.
- Refer to the fig. 2 when dismounting the valve from the DIN rail.

Fig. 1 Manifold mounting procedure

Fig. 2 Manifold dismounting procedure



While pressing the bottom of the valve onto the lip of the DIN rail, pull side B upwards and dismount from the rail.

⚠ Caution When clamping screw ⓐ of the end block is not sufficiently tightened during reassembly, air leakage may result. Before supplying air, check that there are no gaps between valves and that the end block is firmly secured to the DIN rain in order to ensure air supply without leakage.



373

SJ

SYJ

SZ

۷F

VP4

S0700 VO

V04

V05 VQC

VOC4

VOZ


SO

VFS

VFR **VQ7** 

#### **DIN Rail Manifold Exploded View**

#### SY7000



кер	lacement Parts		<b>▼</b> <u>U</u>
No.	Description	Part no.	Note
1	Valve	SY7□60-□□-□(-Q)	□ at the end of part number denotes A. B port size: 02, C8, C10, N9, N11. Includes bushing assembly (SY7000-70-1A) 3 pcs.
2	SUP/EXH block assembly	SY7000-75-1A(-Q)	P,R port size (1: ø12 One-touch fitting, 3: 3/8"One-touch fitting) Includes bushing assembley (SY7000-70-1A) 3pcs.
3	End block assembly	SY7000-56-1A(-Q)	In common for D side and U side (Bushing assembly: Not available for SY7000-70-1A.)
4	Bushing assembly	SY7000-70-1A	
5	DIN rail	VZ1000-11-4-□	Refer to page 364.

#### How to Add Additional Valves to the DIN Rail Valves can be added at any station on the rail.

- 1 Loosen the rail holding screw (a) at both of 2 locations which holds the manifold base either in the U side or D side. When removing the end block assembly from the DIN rail, loosen the
- holding screws for DIN rail at first, then slide it to the edge of the rail. 2 Separate the valves at the point where more valves are to be
- added. 3 Mount the additional valves on the DIN rail as shown in Fig. 1.
- 4 Connect them together while pressing the block assemblies toward each other, and tighten the 2 holding screws (a) for DIN rail alternately (2 to 3 times) with the prescribed torque (1.4 N·m) to fix them to the DIN rail.

#### 

#### Tightening torque

#### SY7000: 1.4 N·m

(While lightly holding the blocks after fixing an end block on one side, tighten the other end block for better sealing after no gap between valves

- . Bushing assembly must be seated properly to each valve block in order to prevent air leaks from occurring.
- Refer to the fig. 2 when dismounting the valve from the DIN rail.

#### Fig. 1 Manifold mounting procedure

#### Fig. 2 Manifold dismounting procedure

Remove upwards from side A Slide it onto side A B side While pressing the bottom of the While pressing the B side stopper valve onto the lip of the DIN rail, pull side A upwards and dismount from the rail. onto the DIN rail, insert into the rail.

Caution When clamping screw (a) of the end block is not sufficiently tightened during reassembly, air leakage may result. Before supplying air, check that there are no gaps between valves and that the end block is firmly secured to the DIN rain in order to ensure air supply without leakage.




### 5 Port Solenoid Valve **Base Mounted Manifold** Bar Stock Type/Individual Wiring Congression Congressi

Note) AC-type models that are CF-compliant have DIN

Series **SY3000/5000/7000** 

#### How to Order Manifold




#### One-touch fitting (Metric size)

		,		
Symbol	Port size	Applicable series	9	
C4	One-touch fitting for ø4	SY3000		
C6	One-touch fitting for ø6	513000		
C6	One-touch fitting for ø6	SY5000		
C8	One-touch fitting for ø8	515000	Г	

#### One-touch fitting (Inch size)

Symbol	Port size	Applicable series
N3	One-touch fitting for ø 5/32"	SY3000
N7	One-touch fitting for ø 1/4"	313000
N7	One-touch fitting for ø 1/4"	SY5000
N9	One-touch fitting for ø5/16"	313000

#### Type 42/External pilot capable



Applicable serie

SY3000 SY5000

SY7000

#### 1/4 1/4 One-touch fitting (Metric size)

1/6


Symbol	Port size	Applicable series
C4	One-touch fitting for ø4	SY3000
C6	One-touch fitting for ø6	513000
C6	One-touch fitting for ø6	SY5000
C8	One-touch fitting for ø8	515000
C10	One-touch fitting for ø10	SY7000

#### One-touch fitting (Inch size)

Symbol	Port size	Applicable series
N3	One-touch fitting for ø5/32"	SY3000
N7	One-touch fitting for ø1/4"	513000
N7	One-touch fitting for ø1/4"	SY5000
N9	One-touch fitting for ø5/16"	515000
N11	One-touch fitting for ø3/8"	SY7000
		SY7000

terminals only.

#### How to Order Manifold Assembly (Example)



\*SY3000-26-9A (-Q) ··· 1 set (Blanking plate assembly part no) The asterisk denotes the symbol for assembly.

Prefix it to the part nos. of the solenoid valve, etc

Add the valve and option part number under the manifold base part number. In the case of complex arrangement, specify them on the manifold specification sheet.

01

## Base Mounted Series SY3000/5000/7000 Type 41 Type



**How to Order Valve** 

Note) AC-type models that are CE-compliant have DIN terminals only.



SJ

LYS

SZ

۷F

VP4

S0700

VO

V04

V05

VOC

VOC4


VOZ

SO

VFS

**VFR** 

**VQ7** 



ctrical entry

	• Electrical entry				
	24, 12, 6,	5, 3 VDC/100, 110, 200	24, 12 VDC/ 100, 110, 200, 220 VAC	24, 12, 6, 5, 3 VDC	
	Grommet	L plug connector	M plug connector	DIN terminal	M8 connector
	G: Lead wire length 300 mm lead H: Lead wire length 600 mm	L: With lead wire (Length 300 mm) LN: Without lead wire LO: Without connector		(SY5000/7000 only) D: With connector DO: Without connector Y: With connector YO: Without connector	WO: Without connector cable  W□: With connector cable Note)
DC	•	•	•	•	•
AC	_	_	_	•	_

\* LN. MN type: with 2 sockets

CE-

- \* "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C). For details, refer to page 519.
- \* For connector cable of M8 connector, refer to page 522.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.
- \* Refer to page 519 for the lead wire length of L and M plug connectors.
- Refer to page 520 for the connector assembly with cover for L and M plug connectors.

Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523.





### **Manifold Specifications**

Model			SS5Y3-41(-Q)	SS5Y3-42(-Q)	SS5Y5-41(-Q)	SS5Y5-42(-Q)	SS5Y7-42(-Q)					
Applica	able			□40		□40	SY7□40					
Manifo	old t	уре		Si	ngle base/B mou	unt	•					
P(SUP)	/R(E)	(H)		Comm	on SUP, Commo	on EXH						
Valve	stati	ons		2	to 20 stations Not	le 1)						
A, B po	A, B port L			Base								
Porting specit	fications	Direction		Side								
	P, E	A, EB port	1/	8	1/	1/4						
Port size	A, B port		M5 x 0.8, C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6)	1/8 C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6)	1/8 C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)	1/4 C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)	1/4 C10 (One-touch fitting for ø10)					
Manifold base weight W (g) n: Stations			W = 30n + 50	W = 37n + 63	W = 61n + 101	W = 79n + 127	W = 100n + 151					

Note 1) For more than 10 stations (more than 5 stations in case of SSSY7), supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

Note 2) Refer to "Manifold Option" on page 416.

#### Flow Characteristics

	Port si	ze	Flow characteristics									
Model	1, 5, 3	4, 2		4/2 (P → A	√B)	4/2 → 5/3 (A/B → EA/EB)						
	(P, EA, EB)	(A, B)	C (dm3/ (s-bar) )	b	Cv	C (dm3/ (s-bar) )	b	Cv				
SS5Y3-41(-Q)	1/8	C6	0.75	0.19	0.18	0.81	0.23	0.20				
SS5Y3-42(-Q)	1/8	C6	0.75	0.20	0.18	0.82	0.20	0.20				
SS5Y5-41(-Q)	1/4	C8	1.8	0.23	0.44	1.9	0.16	0.45				
SS5Y5-42(-Q)	1/4	C8	1.9	0.20	0.46	1.9	0.12	0.43				
SS5Y7-42(-Q)	1/4	C10	3.0	0.25	0.75	3.0	0.12	0.66				

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

## Base Mounted Series SY3000/5000/7000 Type 41


SY3000: SS5Y3-41-Stations -M5, C4,N3 [ ]: AC Grommet (G) With interface regulator (with gauge) (Lead wire length) Approx. 300 SJ With plug SY Manual 4 x ø4.5 override 124.9 SY 111.4 72.3 [74.5] 4 x ø4.5 15.5 88.8 [93.2] 97.3 [101.7] 53.8 SV 15.5 30.6 22.6 5.7 SYJ SZ ล Θ. (29.4)(Pitch) ۷F (P, EA, EB port) 14 4 (Pitch) P = 10.5 28.5 L2 VP4 36.5 11 72.5 [79.5] S0700 (Station 1) - - - - (Station n) For M5 (Light/surge voltage suppressor) VO (Light/surge voltage suppressor) One-touch fitting (A, B port)
Applicable tubing O.D.: Ø4, Ø5/32 VQ4 M5 x 0.8 (A, B port) 57.5 [64.5] ø6, ø1/4" [64.5] VQ5 42.1 57.5 42, 6.5 20.7 88 VQC 0 0 0 0+ 10.5 10.5 (Pitch) (Pitch) VQC4 P = 10.5 VQZ L plug connector (L) M plug connector (M) M8 connector (WO) SQ ead wire length Approx. 300 **VFS** 57.5 [64.5] VFR 42.1 62 M8 x 1 44.5 VQ7 Approx. 300 68.6 [75.6] (Lead wire length) **≤**(†) 72.4 [74.6] á⊕ 8 81.2 117.1 [121.5] 74.9 108.6 [113] [93.4] 97.5 [101.9] 106.8 115.3 00.5 92 89 **(1) a**(+) Note) Refer to page 523 for dimensions of connector types.

Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	38.5	49	59.5	70	80.5	91	101.5	112	122.5	133	143.5	154	164.5	175	185.5	196	206.5	217	227.5
L2	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

## Type 41 Series SY3000/5000/7000

SY5000: SS5Y5-41- Stations -01, C6, N7 C8, N9

Grommet (G)




L plug connector (L)

M plug connector (M)

DIN terminal (D, Y)

M8 connector (WO)

[ ]: AC




Note) Refer to page 523 for dimensions of connector types.


Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	52.5	68.5	84.5	100.5	116.5	132.5	148.5	164.5	180.5	196.5	212.5	228.5	244.5	260.5	276.5	292.5	308.5	324.5	340.5
L2	42	58	74	90	106	122	138	154	170	186	202	218	234	250	266	282	298	314	330


## Base Mounted Series SY3000/5000/7000 11/10 42

SY3000: SS5Y3-42- Stations - C4, N3

[ ]: AC







### 65.5 M8 x 1 48 106.8 φ≾⊕ 115.3 00.5 92

M8 connector (WO)

Note) Refer to page 523 for dimensions of connector types.

Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	38.5	49	59.5	70	80.5	91	101.5	112	122.5	133	143.5	154	164.5	175	185.5	196	206.5	217	227.5
L2	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

VQZ

SQ

**VFS** 


VFR


VQ7

## Type 42 Series SY3000/5000/7000

### SY3000: SS5Y3-42- Stations -01

[ ]: AC





Stations n	2 stations	3	4	5	6	/	8	9	10	- 11	12	13	14	15	16	17	18	19	20 stations
L1	47.5	60	72.5	85	97.5	110	122.5	135	147.5	160	172.5	185	197.5	210	222.5	235	247.5	260	272.5
L2	39.5	52	64.5	77	89.5	102	114.5	127	139.5	152	164.5	177	189.5	202	214.5	227	239.5	252	264.5

## Base Mounted Series SY3000/5000/7000 11/10 42

Grommet (G) (Lead wire length) Approx. 300 M5 x 0.8 (Pilot EXH port) Manual override <In the case of external pilot type solenoid valve> 34 17.6 4 x ø4.5 (For mounting) (DIN: 70.6) 91.5 [93.7] 24 119.8 [124.2] 107.2 [111.6] 69.3 28.9 With interface regulator (with gauge) (P, EA, EB port) <u>8</u> [0 (Pitch) M5 x 0.8 (External pilot port) (14.5) With plug P=16 12 L1 4 x ø4.5 (For mounting) (Station 1) -----(Station n) 9.70 (Light/surge voltage suppressor) 66.6 [73.6] 28.9 51.2 8 27.3 (49.1) 9.5 (Pitch) One-touch fitting 15 P=16 A, B port (Pitch) Applicable tubing O.D.: ø6,ø1/4 89.6 [96.6] P=16 ø8, ø5/16"


L plug connector (L)

SY5000: SS5Y5-42- Stations -C6, N7 C8, N9

M plug connector (M)

DIN terminal (D, Y)

M8 connector (WO)



Note) Refer to page 523 for dimensions of connector types.

Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	52	68	84	100	116	132	148	164	180	196	212	228	244	260	276	292	308	324	340
L2	42	58	74	90	106	122	138	154	170	186	202	218	234	250	266	282	298	314	330

**SMC** 

SJ

[ ]: AC

SY SY

SV

SYJ

SZ

۷F VP4

S0700

VO V04

VQ5 VQC

VQC4

VQZ

SQ **VFS** 


VFR

VQ7

## Type 42 Series SY3000/5000/7000

SY5000: SS5Y5-42- Stations -02

[ ]: AC




L plug connector (L)

M plug connector (M)

DIN terminal (D, Y)

M8 connector (WO)



Note) Refer to page 523 for dimensions of connector types.

St	ations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
	L1	59.5	77	94.5	112	129.5	147	164.5	182	199.5	217	234.5	252	269.5	287	304.5	322	339.5	357	374.5
	L2	49.5	67	84.5	102	119.5	137	154.5	172	189.5	207	224.5	242	259.5	277	294.5	312	329.5	347	364.5

### Base Mounted Series SY3000/5000/7000 Type 42

[ ]: AC

SY7000: SS5Y7-42- Stations -02, C10, N11

Approx. 300 84.1 [91.1]

102.5 [104. 121.6 [126]

134.6 [139]

159.4

172.4

áФ

Φ-

**(** 

52

Ф

0

0

112.3 [114.5] 141.2 [145.6]


54.2 [158.6]

₽

0

•

Grommet (G)



Note) Refer to page 523 for dimensions of connector types.

60

M8 x 1

હ⊕ 8

0

**a** 


Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20 stations
L1	61	80	99	118	137	156	175	194	213	232	251	270	289	308	327	346	365	384	403
L2	49	68	87	106	125	144	163	182	201	220	239	258	277	296	315	334	353	372	391

### 5 Port Solenoid Valve **Base Mounted Manifold** Stacking Type/Individual Wiring

Series SY9000

Note) AC-type models that are CE-compliant have DIN terminals only

#### How to Order Manifold



#### SIID/FYH block assembly specifications

OUI /LAI	block assembly specifications
Symbol	Specifications
Nil	Standard/Internal pilot specification
R	External pilot specification
S	Internal pilot/Built-in silencer
RS	External pilot/Built-in silencer

### A, B port size

IIIIe	au pipilig
Symbol	Port size
02	1/4
03	3/8

#### One-touch fitting (Metric size)

	(
Symbol	Port size
C8	One-touch fitting for ø8
C10	One-touch fitting for ø10
C12	One-touch fitting for ø12
M	Mixed

One-to	ouch fitting (Inch size)
Symbol	Port size
N9	One-touch fitting for ø5/16"
N11	One-touch fitting for ø3/8"
M	Mixed


\* In the case of mixed specifications (M), indicate separately on the manifold specification sheet

#### CE-compliant

Nil	_
Q	CE-compliant

Note) AC-type models that are CF-compliant have DIN terminals only

### How to Order Manifold Assembly (Example)



number. In the case of complex arrangement, specify them on the manifold specification sheet.

### Base Mounted Series SY9000

How to Order Valve

Note) AC-type models that are CE-compliant have DIN terminals only.



SJ

LYS

SZ ۷F

VP4

S0700 VO

V04

V05

VOC

VOC4


VOZ

SO

VFS

**VFR** 

**VQ7** 



Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included

- LN, MN type: with 2 sockets.
- DIN terminal type "Y" which conforms to EN-175301-803C (former DIN43650C) is also available. For details, refer to page 519.
- \* For connector cable of M8 connector, refer to page 522.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details
- \* Refer to page 519 for the lead wire length of L and M plug connectors.
- \* Refer to page 520 for the connector assembly with cover for L and M plug connectors. Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523.

**SMC** 



### **Manifold Specifications**

Model			SS5Y9-43(-Q)
Applic	able valve		SY9□40
Manif	old type		Stacking type
P(SUP	/R(EXH)		Common SUP, Common EXH
Valve	stations		2 to 20 stations (1)
A, B p	ort	Location	Base
Portin	orting specifications Direction		Side
	P, EA, EB po	rt	C12 (One-touch fitting for ø12)
			1/4
Port			3/8
size	A, B port		C8 (One-touch fitting for ø8)
	A, B port		C10 (One-touch fitting for Ø10)
			C12 (One-touch fitting for ø12)
	nifold base weight		W = 107n + 330


Note 1) For more than 10 stations, supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

### Flow Characteristics

	Port si	ze	Flow chara			racteristics		
Model	1, 5, 3	4, 2	1-	1→4/2 (P→A/B) 4/2→5/3 (A/B→E				EA/EB)
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/ (s-bar) )	b	Cv
SS5Y9-43(-Q)	C12	C12	6.4	0.29	1.6	7.3	0.29	1.8

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

Note 2) Refer to "Manifold Option" on page 416.



81.2

dimensions of connector types.

98.7

Note) Refer to page 523 for

Pg7

Max.

Applicable cable O.D ø3.5 to ø7

109.2

120.5

128

105.3 [112.3]


Approx. 300


(Lead wire length)


78.8


94.2 [101.2














## 5 Port Solenoid Valve **Base Mounted Manifold**

Note) CE-compliant: For DC only.

# **Bar Stock Type/Flat Ribbon Cable**

# Series SY3000/5000/7000

#### How to Order Manifold



N3 One-touch fitting for ø5/32"

N7 One-touch fitting for ø 1/4"

N7 One-touch fitting for ø 1/4"

N9 One-touch fitting for ø5/16

SY5000

#### Type 42P/Common external pilot capable


SY5000

C4 One-touch fitting for ø4

C6 One-touch fitting for ø6

C6 One-touch fitting for ø6

C8 One-touch fitting for Ø8



т NPTF

SY5000

SY7000


### 1/4 One-touch fitting (Metric size)

Symbol	Port size	Applicable series	
C4	One-touch fitting for ø4	SY3000	
C6	One-touch fitting for ø6	513000	
C6	One-touch fitting for ø6	SY5000	
C8	One-touch fitting for ø8	515000	ı
C10	One-touch fitting for ø10	SY7000	

One	touch fitting (Inch	size)
Symbol	Port size	Applicable series
N3	One-touch fitting for ø5/32"	SY3000
N7	One-touch fitting for ø1/4"	513000
N7	One-touch fitting for ø1/4"	SY5000
N9	One-touch fitting for ø5/16"	515000
N11	One-touch fitting for ø3/8"	SY7000

Note) CE-compliant: For-DC only.

#### How to Order Manifold Assembly (Example)



Note) Please indicate the connector assembly part no. (page 393) that connects the valve and the manifold

02

## Base Mounted Series SY3000/5000/7000 170-41P 170-4



#### **How to Order Valve**

Note) CE-compliant: For DC only.



SJ

SYJ SZ

۷F

VP4

S0700

VO

V04

V05

VQC

VQC4


VOZ

SQ

VFS

**VFR** 

**VQ7** 



Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

For the other combination, please contact SMC.

Note) Since the electrical entry is "LO", select an appropriate connector assembly part no.

### Connector Assembly

FOF 12, 24 VDC								
Specifications	For SY3000	For SY5000/7000						
For single solenoid	SY3000-37-3A	SY5000-37-3A						
Double solenoid, 3 position type	SY3000-37-4A	SY5000-37-4A						
Single with spacer assembly	SY5000-37-3A	SY5000-37-5A						
Double, 3 position with spacer assembly	SY3000-37-6A	SY5000-37-6A						

#### For 100 VAC

	Specifications	For SY3000	For SY5000/7000
	For single solenoid	SY3000-37-32A	SY5000-37-15A
	Double solenoid, 3 position type	SY3000-37-33A	SY5000-37-16A
	Single with spacer assembly	SY5000-37-15A	SY5000-37-17A
	Double, 3 position with spacer assembly	SY3000-37-34A	SY5000-37-18A
٠,	cor		

#### 400 1/40 /445 1/40

For 100 VAC (115 VAC)							
Specifications	For SY3000	For SY5000/7000					
For single solenoid	SY3000-37-35A	SY5000-37-19A					
Double solenoid, 3 position type	SY3000-37-36A	SY5000-37-20A					
Single with spacer assembly	SY5000-37-19A	SY5000-37-21A					
Double, 3 position with spacer assembly	SY3000-37-37A	SY5000-37-22A					

Note) Spacer assembly indicates Individual SUP/EXH spacer.

#### Multiple valve wiring is simplified through the use of the flat cable connector.

#### Clean appearance

In the case of a flat ribbon cable type, each valve is wired on the print board of manifold base to allow the external wiring to be piped all together with 26 pins MIL connector.



#### Flat Ribbon Cable Manifold Specifications

Model		CCEV2 A1D( O)	CCEV2 42D/ O)	CCEVE A1D/ O)	SS5Y5-42P(-Q)	CCEV7 ADD/ O			
Applicable valve		SY3	□40	SY5	i□40	SY7□40			
Manifo	old type		Si	ngle base/B moi	unt				
P(SUP)	/R(EXH)		Common SUP, Common EXH						
Valve	stations	4 to 12 s	tations (1)	3	to 12 stations Not	e 1)			
A, B po	ort Location			Base					
Porting specifi	ications Direction		Side						
	P, EA, EB port	1,	/8	1,	1/4				
Port		M5 x 0.8	1/8	1/8	1/4	1/4			
size	A, B port	C4 (One-touch fitting for ø4)	C4 (One-touch fitting for ø4)	C6 (One-touch fitting for ø6)	C6 (One-touch fitting for ø6)	74 C10 (One touch filling for a 10)			
		C6 (One-touch fitting for ø6)	C6 (One-touch fitting for ø6)	C8 (One-touch fitting for ø8)	C8 (One-touch fitting for ø8)	GTO (One-load it filling for a ro)			
Manifold base weight W (g), n: Stations		W = 39n + 83	W = 48n + 99	W = 67n + 118	W = 88n + 151	W = 109n + 174			
Applicable flat ribbon cable connector		Flat ribbon cable connector, Socket: 26 pins MIL type with strain relief, Conforming to MIL-C-83503							
	al wiring	In common between +COM and -COM (Z type: +COM only).							
Rated	voltage Note 4)		12, 2	4 VDC, 100, 110	VAC				


Note 1) For more than 10 stations (more than 5 stations in case of SS5Y7), supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

#### Flow Characteristics


	Port size		Flow characteristics							
Model	1, 5, 3	4, 2	1 → 4/2 (P → A/B)			4/2 → 5/3 (A/B → EA/EB)				
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv		
SS5Y3-41P	1/8	C6	0.75	0.19	0.18	0.81	0.23	0.20		
SS5Y3-42P	1/8	C6	0.75	0.20	0.18	0.82	0.20	0.20		
SS5Y5-41P	1/4	C8	1.8	0.23	0.44	1.9	0.16	0.45		
SS5Y5-42P	1/4	C8	1.9	0.20	0.46	1.9	0.12	0.43		
SS5Y7-42P	1/4	C10	3.0	0.25	0.75	3.0	0.12	0.66		

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

#### **Internal Wiring of Manifold**



- For more than 10 stations, both poles of the common should be wired.
- · For single solenoid, connect to the solenoid A side.
- The maximum number of stations that can be accommodated is 12. For more stations, please contact SMC.



#### **∧**Caution

 For non-polar (U) valves, the electrical DC connections can be used with either positive and negative COM. For type (Z), only use with positive COM as the valve does not operate correctly when used with negative COM.



Note 2) The withstand voltage specification for the wiring unit section is JIS C 0704, Grade 1 or its equivalent. Note 3) Refer to "Manifold Option" on page 416.


Note 4) CE-compliant: For DC only.


## Base Mounted Series SY3000/5000/7000 1/10-41P

Base Mounted Series 3 / 3000/3000/ / 000 West


SY3000: SS5Y3-41P- Stations -M5, C6, N7










With interface regulator (with gauge)









Stations n	4	5	6	7	8	9	10	11	12
L1	72.5	85	97.5	110	122.5	135	147.5	160	172.5
12	CAE	77	00 F	100	444E	107	120 E	150	104 E

SJ

[ ]: AC

QV

SV SYJ

SZ

VF

VP4

S0700 VQ

VQ4 VQ5

VQC VQC4

VQZ


SQ VFS

VFR VQ7

# 3 Series **SY3000/5000/7000**

SY5000: SS5Y5-41P- Stations -01, C6,N7


[ ]: AC





# Base Mounted Series SY3000/5000/7000 11/12-22

SY3000: SS5Y3-42P- Stations -01, C4, N3 C6, N7


[ ]: AC








Stations n	4	5	6	7	8	9	10	11	12
L1	72.5	85	97.5	110	122.5	135	147.5	160	172.5
L2	64.5	77	89.5	102	114.5	127	139.5	152	164.5



#### With interface regulator (with gauge)



SJ

SY

SV

SYJ

SZ

۷F VP4

S0700 vo

VQ4

VQ5

vqc VQC4

VQZ

SQ **VFS** 


VFR VQ7

# Series **SY3000/5000/7000**

SY5000: SS5Y5-42P-Stations -02,<sup>C6, N7</sup>

[ ]: AC

#### Grommet (G)



Stations n 3

L2

77 94.5 112 129.5 147 164.5 182 199.5 217

67


4 | 5 | 6 | 7 | 8 | 9 | 10

Triangle mark

11 12

84.5 102 119.5 137 154.5 172 189.5 207 224.5

Base Mounted Series SY3000/5000/7000 11/12 42P




399

### 5 Port Solenoid Valve **Base Mounted Manifold Stacking Type/Flat Ribbon Cable**


# Series SY9000

Note) CE-compliant: For DC only.

#### **How to Order Manifold**



#### How to Order Manifold Assembly (Example)



Note) Please indicate the connector assembly part no. (page 401) that connects the valve and the manifold.

#### CE-compliant

Mixed

One-touch fitting (Inch size) Port size

N9 One-touch fitting for ø5/16" N11 One-touch fitting for ø3/8" Mixed \* In the case of mixed specification: (M), indicate separately on the manifold specification sheet.

Symbol

Nil	_
Q	CE-compliant

Note) CE-compliant: For DC only.


# Base Mounted Series SY9000 Ima



How to Order Valve

Note) CE-compliant: For DC only.





Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

and "Z" types are for DC specifications and "Z" type is for AC specifications. "Z" type for DC is positive common specification only. For the other combination, please contact SMC.

Note) Since the electrical entry is "LO", select an appropriate connector assembly part no.

#### **Connector Assembly**

#### For 12, 24 VDC

,						
Specifications	For SY9000					
For single solenoid	SY9000-37-1A					
Double solenoid, 3 position type	SY9000-37-2A					
Single with spacer assembly	SY9000-37-3A					
Double, 3 position with spacer assembly	SY9000-37-4A					
Note Consessing in the state of the state of CUD/EVII and a						

Note) Spacer indicates Individual SUP/EXH spacer.

#### For 100 VAC

Specifications	For SY9000
For single solenoid	SY9000-37-1B
Double solenoid, 3 position type	SY9000-37-2B
Single with spacer assembly	SY9000-37-3B
Double, 3 position with spacer assembly	SY9000-37-4B
•	

#### For 110 VAC (115 VAC)

101 110 170 (11	0 VAO)		
Specifications	For SY9000		
For single solenoid	SY9000-37-1C		
Double solenoid, 3 position type	SY9000-37-2C		
Single with spacer assembly	SY9000-37-3C		
Double, 3 position with spacer assembly	SY9000-37-4C		

**ØSMC** 

401

SJ

SYJ

SZ

۷F VP4

S0700

VO

V04 V05

voc

VQC4

VOZ

SO

VFS VFR

**VQ7** 



#### Multiple valve wiring is simplified through the use of the flat ribbon cable connector.

#### Clean appearance

In the case of a flat ribbon cable type, each valve is wired on the print board of manifold base to allow the external wiring to be piped all together with 26 pins MIL connector.



#### Flat Ribbon Cable Manifold Specifications

Model		SS5Y9-43P		
Applicable v	alve	SY9□40		
Manifold typ	ре	Stacking type		
P (SUP)/R (I	EXH)	Common SUP, Common EXH		
Valve statio	ns	4 to 12 stations Note 1)		
A, B port	Location	Base		
Porting specifications	Direction	Side		
	P, EA, EB port	C12 (One-touch fitting for ø12)		
Port size	A, B port	1/4 3/6 C8 (One-touch fitting for ø8) C10 (One-touch fitting for ø10) C12 (One-touch fitting for ø12)		
Manifold base weight W (g) n: Stations		W = 114n + 343		
Applicable flat ribb	on cable connector	Flat ribbon cable connection, Socket: 26 pins MIL with strain relief, Conforming to MIL-C-83503		
Internal wir	ing	In common between +COM and -COM (Z type: +COM only)		
Rated volta	ge Note 4)	12, 24 VDC, 100, 110 VAC		

Note 1) For more than 10 stations, supply pressure to P port on both sides and exhaust from EA/EB port on both sides.

Note 2) The withstand voltage specification for the wiring unit section is JIS C 0704, Grade 1 or its equivalent.

Note 3) Refer to "Manifold Option" on page 416.


Note 4) CE-compliant: For DC only.

#### Flow Characteristics

	Port size		Flow characteristics						
Model	1, 5, 3	4, 2	1 → 4/2 (P → A/B)			4/2 → 5/3 (A/B → EA/EB)			
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv	
SS5Y9-43	C12	C12	6.4	0.29	1.6	7.3	0.29	1.8	

Note) The value is for manifold base with 5 stations and individually operated 2 position type.


#### Internal Wiring of Manifold (Non-polar type)





 For non-polar (U) valves, the electrical DC connections can be used with either positive and negative COM. For type (Z), only use with positive COM as the valve does not operate correctly when used with negative COM.

- . For more than 10 stations, both poles of the common should be wired.
- · For single solenoid, connect to the solenoid A side The maximum number of stations that can be accommodated is
- 12. For more stations, please contact SMC.





# Base Mounted Series SY9000 Iype 43P

SY9000: SS5Y9-43P-Stations D -03 C10, N11 (-D)


[ ]: AC


\* When P, R port outlets are indicated on the D side, the P, R ports on the opposite side are plugged.





 Air discharge port on the built-in silencer type and the external pilot's extracting position are in the D side.





Stations n	4 stations	5	6	7	8	9	10 stations
L1	198	223	248	260.5	285.5	310.5	335.5
L2	187.5	212.5	237.5	250	275	300	325
L3	165	189	213	237	261	285	309
L4	16.5	17	17.5	12	12.5	13	13.5
L5	151	175	199	223	247	271	295

SJ

SY SV

SYJ

SZ

VF

VP4

S0700 VO

VQ4 VQ5

VQC

VQC4 VQZ


SQ


VFS

VFR VQ7 SY9000: SS5Y9-43P-Stations U -03 C10, N11 (-D)


[ ]: AC


\* When P, R port outlets are indicated on the U side, the P, R ports on the opposite side are plugged.






 Air discharge port on the built-in silencer type and the external pilot's extracting position are in the U side.





(Station n)-----(Station 1)




Stations n	4 stations	5	6	7	8	9	10 stations
L1	198	223	248	260.5	285.5	310.5	335.5
L2	187.5	212.5	237.5	250	275	300	325
L3	165	189	213	237	261	285	309
L4	16.5	17	17.5	12	12.5	13	13.5
L5	151	175	199	223	247	271	295


# Base Mounted Series SY9000 11/12 43P

SY9000: SS5Y9-43P-Stations B -02 C8, N9 -03 C10, N11 (-D)


[ ]: AC

\* When P, R port outlets are indicated on the B side, the P, R ports on the both sides are in the open state.






 Air discharge port on the built-in silencer type and the external pilot's extracting position are in the B side (both sides).



(Station n)-----(Station 1)



Stations n	4 stations	5	6	7	8	9	10	11	12 stations
L1	198	223	248	260.5	285.5	310.5	335.5	360.5	385.5
L2	187.5	212.5	237.5	250	275	300	325	350	375
L3	165	189	213	237	261	285	309	333	357
L4	16.5	17	17.5	12	12.5	13	13.5	14	14.5
L5	151	175	199	223	247	271	295	319	343

**SMC** 

SJ

SY

SV

SYJ

SZ

VF

VP4

S0700 VO

VQ4

VQ5

VQC VQC4

VQZ

SQ

VFS VFR

VQ7


# Tyne 42SA

# EX510 Gateway-type Serial Transmission System Base Mounted Manifold/Integrated Type Series SY3000/5000/7000

((

#### **How to Order Manifold**


[Option]



The number of the blanking plate assembly is also included.
 Note 1) Double wiring: Use of a single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.

Note 2) Specified layout: Indicate wiring specifications on the manifold specification sheet. (Note that double and 3 position valves cannot be used where single solenoid wiring has been specified.)

#### How to Order Manifold Assembly (Example)



assembly is shipped with the valves (including blanking plates) and connector assembly mounted on it, as the standard specification. Be sure to specify the part nos. of the solenoid valves to be mounted.

#### One-touch fitting (Metric size)

•	4011 IIIIII (IIIII)	
C4	One-touch fitting for ø4	SY3000
C6	One-touch fitting for ø6	513000
C6	One-touch fitting for ø6	SY5000
C8	One-touch fitting for ø8	313000
C10	One-touch fitting for ø10	SY7000

#### One-touch fitting (Inch size)

One-touch nitting (inch size)							
N3	SY3000						
N7	One-touch fitting for ø1/4"	313000					
N7 One-touch fitting for ø1/4'		SY5000					
N9	One-touch fitting for ø5/16"	515000					
N11	One-touch fitting for ø3/8"	SY7000					

#### SI unit part no.


•. •	Pu				
Symbol	SI unit specifications	SI unit part no.	Page		
Nil	NPN output (+COM.)	EX510-S001	P.2143		
N	PNP output (-COM.)	EX510-S101	P.2143		

Refer to page 2124 and the Operation Manual for the details of EX510 Gateway-type Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

# Base Mounted Manifold Series SY3000/5000/7000 Type 42SA



#### **How to Order Valves**



Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

**SMC** 


SO

VFS

VFR VQ7

# 100 A2SA Series SY3000/5000/7000

#### **Dimensions**



Stations n	4 stations	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	72.5	85	97.5	110	122.5	135	147.5	160	172.5	185	197.5	210	222.5
L2	64.5	77	89.5	102	114.5	127	139.5	152	164.5	177	189.5	202	214.5


55.7

(6) (With plug)

112.3

4 x Ø4.5

# Base Mounted Manifold Series SY3000/5000/7000 Type 42SA



(Station n) - - - - - (Station 1)

37.8

Connector lock pin

(Take out when wiring the


connector assembly.)

(Light/surge voltage suppressor)

27.1

SI unit

#### With interface regulator (with gauge)



Stations n	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	77	94.5	112	129.5	147	164.5	182	199.5	217	234.5	252	269.5	287	304.5
L2	67	84.5	102	119.5	137	154.5	172	189.5	207	224.5	242	259.5	277	294.5

**SMC** 

SJ

SY

sv

SYJ

SZ VF

VP4

S0700

VQ

VQ4 VQ5

VOC

VQC4

VQZ

SQ


VFS

VFR

VQ7

# 100 A2SA Series SY3000/5000/7000

#### **Dimensions**



Stations r	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	88	108.5	129	149.5	170	190.5	211	231.5	252	272.5	293	313.5	334	354.5
L2	76	96.5	117	137.5	158	178.5	199	219.5	240	260.5	281	301.5	322	342.5

### **EX510 Gateway-type Serial Transmission System Base Mounted Manifold/Stacking Type**

Series SY9000



SJ

SY

LYS

SZ

۷F

VP4

S0700

VO

V04

V05

VQC

VOC4


VOZ SO

VFS


**VFR** 

**VQ7** 

#### **How to Order Manifold**



#### How to Order Manifold Assembly (Order Example)



SS5Y9-43SA-05B-C12 (-Q) ··· 1 set (43SA type 5-station manifold part no.) \* SY9140-5LOU (-Q) ······· 3 sets (Single solenoid part no.) \* SY9240-5LOU (-Q) ...... 2 sets (Double solenoid part no.)

The asterisk denotes the symbol for assembly. Prefix to the part no. of the solenoid valve, etc.

Add the valve and option part number under the manifold base part number When entry of part numbers becomes complicated, indicate by the manifold specification sheet. For a manifold for an EX510, the length of the lead wire for a connector assembly depends on the number of stations. Therefore, the manifold assembly is shipped with the valves (including blanking plates) and connector assembly mounted on it, as the standard specification. Be sure to specify the part nos. of the solenoid valves to be mounted

C8	One-touch fitting for ø8
C10	One-touch fitting for ø10
C12	One-touch fitting for ø12
М	Mixed

#### One-touch fitting (Inch size)

•	one teach maning (men cize)								
N9	One-touch fitting for ø5/16"								
N11	One-touch fitting for ø3/8"								
M	Mixed								

<sup>·</sup> For the mixed specification, indicate separately on a manifold specification sheet

#### SUP/EXH block assembly specifications

• SUF/	EAR DIOCK assembly specific						
Nil	Standard/Internal pilot						
R	External pilot						
S	Internal pilot, Built-in silencer						
RS	External pilot, Built-in silencer						

#### P. R port outlets

U	U side	3 to 10 stations		
D	D side	13 to 10 stations		
В	Both sides	3 to 16 stations		

#### SI unit part no.


Symbol	SI unit specifications	SI unit part no.	Page
Nil	NPN output (+COM.)	EX510-S001	P.2143
N	PNP output (-COM.)	EX510-S101	P.2143

Refer to page 2124 and the Operation Manual for the details of EX510 Gateway-type Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com










**How to Order Valves** 

Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included. Note 1) Power saving circuit is only available in the "Z" type.


Note 2) When the SI unit is the PNP output (-COM.), only the "U" type is available.

# Base Mounted Manifold Series SY9000 Type 435A


#### **Dimensions**



:ø12




With External Pilot Specifications



- \* When P, R port outlets are indicated on the D side, the P, R ports on the opposite side are plugged.

  \* Air discharge port on the built-in silencer type and the external pilot's extracting
- position are in the U side



Tightening torque: (0.55 to 0.65) N·m

Stations n	3 stations	4	5	6	7	8	9	10 stations
L1	173	198	223	248	260.5	285.5	310.5	335.5
L2	162.5	187.5	212.5	237.5	250	275	300	325
L3	141	165	189	213	237	261	285	309
L4	16	16.5	17	17.5	12	12.5	13	13.5
L5	127	151	175	199	223	247	271	295

SV SYJ

SJ

SY

SZ

۷F

VP4

S0700 VO

VQ4

VQ5

voc VQC4


VQZ


SQ **VFS** 


VFR VQ7




#### **Dimensions**









- When P, R port outlets are indicated on the D side, the P, R ports on the opposite side are plugged.
- Air discharge port on the built-in silencer type and the external pilot's extracting position are in the D side.





Stations n	3 stations	4	5	6	7	8	9	10 stations
L1	173	198	223	248	260.5	285.5	310.5	335.5
L2	162.5	187.5	212.5	237.5	250	275	300	325
L3	141	165	189	213	237	261	285	309
L4	16	16.5	17	17.5	12	12.5	13	13.5
L5	127	151	175	199	223	247	271	295

# Base Mounted Manifold Series SY9000 Type 43SA



Stations n	3 stations	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	173	198	223	248	260.5	285.5	310.5	335.5	360.5	385.5	410.5	435.5	460.5	485.5
L2	162.5	187.5	212.5	237.5	250	275	300	325	350	375	400	425	450	475
L3	141	165	189	213	237	261	285	309	333	357	381	405	429	453
L4	16	16.5	17	17.5	12	12.5	13	13.5	14	14.5	15	15.5	16	16.5
L5	127	151	175	199	223	247	271	295	319	343	367	391	415	439

33.2 41.1 64

(Height when using DIN rail)

(6.7)

SI unit

61.6

(Light/surge voltage suppressor)

Connector lock pin

(Take out when wiring the

connector assembly.)

(95.4) 94.2 66.8 VQ7

### Series SY3000/5000/7000/9000

#### **Manifold Option**

#### ■ Type 41, 42, 43, 42SA, 43SA Blanking plate assembly




Series	Assembly part no.
SY3000	SY3000-26-9A(-Q)
SY5000	SY5000-26-20A(-Q)
SY7000	SY7000-26-22A(-Q)
SY9000	SY9000-26-2A

#### **■** Type 41P, 42P, 43P Blanking plate assembly



Series	Assembly part no.
SY3000	SY3000-26-10A(-Q)
SY5000	SY5000-26-21A(-Q)
SY7000	SY7000-26-23A(-Q)
SVOODO	SV9000-26-4A


#### ■ Gasket assembly part no.



Series	Gasket assembly part no.
SY3000	SY3000-GS-2
SY5000	SY5000-GS-2(-Q)
SY7000	SY7000-GS-2(-Q)
SY9000	SY9000-GS-2

Note) The gasket assembly includes 10 sets of mounting screws and a gasket.

#### ■ Individual SUP spacer assembly




Series	Assembly part no.	Port size	t
SY3000	SY3000-38-2A(-Q)	M5 x 0.8	11
SY5000	SY5000-38-16*A(-Q)	1/8	15
SY7000	SY7000-38-16*A(-Q)	1/4	18
SY9000	SY9000-38-2*A	1/4	20

Note) • The SUP port of SY3000, 5000 and 7000 may be either on the lead wire side or on the end plate side. (An assembly is shipped under the condition shown in the figure.)

. The end plate side is only available to SY9000.


#### ■ Individual EXH spacer assembly



Series	Assembly part no.	Port size	t
SY3000	SY3000-39-2A(-Q)	M5 x 0.8	11
SY5000	SY5000-39-16*A(-Q)	1/8	15
SY7000	SY7000-39-16*A(-Q)	1/4	18
SY9000	SY9000-39-2*A	1/4	20

Note) In case of 41P, 42P and 43P, for protection of the wiring unit section from drainage, piping at the EA port should be arranged so that it will not be directly exposed to exhaust from the valve

#### ■ Individual SUP spacer assembly + Individual EXH spacer assembly (Double spacer)



[ : Available X: Not available -: Not applicable manifold]

N Caution ∗ Th		Thread type			Individual SUP +		Applicable manifold types							
lounting screw		Nil	Rc		Series	Individual EXP Assemble part no.	Port size	41	41P	42	42P	45	45-A 45-NA	45*
gillering torques	- 1	F	G		SY3000	SY3000-120-2A(-Q)	M5 x 0.8		×		×		×	×
12: 0.16 N·m	L	N	NPT			. ,		_		-				
13: 0.8 N·m		Т	NPTF			SY5000-75-1*A(-Q)	1/8	•	X	•		_		_ X
14: 1.4 N·m	_			'	SY7000	SY7000-73-1*A(-Q)	1/4	•	×	•	×	_	_	_

Note) The port on a spacer can be directed to the pilot valve side or end plate side. For mounting the port to the pilot valve side, please make sure to connect the ports to protect the pilot valve wiring section from drainage.

The individual SUP spacer and EXH spacer can be mounted either on the upper side or lower side. (The above illustration shows the condition when the product is shipped out from a factory.)

Mc tig

ghtening torques	F
12: 0.16 N·m	N
13: 0.8 N·m	Т
I4: 1.4 N⋅m	

### 

When mounting a valve or spacer on the manifold base or sub-plate, etc., those mounting directions are determined. If mounted in the wrong direction, the equipment to be connected may cause malfunction. Refer to external dimensions, and then mount it.




### Base Mounted Manifold Series SY3000/5000/7000/9000 Type 42SA Type 43SA

#### **Manifold Option**

■ Connector assembly
For single solenoid (SY3000-37-81A-□-N)





Connector assembly order no. (Can be used for the manifold without a specified layout (8 stations or less)) Integrated type

integrated type		
Model	Part no.	Connector mounting position
	SY3000-37-81A-3-N	Single: For 1 to 4 stations
SS5Y3-42SA	SY3000-37-81A-3-6	Double/3 position: For 1 to 4 stations
55513-425A	SY3000-37-81A-2-N	Single: For 5 to 8 stations
	SY3000-37-81A-2-4	Double/3 position: For 5 to 8 stations
SS5Y5-42SA	SY3000-37-81A-3-N	Single: For 1 to 8 stations
33313-423A	SY3000-37-81A-3-6	Double/3 position: For 1 to 8 stations
	SY3000-37-81A-3-N	Single: For 1 to 4 stations
SS5Y7-42SA	SY3000-37-81A-3-6	Double/3 position: For 1 to 4 stations
33317-423A	SY3000-37-81A-4-N	Single: For 5 to 8 stations
	SY3000-37-81A-4-7	Double/3 position: For 5 to 8 stations

Note) The above is for the station addition or maintenance. When ordering a connector assembly separately, a number would not be printed on the connector.

■ Connector assembly SY3000-37-80A-□



■ Housing (8 pcs./set) SY3000-44-3A



Connector assembly order no. (Can be used for the manifold with a specified layout)

connector assembly order no. (Can be used for the mannoid with a specified layout)						
Model	Part no.		Connector mounting position			
	SY3000-37-80A-3	For A side	For 1 to 8 stations			
SS5Y3-42SA	SY3000-37-80A-6	For B side	FOI 1 to 6 stations			
33313-423A	SY3000-37-80A-4	For A side	For 9 to 16 stations			
	SY3000-37-80A-7	For B side	FOI 9 to 10 Stations			
	SY3000-37-80A-3	For A side	For 1 to 8 stations			
SS5Y5-42SA	SY3000-37-80A-6	For B side	For 1 to 6 stations			
55515-425A	SY3000-37-80A-7	For A side	For 9 to 16 stations			
	SY3000-37-80A-9	For B side	For 9 to 16 stations			
	SY3000-37-80A-4	For A side	For 1 to 8 stations			
SS5Y7-42SA	SY3000-37-80A-7	For B side	FOI 1 to 6 stations			
33317-423A	SY3000-37-80A-8	For A side	For 9 to 16 stations			
	SY3000-37-80A-11	For B side	For 9 to 16 stations			
	SY3000-37-80A-6	For A side	For 1 to 8 stations			
SS5Y9-43SA	SY3000-37-80A-11	For B side	FOI 1 to 6 stations			
	SY3000-37-80A-9	For A side	For 9 to 12 stations			
	SY3000-37-80A-14	For B side	For 9 to 12 stations			
	SY3000-37-80A-13	For A side	For 10 to 16 stations			
	SY3000-37-80A-18	For B side	For 13 to 16 stations			

Note 1) The above is for station addition or maintenance. When ordering a connector assembly separately, a number will not be printed on the connector.

Note 2) After inserting the connector assembly into the housing, be sure to confirm that the lead wire will not come off by lightly pulling the wire. Furthermore, do not reuse the lead wire after it has been inserted and removed.

Note 3) Wiring is set longer than the actual wiring distance.

SJ SY

δī

CV

SYJ

SZ

-

VP4 S0700

VO

V04

V05

voc

VQC4

VQZ

SQ VFS

VFR VO7

#### **Manifold Option**

#### ■SUP blocking disk (For SY9000)

By installing a SUP blocking disk in the pressure supply passage of a manifold base, it is possible to supply two or more different high and low pressures to one manifold.



Series	No.
SY9000	SY9000-57-1A

#### ■ EXH blocking disk (For SY9000)

By installing an EXH blocking disk in the exhaust passage of a manifold base, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to divide both exhausts.)



Series	No.
SY9000	SY9000-57-1A

#### Label for block disk (For SY9000)

The labels shown below are used on manifold stations containing SUP/EXH block disk(s) to show their location. (3 pcs. each)

#### VZ3000-123-1A

Label for SUP block disk Label for EXH block disk Label for SUP/EXH block disk








Note) When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block disk is mounted.

#### Silencer with One-touch fitting (For SY9000)

The silencer plugs directly into the One-touch fittings of the manifold R (exhaust) port.




For Series	Model	Effective area mm <sup>2</sup>	Α	В	С
SY9000 (Ø12)	AN30-C12	41	ø20	43.5	71.5

#### ■ DIN Rail Dimensions/Weight for SY9000



\* Fill in  $\square$  with an appropriate no. listed on the




No.	0	1	2	3	4	5	6	7	8	9
L Dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5
Weight (g)	24.8	28	31.1	34.3	37.4	40.6	43.8	46.9	50.1	53.3
No.	10	11	12	13	14	15	16	17	18	19
INO.	10	- 11	12	13	14	13	10	17	10	10
L Dimension	223	235.5	248	260.5	273	285.5	298	310.5	323	335.5
Weight (g)	56.4	59.6	62.7	65.9	69.1	72.2	75.4	78.6	81.7	84.9
No.	20	21	22	23	24	25	26	27	28	29
L Dimension	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5
Weight (g)	88	91.2	94.4	97.5	100.7	103.9	107	110.2	113.3	116.5

Note) • Refer to page 521 for DIN rail.

 Refer to L1 dimension on pages 389 to 391, 403 to 405 and 413 to 415 for lengths that correspond to the number of manifold stations.

#### ■ Cable assembly



#### Connector Assembly for Flat Ribbon Cables

Commodici riccombiy for that this born cables			
Cable length (L)	Assembly part no.	Note	
1.5m	AXT100-FC26-1	Cable 26 core	
3m	AXT100-FC26-2	x 28 AWG	
5m	AXT100-FC26-3	X 20 AWG	


For other commercial connectors, use a 26 pins with strain relief conforming to MIL-C-83503.

#### Connector manufacturers' example

- · Hirose Electric Company
- Japan Aviation Electronics Industry, Ltd.
- Sumitomo 3M Limited
- J.S.T. Mfg. Co., Ltd.
- Fujitsu Limited

#### ■Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports. Purchasing order is available in units of 10 pieces.



#### Dimensions

Applicable fittings size ød	Model	Α	L	D
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12
12	KQ2P-12	24	44.5	14
1/8"	KQ2P-01	16	31.5	5
5/32"	KQ2P-03	16	32	6
1/4"	KQ2P-07	18	35	8.5
5/16"	KQ2P-09	20.5	39	10
3⁄8"	KQ2P-11	22	43	11.5



# Base Mounted Manifold Series SY3000/5000/7000 41 1/1942P





SJ

SY

SV

SYJ

SZ

۷F

VP4 S0700 VQ V04 VQ5 VOC VOC4

VOZ

SO


VFS VFR

**VQ7** 

#### **Manifold Option**

#### ■ How to Order Interface Regulator






#### Pressure gauge connection port

05	Pressure gauge (G15-10-01) [for odd number station]
06	Pressure gauge (G15-10-01) [for even number station]
M1	Plug (M-5P)

Note) In the case of Series ARBY3000 with a pressure gauge when mounting on the manifold, use caution that the part numbers are different between the odd no. stations and the even no. stations to avoid gauges from interfering from each others

#### Series SY5000



#### Pressure gauge connection port

	Pressure gauge	
M1	Plug (M-5P)	

#### Regulating port

P	P port
A1	A port (P controlled type, A port regulation
B1	B port (P controlled type, B port regulation

ARBY3000-05- -2

(For odd number stations)



Regulating port

P port


Α1


A port (P controlled type, A port regulation


B1 B port (P controlled type, B port regulation)


ARBY3000-M1-□-2


ARBY5000-00-□-2 ARBY5000-M1-□-2











Series SY7000

ARBY7000 - 00

#### Pressure gauge connection port


	Pressure gauge (G15-10-01)		
M1	Plug (M-5P)		


#### Regulating port

ARBY7000-M1-□-2

P	P port
A1	A port (P controlled type, A port regulation)
B1	B port (P controlled type, B port regulation)

Note) ARBY is not CE compliant.





#### Accessory

Series	Round head combination screw Reference screw size	Gasket
ARBY3000	SY3000-23-10 (M2 x 36)	SX3000-57-4
ARBY5000	AC00283 (M3 x 48.5)	SX5000-57-6
ARBY7000	AC00282 (M4 x 58)	SX7000-57-5




Mounting screw tightening torques M2: 0.16 N·m

M3: 0.8 N·m M4: 1.4 N·m




# Type 43 Type 43P Type 43\$A Series SY9000

#### **Base Mounted Manifold Exploded View**



#### SUP/EXH block assembly no. (D side mounting)



Specifications

1	Internal pilot type
3	External pilot type
4	Internal pilot / Built-in silencer type
5	External pilot / Built-in silencer type

### ③ SUP/EXH block assembly no. (U side mounting)

Direct mount type: SY9000-71- A DIN rail mount type: SY9000-73- A P, R port
 C12 One-touch fitting for ø12

N11

00 Plug

One-touch fitting for ø3/8

Specifications				
1	Internal pilot type			
3	External pilot type			
4	Internal pilot / Built-in silencer type			
5	External pilot / Built-in silencer type			

# Base Mounted Manifold Series SY9000 Type 43 Ty

#### How to Increase Manifold Bases (Series SY9000 only) Manifold case can be added at any location.

When a type 43 manifold base is added, tension bolts as well as manifold block assembly will be required. Order the tension bolt suitable for the stations after a station was increased (decreased), since the length of a tension bolt differs by the number of stations. (For changing the number of stations for a type 43P manifold, wiring unit for the stations and lead assembly will be required.)

1 Loosen the tension bolts connecting the manifold base, and pull out both of 2 tension bolts.

(When equipped with a DIN rail, loosen one DIN rail holding screw on either U side or D side.)

Separate the blocks at the location where station expansion is desired.

Mount additional manifold block assembly.

| Press block-to-block so that there's no gap. After connection, insert a tension bold for desired stations and then tighten it.

▲ Caution (Tightening torque: 2.9 N·m)


(When equipped with a DIN rail, be sure to tighten the DIN rail holding screws after tightening the tension bolts. Tightening torque: 1.4 N·m)

#### 

- 1. Be sure to shut off the power and air supplies before disassembly. Furthermore, since air may remain inside the actuator, piping and manifold, confirm that the air is completely exhausted before performing any work.
- 2. When disassembly and assembly are performed, air leakage may result if connections between blocks and tightening of the end block's holding screw, is inadequate.
- 3. By adding wiring unit assembly to type 43 manifold, it can be changed to type 43P manifold, too.

#### How to Replace A, B Port Fitting Assembly

By replacing manifold block fitting assemblies or the threaded port block assembly of a type 43(P) manifold, the port size of the A and B ports can be changed. To replace these parts, remove the clip with a flat head screwdriver after the valve has been removed. Insert the fitting assemblies or threaded port block assembly, and then reinsert the clip so that it does not protrude from the manifold block.



#### Fitting Assembly Part No

Fitting Assembly Part No.								
Port size	No.	Note						
One-touch fitting assembly for ø8	VVQ4000-50B-C8							
One-touch fitting assembly for ø10	VVQ4000-50B-C10							
One-touch fitting assembly for ø12	VVQ4000-50B-C12							
One-touch fitting for ø 5/16"	VVQ4000-50B-N9							
One-touch fitting for ø 3/8"	VVQ4000-50B-N11							
1/4 threaded type port block assembly	SY9000-58A-02*	-* at the end of part number denotes the thread type.						
3/8 threaded type port block assembly	SY9000-58A-03*	-* at the end of part number denotes the thread type.						
Plug assembly	SY9000-62-1A							

Note 1) Be careful to avoid damage or contamination of O-rings, as this can cause air leakage.

Note 2) Although replacing One-touch fittings of P, R port is also possible, use caution to the cases, etc. in which solenoid valves are often used at the same time by using the smaller sized fittings than the standard size (ø12). Because there may not be able to supply or exhaust air sufficiently in comparison with the valve performances. Besides, although fittings used for A, B port are the same, it is not possible to use the threaded type port block assembly.

Note 3) The basic order unit of the One-touch fitting is 10 pcs.



421

LYS

SZ ۷F

VP4

S0700

VO

V04

V05

VOC

VOC4 VOZ

SO VFS **VFR VQ7** 

# 5 Port Solenoid Valve Base Mounted Manifold


Note) AC-type models that are CE-compliant have DIN terminals only. [Option]

Stacking Type/DIN Rail Mounted/Individual Wiring

# Туре 45

# Series **SY3000/5000**

#### **How to Order Manifold**



Option 

When a longer DIN rail is desired than the specified stations, specify the station number to be required. (20 stations at maximum)

### CE-compliant

Q CE-compliant

Note) AC-type models that are

CE-compliant have DIN

terminals only.


#### A, B port size

One-touch fitting (Metric size						
Symbol	Port size	Applicable series				
C4	One-touch fitting for ø4					
C6	One-touch fitting for ø6	SY3000				
M	Mixed					
C4	One-touch fitting for ø4					
C6	One-touch fitting for ø6	SY5000				
C8	One-touch fitting for ø8	010000				
M	Mixed					

•)	One-touch fitting (Inch size)							
	Symbol	Port size	Applicable series					
	N3	One-touch fitting for ø 5/32"						
	N7	One-touch fitting for ø 1/4"	SY3000					
	M	Mixed						
	N3	One-touch fitting for ø 5/32"						
	N7	One-touch fitting for ø 1/4"	SY5000					
	N9	One-touch fitting for ø 5/16"	515000					
	M	Mixed						

- \* In the case of mixed specifications (M), indicate separately on the manifold specification sheet.
- Refer to pages 502 to 506 for external pilot specifications and built-in silencer.

#### How to Order Manifold Assembly (Example)



### Base Mounted Series SY3000/5000



**How to Order Valve** 

Note) AC-type models that are CE-compliant have DIN terminals only



LYS

SZ

۷F

VP4

VO

V04

V05

VOC

VOC4


VOZ

SO

VFS

**VFR** 

**VQ7** 



- \* LN, MN type: with 2 sockets.
- \* D and DO only available for SY5000.
  - 'Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C).
- Refer to page 519 for details.
- \* Refer to page 522 for connector cable of M8 connector.
- \* M8 connector conforming to IEC60947-5-2 standard is also available. Refer to page 509 for details.
- \* Refer to page 519 for the lead wire length of L and M plug connectors.
- Refer to page 520 for the connector assembly with cover for L and M plug connectors.

<sup>\*</sup> When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the integrated manifold are supplied with the solenoid valve, but the stacking type gaskets are not included. When the stacking type gaskets are required, order them separately.



Note) Enter the cable length symbols in □. Please be sure to fill in the blank referring to page 523.

# Type 45 Series SY3000/5000



#### **Manifold Specifications**

Model		SS5Y3-45(-Q)	SS5Y5-45(-Q)		
Applicable valve		SY3□40	SY5□40		
Manifold type		Stacking type/DIN rail mounted			
P (SUP)/R (EXH)		Common SUP, Common EXH			
Valve stations		2 to 20 stations Note 1)			
A, B port	Location	Base			
Porting specifications	Direction	Side			
	P, R port	C8 (One-touch fitting for ø8)	C10 (One-touch fitting for ø10)		
Port size	A, B port	C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6)	C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)		
Manifold base we		2 to 10 stations: W = 22n + 118 2 to 10 stations: W = 47n + 15			
W (g), n: Stations		11 to 20 stations: W = 22n + 140	11 to 20 stations: W = 47n + 190		

Note 1) For more than 11 stations, supply pressure to P port on both sides and exhaust from R port on both

#### Flow Characteristics

	Port	size		Flow characteristics						
Model	1,5,3	4 ,2	1 →	$1 \rightarrow 4/2 \ (P \rightarrow A/B)$		4/2 → 5/3 (A/B → EA/EB				
	(P,EA,EB)	(A ,B)	C (dm3/(s-bar))	b	Cv	C (dm3/ (s-bar) )	b	Cv		
SS5Y3-45	C8	C6	0.88	0.21	0.22	0.95	0.18	0.22		
SS5Y5-45	C10	C8	2.2	0.24	0.53	2.5	0.18	0.58		


Note) The value is for manifold base with 5 stations and individually operated 2 position type.


# Base Mounted Series SY3000/5000 IVIS



#### **Manifold Option**

#### ■Individual SUP spacer assembly ■Individual EXH spacer assembly ■SUP blocking disk





	Assembly part no.		
SY3000	SY3000-38-2A(-Q)	M5 x 0.8	11
SY5000	SY5000-38-16*A(-Q)	1/8	15

Note) The SUP port may be either on the lead wire side or on the end plate side. (An assembly is shipped under the condition shown in the figure.)

	Assembly part no.		
SY3000	SY3000-39-2A(-Q)		
SY5000	SY5000-39-16*A(-Q)	1/8	15


Note) The EXH port may be either on the lead wire side or on the end plate side. (An assembly is shipped under the condition shown in the figure.)

### ■Dimensions/DIN rail

#### VZ1000-11-1-□

#### Refer to L dimensions

Fill in 
with an appropriate no. listed on the table of DIN rail dimensions shown below.



No.	0	1	2	3	4	5	6	7	8	9	10
L Dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223
No.	11	12	13	14	15	16	17	18	19	20	21
L Dimension	235.5	248	260.5	273	285.5	298	310.5	323	335.5	348	360.5
No.	22	23	24	25	26	27	28	29	30	31	32
L Dimension	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498
No.	33	34	35	36	37	38	39	40	41	42	43
L Dimension	510.5	523	535.5	548	560.5	573	585.5	598	610.5	623	635.5
No.	44	45	46	47	48	49	50	51	52	53	54
L Dimension	648	660.5	673	685.5	698	710.5	723	735.5	748	760.5	773
No.	55	56	57	58	59	60	61	62	63	64	65
L Dimension	785.5	798	810.5	823	835.5	848	860.5	873	885.5	898	910.5
No.	66	67	68	69	70	71					

L Dimension 923 935.5 948 960.5 973 985.5 \* Refer to L1 dimension on pages starting with pages 428 to 431 for lengths that correspond to the number of manifold stations.

By installing a SUP blocking disk in the pressure supply passage of a manifold valve, it is possible to supply two or more different high and low pressures to one manifold.



Series	Part no.
SY3000	SX3000-77-1A
SY5000	SX5000-77-1A

#### ■EXH blocking disk

By installing an EXH blocking disk in the exhaust passage of a manifold valve, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to divide both exhausts.)



eries	Part no.	1	Series	Part no.
/3000	SX3000-77-1A	1	SY3000	SX3000-77-1A
/5000	SX5000-77-1A	1	SY5000	SX5000-77-1A
		•		

#### Label for block disk

The labels shown below are used on manifold stations containing SUP/EXH blocking disk(s) to show their location. (3 pcs. each)

#### VZ3000-123-1A

Label for SUP block disk Label for EXH block disk Label for SUP/EXH block disk








Note) When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block disk is mounted.

#### Silencer with One-touch fitting

The silencer plugs directly into the One-touch fittings of the manifold.



Series	Model	Effective area mm²	Α	В	С
For SY3000 (Ø8)	AN15-C08	20	ø13	20	45
For SY5000 (Ø10)	AN20-C10	30	ø16.5	30.5	57.5

#### ■Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports. Purchasing order is available in units of 10 pieces.



#### **Dimensions**

Applicable fittings size ød	Model	Α	L	D
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12
1/8"	KQ2P-01	16	31.5	5
5/32"	KQ2P-03	16	32	6
1/4"	KQ2P-07	18	35	8.5
5/16"	KQ2P-09	20.5	39	10

LYS

SZ ۷F

VP4

S0700 VO

V04

V05 VQC

VOC4

VOZ SO


VFS **VFR** 

**VQ7** 

#### **Manifold Option**

■ How to Order Interface Regulator (SY3000, 5000 only)





P P port


A1 A port (P controlled type, A port regulation)
B1 B port (P controlled type, B port regulation)

#### ♦ Pressure gauge connection port

05	Pressure gauge (G15-10-01) [for odd number station]
06	Pressure gauge (G15-10-01) [for even number station]
M1	Plug (M-5P)

In the case of Series ARBY3000 with a pressure gauge when mounting on the manifold, use caution that the part numbers are different between the odd no. stations and the even no. stations to avoid gauges from interfering from each others.

#### Series SY5000



Regulating port


P P port
A1 A port (P controlled type, A port regulation)
B1 B port (P controlled type, B port regulation)

Pressure gauge connection port


00 Pressure gauge (G15-10-01)

M1 Plug (M-5P)


ARBY3000-05-□-2 (For mounting odd number stations)



ARBY3000-06-□-2 (For mounting even number stations)




ARBY3000-M1-□-2



ARBY5000-00-□-2

ARBY5000-M1-□-2



Note) ARBY is not CE-compliant.

#### Accessory


Series	Round head combination screw Reference screw size	Gasket
ARBY3000	SY3000-23-10 (M2 x 36)	SX3000-57-4
ARBY5000	AC00283 (M3 x 48.5)	SX5000-57-6

**⚠** Caution

Mounting screw tightening torques

M2: 0.17 N·m M3: 0.8 N·m

# Type 45 Series SY3000/5000




14.5 15.5

16.5 17.5 12.5

13.5 14.5 15.5

#### With interface regulator (with gauge)




Block separation button (Push type)


# Base Mounted Series SY3000/5000 Type 45

[ ]: AC

**Dimensions: Series SY3000** 


#### SS5Y3-45- Stations B- C4, N3






Stations n	2 stations	3	4	5	6	7	8	9	10 stations	
L1	110.5	123	135.5	148	160.5	173	185.5	185.5	198	
L2	100	112.5	125	137.5	150	162.5	175	175	187.5	
L3	87	97.5	108	118.5	129	139.5	150	160.5	171	
L4	11.5	12.5	13.5	14.5	15.5	16.5	17.5	12.5	13.5	
Stations n	11 stations	12	13	14	15	16	17	18	19	20 stations
Stations n	11 stations 210.5		13 235.5		<b>15</b> 248	<b>16</b> 260.5		18 285.5		20 stations 310.5
	210.5		235.5	248	-	260.5		285.5		310.5
L1	210.5 200	223 212.5	235.5	248 237.5	248	260.5 250	273	285.5 275	298	310.5 300


#### L plug connector



#### M plug connector



#### M8 connector (WO)



Note) Refer to page 523 for dimensions of connector types. SJ

SY

SV

SYJ

SZ

۷F VP4

S0700

vo VQ4

VQ5


vqc VQC4

VQZ


SQ **VFS** 

VFR VQ7

# Type 45 Series SY3000/5000




#### With interface regulator (with gauge)




### Base Mounted Series SY3000/5000 Type 45

#### **Dimensions: Series SY5000**









										_
Stations n	2 stations	3	4	5	6	7	8	9	10 stations	
L1	135.5	148	160.5	185.5	198	210.5	223	248	260.5	
L2	125	137.5	150	175	187.5	200	212.5	237.5	250	
L3	102	118	134	150	166	182	198	214	230	
L4	16.5	15	13	17.5	16	14	12.5	17	15	
Stations n	11 stations	12	13	14	15	16	17	18	19	<b>20</b> statio
L1	273	285.5	310.5	323	335.5	360.5	373	385.5	398	423
L2	262.5	275	300	312.5	325	350	362.5	375	387.5	412.
L3	246	262	278	294	310	326	342	358	374	390

L4 13.5 11.5 16 14.5 12.5 17 15.5 13.5 12 16.5

#### L plug connector



#### M plug connector




#### M8 connector (WO)

### 137.8 123 10.4 25.2 58.1 M8 x 1

Note) Refer to page 523 for dimensions of connector types.

#### DIN terminal (D, Y)



SJ

SY

SV

SYJ

SZ

۷F VP4

S0700

vo

VQ4 VQ5

voc

VQC4


VQZ SQ

**VFS** 

VFR VQ7

# Type 45 Series SY3000/5000

# DIN Rail Manifold Exploded View Type 45



Replacement Parts

	neplacement raits								
No.	Description	Part no.		Note					
IVO.	Description	SY3000	SY5000	Note					
1	Manifold block assembly	SX3000-50-1A-□□(-Q)	SX5000-50-1A-□□(-Q)	□□: SY3000 (Metric size) C4: With One-touch fitting for ø4 (Inch size)  SY5000 (Metric size) C4: With One-touch fitting for ø6 SY5000 (Metric size) C4: With One-touch fitting for ø6 C6: With One-touch fitting for ø6 C8: With One-touch fitting for ø6 C8: With One-touch fitting for ø6 C8: With One-touch fitting for ø8 (Gasket 6 is supplied as an accessory.)					
2	SUP/EXH block assembly	(Metric size) SX3000-51-1A (Inch size) SX3000-51-15A	(Metric size) SX3000-51-1A (Inch size) SX5000-51-15A	P, R port SY3000 (Metric size) With One-touch fitting for ø8 (Inch size) With One-touch fitting for ø5/re* P, R port SY5000 (Metric size) With One-touch fitting for ø10 (Inch size) With One-touch fitting for ø3/re*					
3	End block assembly R	SX3000-52-1A(-Q)	SX5000-52-1A(-Q)	For D side					
4	End block assembly L	SX3000-53-1A(-Q)	SX5000-53-1A(-Q)	For U side					
_	Round head combination screw	SY3000-23-4	AC00077						
5	Reference screw size	(M2 x 21)	(M3 x 26)						
6	Gasket	SX3000-57-4	SX5000-57-6						
7	DIN rail VZ1000-11-1-□			Refer to page 425.					

### Base Mounted Series SY3000/5000 Type 45

#### **DIN Rail Manifold Exploded View**

#### How to Increase Manifold Bases Station expansion is possible at any position.


- Loosen DIN rail holding screw (a) fixing the manifold base until it begins to turn idly. (While pressing DIN rail releasing buttons (c), at two locations, separate the manifold base from the DIN rail.)
- Press manifold block assembly dividing button (b), that are at the location where manifold bases are to be added, until button (b) locks, and then separate the block assemblies.
- Mount additional manifold block assembly on the DIN rail as shown in the figure 1.
- - (While lightly holding the blocks after fixing an end block on one side, tighten the other end block for for better sealing.)

#### **⚠** Caution

Note 1) When there are 10 or fewer manifold block assemblies, and more are added to make a total of 11 or more, a supply/exhaust block assembly must also be added.


Note 2) When disassembly and assembly are performed, air leakage may result if connections between blocks and tightening of the end block's holding screw, is inadequate. Before supplying air, confirm that there are no gaps, etc. between blocks, and that manifold blocks are securely fastened to the DIN rail. Then supply air and confirm that there is no air leakage before operating.

#### Fig. (1) Block mounting procedure



Hook the DIN rail here and press down in the direction of the arrow until a click sound is heard.

#### **How to Change Fitting Assembly**



Type 45 manifold permits change in the A and B port sizes by changing the manifold block fitting assembly.

After removing the valve, remove the clip with a screwdriver, etc. For mounting a new fitting assembly, insert it and then insert a clip until it will not come out of the manifold block.

#### Fitting Assembly Part No.

#### Metric size

SY3000		One-touch fitting for ø4	VVQ1000-50A-C4
513000	One-touch fitting for ø6	VVQ1000-50A-C6	
SY5000	One-touch fitting for ø4	VVQ1000-51A-C4	
	One-touch fitting for ø6	VVQ1000-51A-C6	
		One-touch fitting for ø8	VVQ1000-51A-C8

#### Inch size

	0.20		
	SY3000	One-touch fitting for ø5/32"	VVQ1000-50A-N3
	513000	One-touch fitting for ø 1/4"	VVQ1000-50A-N7
	SY5000	One-touch fitting for ø5/32"	VVQ1000-51A-N3
		One-touch fitting for ø 1/4"	VVQ1000-51A-N7
		One-touch fitting for ø5/16"	VVQ1000-51A-N9

Note 1) P and R ports cannot be changed.

Note 2) Use caution that O-rings must be free from scratches and dust.
Otherwise, air leakage may result.

Note 3) Purchasing order is available in units of 10 pieces.

SJ

SY

SY

SYJ

SZ

VF

VP4

S0700 VO

VQ4

VQ5 VOC

VOC4

VQZ

SO

VFS

VFR VO7

# 5 Port Solenoid Valve **Base Mounted Manifold**


Stacking Type/DIN Rail Mounted/Connector Box





# Series SY3000/5000

#### **How to Order Manifold**



#### Option

When a longer DIN rail is desired than the specified stations, specify the station number to be required. (Max. 20 stations)

#### A/B port size

One-touch fitting (Metric size)			One-touch fitting (Inch size)			
Symbol	Port size	Applicable series	Symbol		Applicable serie	
C4	One-touch fitting for ø4			One-touch fitting for ø5/32'		
C6	One-touch fitting for ø6	SY3000	N7	One-touch fitting for ø1/4"	SY3000	


Symbol	Port size	Applicable series			
C4	One-touch fitting for ø4				
C6	One-touch fitting for ø6	SY3000			
M	Mixed				
C4	One-touch fitting for ø4				
C6	One-touch fitting for ø6	SY5000			
C8	One-touch fitting for ø8	515000			
M	Mixed				

Mixed N3 One-touch fitting for ø<sup>5</sup>/32 N7 One-touch fitting for ø1/4" SY5000 N9 One-touch fitting for ø5/16 М Mixed \* In the case of mixed specifications, indicate separately on the


manifold specification sheet.

CE-compliant Nil Q CE-compliant

#### How to Order Manifold Assembly (Example)



#### **How to Order Valve**



\* When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the integrated manifold are supplied with the solenoid valve, but the stacking type gaskets are not included. When the stacking type gaskets are required, order them separately.



Refer to pages 502 to 506 for external pilot specifications and built-in silencer

### Base Mounted Series SY3000/5000 TOP 15 AM

#### **Manifold Specifications**

Model		SS5Y3-45-A-(Q)	SS5Y5-45-A-(Q)		
Applicable valve		SY3□40	SY5□40		
Manifold type		Stacking type/D	IN rail mounted		
P (SUP)/R (EXH)		Common SUP,	Common EXH		
Valve stations		2 to 16 sta	tions Note 1, 2)		
A, B port	Location	Ba	se		
Porting specifications	Direction	Side			
	P, R port	C8 (One-touch fitting for ø8)	C10 (One-touch fitting for ø10)		
Port size	A, B port	C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6)	C4 (One-touch fitting for ø4) C6 (One-touch fitting for ø6) C8 (One-touch fitting for ø8)		
Manifold base weight W (g) n: Stations		2 to 10 stations: W = 26n + 207 11 to 20 stations: W = 26n + 229	2 to 10 stations: W = 52n + 245 11 to 16 stations: W = 52n + 279		
Applicable flat ribbon cable connector		Flat ribbon cable connector Socket: 20 pins MIL type with strain relief conforming to MIL-C-83503			
Wiring specificati	ons	+COM specifications (Type 45-A), -COM specifications (Type 45-NA)			

Note 1) For more than 11 stations, supply pressure to P port on both sides and exhaust from R port on both sides


Note 2) There is a limit depending on the number of solenoids. Refer to "How to Order".

#### Flow Characteristics

	Port size		Flow characteristics						
Model 1, 5, 3 4, 2		4, 2	$1 \rightarrow 4/2 (P \rightarrow A/B)$			4/2 → 5/3 (A/B → EA/EB)			
	(P, EA, EB)	(A, B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	C۷	
SS5Y3-45-□	C8	C6	0.88	0.21	0.22	0.95	0.18	0.22	
SS5Y5-45-□	C10	C8	2.2	0.24	0.53	2.5	0.18	0.58	
** * * ***									


Note) The value is for manifold base with 5 stations and individually operated 2 position type.


#### Manifold Wiring Diagram (Circuit diagram for the reference layout)



- Connector box for +COM allows transmission until G71-OD16, manufactured by OMRON Corp., to be connected directly for serial transmission. Additionally, it can also be used for the PC wiring system
- When an external power source must be supplied to the manifold, correct polarity must be observed, otherwise damage to PLC is possible.
- . The wiring of solenoid valves, corresponds with the labeled connector box 0 to 15 from D side.
- If valves other than non-polar type are used, this may cause malfunction.

#### -COM electric circuit diagram





SJ SY

SYJ

SZ

۷F

VP4

S0700

VO

V04

VQ5 VQC

VOC4

VOZ


SO VFS


VFR

**VQ7** 

#### **Manifold Option**

#### Individual SUP spacer assembly Individual EXH spacer assembly SUP blocking disk





	Assembly part no.		t
	SY3000-38-2A(-Q)		11
SY5000	SY5000-38-16+A(-Q)	1/8	15

Note) The SUP port may be either on the lead wire side or on the end plate side. (An assembly is shipped under the condition shown in the figure.)

Cable assembly

AXT100-FC20

	Assembly part no.		
SY3000	SY3000-39-2A(-Q)	M5 x 0.8	11
SY5000	SY5000-39-16+A(-Q)	1/8	15

Note) The EXH port may be either on the lead wire side or on the end plate side. (An assembly is shipped under the condition shown in the figure.)

By installing a SUP blocking disk in the pressure supply passage of a manifold valve, it is possible to supply two or more different high and low pressures to one manifold.



Series	Part no.
SY3000	SX3000-77-1A
SY5000	SX5000-77-1A

#### ■EXH blocking disk

By installing an EXH blocking disk in the exhaust passage of a manifold valve, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to divide both exhausts.)



Series	Part no.
SY3000	SX3000-77-1A
SY5000	SX5000-77-1A

#### Label for block disk

The labels shown below are used on manifold stations containing SUP/EXH blocking disk(s) to show their location. (3 pcs. each)

#### VZ3000-123-1A

Label for SUP block disk Label for EXH block disk

Label for SUP/EXH block disk








Note) When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block dick is mounted

#### Silencer with One-touch fitting

The silencer plugs directly into the One-touch fittings of the manifold.



Series	Model	Effective area mm <sup>2</sup>	Α	В	O
For SY3000 (Ø8)	AN15-C08	20	ø13	20	45
For SY5000 (Ø10)	AN20-C10	30	ø16.5	30.5	57.5

#### ■ Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports. Purchasing order is available in units of 10 pieces.



#### **Dimensions**

Applicable fittings size ød	Model	Α	L	D
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12
1/8"	KQ2P-01	16	31.5	5
5/32"	KQ2P-03	16	32	6
1/4"	KQ2P-07	18	35	8.5
5/16"	KQ2P-09	20.5	39	10

### Red Terminal number (15.6)

#### **Connector Assembly for Flat Ribbon Cables**

Cable length (L)	Assembly part no.	Note
1.5 m	AXT100-FC20-1	Cable 20 core
3 m	AXT100-FC20-2	x 22 AWG
5 m	AXT100-FC20-3	X 22 AWG

<sup>\*</sup> For other commercial connectors, use a 20 pins with strain relief conforming to MII -C-83503

#### Connector manufacturers' example

- . Sumitomo 3M Limited
- Fujitsu Limited
- · Japan Aviation Electronics Industry, Ltd.
- . J.S.T. Mfg. Co., Ltd.



When mounting a valve or spacer on the manifold base or sub-plate, etc., those mounting directions are determined. If mounted in the wrong direction, the equipment to be connected may cause malfunction. Refer to external dimensions, and then mount it.



SJ SY

SY

SV

SYJ

SZ

۷F

VP4


S0700 VQ

V04 V05 VOC VQC4 VQZ SQ VFS VFR VQ7

#### **Manifold Option**

■ How to Order Interface regulator (SY3000, 5000 only)





Regulating port Р


P port A port (P controlled type, A port regulation) Α1 B1 B port (P controlled type, B port regulation)

#### Pressure gauge connection port

05	Pressure gauge (G15-10-01) [for odd number stat
06	Pressure gauge (G15-10-01) [for even number sta
M1	Plug (M-5P)

\* In the case of Series ARBY3000 with a pressure gauge when mounting on the manifold, use caution that the part numbers are different between the odd no. stations and the even no. stations to avoid gauges from interfering from each others.

#### Series SY5000



Regulating port

P port Р A port (P controlled type, A port regulation) Α1 B1 B port (P controlled type, B port regulation)

Pressure gauge connection port


00 Pressure gauge (G15-10-01)


M1 Plug (M-5P)


ARBY3000-05-□-2 (For odd number stations) ARBY3000-06-□-2 (For even number stations) ARBY3000-M1-□-2


ARBY5000-00-□-2

ARBY5000-M1-□-2









Note) ARBY is not CE-compliant.

#### Accessory

Series	Round head combination screw Reference screw size	Gasket
ARBY3000	SY3000-23-10 (M2 x 36)	SX3000-57-4
ARBY5000	AC00283 (M3 x 48.5)	SX5000-57-6


Caution

Mounting screw tightening torques

M2: 0.16 N·m M3: 0.8 N·m


### Type 45-AA Series SY3000/5000

#### **Dimensions: Series SY3000**



### Base Mounted Series SY3000/5000





439

L3 84 100 116 132 148 164 180 196 212 246 262 278 294 310 326 L4 11.5 16 14.5 12.5 17 15.5 13.5 12 16.5 12 16.5 14.5 13 17.5 15.5

\* Two SUP/EXH blocks are provided for models with 11 stations or more.


42.7

Block separation button

(Push type)

### Type 45-NA Series SY3000/5000

### **DIN Rail Manifold Exploded View**



Replacement Parts

No.	Description	Par	t no.				Not	10		
NO.	Description	SY3000	SY5000				INO	te		
1	Manifold block assembly	SX3000-50-1A-□□(-Q)	SX5000-50-1A-□□(-Q)	C6: With •SY5000 (Metric si C4: With C6: With C8: With	One-touch One-touch	fitting for ø fitting for ø fitting for ø fitting for ø	4 1 6 1 ( 4 1 6 1 8 1	Inch size) 13: With One-touch fitting for ø5/32' 17: With One-touch fitting for ø1/4* Inch size) 13: With One-touch fitting for ø5/32' 17: With One-touch fitting for ø5/32' 19: With One-touch fitting for ø5/16' 19: With One-touch fitting for ø5/16' 10: With One-touch fitting for ø5/32'		
2	SUP/EXH block assembly	(Metric size) SX3000-51-1A (Inch size) SX3000-51-15A	(Metric size) SX3000-51-1A (Inch size) SX5000-51-15A	, ,	(Ir SY5000 (M	nch size)	With	n One-touch fitting for ø8 n One-touch fitting for ø5/ <sub>16</sub> " n One-touch fitting for ø10 n One-touch fitting for ø3/ <sub>8</sub> "		
3	End block assembly R	SX3000-52-1A(-Q)	SX5000-52-1A(-Q)	A(-Q) For D side				side		
4	End block assembly L	SX3000-53-1A(-Q)	SX5000-53-1A(-Q)			F	or U	side		
5	Connector box	VZ3000	-106-1A	For 24 VDC only						
6	Rail stopper	TXE1	-SMC	Made by Kasuga Electric Works						
		SY3000-43-1A-	SY3000-43-2A-□	+COM		to 8 statio to 16 stati				
7	0	SY3000-43-2A-	SY3000-43-3A-□	+COM		to 16 stati to 8 statio		□ : Mark tube no.		
′	Connecter assembly	SY3000-43-1NA-	SY3000-43-2NA-	-СОМ		to 8 station to 16 station		. Wark tube no.		
		SY3000-43-2NA-	SY3000-43-3NA-	-СОМ		to 16 station		1		
8	Dust cap	VZ300	0-63-2					•		
9	Round head combination screw	SY3000-23-4	AC00077					-		
3	Reference screw size	(M2 x 21)	(M3 x 26)							
10	Gasket	SX3000-57-4	SX5000-57-6							
11	DIN rail VZ1000-11-1-□					Refer	to pa	age 425.		

### Base Mounted Series SY3000/5000



#### **How to Increase Manifold Bases**

Station expansion is possible at any position.

1 Loosen DIN rail holding screw (a) fixing the manifold base until it begins to turn idly. (While pressing DIN rail releasing buttons ©, at two locations, separate the manifold base from the DIN rail.)

Press manifold block assembly dividing button (b), that are at the location where manifold bases are to be added, until button (b) locks, and then separate the block assemblies.

3 Mount additional manifold block assembly on the DIN rail as shown in the figure 1.

4 Press the block assemblies until a click sound is produced, and tighten the DIN rail holding screw (a) to fix them to the DIN rail. **△Caution** (Tightening torque: 1.4 N·m)

(While lightly holding the blocks after fixing an end block on one side, tighten the other end block for for better sealing.)

5 Untighten the rail stopper bolt (1) to demount the connector box from the DIN rail, and when remounting it, tighten the bolt while pressing it against the rail.

#### **∆**Caution


Note 1) When there are 10 or fewer manifold block assemblies, and more are added to make a total of 11 or more, a supply/exhaust block assembly must also be added.

Note 2) When disassembly and assembly are performed, air leakage may result if connections between blocks and tightening of the end block's holding screw, is inadequate. Before supplying air, confirm that there are no gaps, etc. between blocks, and that manifold blocks are securely fastened to the DIN rail. Then supply air and confirm that there is no air leakage before operating.

Note 3) One connector assembly is necessary for one solenoid. When a number is necessary for the connector assembly mark tube, suffix the number to the part no. (0 to 15 are provided as mark tube numbers.)

Ex) +COM spec.: D type for 2 to 8 stations: No. 10 SY3000-43-1A-10

#### Fig. (1) Block mounting procedure



SJ

LYS

SZ

VP4

S0700

VO

V04

V05

VOC

VOC4

VOZ

SO

VFS **VFR** 

V07

#### How to Change Fitting Assembly

Type 45 manifold permits change in the A and B port sizes by changing the manifold block fitting assembly.

After removing the valve, remove the clip with a screwdriver, etc. For mounting a new fitting assembly, insert it and then insert a clip until it will not come out of the manifold block.

#### Fitting Assembly Part No.

#### Metric size

SY3000	One-touch fitting for ø4	VVQ1000-50A-C4
513000	One-touch fitting for ø6	VVQ1000-50A-C6
	One-touch fitting for ø4	VVQ1000-51A-C4
SY5000	One-touch fitting for ø6	VVQ1000-51A-C6
	One-touch fitting for ø8	VVQ1000-51A-C8


#### Inch size

SY3000	One-touch fitting for ø5/32"	VVQ1000-50A-N3
513000	One-touch fitting for ø 1/4"	VVQ1000-50A-N7
	One-touch fitting for ø5/32"	VVQ1000-51A-N3
SY5000	One-touch fitting for ø 1/4"	VVQ1000-51A-N7
	One-touch fitting for ø5/16"	VVQ1000-51A-N9

Note 1) P and R ports cannot be changed.


Note 2) Use caution that O-rings must be free from scratches and dust. Otherwise, air leakage may result.

Note 3) Purchasing order is available in units of 10 pieces.



### **EX510 Gateway-type Serial Transmission System** Base Mounted Manifold/Stacking Type [Option] Series SY3000/5000

#### **How to Order Manifold**



SS5Y3-45S6AD-05D-C6 (-Q) 1 set (45S6A type 5-station manifold part no.) \* SY3140-5LOU (-Q) 3 sets (Single solenoid part no.)

\* SY3240-5LOU (-Q) 2 sets (Double solenoid part no.) The asterisk denotes the symbol for assembly. Prefix to the part no. of the

Add the valve and option part number under the manifold base part number When entry of part numbers becomes complicated, indicate by the manifold specification sheet. For a manifold for an EX510, the length of the lead wire for a connector assembly depends on the number of stations. Therefore, the manifold assembly is shipped with the valves (including blanking plates) and connector assembly mounted on it, as the standard specification. Be sure to specify the part nos, of the solenoid valves to be mounted.

#### SI unit part no.

\*For the special specifications, indicate

separately on a manifold specification sheet.


Symbol	SI unit specifications	SI unit part no.	Page
Nil	NPN output (+COM.)	EX510-S001	P.2143
N	PNP output (-COM.)	EX510-S101	P.2143

Refer to page 2124 and the Operation Manual for the details of EX510 Gateway-type Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

### Base Mounted Manifold Series SY3000/5000 Type 45S6A

# pe 4330A

#### **How to Order Valves**



• When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the integrated manifold are supplied with the solenoid valve, but the stacking type gaskets are not included. When the stacking type gaskets are required, order them separately. SJ

SY

SV

SYJ

SZ VF

VP4

S0700

VO

VQ4

VQ5

VQC

VQC4

VQZ

SQ VFS


VFR


VQ7


### 45S6A Series **SY3000/5000**

#### **Dimensions**


SY3000: SS5Y3-45S6A D- Stations U-C4, N3







(Station n)--- (Station 1)




Stations n	2 stations	3	4	5	6	7	8	9	10 stations
L1	135.5	148	148	160.5	173	185.5	198	210.5	223
L2	125	137.5	137.5	150	162.5	175	187.5	200	212.5
L3	70.5	81	91.5	102	112.5	123	133.5	144	154.5
L4	16	17	12	13	14	15	16	17	18


444

### Base Mounted Manifold Series SY3000/5000 Type 45\$6A







#### With interface regulator (with gauge)



(Station n) - - - (Station 1)

connector assembly.)





VQ5 vqc VQC4

> VQZ SQ

SJ SY

SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

VQ4

VFS VFR


VQ7


Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	148	160.5	173	185.5	185.5	198	210.5	223	235.5	248	260.5	260.5	273	285.5	298
L2	137.5	150	162.5	175	175	187.5	200	212.5	225	237.5	250	250	262.5	275	287.5
L3	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234
L4	14	15	16	17	12	13	14	15	16	17	18	12.5	13.5	14.5	15.5

### 100 45S6A Series SY3000/5000


#### **Dimensions**

### SY5000: SS5Y5-45S6A D- Stations U-C4, N3











Stations n	2 stations	3	4	5	6	7	8	9	10 stations
L1	148	160.5	173	198	210.5	223	248	260.5	273
L2	137.5	150	162.5	187.5	200	212.5	237.5	250	262.5
L3	84	100	116	132	148	164	180	196	212
L4	15.5	14	12	16.5	15	13	17.5	16	14

446


# Base Mounted Manifold Series SY3000/5000 110-4556A

### SY5000: SS5Y5-45S6A U-Stations B-C6, N9





#### With interface regulator (with gauge)



VQ4 VQ5 VOC

VQC4

SJ SY

SV

SYJ SZ

VP4

S0700


VO

VQZ SQ

VFS

VFR VQ7

(Station n) - - - (Station 1)





Stations n	2 stations	3	4	5	6	7	8	9	10	11	12	13	14	15	16 stations
L1	160.5	185.5	198	210.5	223	248	260.5	273	298	310.5	323	335.5	360.5	373	385.5
L2	150	175	187.5	200	212.5	237.5	250	262.5	287.5	300	312.5	325	350	362.5	375
L3	102	118	134	150	166	182	198	214	230	246	262	278	294	310	326
L4	13	17.5	15.5	14	12	16.5	15	13	17.5	16	14	12.5	17	15	13.5

#### **Manifold Option**

■ Connector assembly For single solenoid (SY3000-37-81A- -N)

#### For double solenoid (SY3000-37-81A-□-□)





Connector assembly order no. (Can be used for the manifold without a specified layout (8 stations or less)) Integrated type

Model	Part no.	Connector mounting position
····ouo·	SY3000-37-81A-3-N	Single : Starting from the SI unit side From unit 1 to unit 4
	SY3000-37-81A-3-3	Double/3 position: Starting from the SI unit side From unit 1 to unit 4
SS5Y3-45S6A	SY3000-37-81A-4-N	Single : Starting from the SI unit side From unit 5 to unit 8
	SY3000-37-81A-4-4	Double/3 position: Starting from the SI unit side From unit 5 to unit 8
	SY3000-37-81A-4-N	Single : Starting from the SI unit side From unit 1 to unit 4
SS5Y5-45S6A	SY3000-37-81A-4-4	Double/3 position: Starting from the SI unit side From unit 1 to unit 4
55515-4550A	SY3000-37-81A-6-N	Single : Starting from the SI unit side From unit 5 to unit 8
	SY3000-37-81A-6-6	Double/3 position: Starting from the SI unit side From unit 5 to unit 8
	SY3000-37-81A-4-N	Single : For 1 to 4 stations
SS5Y9- 23 SA	SY3000-37-81A-4-9	Double/3 position: For 1 to 4 stations
33313- 43 3A	SY3000-37-81A-6-N	Single : For 5 to 8 stations
	SY3000-37-81A-6-11	Double/3 position: For 5 to 8 stations

Note) The above is for the station addition or maintenance. When ordering a connector assembly separately, a number would not be printed on the connector.

#### ■ Connector assembly SY3000-37-80A-



#### ■ Housing (8 pcs./set) SY3000-44-3A



#### Connector assembly order no. (Can be used for the manifold with a specified layout)

Connector assembly order no. (Can be asea for the mannola with a specifica layout)				
Model Part no.		Connector mounting position		
	SY3000-37-80A-3	Starting from the SI unit side: From unit 1 to unit 4		
SS5Y3-45S6A	SY3000-37-80A-4	Starting from the SI unit side: From unit 5 to unit 8		
33313-4330A	SY3000-37-80A-6	Starting from the SI unit side: From unit 9 to unit 12		
	SY3000-37-80A-7	Starting from the SI unit side: From unit 13 to unit 16		
	SY3000-37-80A-4	Starting from the SI unit side: From unit 1 to unit 4		
SS5Y5-45S6A	SY3000-37-80A-6	Starting from the SI unit side: From unit 5 to unit 8		
33313-4330A	SY3000-37-80A-8	Starting from the SI unit side: From unit 9 to unit 12		
	SY3000-37-80A-10	Starting from the SI unit side: From unit 13 to unit 16		

Note 1) The above is for station addition or maintenance. When ordering a connector assembly separately, a number will not be printed on the connector.

Note 2) After inserting the connector assembly into the housing, be sure to confirm that the lead wire will not come off by lightly pulling the wire. Furthermore, do not reuse the lead wire after it has been inserted and removed.

Note 3) Wiring is set longer than the actual wiring distance.



### Base Mounted Series SY3000/5000 Type 45 Type 45-NA Type 45S6A

#### Stacking Type/DIN Rail Mounted/Individual Wiring: Common Manifold Option

#### ■Blanking plate assembly



(The shape varies depending on the series.)

Series	Assembly part no.
SY3000	SX3000-75-1A(-Q)
SY5000	SX5000-76-5A(-Q)

### \* Thread type

Nil	Rc
F	G
N	NPT
T	NPTF

### **⚠** Caution

Mounting screw tightening torques

M2: 0.16 N·m M3: 0.8 N·m M4: 1.4 N·m SJ

SY

SY

SV SYJ

SZ

VF

VP4

S0700

VQ VQ4

VQ5

VQC

VQC4

VQZ SQ

VFS VFR

VQ7


# 5 Port Solenoid Valve **Base Mounted Manifold**

Stacking Type/DIN Rail Mounted/Plug-in



# Series SY3000/5000

#### **How to Order Manifold**



#### A. B port size •

One-touch fitting (Metric size)				
Symbol	Port size	Applicable series		
C4	One-touch fitting for ø4			
C6	One-touch fitting for ø6	SY3000		
M	Mixed			
C4	One-touch fitting for ø4			
C6	One-touch fitting for ø6			
C8	One-touch fitting for ø8			
М	Mixed			

Symbol	Port size	Applicable series	
N3	One-touch fitting for ø 5/32"		
N7	One-touch fitting for ø 1/4"	SY3000	
M	Mixed		
N3	One-touch fitting for ø 5/32"		
N7	One-touch fitting for ø 1/4"	SY5000	
		1 3 1 3 0 0 0 1	

One-touch fitting (Inch size)

M \* In the case of mixed specifications (M), indicate separately on the manifold specification sheet

\* For special specifications, indicate separately by the manifold specification sheet.

#### Option 6

CE-compliant

When a longer DIN rail is desired than the specified stations, specify the station number to be required. (20 stations at maximum)

N9 One-touch fitting for ø 5/16"


Mixed


#### CE-compliant Nil

a

\* Refer to pages 502 to 506 for external pilot specifications and built-in silencer

#### How to Order Manifold Assembly (Example)





\* When ordering plug-in type solenoid valve as a single unit, gaskets are not included. Order them separately, if necessary. (Refer to page 478 for details.)

### Base Mounted Series SY3000/5000








SJ

SY

LYS

SZ

VP4



Symbol Mounting position Stations U 2 to 10 stations D D side 2 to 10 stations B Both sides 2 to 20 stations

Special specifications

When a longer DIN rail is desired than the specified stations, specify the station number to be required. (20 stations at maximum)

CE-compliant Nil For special specifications, indicate separately by the manifold specification sheet. CE-compliant

Option 6

Applicable series

SY3000

SY5000

Valve stations (Blanking plate assemblies are included.)

D

D side

26 pins (P) connector			
Symbol	Stations	Note	
02	2 stations	Single wiring spec.	
- 1	1	(Applicable up to 20	
20	20 stations	solenoid valves.)	

20 pins (PG) cor			
Symbol	Stations		
02	2 stations	Singl	
	- :	(Appli	

ZU PII	113 (F <i>)</i>	COMMECTOR		ZU PII	113 (F	a) cominector
Symbol	Stations	Note		Symbol	Stations	Note
02	2 stations			02	2 stations	Single wiring spec.
- :	:	(Applicable up to 20		:	- i	(Applicable up to 16
20	20 stations	solenoid valves.)		16	16 stations	solenoid valves.)
• Two stations are necessary for the double, 3 position (Dual body type).						

Symbol	Stations	Note
02	2 stations	Single wiring spec.
:	:	(Applicable up to 8
08	8 stations	solenoid valves)

10 pins (PH) connector

VQ5
voc

V04

VOC4

VOZ

SO

VFS

**VFR** 

**VQ7** 

Type 45T (9 pins terminal bloc	:k)	
SS5Y3-45TD-05	U-	C4

Series 3 SY3000 5 SY5000

#### Terminal block mounting position

Symbol	Mounting position
U	U side
D	D side

#### Valve stations

	Symbol	Stations	Note
	02	2 stations	Cinale wiring ones
	:	- :	Single wiring spec. (Applicable up to 8 solenoid valves)
Ī	08	8 stations	(Uhhiranie ah in 0 soigiloin saises)

- \* This also includes the number of blanking plate assemblies.
- \* Two stations are necessary for the double, 3 position (Dual body type).

#### SUP/EXH block assembly mounting position •

Symbol	Mounting position	Stations	
U	U side	2 to 8 stations	
D	D side	2 to 8 stations	
В	Both sides	2 to 8 stations	
M	Special specifications		

\* For special specifications, indicate separately by the manifold specification sheet.

Note) The terminal block (45T□) manifold has no common polarity. It can be used for both positive and negative common.

#### specified stations, specify the station number to be required. (20 stations at maximum) CE-compliant e

When a longer DIN rail is desired than the

Q CE-compliant

#### A, B port size

Option •

One-touch fitting (Metric size)					
Symbol	Port size	Applicable series			
C4	One-touch fitting for ø4				
C6	One-touch fitting for ø6	SY3000			
M	Mixed				
C4	One-touch fitting for ø4				
C6	One-touch fitting for ø6	SY5000			
C8	One-touch fitting for ø8	313000			
M	Mixed				

### One-touch fitting (Inch size)

Symbol	Port size	Applicable series
N3	One-touch fitting for ø 5/32"	
N7	One-touch fitting for ø 1/4"	SY3000
M	Mixed	
N3	One-touch fitting for ø 5/32"	
N7	One-touch fitting for ø 1/4"	SY5000
N9	One-touch fitting for ø 5/16"	313000
M	Mixed	

\* In the case of mixed specifications (M), indicate separately on the manifold specification sheet.

### Type 45T1 (18 pins terminal block)

SS5Y 3 - 45T1 D Series Option • 3 SY3000 When a longer DIN rail is desired than the 5 SY5000 specified stations, specify the station number to be required. (20 stations at maximum) Terminal block mounting position CE-compliant Symbol Mounting position u I I side

#### Valve stations

Symbol	Stations	Note				
02	2 stations	Cinale wining once				
	:	Single wining spec. (Applicable up to 17 solenoid valves.)				
17	17 stations	(Applicable up to 17 Soletion valves.)				

D side

- \* This also includes the number of blanking plate assemblies.
- \* Two stations are necessary for the double, 3 position (Dual body type).

#### SUP/EXH block assembly mounting position •

Mounting position	Stations		
U side	2 to 10 stations		
D side	2 to 10 stations		
Both sides	2 to 17 stations		
Special specifications			
	D side Both sides		

\* For special specifications, indicate separately by the manifold specification sheet.

C4	One-touch fitting for ø4	
C6	One-touch fitting for ø6	SY3000
М	Mixed	
C4	One-touch fitting for ø4	
C6	One-touch fitting for ø6	SY5000
C8	One-touch fitting for ø8	515000
M	Mixed	
One-	touch fitting (Inch	size)
$\overline{}$		

One-touch fitting (Metric size) Symbol Port size Applicable serie

A, B port size

Q CE-compliant

Symbol	Port size	Applicable series
N3	One-touch fitting for ø 5/32"	
N7	One-touch fitting for ø 1/4"	SY3000
M	Mixed	
N3	One-touch fitting for ø 5/32"	
N7	One-touch fitting for ø 1/4"	SY5000
N9	One-touch fitting for ø 5/16"	515000
M	Mixed	

\* In the case of mixed specifications (M). indicate separately on the manifold specification sheet.








#### **How to Order Manifold**








For special specifications, indicate separately by the manifold specification sheet.

#### **How to Order Valve**



<sup>\*</sup> When ordering plug-in type valve as a single unit, gaskets are not included. Order them separately, if necessary. (Refer to page 478 for details.)



# Base Mounted Series SY3000/5000 Type 45

### **Manifold Specifications**







The state of the s					Florida and a selection				
Model		D-sub connector	Flat ribl	on cable Type	45PI	Termin	al block	Flat ribbon cable PC wiring system compatible	
			Type 45F	Type 45P	Type 45PG	Type 45PH	Type 45T	Type 45T1	Type 45G
Manifold					Plug-in				
P (SUP)/R (EXH)				Common	SUP, Commo	n EXH			
Valve stations Note 1, 2)		2 to 2	0 stations	2 to 16 stations	2 to 8 st	ations	2 to 17 stations	2 to 16 stations	
A, B port Location		Location				Base			
Porting speci	ifications	Direction				Side			
	D D mant	SY3000			C8 (One	-touch fitting for	or ø8)		
Port size	P, R port	SY5000		C10 (One-touch fitting for ø10)					
FUIT SIZE	A D mark	SY3000	C4 (One-touch fitting for ø4)/C6 (One-touch fitting for ø6)						
	A, B port	SY5000	C4 (One-	touch fitting fo	or ø4)/C6 (One	-touch fitting for	or ø6)/C8 (	One-touch	fitting for ø8)
Applicable connector			D-sub connector Complies with MIL-C-24308 JIS-X-5101	Socket: 26 pins MIL type with strain relief	Flat ribbon cable connector Socket: 20 pins MIL type with strain relief Conforming to MIL-C-83503	Socket: 10 pins MIL type with strain relief	(M3)	Terminal block (M3) 18 pins	Flat ribbon cable connector Socket: 20 pins MIL type with strain relief Conforming to MIL-C-83503
Internal w	viring		+CON	1 (Type 45□),	-COM (Type 4	I5N□)	In common between	+COM and -COM.	+ COM
Manifold	base	SY3000		2 to 10 stations: W = 26n + 172					
weight W (g) n: Stations		313000			11 to 20 s	stations: $W = 2$	26n + 199		
		SY5000	2 to 10 stations: W = 54n + 227						
(D-sub con	nector)	313000		11 to 20 stations: W = 52n + 264					
Note 1) For more than 11 stations, supply pressure to P port on both sides and exhaust from R port on both sides					eidee				

Note 2) There is a limit depending on the number of solenoids. Refer to "How to Order".

#### Flow Characteristics

	Port size		Flow characteristics					
Model	1 ,5 ,3	4 ,2	$1 \rightarrow 4/2 \ (P \rightarrow A/B)$			$4/2 \rightarrow 5/3 \text{ (A/B} \rightarrow \text{EA/EB)}$		
	(P,EA,EB)	(A ,B)	C (dm3/(s-bar))	b	Cv	C (dm3/(s-bar))	b	Cv
SS5Y3-45□	C8	C6	0.88	0.21	0.22	0.95	0.18	0.22
SS5Y5-45□	C10	C8	2.2	0.24	0.53	2.5	0.18	0.58

Note) The value is for manifold base with 5 stations and individually operated 2 position type.

SJ

SYJ

SZ

۷F VP4

S0700

VQ VQ4

VQ5

vqc

VQC4

VQZ


SQ

VFS VFR

VQ7

#### **Manifold Option**

#### D-sub connector (25 pins)/Cable assembly



#### D-sub connector cable

D-Sub C	connector cable	
Cable length ( <b>L</b> )	Assembly part no.	Note
1.5 m	AXT100-DS25-015	Cable 25 core
3 m		x 24 AWG
5 m	AXT100-DS25-050	X 24 AVVG

\* When a commercially available connector is required, use a 25 pin female connector conforming to MIL-C24308.

#### Electric characteristics

Electric characteristics					
Item	Characteristics				
Conductor resistance Ω/km, 20°C	65 or less				
Voltage limit V, 1 min, AC	1000				
Insulation resistance MΩkm, 20°C	5 or more				

Note) The min. bending radius of D-sub cable assembly is 20 mm.

#### D-sub connector cable assembly


Terminal numbers							
Terminal no.	Lead wire color	Dot marking					
1	Black	None					
2	Brown	None					
3	Red	None					
4	Orange	None					
5	Yellow	None					
6	Pink	None					
7	Blue	None					
8	Purple	White					
9	Gray	Black					
10	White	Black					
11	White	Red					
12	Yellow	Red					
13	Orange	Red					
14	Yellow	Black					
15	Pink	Black					
16	Blue	White					
17	Purple	None					
18	Gray	None					
19	Orange	Black					
20	Red	White					
21	Brown	White					
22	Pink	Red					
23	Gray	Red					
24	Black	White					
25	White	None					

#### Connector manufacturers' example

- Hirose Electric Co., Ltd.
- · Fujitsu Limited
- · Japan Aviation Electronics Industry, Ltd.
- J.S.T. Mfg. Co., Ltd.

### ■ Flat Ribbon Cable Connector/Cable assembly





#### Flat Ribbon Cable Assembly

Cable length (L)	10 pins	20 pins	26 pins
1.5 m	AXT100-FC10-1	AXT100-FC20-1	AXT100-FC26-1
3 m	AXT100-FC10-2	AXT100-FC20-2	AXT100-FC26-2
5 m	AXT100-FC10-3	AXT100-FC20-3	AXT100-FC26-3
Connector width (W)	17.2	30	37.5

\* For other commercial connectors, use a type with strain relief that conform to MIL-C-83503.


#### Connector manufacturers' example

- · Hirose Electric Co., Ltd.
- Sumitomo 3M Limited
- Fujitsu Limited
- · Japan Aviation Electronics Industry, Ltd.
- J.S.T. Mfg. Co., Ltd.

#### ■ Dimensions/DIN rail

VZ1000 - 11 - 1 -Refer to L dimensions

> \* Fill in 
>
> with an appropriate no. listed on the table of DIN rail dimensions shown below.



No.	0	1	2	3	4	5	6	7	8	9	10
L Dimension	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223
No.	11	12	13	14	15	16	17	18	19	20	21
L Dimension	235.5	248	260.5	273	285.5	298	310.5	323	335.5	348	360.5
No.	22	23	24	25	26	27	28	29	30	31	32
L Dimension	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498
No.	33	34	35	36	37	38	39	40	41	42	43
L Dimension	510.5	523	535.5	548	560.5	573	585.5	598	610.5	623	635.5
No.	44	45	46	47	48	49	50	51	52	53	54
L Dimension	648	660.5	673	685.5	698	710.5	723	735.5	748	760.5	773
No.	55	56	57	58	59	60	61	62	63	64	65
L Dimension	785.5	798	810.5	823	835.5	848	860.5	873	885.5	898	910.5
No.	66	67	68	69	70	71					
L Dimension	923	935.5	948	960.5	973	985.5					

<sup>\*</sup> Refer to L1 dimension on pages starting with pages 460 to 477 for lengths that correspond to the number of manifold stations.





### Base Mounted Series SY3000/5000 Type 45

#### **Manifold Internal Wiring**

#### 45(N)F/D-sub Connector

A D-sub connector used for electric wiring reduces labor during wiring operation. Connectors conforming to MIL are used for interchangeability.








- . The power source terminal is used for connecting to an external power source.
- The maximum number of stations that can be accommodated is 20 manifold stations, with up to 20 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.

#### Type 45(N)P/Flat Ribbon Cable (26 pins)

A flat ribbon cable connector used for electric wiring reduces labor during wiring operation. Connectors conforming to MIL are used for interchangeability.







- . The power source terminal is used for connecting to an external power source.
- The maximum number of stations that can be accommodated is 20 manifold stations, with up to 20 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.

OV

SYJ

SJ

SY

VF

VP4 S0700

VQ

VQ4

VQ5

VQC

VQC4

VQZ SO

VFS

VFR VQ7


@SMC


### Type 45 Series SY3000/5000


#### Manifold Internal Wiring

#### Type 45(N)PG/Flat Ribbon Cable (20 pins)

A flat ribbon cable connector used for electric wiring reduces labor during wiring operation. Connectors conforming to MIL are used for interchangeability.










- . The power source terminal is used for connecting to an external power source.
- The maximum number of stations that can be accommodated is 16 manifold stations, with up to 16 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.

#### Type 45(N)PH/Flat Ribbon Cable (10 pins)

A flat ribbon cable connector used for electric wiring reduces labor during wiring operation. Connectors conforming to MIL are used for interchangeability.







- The power source terminal is used for connecting to an external power source.
- The maximum number of stations that can be accommodated is 8 manifold stations, with up to 8 solenoids.
   (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.




### Base Mounted Series SY3000/5000 1798 45 1

#### **Manifold Internal Wiring**


#### Type 45T/Terminal Block


A terminal block style permits direct cable connection without treatment of lead wires.



- The maximum number of stations that can be accommodated is 8 manifold stations, with up to 8 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.
- There is no polarity in the COM wiring. Supply positive power for +COM spec. and negative power for -COM spec.

Type 45T1/Terminal Block





- The maximum number of stations that can be accommodated is 17 manifold stations, with up to 17 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.
- There is no polarity in the COM wiring. Supply positive power for +COM spec. and negative power for -COM spec.

SJ

SY

3 Y

SYJ

SZ

VP4

S0700

VQ

VQ4

VQ5

VQC

VQC4

VQZ

SQ VFS

VFR


VQ7


# Type 45 Series SY3000/5000

#### **Manifold Internal Wiring**

### Type 45G Flat Ribbon Cable (PC Wiring System compatible)

It's the manifold for 20 pins flat ribbon cable connector which is compliant for PC wiring system.





- The maximum number of stations that can be accommodated is 16 manifold stations, with up to 16 solenoids. (For more stations, please contact SMC.)
- Regardless of the connector mounting position, stations are to be counted from D side as the 1st one.

( For details about the PC wiring system, refer to catalog CAT.E02-20 separately.

### Base Mounted Series SY3000/5000 1798 45 1


#### How to Connect SS5Y□-45□ (Plug-in)

Power terminal is equipped with plug-in manifold of Series SY as standard.


Power terminal enables the power supply to valve from either of manifold or controller side.

The wiring examples should be used for reference when wiring is performed.

#### 1. Wiring example when using manifold power supply terminals



2. Wiring example when not using manifold power supply terminals (Power is supplied to the controller side or along the wiring, etc.)



#### 

Single wire, COM position, etc. of PLC are different from each manufacturer. When connecting with PLC, read the specifications carefully and understand the electrical circuit. Poor wiring could cause damage to PLC, power source, etc. as well as manifold and valve.

SJ

SY

SV.

SYJ

SZ

VP4

S0700

VQ VQ4

VQ5

VQC VOC4


VQZ

SQ VFS

VFR V07

### Series **SY3000/5000**

#### SY3000: D-sub Connector/Plug-in



### Base Mounted Series SY3000/5000 Type 45

Stations n 2 stations

L1 123

L4 15.5

L3 91.5 102

3 4 5 6

112.5 125

135.5 148

148

137.5 137.5 150

112.5 123

16.5 17.5 12.5


160 5 173

133.5 144

162.5 175

#### SY3000: D-sub Connector/Plug-in





МЗ

Terminal screw

39

Block separation button (Push type) Note) The L1 to L4 dimensions of SS5Y3-45FD-Stations D-C4, N3 re identical to those of SS5Y3-45FD-Stations U-C4.N3 - SS5Y3-55FD-Stations U-C4.N3 - SS5Y3-55FD-Stations U-C4.N3 - SS5Y3-55FD-Stations U-C4.N3 - SS5Y3-SS5Y3-SS5Y3-SS5Y3- SS5Y3-SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3-SS5Y3- SS5Y3- 
sv

SJ SY

SYJ

SZ

VF

**VP4** S0700

VO

VQ4

VQ5

VQC

210.5

187.5 200

154.5 165 175.5

8 9 10 stations

13.5 14.5 15.5 16.5 17.5

185 5 198

VQC4

VQZ


SQ VFS

VFR


VQ7

#### - C4 N2

(Light/surge voltage suppressor)




(Station n) - - - (Station 1)



Stations n	2 stations	3	4	5	6	7	8	9	10 stations	
L1	135.5	148	160.5	173	185.5	185.5	198	210.5	223	
L2	125	137.5	150	162.5	175	175	187.5	200	212.5	
L3	108	118.5	129	139.5	150	160.5	171	181.5	192	
L4	13.5	14.5	15.5	16.5	17.5	12.5	13.5	14.5	15.5	
Stations n	11 stations	12	13	14	15	16	17	18	19	20 stations
14	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323
L1	233.3	240								
L2	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5
		_	_		_	-		300 276	-	312.5 297


# Series **SY3000/5000**

#### SY5000: D-sub Connector/Plug-in



### Base Mounted Series SY3000/5000 Type 45


#### SY5000: D-sub Connector/Plug-in



**SMC** 

# Series SY3000/5000


#### SY3000: Flat Ribbon Cable/Plug-in



**SMC** 

### Base Mounted Series SY3000/5000 Type 45


### SY3000: Flat Ribbon Cable/Plug-in



**SWC** 


# Series **SY3000/5000**

#### SY5000: Flat Ribbon Cable/Plug-in



### Base Mounted Series SY3000/5000 Type 45


### SY5000: Flat Ribbon Cable/Plug-in




**ØSMC** 

# Series **SY3000/5000**


#### SY3000: 9 Pins Terminal Block/Plug-in



Note) The L1 to L4 dimensions of \$S\$Y3-45TU
[Stations]U-C<sub>6</sub><sup>1,19</sup>, \$S\$Y3-45TD-[Stations]U-C<sub>6</sub><sup>1,19</sup>, \$S\$Y3-45TD-[Stations]U-C<sub>6</sub><sup>1,19</sup>, are identical those of \$S\$Y3-45TU-[Stations]D-C<sub>6</sub><sup>1,19</sup>, for the state of \$S\$Y3-45TU-[Stations]D-C<sub>6</sub>, for th



Stations n	2 stations	3	4	5	6	7	8 stations
L1	123	135.5	148	148	160.5	173	185.5
L2	112.5	125	137.5	137.5	150	162.5	175
L3	91.5	102	112.5	123	133.5	144	154.5
L4	15.5	16.5	17.5	12.5	13.5	14.5	15.5




Note) The L1 to L4 dimensions of SS5Y3-45TD-Stations B-C4, N3 are identical to those of SS5Y3-45TU-[Stations] B-C4, N3-SS5Y3-45TU-[Stations] B-C4, N3-N3-

		Applicable tubing O.D.: Ø4, Ø5/32" Ø6, Ø1/4"
U sid		(L4) D side
35 35	27 M3 © E C O O O O O O O O O O O O O O O O O O	DIN rail holding screw
	(Rail mounting hole pitch: 12	2.5)

9	Stations n	2 stations	3	4	5	6	7	8 stations
	L1	135.5	148	160.5	173	185.5	185.5	198
	L2	125	137.5	150	162.5	175	175	187.5
	L3	108	118.5	129	139.5	150	160.5	171
ı	L4	13.5	14.5	15.5	16.5	17.5	12.5	13.5

# Base Mounted Series SY3000/5000 Type 45


# SY5000: 9 Pins Terminal Block/Plug-in



**ØSMC** 

469


## SY3000: 18 Pins Terminal Block/Plug-in



**SMC** 


# Base Mounted Series SY3000/5000 Type 45

# SY3000: 9 Pins Terminal Block/Plug-in




**SMC** 

## SY5000: 18 Pins Terminal Block/Plug-in



# Base Mounted Series SY3000/5000 Type 45

## SY5000: 18 Pins Terminal Block/Plug-in



**SMC** 

(Rail mounting hole pitch: 12.5)

SYJ

SZ

۷F VP4

S0700

VO

V04

VQ5 VQC

VQC4

VQZ

SO

VFS

VFR **VQ7** 

272 288 304 320 336 352 368


13

17.5 15.5 14

12

16.5 15

## SY3000: PC Wiring System Compatible (Flat ribbon cable/Plug-in)



11

**SMC** 

# Base Mounted Series SY3000/5000 INDE 15

Stations n 2 stations 3

L2 112.5 125

L1 123 135.5 148

91.5 102

4 5 6 7 8 9

112.5 123

148


137.5 137.5 150

L4 15.5 16.5 17.5 12.5 13.5 14.5 15.5 16.5 17.5

160.5 173

133.5 144

## SY3000: PC Wiring System Compatible (Flat ribbon cable/Plug-in)



Note) The L1 to L4 dimensions of SS5Y3-45GD-Stations D-C4, N3 are identical to those of SS5Y3-45GD-Stations U-C4, N3,

SY

SJ

SYJ

SZ

۷F

VP4

S0700

VO

VQ4

VQ5 VQC

10 stations

210.5

185.5 198

162.5 175 187.5 200

154.5 165


VQC4

VQZ

SO VFS

**VFR** 

**VQ7** 



39


D side


Block separation button (Push type)

# SS5Y3-45GD- Stations B-C4, N3

U side


63






335	03)									
	Stations n	2 stations	3	4	5	6	7	8	9	10 stations
	L1	135.5	148	160.5	173	185.5	185.5	198	210.5	223
	L2	125	137.5	150	162.5	175	175	187.5	200	212.5
	L3	108	118.5	129	139.5	150	160.5	171	181.5	192
	L4	13.5	14.5	15.5	16.5	17.5	12.5	13.5	14.5	15.5
	Stations n	11 stations	12	13	14	15	16 stations			
	L1	235.5	248	248	260.5	273	285.5			
ls	L2	225	237.5	237.5	250	262.5	275			
1	L3	202.5	213	223.5	234	244.5	255			
;.]	L4	16.5	17.5	12	13	14	15			

## SY5000: PC Wiring System Compatible (Flat ribbon cable/Plug-in)



# Base Mounted Series SY3000/5000 179-45

## SY5000: PC Wiring System Compatible (Flat ribbon cable/Plug-in)



**ØSMC** 

477

SJ

SY

SV

SYJ

SZ VF

**VP4** S0700

VO

V04

VQ5

VQC

VQC4


VQZ

SO

VFS VFR V07

# **DIN Rail Manifold Exploded View**

## Type 45F (D-sub Connector) Manifold



	5	Part no.		Note			
No.	Description	SY3000	SY5000	No.	ote		
1	Manifold block assembly			according to an attached lead wire assembly based on the connector spec. Select an nifold block assembly part number shown below. (Gasket 7 is supplied as an accessory.)			
2	SUP/EXH block assembly	(Metric size) SX3000-51-2A (Inch size) SX3000-51-16A	(Metric size) SX3000-51-2A (Inch size) SX5000-51-16A	Metric size Inch size SY3000: P, R port with One-touch fitting for ø8 With One-touch fitting for ø9 SY5000: P, R port with One-touch fitting for ø10 With One-touch fitting for ø10			
3	End block assembly	SX3000-52-2A(-Q)	SX5000-52-2A(-Q)	For D side			
4	End block assembly	SX3000-53-2A(-Q)	SX5000-53-2A(-Q)	For U side			
5-1	Connector block assembly (for D-sub connector)	SX3000-64-1A	SX5000-64-1A	-1A: +COM -1NA: -COM			
5-2	Connector block assembly (for 26 pins flat cable)	SX3000-64-2A 2NA-26	SX5000-64-2A 2NA-26		Note) For 24 VDC		
5-3	Connector block assembly (for 20 pins flat cable)	SX3000-64-2A 2NA-20	SX5000-64-2A 2NA-20	-2A: +COM -2NA: -COM			
5-4	Connector block assembly (for 10 pins flat cable)	SX3000-64-2A 2NA-10	SX5000-64-2A 2NA-10				
5-5	Connector block assembly (for 2 to 8 stations (T, T1) terminal block)	SX3000-64-3A	SX5000-64-3A	In common between +COM and -COM.			
5-6	Connector block assembly (for 9 to 17 stations (T1) terminal block)	SX3000-64-8A	SX5000-64-8A				
	Round head combination screw	SY3000-23-4	AC00077				
	Reference screw size	(M2 x 21)	(M3 x 26)				
7	Gasket	SX3000-57-4	SX5000-57-6				
_ 8	DIN rail	VZ1000	0-11-1- □	Refer to p	page 454.		

Note 1) The numbers 5-1 to 4 are for 24 VDC. For 12 VDC, suffix "-12V" to the end of parts number. (Example) SX3000-64-1A-12 V

Note 2) Two manifold block assemblies are necessary for the double, 3 position (Dual body type).

Style of manifold	Manifold block assembly part no.	Note
For 45(N)F (D-sub connector)	SX <sub>5</sub> <sup>3</sup> 000-50-3A-□□(-Q)	□□: AB port SY3000 (metric size) C4: With One-touch fitting for ø4 C6: With One-touch fitting for ø6
For 45(N) <sup>PG</sup> <sub>PH</sub> (Flat ribbon cable)		(inch size) N3: With One-touch fittign for $\sigma 5/20^\circ$ N7: With One-touch fitting for $\sigma 1/4^\circ$
For 45G PC Wiring System compatible	SX <sub>5</sub> <sup>3</sup> 000-50-5A-□□(-Q)	A, B port SY5000 (metric size) C4: With One-touch fitting for ø4 C6: With One-touch fitting for ø6 C8: With One-touch fitting for ø8
For 45 <sup>T</sup> <sub>11</sub> (Terminal block)	SX <sub>5</sub> <sup>3</sup> 000-50-7A-□□(-Q)	(inch size) N3: WIth One-touch fitting for ø5∕₃2" N7: With One-touch fitting for ø1∕₄" N9: With One-touch fitting for ø5∕₁₅"

Note) The lead wire assembly is supplied with the manifold block assembly.



# Base Mounted Series SY3000/5000 Ine 45

#### How to Increase Manifold Bases

Loosen DIN rail holding screw (a) fixing the manifold base until it begins to turn idly. (While pressing DIN rail releasing buttons ©, at two locations, separate the manifold base from the DIN rail.)

Additional bases are to be added to the U side. Press splitting button (b) of the manifold block assembly on the U side until button (b) locks, and then separate the block assemblies.

Separate the connector block assembly in the same manner as 2, and remove the connector mounting screw shown in Fig. 1.

Loosen the valve mounting screw on the U side, remove the valve, and take out the receptacle housing. (Refer to Fig. 2.)


Insert the common wire (red) of the manifold block assembly to be added into the pin insertion section (N mark) of the receptacle housing that was taken out in 4, mount it on the manifold block, and mount the removed valve.

6 As shown in Fig. 3, mount the additional manifold block assembly on the DIN rail on the U side. Refer to the circuit diagram, and insert the lead wire (black) as shown in Fig. 4.

Press the blocks against each other until a click sound is produced, place the lead wire in the manifold block, and close the lid without pinching the lead wire.

8 While lightly holding the blocks together so that there are no gaps between them, secure them to the DIN rail by tightening the DIN rail holding screws (a). △ (Tightening torque: 1.4 N·m)


- ⚠ Caution 1. Depending on the connector, there is a limit to the number of solenoids that can be used. Manifold bases that can be added cannot exceed the number of usable solenoids
  - 2. The manifold block assembly mounting position for additional manifold bases is always on the U side. because wires are connected to respective connectors sequentially from the D side
  - 3. When DIN rail holding screw (a) for the end block is not sufficiently tightened during reassembly, air leakage may result. Before supplying air, check that there is no gap between blocks and that the manifold block is firmly fixed to the DIN rail in order to ensure air supply without leakage.




D-sub connector (45F)







Insert pins after removing the Insert tab terminals connectorfrom the main unit. completely. After inserting pins, lightly pull lead wires to check that the pins are locked.



SJ

LYS

SZ

VP4

S0700

VO

V04

V05

VOC

VOC4

VOZ

SO

VFS

**VFR** 

V07

Note)

# How to Change Fitting Assembly

Type 45 manifold permits change in the A and B port sizes by changing the manifold block fitting assembly.

After removing the valve, remove the clip with a screwdriver, etc. For mounting a new fitting assembly, insert it and then insert a clip until it will not come out of the manifold block.

#### Fitting Assembly Part No.

Metric size


cvanno	One-touch fitting for ø4 One-touch fitting for ø6	VVQ1000-50A-C4
313000	One-touch fitting for ø6	VVQ1000-50A-C6
	One-touch fitting for ø4	VVQ1000-51A-C4
SY5000	One-touch fitting for ø6	VVQ1000-51A-C6
	One-touch fitting for ø8	VVQ1000-51A-C8

Inch size

	evanno	One-touch fitting for ø5/32"	VVQ1000-50A-N3
1	513000	One-touch fitting for ø 1/4"	VVQ1000-50A-N7
]		One-touch fitting for ø5/32"	VVQ1000-51A-N3
1	SY5000	One-touch fitting for ø 1/4"	VVQ1000-51A-N7
1		One-touch fitting for ø5/16"	VVQ1000-51A-N9
4		J	

Note 1) P and R ports cannot be changed

Note 2) Use caution that O-rings must be free from scratches and dust. Otherwise, air leakage may result. Note 3) Purchasing order is available in units of 10 pieces.



479






# SY3000/5000 Base Mounted Manifold Stacking Type/DIN Rail Mounted

Note) Refer to the SI unit part no. for



# EX122 Integrated-type (For Output) Serial Transmission System

#### How to Order Manifold



- \* This also includes the number of blanking plate assemblies
- \* Two stations are necessary for the double, 3 position (Dual body type)

#### SUP/EXH block assembly mounting position •

Symbol	Mounting position	Stations			
U	U side	2 to 10 stations			
D	D side	2 to 10 stations			
В	(Both sides)	2 to 16 stations			
M	M Special specifications				
. For appoint appointment indicate concretch, by the					


manifold specification sheet.

#### A, B port size •


One-touch fitting (Metric size)				One-touch fitting (Inch size)			
Symbol	Port size	Applicable series		Symbol		Applicable serie	
C4	One-touch fitting for ø4			N3	One-touch fitting for ø5/32"		
C6	One-touch fitting for ø6	SY3000		N7	One-touch fitting for ø1/4"	SY3000	
M	Mixed			M	Mixed		
C4	One-touch fitting for ø4			N3	One-touch fitting for ø5/32"		
C6	One-touch fitting for ø6	SY5000		N7	One-touch fitting for ø1/4"	SY5000	
C8	One-touch fitting for ø8	515000		N9	One-touch fitting for ø5/16"	515000	
M	Mixed				Mixed		

\* In the case of mixed specifications, indicate separately on the manifold specification sheet

## How to Order Manifold Assembly (Example)



## How to Order Valve



#### SI Unit Part No.

Symbol	Protocol type	SI unit No.	CE-compliant	Symbol	Protocol type	SI unit No.	CE-compliant
F1	NKE Corp.: Fieldbus System	EX122-SUW1	_	R1	OMRON Corp.: CompoBus/S (16 outputs) compatible	EX122-SCS1	0
Н	NKE Corp.: Fieldbus H System	EX122-SUH1	_	R2	OMRON Corp.: CompoBus/S (8 outputs) compatible	EX122-SCS2	0
J1	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (16 outputs)	EX122-SSL1	_	٧	CC-LINK	EX122-SMJ1	0
J2	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (8 outputs)	EX122-SSL2	_	ZB	CompoNet <sup>™</sup> (Positive common)	EX122-SCM1	0
Q	DeviceNet	EX122-SDN1	0	ZBN	CompoNet™ (Negative common)	EX122-SCM3	0

number to be required

(Max. 20 stations)

Refer to page 2051 and the Operation Manual for the details of EX122 Integrated-type (For Output) Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

Nil


Main valve fluororubber (Refer to page 510.) CE-compliant CE-compliant



<sup>\*</sup> When ordering plug-in type solenoid valve as a single unit, gaskets are not included. Order them separately, if necessary. (Refer to page 478 for details.)

# Base Mounted **SY3000/5000** Type **45S**

## Series SY3000: EX122 Integrated-type (For Output) Serial Transmission System/Plug-in




28.8 10

(L4)

SS5Y3-45S□-Stations B-C4, N3 C6, N7

8

Block separation button (Push type)



**SMC** 

SJ

SY

SV

SYJ SZ

۷F

VP4

S0700

VO

VQ4

VQ5

VQC

VQC4

VOZ

SO


VFS

**VFR** 

**VQ7** 



## Series SY5000: EX122 Integrated-type (For Output) Serial Transmission System/Plug-in






# SY3000/5000 Base Mounted Manifold **Stacking Type/DIN Rail Mounted** Note) Refer to the SI unit part no. for EX 121 Separate Type (For Output) Serial Transmission System



# **How to Order Manifold**

5 SY5000



	SI unit specifications				
Symbol	Protocol type				
0	Without SI unit				
F1	NKE Corp.: Fieldbus System				
Н	NKE Corp.: Fieldbus H System				
J1	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (16 outputs				
J2	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (8 outputs)				
Q	DeviceNet				
R1	OMRON Corp.: CompoBus/S (16 outputs) compatible				
R2	OMRON Corp.: CompoBus/S (8 outputs) compatible				
٧	CC-LINK				
ZB	CompoNet™ (Positive common)				
ZBN	ZBN CompoNet™ (Negative common)				
• Evo	- Even though when it is not equipped with CI				

. Even though when it is not equipped with SI unit, DIN rail length is long enough for future expectancy of mounting SI unit. When a shorter rail is required (same as type 45□), suffix "0" in the optional blank at the end of part number.

#### SI unit mounting positio

••	t inounting position •						
	Symbol	Mounting position					
	U	U side					
	D	D side					

## 

Nil	_
Q	CE-compliant

\* Refer to the SI unit part no. for the SI unit compatible with CE

#### Option

When a longer DIN rail is desired than the specified stations, specify the station number to be required. (Max. 20 stations)

#### A. B port size

e-tou	ch fitting (Metric size)		One-touch fitting (Inch		
nhol	Port size	Annlicable series	Symbol	Port size	

Symbol Port size		Applicable series		Symbol	Port size
C4	One-touch fitting for ø4	SY3000		N3	One-touch fitting for ø 5/32"
C6	One-touch fitting for ø6			N7	One-touch fitting for ø 1/4"
M	Mixed			M	Mixed
C4	One-touch fitting for ø4			N3	One-touch fitting for ø 5/32"
C6	One-touch fitting for ø6	SY5000		N7	One-touch fitting for ø 1/4"
C8	One-touch fitting for ø8			N9	One-touch fitting for ø 5/16"
M	Mixed			M	Mixed

\* In the case of mixed specifications, indicate separately on the manifold specification sheet.

#### SUP/EXH block assembly mounting position

Symbol	Mounting position	Stations				
U	U side	2 to 10 stations				
D	D side	2 to 10 stations				
В	Both sides	2 to 16 stations				
М	Special specifications					

<sup>\*</sup> For special specifications, indicate separately by the manifold specification sheet.

#### Valve stations

Symbol	Stations	Note
02	2 stations	Single wiring spec.
:	:	(Applicable up to 16
16	16 stations	solenoid valves.)

<sup>\*</sup> This also includes the number of blanking plate

#### SI Unit Part No.

Symbol	Protocol type	SI unit No.	CE-compliant	Symbol	Protocol type	SI unit No.	CE-compliant
F1	NKE Corp.: Fieldbus System	EX121-SUW1	_	R1	OMRON Corp.: CompoBus/S (16 outputs) compatible	EX121-SCS1	0
Н	NKE Corp.: Fieldbus H System	EX121-SUH1		R2	OMRON Corp.: CompoBus/S (8 outputs) compatible	EX121-SCS2	0
J1	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (16 outputs)	EX121-SSL1	_	٧	CC-LINK	EX121-SMJ1	0
J2	Panasonic Industrial Devices SUNX Co., Ltd.: S-LINK (8 outputs)	EX121-SSL2	_	ZB	Compo Net™ (Positive common)	EX121-SCM1	0
Q	DeviceNet	EX121-SDN1	0	ZBN	CompoNet™ (Negative common)	EX121-SCM3	0

<sup>.</sup> For external pilot specifications and built-in silencer, refer to pages 502 to 506.

Refer to page 2051 and the Operation Manual for the details of EX121 Separate Type (For Output) Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

SJ SY

LYS

SZ

۷F

Applicable series

SY3000

SY5000

S0700

VO V04

VQ5

VOC

VOC4

VOZ

SO

VFS


**VFR** 

**VQ7** 

<sup>\*</sup> Two stations are necessary for the double, 3 position (Dual body type).




## How to Order Valve Manifold Assembly (Example)



## How to Order Valve





\* When ordering plug-in type solenoid valve as a single unit, gaskets are not included. Order them separately, if necessary. (Refer to page 478 for details.)

# Base Mounted **SY3000/5000** Type **45S1**

SJ

SY

SY

SV

SYJ

SZ

۷F

**VP4** S0700

VO

VQ4

VQ5

VQC

VQC4


VQZ

SO

VFS


VFR VO7

## SY3000: EX121 Separate Type (For Output) Serial Transmission System/Plug-in



# Type 45\$1 SY3000/5000

# SY3000: EX121 Separate Type (For Output) Serial Transmission System/Plug-in




Note) The L1 to L4 dimensions of SS5Y3-45S1□D
Stations]D-C4, N3 are identical to those of SS5Y3-45S1□D
Stations] U-C6, N7.



(Station n) (Station 1)								
Light/surge voltage suppressor								
34.55								
Block separation button (Push type) L3 30.8 10 (L4)								

Stations n	2 stations	3	4	5	6	7	8	9	10 stations
L1	160.5	173	185.5	198	198	210.5	223	235.5	248
L2	150	162.5	175	187.5	187.5	200	212.5	225	237.5
L3	91.5	102	112.5	123	133.5	144	154.5	165	175.5
L4	14	15	16	17	12	13	14	15	16

# SS5Y3-45S1 D-Stations B-C4, N3




11

**SMC** 

Stations n	2 stations	3	4	5	6	7	8	9	10 stations
L1	173	185.5	198	210.5	223	235.5	235.5	248	260.5
L2	162.5	175	187.5	200	212.5	225	225	237.5	250
L3	108	118.5	129	139.5	150	160.5	171	181.5	192
L4	12	13	14	15	16	17	12	13	14
Stations n	11 stations	12	13	14	15	16 stations			
Stations n	11 stations 273	<b>12</b> 285.5	_	<b>14</b> 298	<b>15</b> 310.5	16 stations 323			
		285.5	_		310.5				
L1	273	285.5 275	298 287.5	298	310.5	323 312.5	]		
L1 L2	273 262.5	285.5 275	298 287.5	298 287.5	310.5 300	323 312.5	] ] ]		

# Base Mounted **SY3000/5000** Type **45S1**

## SY5000: EX121 Separate Type (For Output) Serial Transmission System/Plug-in



**SMC** 

487

SJ

SY

SY

SV

SYJ SZ

VF VP4 S0700

VO

V04

VQ5

VQC

VQC4

VOZ

SO

VFS


**VFR** 

**VQ7** 



488

## SY5000: EX121 Separate Type (For Output) Serial Transmission System/Plug-in



**SMC** 

SJ

SY

SY

SV SYJ

SZ

VF

VP4

\$0700 **VQ** 

VQ4

VQ5

VQC

VQC4

VQZ

SQ

VFS VFR

VQ7


# Type 45S6B

# **EX510 Gateway-type Serial Transmission System**

Base Mounted Manifold/Stacking Type/Plug-in Type [Option]

# Series SY3000/5000

## **How to Order Manifold**




## 16 stations \*The number of the blanking plate assembly is also included

Compatible with 16 solenoid valves

#### SI unit part no.

Symbol	SI unit specifications	SI unit part no.	Page
Nil	NPN output (+COM.)	EX510-S002A	P.2143
N	PNP output (-COM.)	EX510-S102A	P.2143

# How to Order Manifold Assembly (Example)



They will be assembled in the order listed starting at the first station at the D side whether the connector box is located at either end.

• When ordering double solenoid valves/3 position (dual body style), please keep in

#### One-touch fitting (Inch size)

One-touch fitting for ø4

One-touch fitting for ø6

One-touch fitting for ø8

SY5000

Symbol Port size						
One-touch fitting for ø5/	32"					
One-touch fitting for ø1/	4" SY3000					
Mixed						
One-touch fitting for ø5/	32"					
One-touch fitting for ø1/	Y4" SY5000					
One-touch fitting for ø5/	16"					
M Mixed						
	One-touch fitting for ø5/ One-touch fitting for ø1/ Mixed One-touch fitting for ø5/ One-touch fitting for ø1/ One-touch fitting for ø5/					

<sup>·</sup> For the mixed specification, indicate separately on a manifold specification sheet.

#### Pilot specifications

C4

C6

C8

Nil	Internal pilot
S	Internal pilot/built-in silencer
R	External pilot
RS	External pilot/built-in silencer

#### SUP/EXH block assembly mounting position

U	U side	2 to 10 stations				
D	D side	2 to 10 stations				
В	Both sides	2 to 16 stations				
M	Special specifications*					

<sup>\*</sup>For the special specifications, indicate separately on a manifold specification sheet


Refer to page 2124 and the Operation Manual for the details of EX510 Gateway-type Serial Transmission System. Please download the Operation Manual via our website, http://www.smcworld.com

mind that they require two manifold stations.

# Base Mounted Manifold Series SY3000/5000 110 45 56B

## **How to Order Valves**







<sup>\*</sup> When ordering plug-in type solenoid valve as a single unit, gaskets are not included. Order them separately, if necessary. (Refer to page 478 for details.)


# 100 Apriles SY3000/5000


#### **Dimensions**

## SS5Y3-45S6B D- Stations U-C4, N3










L: Di	L: Dimensions n: Station										
	n 2	3	4	5	6	7	8	9	10		
L1	148	160.5	173	185.5	198	210.5	223	223	235.5		
L2	137.5	150	162.5	175	187.5	200	212.5	212.5	225		
L3	124.5	135	145.5	156	166.5	177	187.5	198	208.5		
L4	12	13	14	15	16	17	18	12.5	13.5		


492


# Base Mounted Manifold Series SY3000/5000 1110 45\$6B


## **Dimensions**

SS5Y3-45S6B U- Stations B-C4, N3









L: Dim	L: Dimensions n: Stations														
_ n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	173	185.5	198	198	210.5	223	235.5	248	260.5	273	273	285.5	298	310.5	323
L2	162.5	175	187.5	187.5	200	212.5	225	237.5	250	262.5	262.5	275	287.5	300	312.5
L3	141	151.5	162	172.5	183	193.5	204	214.5	225	235.5	246	256.5	267	277.5	288
L4	16	17	18	13	14	15	16	17	18	19	13.5	14.5	15.5	16.5	17.5

**SMC** 

SJ

SY SY

SV

SYJ

SZ

VF

VP4 S0700

VO

VQ4

VQ5

VQC4


VQZ


SQ VFS


VFR

VQ7


#### **Dimensions**







(Station n) - - - - - (Station 1)



	L: Dimensions n: Statio										
Ī		2	3	4	5	6	7	8	9	10	
	L1	173	185.5	198	210.5	235.5	248	260.5	285.5	298	
Ī	L2	162.5	175	187.5	200	225	237.5	250	275	287.5	
	L3	138	154	170	186	202	218	234	250	266	
	L4	17.5	16	14	12.5	17	15	13.5	18	16	


494



# Base Mounted Series SY3000/5000 Type 455 Type 45S Type 45

## **Manifold Option**

#### Blanking plate assembly



Series	Assembly part no.
SY3000	SX3000-75-2A(-Q)
CVENNO	CVEDOD 76 6A/ O)

Note) • When mounting blanking plate, be sure to mount a short can

Two stations are necessary for the double, 3 position (Dual body type).

#### SUP blocking disk

By installing a SUP blocking disk in the pressure supply passage of a manifold valve, it is possible to supply two or more different high and low pressures to one manifold.



Series	Part no.
SY3000	SX3000-77-1A
SY5000	SX5000-77-1A

#### ■ EXH blocking disk

By installing an EXH blocking disk in the exhaust passage of a manifold valve, it is possible to divide the valve's exhaust so that it does not affect another valve. (Two blocking disks are needed to divide both exhausts.)



Series	Part no.
SY3000	SX3000-77-1A
SY5000	SX5000-77-1A

#### Label for block disk

The labels shown below are used on manifold stations containing SUP/EXH block disk(s) to show their location. (3 pcs. each)

VZ3000-123-1A (In common with SY3000, 5000)

Label for SUP block disk Label for EXH block disk Label for SUP/EXH block disk







SY

SV

SYJ

SZ

۷F

VP4

S0700

VO

V04

V05

VQC


VOC4

VQZ SQ VFS

VFR VO7

Note) When a block disk is concurrently ordered by specifying on the manifold specification sheet, etc., a label will be stuck on the position where block disk is mounted.

■ Silencer with One-touch fitting



		(	Hesin)	(Hesin sir	itered body)
Series	Model	Effective area mm2	Α	В	С
For SY3000 (Ø8)	AN15-C08	20	ø13	20	45
For SY5000 (Ø10)	AN20-C10	30	ø16.5	30.5	57.5

#### Plug (white)

These are inserted in unused cylinder ports and SUP, EXH ports. Purchasing order is available in units of 10 pieces.

## Dimensions


Model	Α	L	D
KQ2P-04	16	32	6
KQ2P-06	18	35	8
KQ2P-08	20.5	39	10
KQ2P-10	22	43	12
KQ2P-01	16	31.5	5
KQ2P-03	16	32	6
KQ2P-07	18	35	8.5
KQ2P-09	20.5	39	10
	KQ2P-04 KQ2P-06 KQ2P-08 KQ2P-10 KQ2P-01 KQ2P-03 KQ2P-07	KQ2P-04 16 KQ2P-06 18 KQ2P-08 20.5 KQ2P-10 22 KQ2P-01 16 KQ2P-03 16 KQ2P-07 18	KQ2P-04         16         32           KQ2P-06         18         35           KQ2P-08         20.5         39           KQ2P-10         22         43           KQ2P-01         16         31.5           KQ2P-03         16         32           KQ2P-07         18         35


# **⚠** Caution

Mounting screw tightening torques

M2: 0.17 N·m M3: 0.8 N·m M4: 1.4 N·m

■ Individual EXH spacer assembly ■ Individual SUP spacer assembly





OCITICS	Assembly part no.	Port no.	t
SY3000	SY3000-39-3A(-Q)	M5 x 0.8	11
SY5000	Assembly part no. SY3000-39-3A(-Q) SY5000-39-17A(-Q)	1/8	15

ne)	Please de careiul decause the i
	dual body type (double solenoid,
	3-position) requires two pieces.
	In this case, the exhaust is
	performed in the direction of the
	arrow mark indicated on the
	valve surface.

	Series	Assembly part no.	Port no.	t
1	SY3000	SY3000-38-3A(-Q)	M5 x 0.8	11
1	SY5000	Assembly part no. SY3000-38-3A(-Q) SY5000-38-17A(-Q)	1/8	15

Note) Please be careful because the dual body type (double solenoid, 3-position) requires two pieces. In this case, both supply ports require the piping.