Vishay Foil Resistors

# Ultra High Precision Z-Foil Flip Chip Resistor with TCR of ± 0.05 ppm/°C, 35 % Space Saving vs. Wraparound Design and PCR of 5 ppm at Rated Power



#### INTRODUCTION

**Bottom View** 

One of the most important parameters influencing stability is the temperature coefficient of resistance (TCR). Although the TCR of Bulk Metal® Foil resistors is considered extremely low, this characteristic has been further refined over the years.

The VFCP Series utilizes ultra precision Bulk Metal® Z-Foil.

The Z-Foil technology provides a significant reduction to the resistive element's sensitivity to ambient temperature variations (TCR) and to self heating when power is applied (power coefficient).

Along with the inherently low PCR and TCR, Z-Foil technology also provides remarkably improved load life stablility, low noise and availability of tight tolerance.

The flip chip configuration provides a substantial PCB space saving of more than 35 % vs. a surface mount chip with wraparound terminations. The VFCP is available in any value within the specified resistance range.

Our application engineering department is available to advise and make recommendations. For non-standard technical requirements and special applications, please contact us.

	TABLE 1 - TOLERANCE AND TCR VS. RESISTANCE VALUE					
RESISTANCE VALUE (Ω)	TOLERANCE (%)	TYPICAL TCR AND MAX. SPREAD (- 55 °C to + 125 °C, + 25 °C Ref.)				
250 to 125K	± 0.01	± 0.2 ± 1.6				
100 to < 250	± 0.02	± 0.2 ± 1.6				
50 to < 100	± 0.05	± 0.2 ± 1.8				
25 to < 50	± 0.1	± 0.2 ± 2.8				
10 to < 25	± 0.25	± 0.2 ± 2.8				

#### **FEATURES**

Temperature coefficient of resistance (TCR):
 ± 0.05 ppm/°C typical (0 °C to + 60 °C)
 ± 0.2 ppm/°C typical (- 55 °C to + 125 °C, + 25 °C ref.)




RoHS

Tolerance: to ± 0.01 % (100 ppm)

- Power coefficient "ΔR due to self heating"
   5 ppm at rated power
- Load life stability (70 °C for 2000 h): ± 0.005 % (50 ppm)
- Power rating to: 600 mW at + 70 °C
- Electrostatic discharge (ESD) up to 25 000 V
- Resistance range: 10  $\Omega$  to 125  $k\Omega$  (for lower and higher values, please contact us)
- Foil resistors are not restricted to standard values; specific "as required" values can be supplied at no extra cost or delivery (e.g. 1K2345 vs. 1K)
- Non-inductive, non-capacitive design
- Short time overload ≤ 0.005 % (50 ppm)
- Non hot spot design
- · Rise time: 1 ns effectively no ringing
- Current noise: 40 dB
- Voltage coefficient < 0.1 ppm/V</li>
- Non-inductive: < 0.08 μH
- Terminal finishes available: lead (Pb)-free, tin/lead alloy
- Compliant to RoHS directive 2002/95/EC
- Matched sets are available per request
- Prototype quantities available in just 5 working days or sooner. For more information, please contact foil@vishaypg.com
- For better performances please contact us

#### **APPLICATIONS**

- Automatic test equipment (ATE)
- High precision instrumentation
- Laboratory, industrial and medical
- Audio
- EB applications (electron beam scanning and recording equipment, electron microscopes)
- · Military and space
- Airborne
- Down hole instrumentation
- Communication



<sup>\*</sup> Pb containing terminations are not RoHS compliant, exemptions may apply

Document Number: 63106 Revision: 25-Mar-10

## Vishay Foil Resistors






TABLE 2 - SPECIFICATIONS					
CHIP SIZE	RATED POWER (mW) at + 70 °C	$\begin{array}{c} \text{MAXIMUM} \\ \text{VOLTAGE} \\ \text{RATING} \\ (\leq \sqrt{P \times R} \ ) \end{array}$	RESISTANCE RANGE (Ω)	MAXIMUM WEIGHT (mg)	
0805	100 mW	28 V	10 to 8K	5.2	
1206	250 mW	79 V	10 to 25K	10.3	
1506	300 mW	95 V	10 to 30K	12	
2010	400 mW	167 V	10 to 70K	25	
2512	600 mW	220 V	10 to 125K	35	


	TABLE 3 - LOAD LIFE STABILITY (+ 70 °C for 2000 h)					
	CHIP SIZE	MAXIMUM AR LIMITS				
<b>\</b>	0805	± 0.005 % at 50 mW ± 0.01 % at 100 mW				
	1206	± 0.005 % at 150 mW ± 0.01 % at 250 mW				
	1506	± 0.005 % at 150 mW ± 0.01 % at 300 mW				
	2010	± 0.005 % at 200mW ± 0.01 % at 400 mW				
	2512	± 0.005 % at 500 mW ± 0.01 % at 600 mW				

TABLE 4 - PERFORMANCES				
TEST OR CONDITION	MIL-PRF-55342 CHARACTERISTIC E ∆R LIMITS	TYPICAL AR LIMITS	MAXIMUM  AR LIMITS (1)	
Thermal Shock	± 0.1 %	± 0.005 % (50 ppm)	± 0.01 % (100 ppm)	
Low Temperature Operation	± 0.1 %	± 0.005 % (50 ppm)	± 0.01 % (100 ppm)	
Short Time Overload	± 0.1 %	± 0.005 % (50 ppm)	± 0.01 % (100 ppm)	
High Temperature Exposure	± 0.1 %	± 0.01 % (100 ppm)	± 0.02 % (200 ppm)	
Resistance to Soldering Heat	± 0.2 %	± 0.005 % (50 ppm)	± 0.015 % (150 ppm)	
Moisture Resistance	± 0.2 %	± 0.005 % (50 ppm)	± 0.02 % (200 ppm)	
Load Life Stability + 70 °C for 2000 hours at Rated Power	± 0.5 %	± 0.005 % (50 ppm)	± 0.01 % (100 ppm)	

#### Note


(1) As shown + 0.01 W to allow for measurement errors at low values.






#### Notes

- · Avoid the use of cleaning agents which could attack epoxy resins, which form part of the resistor construction
- Vacuum pick up is recommended for handling
- · Soldering iron is not applicable





#### Note


• The TCR values for < 100  $\Omega$  are influenced by the termination composition and result in deviation from this curve

Document Number: 63106 Revision: 25-Mar-10

## VFCP Series (0805, 1206, 1506, 2010, 2512) (Z-Foil)

Vishay Foil Resistors





#### Note

(1) For non-standard requests, please contact application engineering.





Vishay Precision Group

### **Disclaimer**

ALL PRODUCTS. PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay Precision Group"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify Vishay Precision Group's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

Vishay Precision Group makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. To the maximum extent permitted by applicable law, Vishay Precision Group disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on Vishay Precision Group's knowledge of typical requirements that are often placed on Vishay Precision Group products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of Vishay Precision Group.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Document No.: 63999 Revision: 27-Apr-11