



Vishay High Power Products

Power Silicon Rectifier Diodes,

35 A/40 A/60 A



DO-203AB (DO-5)

35 A/40 A/60 A

1040

16 100


50 to 600 (1)

DESCRIPTION/FEATURES

2650

41 000

50 to 600 (1)





- · Good surge current capability up to 1000 A
- · Can be supplied to meet stringent military, aerospace and other high reliability requirements

3400

52 500

50 to 600 (1)

A²√s

· RoHS compliant

	<u>.</u>		_					
MAJOR RATINGS AND CHARACTERISTICS								
PARAMETER	TEST CONDITIONS	1N1183	1N3765	1N1183A	1N2128A	UNITS		
I _{F(AV)}		35 (1)	35 ⁽¹⁾	40 (1)	60 ⁽¹⁾	Α		
	T _C	140 (1)	140 (1)	150 ⁽¹⁾	140 (1)	°C		
I _{FSM}	50 Hz	480	380	765	860	^		
	60 Hz	500 ⁽¹⁾	400 (1)	800 (1)	900 (1)	A		
l ² t	50 Hz	1140	730	2900	3700	A ² s		
1-L						A-5		

670

10 300

700 to 1000 (1)

I²√t

 V_{RRM}

PRODUCT SUMMARY

I_{F(AV)}

ELECTRICAL SPECIFICATIONS

60 Hz

Range

VOLTAGE RATINGS						
TYPE NUMBER		V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RM} , MAXIMUM DIRECT REVERSE VOLTAGE V			
			$T_{\rm J}$ = - 65 °C TO 200 °C ⁽²⁾	T_J = - 65 °C TO 200 °C ⁽²⁾		
1N1183	1N1183A	1N2128A	50 ⁽¹⁾	50 ⁽¹⁾		
1N1184	1N1184A	1N2129A	100 (1)	100 (1)		
1N1185	1N1185A	1N2130A	150 ⁽¹⁾	150 ⁽¹⁾		
1N1186	1N1186A	1N2131A	200 (1)	200 (1)		
1N1187	1N1187A	1N2133A	300 (1)	300 (1)		
1N1188	1N1188A	1N2135A	400 (1)	400 (1)		
1N1189	1N1189A	1N2137A	500 ⁽¹⁾	500 ⁽¹⁾		
1N1190	1N1190A	1N2138A	600 (1)	600 ⁽¹⁾		
1N3765			700 (1)	700 (1)		
1N3766			800 (1)	800 (1)		
1N3767			900 (1)	900 (1)		
1N3768			1000 (1)	1000 (1)		

Notes

- (1) JEDEC registered values
- $^{(2)}$ For 1N1183 Series and 1N3765 Series T_{C} = 65 to 190 $^{\circ}C$
- Basic type number indicates cathode to case. For anode to case, add "R" to part number, e.g., 1N1188R, 1N3766R, 1N1186AR, 1N2135AR

Document Number: 93492 Revision: 02-Mar-09

⁽¹⁾ JEDEC registered values



Vishay High Power Products Power Silicon Rectifier Diodes, 35 A/40 A/60 A

PARAMETER	SYMBOL	TEST CONDITIONS		1N1183	1N3765	1N1183A	1N2128A	UNITS
Maximum average forward current at case temperature	I _{F(AV)}	1-phase operation, 180° sinusoidal conduction		35 ⁽¹⁾	35 ⁽¹⁾	40 ⁽¹⁾	60 ⁽¹⁾	A °C
<u> </u>		Half cycle 50 Hz sine wave or 6 ms rectangular pulse	Following any rated load condition and with rated V _{RRM} applied	480	380	765	860	A
Maximum peak one cycle	I _{FSM}	Half cycle 60 Hz sine wave or 5 ms rectangular pulse		500 (1)	400 (1)	800 (1)	900 (1)	
non-repetitive surge current		Half cycle 50 Hz sine wave or 6 ms rectangular pulse	Following any rated load condition and with ½ V _{RRM} applied following surge = 0	570	455	910	1000	
		Half cycle 60 Hz sine wave or 5 ms rectangular pulse		595	475	950	1050	
Mariana 121 for facility	- l ² t	t = 10 ms	With rated V_{RRM} applied following surge, initial $T_J = T_J$ maximum With $V_{RRM} = 0$ following surge, initial $T_J = T_J$ maximum	1140	730	2900	3700	- A ² s
Maximum I ² t for fusing		t = 8.3 ms		1040	670	2650	3400	
Maximum I ² t for individual		t = 10 ms		1610	1030	4150	5250	
device fusing		t = 8.3 ms		1470	940	3750	4750	
Maximum l²√t for individual device fusing	l 2√ t (2)	t = 0.1 to 10 ms, V _{RRM} = 0 following surge		16 100	10 300	41 500	52 500	A²√s
Maximum peak forward voltage	V	T _ 05 °C		1.7 (1)	1.8 (1)	1.3 ⁽¹⁾	1.3 ⁽¹⁾	V
at maximum forward current (I _{FM})	V _{FM}	T _J = 25 °C		110	110	126	188	Α
V _{RRM} = 700				-	5.0 ⁽¹⁾	-	-	
V _{RRM} = 800		Maximum rated I	$_{ m AV)}$ and ${ m T_C}$	-	4.0 (1)	-	-	mA
Maximum average reverse current $V_{RRM} = 900$	I _{R(AV)}	Maximum rated I _{F()}		-	3.0 (1)	-	-	
V _{RRM} = 1000				-	2.0 (1)	-	-	
		Maximum rated I _{F(AV)} , V _{RRM} and T _C		10 ⁽¹⁾	-	2.5 ⁽¹⁾	10 (1)	

Notes

⁽¹⁾ JEDEC registered values

⁽²⁾ I²t for time $t_x = I^2 \sqrt{t} \times \sqrt{t_x}$



Power Silicon Rectifier Diodes, Vishay High Power Products 35 A/40 A/60 A

THERMAL AND MECHANICAL SPECIFICATIONS								
PARAMETER		SYMBOL	TEST CONDITIONS	1N1183	1N3765	1N1183A	1N2128A	UNITS
Maximum operating case temperature range		T _C		- 65 to 190 ⁽¹⁾		- 65 to 200		°C
Maximum storage temperature range		T _{Stg}		- 65 to 175 ⁽¹⁾		- 65 to 200		
Maximum internal thermal resistance, junction to case		R _{thJC}	DC operation	1.00 (1)		1.1 (1)	0.65 (1)	°C/W
Thermal resistance, case to sink		R _{thCS}	Mounting surface, smooth, flat and greased	0.25		*C/VV		
minimum			Non-lubricated threads	2.3 (20)				N·m
Mounting torque -	maximum		Non-lubricated trireads	3.4 (30)				(lbf · in)
Approximate weight				17				g
				0.6				OZ.
Case style			JEDEC		DC	D-203AB (DC	D-5)	

Note

(1) JEDEC registered values




Fig. 1 - Maximum Allowable Case Temperature vs. Average Forward Current, 1N1183 and 1N3765 Series




Fig. 2 - Typical Low Level Forward Power Loss vs. Average Forward Current (Sinusoidal Current Waveform), 1N1183 and 1N3765 Series




Fig. 3 - Typical High Level Forward Power Loss vs. Average Forward Current (Sinusoidal Current Waveform), 1N1183 and 1N3765 Series




Fig. 4 - Typical Forward Voltage vs. Forward Current, 1N1183 and 1N3765 Series

Vishay High Power Products Power Silicon Rectifier Diodes, 35 A/40 A/60 A






Fig. 5 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N1183 and 1N3765 Series




Fig. 6 - Average Forward Current vs. Maximum Allowable Case Temperature, 1N1183A Series




Fig. 7 - Maximum Low Level Forward Power Loss vs. Average Forward Current, 1N1183A Series




Fig. 8 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N1183A Series




Fig. 9 - Maximum Forward Voltage vs. Forward Current, 1N1183A Series




Fig. 10 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N1183A Series



Power Silicon Rectifier Diodes, Vishay High Power Products 35 A/40 A/60 A




Fig. 11 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N2128A Series




Fig. 12 - Maximum Allowable Case Temperature vs. Average Forward Current, 1N2128A Series




Fig. 13 - Maximum Low Level Forward Power Loss vs. Average Forward Current, 1N2128A Series




Fig. 14 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N2128A Series




Fig. 15 - Maximum Forward Voltage vs. Forward Current, 1N2128A Series

LINKS TO RELATED DOCUMENTS					
Dimensions www.vishay.com/doc?95360					

Document Number: 93492 For technical questions, contact: <u>ind-modules@vishay.com</u> Revision: 02-Mar-09



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com