



Features:

- 2 stage charging characteristic
- Universal AC input / Full range
- Built-in active PFC function, PF>0.97
- No load power consumption<0.5W
- 3 pole AC inlet IEC320-C14
- Class I power (with earth pin)
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection
- Fully enclosed plastic case
- 2 color LED indicator for charging status
- Approvals: TUV / UL / CB / FCC / CE
- 2 years warranty







ORDER NO.	OUTPUT CONNECTOR	SAFETY			
GC120Axx-R7B (standard model)	4pin power din	TUV / CB / FCC / CE			
GC120Axx-AD1 (optional model)	Anderson connector	UL/TUV/CB/FCC/CE			
GC120Axx-□ xx=12,24,48; □=R7B,AD1					

SPECIFICATION

ORDER NO.		GC120A12-	GC120A24-	GC120A48-		
SAFETY MODEL NO.		GC120A12	GC120A24	GC120A48		
ОИТРИТ	DC VOLTAGE (Typ.)	13.6V	27.2V	54.4V		
	RECOMMENDED BATTERY CAPACITY Note.2	40 ~ 100Ah	20 ~ 65Ah	10 ~ 35Ah		
	CONTINUOS OUTPUT CURRENT (Typ.)	7.5A	4.42A	2.21A		
	RATED POWER	102W	120.2W	120.2W		
	LED INDICATOR	Charging(CC): RED Floating charging(CV): GREEN				
	VOLTAGE RANGE Note.3	85 ~ 264VAC 120 ~ 370VDC				
	FREQUENCY RANGE	47 ~ 63Hz				
	POWER FACTOR (Typ.)	PF>0.97 / 230VAC PF>0.99 / 115VAC at full load				
INPUT	EFFICIENCY (Typ.)	86.5%	90%	91%		
	AC CURRENT	1.4A / 115VAC 0.7A / 230VAC				
	INRUSH CURRENT (max.)	70A / 230VAC				
	LEAKAGE CURRENT(max.)	0.75mA / 240VAC				
PROTECTION	OVERLOAD Note.4	90 ~ 110% rated output power				
		Protection type: Constant current limiting recovers automatically after fault condition is removed				
	SHORT CIRCUIT	Protection type: Hiccup mode, recovers automatically after fault condition is removed				
	OVER VOLTAGE	14 ~ 16.5V 29 ~ 33V 59 ~ 69V Protection type: Shut down o/p voltage, re-power on to recover				
	OVER TEMPERATURE	100°C ±10°C (RTH2) detect on inside ambient temperature				
	WORKING TEMP	Protection type: Shut down o/p voltage, re-power on to recover				
ENVIRONMENT	WORKING TEMP. WORKING HUMIDITY	-30 ~ +70°C (Refer to output load derating curve) 20% ~ 90% RH non-condensing				
		5				
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH				
	TEMP. COEFFICIENT	±0.03% / °C (0~50°C)				
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes				
SAFETY & EMC (Note. 5)	SAFETY STANDARDS WITHSTAND VOLTAGE	UL1012 (for GC120Axx-AD1 only), TUV EN60950-1 approved I/P-O/P: 3KVAC				
		I/P-O/P: 3RVAC				
	ISOLATION RESISTANCE	-				
	HARMONIC CURRENT					
	EMS IMMUNITY	Compliance to EN61000-3-2,3				
OTHERS	MTBF	Compliance to EN61000-4-2,3,4,5,6,8,11, light industry level, criteria A				
	DIMENSION	400.7Khrs min. MIL-HDBK-217F(25°C) 167*67*35mm (L*W*H)				
	PACKING	,				
		0.62Kg; 20pcs/13.4Kg/0.9CUFT				
CONNECTOR	PLUG CABLE	See page 2; Other type available by customer requested				
	-					
NOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25℃ of ambient temperature. This is MeanWell's suggested range, please consult your battery manufacturer for their suggestions about maximum charging current limitation. Derating may be needed under low input voltage. Please check the derating curve for more details. Constant current operation region is within 50~100% rated output voltage. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. 					



