



Features:

- Universal AC input/Full range
- Low leakage current<0.5mA
- Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- 100% full load burn-in test
- Fixed switching frequency at 65KHz
- 2 years warranty

SPECIFICATION



MODEL		PT-65A			PT-65B			PT-65C			PT-65D			
	OUTPUT NUMBER	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	CH3	
ОИТРИТ	DC VOLTAGE	5V	12V	-5V	5V	12V	-12V	5V	15V	-15V	5V	12V	24V	
	RATED CURRENT	5.5A	2.5A	0.5A	5.5A	2.5A	0.5A	5.5A	2A	0.5A	4A	2A	1A	
	CURRENT RANGE	0.4 ~ 7A	0.2 ~ 3.2A	0 ~ 0.7A	0.4 ~ 7A	0.2 ~ 3.2A	0 ~ 0.7A	0.4 ~ 7A	0.2 ~ 2.6A	0 ~ 0.7A	0.5 ~ 5A	0.2 ~ 4A	0.2 ~ 1.3A	
	RATED POWER	60W	<u>'</u>	'	63.5W	•	•	65W			68W			
	OUTPUT POWER (max.)	Rated out	put power f	or convecti	on; 72W with 18CFM min. Forced			air						
	RIPPLE & NOISE (max.) Note.2	50mVp-p	120mVp-p	50mVp-p	50mVp-p	120mVp-p	100mVp-p	50mVp-p	120mVp-p	100mVp-p	50mVp-p	100mVp-p	200mVp-p	
	VOLTAGE ADJ. RANGE	CH1:4.75 ~ 5.5V												
	VOLTAGE TOLERANCE Note.3	±4.0%	±7.0%	±5.0%	±4.0%	±7.0%	±5.0%	±4.0%	±7.0%	±5.0%	±4.0%	±6.0%	±6.0%	
	LINE REGULATION	±1.0%	±2.0%	±1.0%	±1.0%	±2.0%	±1.0%	±1.0%	±2.0%	±1.0%	±1.0%	±2.0%	±3.0%	
	LOAD REGULATION	±3.0%	±4.0%	±1.0%	±3.0%	±4.0%	±1.0%	±3.0%	±4.0%	±1.0%	±2.0%	±5.0%	±5.0%	
	SETUP, RISE TIME	800ms, 20	800ms, 20ms at full load											
	HOLD UP TIME (Typ.)	60ms at fu	60ms at full load											
INPUT	VOLTAGE RANGE	90 ~ 264VAC 127 ~370VDC												
	FREQUENCY RANGE	47 ~ 440Hz												
	EFFICIENCY(Typ.)	76% 77% 77%									79%			
	AC CURRENT (Typ.)	1.5A/115VAC 0.9A/230VAC												
	INRUSH CURRENT (Typ.)	COLD START 20A/115VAC 40A/230VAC												
	LEAKAGE CURRENT	<0.75mA												
PROTECTION	OVERLOAD	73 ~ 95W rated output power 74.8 ~ 98.6W rated output power												
	OVERLOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed.												
	OVER VOLTAGE	5.75 ~ 6.75VDC on CH1												
		Protection type: Hiccup mode, recovers automatically after fault condition is removed.												
ENVIRONMENT	WORKING TEMP.	-10 ~ +60°C (Refer to "Derating Curve")												
	WORKING HUMIDITY	20 ~ 90% RH non-condensing												
	STORAGE TEMP., HUMIDITY	-20 ~ +85°C, 10 ~ 95% RH												
	TEMP. COEFFICIENT	$\pm 0.04\%$ °C (0 ~ 50°C) on +5V output												
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes												
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1 approved												
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC 1min.												
EMC (Note 4)	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH												
	EMC EMISSION	Compliance to EN55022 (CISPR22) Class B, EN61000-3-2,-3												
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, light industry level, criteria A												
OTHERS	MTBF	277.2K hrs min. MIL-HDBK-217F (25°C)												
	DIMENSION	127*76*42mm (L*W*H)												
	PACKING	0.25Kg; 5	0.25Kg; 54pcs/15.9Kg/1.35CUFT											
NOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. Tolerance: includes set up tolerance, line regulation and load regulation. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) Mounting holes M1 and M2 should be grounded for EMI purposes. Heat Sink HS1,HS2 can not be shorted. 													



