

Three Phase Bridge (Power Modules), 25/35 A



D-63



RoHS
COMPLIANT

FEATURES

- Universal, 3 way terminals: push-on, wrap around or solder
- High thermal conductivity package, electrically insulated case
- Center hole fixing
- Excellent power/volume ratio
- UL E300359 approved
- Gold plated terminals solderable using lead (Pb)-free solder; solder alloy Sn/Ag/Cu (SAC305); solder temperature 260 to 275 °C
- RoHS compliant
- Designed and qualified for industrial and consumer level

DESCRIPTION

PRODUCT SUMMARY	
I _O	25/35 A

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and instrumentation applications.

MAJOR RATINGS AND CHARACTERISTICS				
SYMBOL	CHARACTERISTICS	26MT	36MT	UNITS
I _O		25	35	A
	T _C	70	60	°C
I _{FSM}	50 Hz	360	475	A
	60 Hz	375	500	
I ² t	50 Hz	635	1130	A ² s
	60 Hz	580	1030	
V _{RRM}		100 to 1600		V
T _J		- 55 to 150		°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} MAXIMUM AT T _J MAXIMUM mA
26MT../36MT..	10	100	150	2
	20	200	275	
	40	400	500	
	60	600	725	
	80	800	900	
	100	1000	1100	
	120	1200	1300	
	140	1400	1500	
	160	1600	1700	

26MT../36MT.. Series

Vishay High Power Products

Three Phase Bridge
(Power Modules), 25/35 A



FORWARD CONDUCTION

PARAMETER	SYMBOL	TEST CONDITIONS			VALUES		UNITS		
			26MT	36MT					
Maximum DC output current at T_c	I_o	120° rect. conduction angle			25	35	A		
			70	60			°C		
Maximum peak, one-cycle non-repetitive forward current	I_{FSM}	$t = 10 \text{ ms}$	No voltage reapplied 100 % V_{RRM} reapplied	Initial $T_J = T_J$ maximum	360	475	A		
		$t = 8.3 \text{ ms}$			375	500			
		$t = 10 \text{ ms}$			300	400			
		$t = 8.3 \text{ ms}$			314	420			
Maximum I^2t for fusing	I^2t	$t = 10 \text{ ms}$	No voltage reapplied 100 % V_{RRM} reapplied	$T_J = T_J$ maximum	635	1130	A^2s		
		$t = 8.3 \text{ ms}$			580	1030			
		$t = 10 \text{ ms}$			450	800			
		$t = 8.3 \text{ ms}$			410	730			
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	I^2t for time $t_x = I^2\sqrt{t} \times \sqrt{t_x}$; $0.1 \leq t_x \leq 10 \text{ ms}$, $V_{RRM} = 0 \text{ V}$			6360	11 300	$\text{A}^2\sqrt{\text{s}}$		
Low level of threshold voltage	$V_{F(TO)1}$	$(16.7 \% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, T_J maximum			0.88	0.86	V		
High level of threshold voltage	$V_{F(TO)2}$	$(I > \pi \times I_{F(AV)})$, T_J maximum			1.13	1.03			
Low level forward slope resistance	r_{t1}	$(16.7 \% \times \pi \times I_{F(AV)} < I < \pi \times I_{F(AV)})$, T_J maximum			7.9	6.3	$\text{m}\Omega$		
High level forward slope resistance	r_{t2}	$(I > \pi \times I_{F(AV)})$, T_J maximum			5.2	5.0			
Maximum forward voltage drop	V_{FM}	$T_J = 25 \text{ }^\circ\text{C}$, $I_{FM} = 40 \text{ Apk}$ - per single junction			1.26	1.19	V		
Maximum DC reverse current	I_{RRM}	$T_J = 25 \text{ }^\circ\text{C}$, per junction at rated V_{RRM}			100		μA		
RMS isolation voltage	V_{INS}	$T_J = 25 \text{ }^\circ\text{C}$, all terminal shorted; $f = 50 \text{ Hz}$, $t = 1 \text{ s}$			2700		V		

THERMAL - MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES		UNITS
			26MT	36MT	
Maximum junction and storage temperature range	T_J , T_{Stg}		- 55 to 150		°C
Maximum thermal resistance, junction to case	R_{thJC}	DC operation per bridge (based on total power loss of bridge)	1.42	1.35	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth, flat and greased	0.2	0.2	
Approximate weight			20		g
Mounting torque $\pm 10 \%$		Bridge to heatsink with screw M4	2.0		Nm


26MT../36MT.. Series

Vishay High Power Products


Three Phase Bridge
(Power Modules), 25/35 A



ORDERING INFORMATION TABLE



CIRCUIT CONFIGURATION



D-63

DIMENSIONS in millimeters (inches)
