
Inch-size One-touch Fittings Series KQ2

Applicable Tubing: Inch Size Connection Thread: UNF, NPT



Plug-in reducer


Bulkhead union

Bulkhead connector
Bulkhead union elbow *

* Available only for KQ2 (White color body).

R

Ε





Product's Color

Series	Body	Release button
Series KQ2	White	Orange
Series KQ	Black	Red

Applicable Tubing

Tubing material	Nylon, Soft nylon, Polyurethane
Tubing O.D. (inch)	ø1/8, ø5/32, ø3/16, ø1/4, ø5/16, ø3/8, ø1/2

Specifications

Fluid		Air/Water Note)					
Maximum operating	pressure	1.0 MPa					
Operating vacuum p	ressure	-100 kPa					
Proof pressure		3.0 MPa					
Ambient and fluid te	mperature	-5 to 60°C, Water: 0 to 40°C (No freezing)					
	Mounting section	ANSI/ASMEB1.20.1-1983 (NTP thread)					
Thread	Wounting Scotlon	JIS B 0212 2A, Class 2B (UNF thread)					
	Nut section	JIS B 0212 2A, Class 2B (UNF thread)					
Seal (Thread portion	1)	With thread seal					
Note) Applicable for	gonoral industrial water	r Places consult with SMC if using for other kinds					


Note) Applicable for general industrial water. Please consult with SMC if using for other kinds of fluid.

Also, the surge pressure must be under the maximum operatin g pressure.

Principal Parts Material

Body	C3604BD, PBT, PP
Stud	C3604BD (Thread portion)
Chuck	Stainless steel 304
Guide	Stainless steel 304, C3604BD, POM
Collet	POM
Release button	POM
Seal, O-ring	NBR
Gasket	Stainless steel 304, NBR

Series KQ2



Part no.: M-10/32G


Material: Stainless steel 304, NBR

Series KQ2

Different Diameter Plug-in "Y": KQ2X




Applicable tubing O.D. (inch)	Applicable fitting size ød	Model	Note) Ø D	L1	L2	A	Р	Q	М	Min. port size	Weight (g)
1/8	5/32	KQ2X01-03	10.4	51.5	18	35.5	10.4	9.7	15.5	2.5	5
5/32	3/16	KQ2X03-05	11.4	56	20.5	39.5	11.4	10.6	16	3.5	10
3/16	1/4	KQ2X05-07	13.2	56.5	21.5	39.5	13.2	12	16.5	4.6	9
1/4	⁵ /16	KQ2X07-09	15.2	64.5	24.5	46	15.2	13.7	17	6	21



Plug-in Reducer: KQ2R



Applicable tubing O.D. (inch)	Applicable fitting size ød (inch)	Model	Note) Ø D	L	A	М	Min. port size	Weight (g)
	5/32	KQ2R01-03	9.6	34.5	18.5			2
1/8	3/16	KQ2R01-05	9.2	34	17.5	15.5	2.5	7
	1/4	KQ2R01-07	9.2	34	17			9
5/32	3/16	KQ2R03-05	10	34	17.5	16	3	8
9/32	1/4	KQ2R03-07	10.4	34.5	17.5	10	3	9
3/16	1/4	KQ2R05-07	11.4	34.5	18.5	16.5	3.5	4
9 16	5/16	KQ2R05-09	10.7	36.5	18	16.5	3.5	14
1/4	5/16	KQ2R07-09	13.2	37	18.5	17	4.6	17
74	3/8	KQ2R07-11	13.2	40	19.5	17	4.0	19
5/16	3/8	KQ2R09-11	14	40	10	10.5		24
9/16	1/2	KQ2R09-13	14	41	19	18.5	6	32
3/8	1/2	KQ2R11-13	17.9	44	22	21	7	32




Note) ØD: Max. diameter

Note) øD: Max. diameter

Bulkhead Union: KQ2E



Applicable tubing O.D.	Model	Connection thread	H (Width across	L	Mounting hole	М	Min.	Weight	
(inch)		UNF	flats)		11010		size	(g)	
1/8	KQ2E01-00	1/2-20	17.46	32.5	13.5	15.5	2.5	26	
5/32	KQ2E03-00	1/2-20	17.46	32.5	13.5	16	3	26	
3/16	KQ2E05-00	9/16-18	17.46	34	15	16.5	3.5	33	
1/4	KQ2E07-00	9/16-18	17.46	34.5	15	17	4.6	33	
5/16	KQ2E09-00	3/4-16	22.23	38	20	18.5	6	52	
3/8	KQ2E11-00	7/8-14	25.4	42.5	23	21	7	70	
1/2	KQ2E13-00	1-12	28.6	44.5	26	22	9.6	97	



Bulkhead Male Elbow: KQ2LE



Applicable tubing O.D. (inch)	Model	Т		H2 (Width across flats)		E	Note) Ø D	Mounting hole	М	Min. port size	Weight (g)
1/8	KQ2LE01-00	1/2-20 UNF	17.46	17.46	17.5	31	9.6	13.5	15.5	2.5	27
5/32	KQ2LE03-00	1/2-20 UNF	17.46	17.46	18	31	10.4	13.5	16	3	26
3/16	KQ2LE05-00	9/16-18 UNF	17.46	17.46	19.5	34.5	11.4	15	16.5	3.5	32
1/4	KQ2LE07-00	9/16-18 UNF	17.46	17.46	20.5	35	13.2	15	17	4.6	29
5/16	KQ2LE09-00	3/4-16 UNF	22.23	22.23	23.5	38.5	15.2	20	18.5	6	53
3/8	KQ2LE11-00	7/8-14 UNF	25.4	25.4	25.5	43	17.9	23	21	7	85
1/2	KQ2LE13-00	1-12 UNF	28.6	28.6	28	46	21.7	26	22	9.6	105

