Rectangular Multi-connector Connecting Tube: 10, 20

Series KDM

Multi-connector is effective in saving labor for separate transportation of the panel and the machine and for exchanging units due to failure.

Substantial reduction in mounting space


In comparison with a model requiring many union joints for panels and partitions, this model needs only a small space.

One-touch connection/ disconnection of connector

Multiple pipes can be connected/disconnected in one-touch opperation without connection error. Thus man-hours for connection/disconnection is cut down substantially.


One-touch tube connection

One-touch fittings substantially cuts down man-hours for piping.



△Caution

Be sure to read before handling. Refer to p.0-26 and 0-27 for Safety I Instructions and common precautions on the products mentioned in this catalog, and refer to p.2.0-7 and 2.0-8 for more detailed precautions of every series.



Model

No. of connecting tubes	Tube O.D.	Part No.	Weight	Color of release button
10	ø3.2	KDM10-23		
	ø4	KDM10-04	300g	
	ø6	KDM10-06		
	ø8	KDM10-08	520g	Blue
20	ø3.2	KDM20-23	520g	Diue
	ø4	KDM20-04		
	ø6	KDM20-06		
	ø8	KDM20-08	950g	

Applicable Tubing

Tube material	Nylon, Soft nylon, Polyurethane	
Tube O.D.	ø3.2, ø4, ø6, ø8	

Specifications

Operating fluid	Air
Max.operating pressure	1.0MPa
Max.operating vacuum pressure	-100kPa
Proof pressure	1.5MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)

Multi-connector Series KDM

Component Materials

Plug case, Socket case		Polyacetal (POM)
Plate, Bracket		SPCC Plated
Plug connector, Socket connector	Body	PBT, C3604BD Electroless nickel plated (ø8)
	Chuck	SUS304
	Guide	Stainless steel (SUS304), C3604BD Electroless nickel plated, POM (Ø8)
	Collet, Release button	Polyacetal (POM)
	Packing	NBR
Clamp bolt, Screw for bracket, Cross-recessed head machine screw		SWRM, Nickel plated
E type snap ring		Stainless steel (SUS304)

Part Numbers

No.of connecting	Tube	Part No.		Color of	
tubes	O.D.	Plug	Socket	release button	
10	ø3.2	KDM10P-23	KDM10S-23		
	ø4	KDM10P-04	KDM10S-04		
	ø6	KDM10P-06	KDM10S-06		
	ø8	KDM10P-08	KDM10S-08	Dive	
20	ø3.2	KDM20P-23	KDM20S-23	Blue	
	ø4	KDM20P-04	KDM20S-04		
	ø6	KDM20P-06	KDM20S-06		
	ø8	KDM20P-08	KDM20S-08		


Mixed Sizes of Plug Connectors and Socket Connectors

The rectangular multi-connector permits connector exchange in any desired position, thus allowing use of different sizes of tubes.


Part Numbers

Connector	Tube O.D.	Part No.	Color of release button	
Plug connector	ø3.2	KDMP-23		
	ø4	KDMP-04		
	ø6	KDMP-06		
	ø8	KDMP-08	Blue	
Socket co nnector (With packing)	ø3.2	KDMS-23	Dide	
	ø4	KDMS-04		
	ø6	KDMS-06		
	ø8	KDMS-08		

①Loosen the cross-recessed head machine screw using a Phillips screwdriver to remove the plate from the case.



②After exchanging connectors in desired places, fix the plate with a Phillips screwdriver to the case.




How to Use

A Caution


Separation

Loosen the clamp bolt to separate the plug side from the socket side.




Connection

Put together the irregular faces for engagement and connect the plug case to the socket. After tightening the clamp bolt by hand, tighten it further with allen wrench(nominal width across flats: 4).




Panel mounting


①Loosen (4) screws for bracket on the socket side using a Phillips screwdriver (JIS nominal No.2) until the bracket touches the stop ring.




②Shift the panel mounting bracket to the inside (Move the screw for bracket in the longitudinal direction of the slot) and put the connector in the panel mounting hole. (Panel mounting hole: See Dimensions.)



③After shifting the bolt for bracket to the outside, tighten the bolt with a Phillips screwdriver to fix the socket case.




(4) Loosen the screw for bracket until the bracket touches the stop ring and shift the bracket to the inside to remove the connector from the panel.



 $\mathsf{K}\square$

Series KDM



Made to Order

Contact SMC for detailed specifications, dimensions and delivery.

■Mixed tube sizes
Mixed tube size manifolds are available to meet your individual requirements. Consult your SMC sales representative for availability.

■Other tube sizes

Tube size (O.D.)	Number of tubes	Part No.
ø10	6	IN-254-52
ø12	6	IN-254-53