2-Color Display High-Precision Digital Pressure Switch

Settings can be copied to up to 10 slave sensors at once.

The settings of the master sensor can be copied to the slave sensors.

Reduced setting efforts
 Reduced chance of set-value input error




3-step setting





Added vacuum range.

■ Rated pressure range: 0.0 to -101.0 kPa



Expanded pressure range for positive-pressure type to the vacuum range.

Rated pressure range: -0.100 to 1.000 MPa

2 added outputs

- NPN or PNP open collector 2 outputs
- NPN or PNP open collector 1 output + Analog output (1 to 5 V or 4 to 20 mA)




RoHS compliant

Series ZSE30A(F)/ISE30A




Mounting

Bracket configuration allows mounting in four orientations.



Panel mount


Mountable side by side without clearance



One opening!


- Reduction of panel-cut job
- Space-saving

Series




Replaceable one-touch fittings

The clip type allows easy removal of fittings. Fitting's type and size can be changed.



Lead wire

Added the connector cover.



4-digit display

4-digit display allows easy reading of displayed values.

Example: 0.5 MPa



Possible to check set-value during key locking

Additional functions

Secret code setting function

The key locking function keeps unauthorized persons from tampering with buttons.

Power-saving function

Power consumption is reduced by turning off the monitor. (Reduce power consumption by up to 20%.)

Resolution-switch function

It reduces the monitor to flicker.




(Accuracy is not changed, only the displayed values.)

◆ MPa/kPa switch function

Vacuum, compound and/or positive pressure can be displayed in MPa or kPa.



2-Color Display High-Precision **Digital Pressure Switch** Series ZSE30A(F)/ISE30A



How to Order

Output

ı	N	NPN open collector 1 output			
P PNP open collector 1 output					
ı	Α	NPN open collector 2 outputs			
ı	В	PNP open collector 2 outputs			
l	C*	NPN open collector 1 output + Analog voltage output			
ı	D*	NPN open collector 1 output + Analog current output			
ı	E*	PNP open collector 1 output + Analog voltage output			

F* PNP open collector 1 output + Analog current output

* Made to Order

Option 1

For positive pressure

For vacuum/ compound pressure

ZSE30AF

01-N-M

Rated pressure range ZSE30A 0 to -101 kPa

-100 to 100 kPa

Piping •

Option 3						
Cumbal	Operating	Calibration				
Symbol	Booklet	CD-ROM	certificate			
Nil	0	_				
Υ	_	_	-			
W	_	0	-			
K	0	_	0			
Т	_	_	0			
R	_	0	0			

		i ipilig •			
01	R1/8 (M5 female threaded)				
N01*	NPT1/8 (M5 female threaded)				
C4H	One-touch fitting ø4 mm, ø5/32 inch	Straight type			
С6Н	One-touch fitting ø6 mm				
N7H	One-touch fitting ø1/4 inch	0			
C4L	One-touch fitting ø4 mm, ø5/32 inch	Elbow type			
C6L	One-touch fitting ø6 mm				
N7L	One-touch fitting ø1/4 inch				
* Made to Order					

• Optic	Option 2		
Nil	None		
A 1	Bracket A		
A2	Bracket B		
	Panel mount adapter		
В			

Panel mount adapter + Front protection cover

switching function Fixed SI unit Note 2) M With unit display Note 1) switching function (Initial value PSI)

Display unit •

With unit display Note 1)

* Made to Order

Nil

Note 1) Under the New Measurement Law, sales of switches with the unit switching function have not been allowed for use in Japan.

Note 2) Fixed unit kPa, MPa

Nil	Without lead wire	
L	Lead wire with connector (Lead wire length 2 m) Note)	
G	Lead wire with connector (Lead wire length 2 m) Note) With connector cover	Connector cover

Note) For output types N and P, the number of core of lead wires will be 3, and for other types, it will be 4.



Specifications

Model		odel	ZSE30A (Vacuum pressure)	ZSE30	OAF (Compound pressure)	ISE30A (Positive pressure)	
Rated pressure range			0.0 to -101.0 kPa		-100.0 to 100.0 kPa	-0.100 to 1.000 MPa	
Set pressure range			10.0 to -105.0 kPa		-105.0 to 105.0 kPa	-0.105 to 1.050 MPa	
Withstand pressure			500 kPa		500 kPa	1.5 MPa	
Minimum	unit settin	g	0.1 kPa		0.1 kPa	0.001 MPa	
Applicable	e fluid		Air, Non-corrosive gas, Non-flammable gas				
Power su	oply voltag	ge	12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection)				
Current co	onsumptio	on	40 mA or less				
Switch ou	tput		NPN or PNP open colle	ector 1 out	put, NPN or PNP open collector	or 2 outputs (selectable)	
	Maximum	load current			80 mA		
	Maximum	applied voltage			28 V (at NPN output)		
	Residual	voltage		1 V or les	ss (with load current of 80 mA)		
	Response	e time	2.5 ms or less (w	vith anti-ch	nattering function: 20, 100, 500	, 1000, 2000 ms)	
	Short circ	cuit protection			Yes		
Repeatabi	ility				±0.2% F.S. ±1 digit		
Hystere-	Hysteresi	s mode		Vo	rights (0 or above) Note 1)		
sis	Window o	comparator mode	Variable (0 or above) Note 1)				
	Note 2) Output voltage (Rated pressure r		1 to 5V ±2	2.5% F.S.		0.6 to 5 V ±2.5% F.S.	
	Voltage output	Linearity	±1% F.S. or less				
	output	Output impedance	Approx. 1 kΩ				
Analog output	Note 3)	Output current (Rated pressure range)	4 to 20 mA ±2.5% F.S. 2.4 to 20 mA ±2.5% F				
Juiput	Current	Linearity	±1% F.S. or less				
	output	Load impedance	Maximum load impedance: F Minimum load impedance: 50		ply voltage 12 V: 300 Ω , Power	r supply voltage 24 V: 600 Ω	
Display			4-digit, 7-segment, 2-color LCD (Red/Green)				
Display ad	ccuracy		±2% F.S. ±1 digit (Ambient temperature of 25 ±3°C)				
Indicator	light		Lights up when switch output is turned ON. OUT1: Green, OUT2: Red				
	Enclosu	ıre	IP40				
	Operati	ng temperature range	Operating: 0 to 50°C, Stored: –10 to 60°C (No freezing or condensation)				
Environ-	Operati	ng humidity range	Operating/Stored: 35 to 85% RH (No condensation)				
ment	Withsta	nd voltage	1000 VAC for 1 minute between live parts and case				
resistance			50 $M\Omega$ or more between live parts and case (at 500 VDC Mega)				
	Vibration resistance		10 to 150 Hz at whichever is smaller of 1.5 mm amplitude or 20 m/s ² acceleration, in X, Y, Z directions, for 2 hours each (Non-energized)				
	Impact resistance		100 m/s ² in X, Y, Z directions, 3 times each (Non-energized)				
Temperature characteristics			±2% F.S. (Based on 25°C)				
Lead wire			Oilproof heavy-duty vinyl cable,			WG26), Insulator O.D.: 1.0 mm	
Standards	3			CE Markii	ng, UL/CSA, RoHS compliance		
			t value, set the bysteresis above the fluctual				

Note 1) If applied pressure fluctuates near the set value, set the hysteresis above the fluctuation range to prevent chattering.

Piping Specifications

	Model	01	N01	C4H	C6H	N7H	C4L	C6L	N7L
Port size		R1/8 M5 x 0.8	NPT1/8 M5 x 0.8	_	_	_	_	_	_
	One-touch fitting, Straight type	_	_	ø4 mm ø5/32 inch	ø6 mm	ø1/4 inch	_	_	_
	One-touch fitting, Elbow type	_	_	_	_	_	ø4 mm ø5/32 inch	ø6 mm	ø1/4 inch
Wetted	Sensor pressure receiving area	Sensor pressure receiving area: Silicon							
parts material	Piping port	C3602 (electroless nickel plated) O-ring: HNBR		PBT, POM, Stainless steel 304, C3604 (electroless nickel plated) O-ring: NBR			ed)		
	Including lead wire with connector (3 cores, 2 m)	81 g		70 g	71 g	73 g	75 g	73 g	75 g
Weight	Including lead wire with connector (4 cores, 2 m)	85 g		74 g	75 g	77 g	79 g	77 g	79 g
	Excluding lead wire with connector	43 g		32 g	33 g	35 g	37 g	35 g	37 g

Optional Part No.

When optional parts are required separately, use the following part numbers to place an order.

Part no.	Option	Note
ZS-38-A1	Bracket A	Mounting screw (with 2 pcs. of M3 x 5L)
ZS-38-A2	Bracket B	Mounting screw (with 2 pcs. of M3 x 5L)
ZS-27-C	Panel mount adapter	Mounting screw (with 2 pcs. of M3 x 8L)
ZS-27-D	Panel mount adapter + Front protection cover	Mounting screw (with 2 pcs. of M3 x 8L)
ZS-27-01	Front protection cover	
ZS-38-3L	Lead wire with connector	3 cores, for 1 output, 2 m
ZS-38-4L	Lead wire with connector	4 cores, for 2 outputs, 2 m
ZS-38-3G	Lead wire with connector (with connector cover)	3 cores, for 1 output, 2 m
ZS-38-4G	Lead wire with connector (with connector cover)	4 cores, for 2 outputs, 2 m


Part no.	Option	Note
ZS-38-5L	Lead wire with a connector for copying	3 cores, copy function, 1 m
ZS-38-U	Lead wire unit with a connector for copying	Copy function (up to 10 slaves)
ZS-38-C4H	One-touch fittings ø4 mm straight	O-ring, one-touch clip included
ZS-38-C6H	One-touch fittings ø6 mm straight	O-ring, one-touch clip included
ZS-38-N7H	One-touch fittings ø1/4 inch straight	O-ring, one-touch clip included
ZS-38-C4L	One-touch fittings ø4 mm elbow	O-ring, one-touch clip included
ZS-38-C6L	One-touch fittings ø6 mm elbow	O-ring, one-touch clip included
ZS-38-N7L	One-touch fittings ø1/4 inch elbow	O-ring, one-touch clip included
ZS-38-H	Operating manual CD-ROM	



Note 2) When analog voltage output is selected, analog current output cannot be used together. Note 3) When analog current output is selected, analog voltage output cannot be used together.

2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A

Analog Output



S

Descriptions

Unit display

Displays present unit (only for units of kPa and MPa).

Output (OUT1) display (Green)

Lights up when switch output (OUT1) is turned ON.

△ button (UP)

Use this button to select the mode or increase the $\ensuremath{\mathsf{ON}}/\mathsf{OFF}$ set-value.

It is also used for switching to the peak display mode.

S button (SET)

Use this button to change the mode or confirm the set-value.

LCD

Displays the current pressure, set mode, and error code. Always use red or green display; or switch between green and red according to the output. Four different display settings are available.

Output (OUT2) display (Red)

Lights up when switch output (OUT2) is turned ON.

▽ button (DOWN)

Use this button to select the mode or decrease the ON/OFF set-value.


It is also used for switching to the bottom display mode.

Functions (Refer to pages 10 and 11 for details.)

Copy function	Copies the settings of the master sensor to the slave sensors.	
Auto-preset function	Calculates and enters rough set values automatically from the actual operating conditions.	
Precision indicator setting function	Evens out deviations in the displayed value.	
Peak display function	Can retain the maximum pressure value displayed during measurement.	
Bottom display function	Can retain the minimum pressure value displayed during measurement.	
Key lock function (Security code input can be selected.)	The key board can be locked to prevent any incorrect function of the operation switch.	
Zero-out function	The pressure display can be set at zero when the pressure is open to the atmosphere.	
Anti-chattering function	Prevents possible malfunction due to sudden fluctuations in the primary pressure by adjusting the response time.	
Unit display switching function	Can convert the display value.	
Power-saving mode	Reduces power consumption.	
Display resolution-switch function	Converts display resolution from the normal value of 1/1000 to 1/100. It reduces the monitor to flicker.	
kPa⇔MPa switch function	Converts the unit between kPa and MPa.	




Internal Circuits and Wiring Examples






NPN (1 output)



Max. 28 V, 80 mA Residual voltage 1 V or less

Р


PNP (1 output)



Max. 80 mA Residual voltage 1 V or less




NPN (2 outputs)



Max. 28 V, 80 mA Residual voltage 1 V or less



PNP (2 outputs)




Max. 80 mA Residual voltage 1 V or less

* The FUNC terminal is connected using a dedicated lead wire (ZS-38-5L or ZS-38-U) when the copy function is used. (Refer to "Copy function" on page 10.)

2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A



NPN (1 output) + Analog voltage output




Max. 28 V, 80 mA Residual voltage 1 V or less

Analog voltage output Output impedance: Approx. 1 $k\Omega$

Ε

PNP (1 output) + Analog voltage output




Max. 80 mA Residual voltage 1 V or less

Analog voltage output Output impedance: Approx. 1 $k\Omega$



NPN (1 output) + Analog current output




Max. 28 V, 80 mA Residual voltage 1 V or less

Analog current output Max. load impedance:

Power supply voltage 12 V: 300 Ω Power supply voltage 24 V: 600 Ω Min. load impedance: 50 Ω



PNP (1 output) + Analog current output



Max. 80 mA Residual voltage 1 V or less


Analog current output Max. load impedance:

Power supply voltage 12 V: 300 Ω Power supply voltage 24 V: 600 Ω Min. load impedance: 50 Ω





^{*} The FUNC terminal is connected using a dedicated lead wire (ZS-38-5L or ZS-38-U) when the copy function is used. (Refer to "Copy function" on page 10.)

Dimensions




01 / N01






C4H

One-touch fitting ø4 mm ø5/32 inch straight




С6Н

One-touch fitting ø6 mm straight




N7H

One-touch fitting ø1/4 inch straight




C4L

One-touch fitting ø4 mm ø5/32 inch elbow




C6L

One-touch fitting ø6 mm elbow




N7L

One-touch fitting ø1/4 inch elbow




2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A








Bracket A

(Option unit part no.: ZS-38-A1)











* Bracket configuration allows mounting in four orientations.




Bracket B


(Option unit part no.: ZS-38-A2)








* Bracket configuration allows mounting in four orientations.



Dimensions


Panel mount








Panel mount adapter

(Option unit part no.: ZS-27-C)













Panel mount adapter + Front protection cover (Option unit part no.: ZS-27-D)







2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A


Panel-cut dimensions




Multiple (2 pcs. or more) horizontal mounting








Multiple (2 pcs. or more) vertical mounting







Function Details

A Copy function (F97)

The settings of the master sensor can be copied to the slave sensors.

It is to reduce the time taken for setting and prevent the input of wrong values.

Settings can be copied to up to 10 slave sensors at once.

(Max. transmission distance: 4 m)



Slave-side sensor Master-side Unit n Unit 1 Unit 2 sensoi (Max. 10 units) UT2 (-) () C Z Z (±) () N T T (±) Brown (Line for copying) (Line for copying) (Line for copying) (Line for copying) ZS-38-5L (n + 1 pc.) 7S-38-U

 The sensors are connected by a dedicated lead wire (ZS-38-5L (for master and one slave) or ZS-38-U (for master and up to 10 slaves)). Copying is performed through a dedicated communication line.

Make the slave sensor which needs to be the master into the master by button operation. (Initially all sensors are set as slaves.)

Press the S button on the master sensor to start copying.


B Auto-preset function (F5)

Auto-preset function, when selected in the setting, calculates and stores the set-value from the measured pressure.

The optimum set-value is determined automatically by repeating vacuum and break with the target workpiece several times.


Suction Verification

Power



C Precision indicator setting function (F6)

Fine adjustment of the indicated value of the pressure sensor can be made within the range of $\pm 5\%$ of the read value. The scattering of the indicated value can be eliminated.



Note) When the precision indicator setting function is used, the set pressure value may change ± 1 digit.

Formula for Obtaining the Set-Value

P_1 or P_2	H_1 or H_2
P_1 (P_2) = A - (A-B)/4 n_1 (n_2) = B + (A-B)/4	H_1 (H_2) = (A-B)/2

D Peak and bottom display function

This function constantly detects and updates the maximum (minimum) value and allows to hold the maximum (minimum) pressure value.

When the \triangle ∇ buttons are simultaneously pressed for 1 second or longer, while "holding", the held value will be reset.

E Key lock function

This function prevents incorrect operations such as accidentally changing the set-value.

F Zero-out function

This function clears and resets the zero value on the display of measured pressure.

For the pressure switch with analog output, the analog output shifts according to the indication. A displayed value can be adjusted within $\pm 7\%$ F.S. of the pressure when ex-factory. ($\pm 3.5\%$ F.S. for ZSE30AF (compound pressure))



2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A

 $\mathsf{F}\square$ in brackets stand for the function codes. Refer to the operating manual for how to operate and function codes in detail.

G Error indication function

Error name	Error code	Description	Solution		
Overcurrent error	Er 1	Load current of switch output (OUT1) exceeds 80 mA.	Shut off the power supply. After eliminating the out-		
	ErZ	Load current of switch output (OUT2) exceeds 80 mA.	put factor that caused the excess current, turn the power supply back on.		
Residual pressure error	Er3	A pressure of $\pm 7\%$ F.S. of atmospheric pressure is applied in the zero-out function. ($\pm 3.5\%$ F.S. or more for ZSE30AF (compound pressure)) The switch will automatically return to measuring mode in 1 second, however. Due to individual product differences, the setting range of the zero-out function varies within $\pm 1\%$ F.S.	Bring the pressure back to atmospheric pressure and try using the zero-out function.		
Applied pressure error	HHH	Supply pressure exceeds the maximum set pressure.	Bring the pressure back to within the set pressure		
	LLL	Supply pressure is below the minimum set pressure.	range.		
System error	ErO		Shut off the power supply. Turn the power supply		
	Ery				
	E-8	Internal data error			
	Er7	Internal data error	back on. If the switch will not recover to normal, consult SMC for investigation.		
	Er8				
	E-9				

If the switch will not recover to normal even after all of the above-mentioned solutions have been applied, consult SMC for investigation.


H Anti-chattering function (F3)

A large bore cylinder or ejector consumes a large volume of air in operation and may experience a temporary drop in the supply pressure. This function prevents detection of such temporary drops in the supply pressure as an error.

Available response time settings
20 ms, 100 ms, 500 ms, 1000 ms, 2000 ms

Principle

This function averages pressure values measured during the response time set by the user and then compares the average pressure value with the pressure set point value to output the result on the switch.



Unit display switching function (F0)

Display units can be switched with this function.

Display unit	PA		GF	bAr	PSi	inH	mmH
Min. unit setting	kPa	MPa*	kgf/cm ²	bar	psi	inHg	mmHg
ZSE30A (Vacuum pressure)	0.1	0.001	0.001	0.001	0.01	0.1	1
ZSE30AF (Compound pressure)	0.1	0.001	0.001	0.001	0.01	0.1	1
ISE30A (Positive pressure)	1	0.001	0.01	0.01	0.1		

^{*} For the ZSE30A (vacuum pressure) and ZSE30AF (compound pressure), when the display unit is MPa, setting and display resolutions are changed.

J Power-saving mode (F7)

Power-saving mode can be selected.

It shifts to the power-saving mode without button operation for 30 seconds. It is set to the normal mode (Power-saving mode is OFF.) when ex-factory. (Decimal points and operation indicator light (only when the switch output is turned ON.) blink in the power-saving mode.)

K Secret code setting (F8)

It can be set whether code number input is required or not when key is locked. It is set to input no code number when ex-factory.





Series ZSE30A(F)/ISE30A Specific Product Precautions 1

Be sure to read this before handling.

Refer to the back of pages 1 and 2 for Safety Instructions and "Precautions for Handling Pneumatic Devices" (M-03-E3A) for Pressure Switches Precautions.

Handling

⚠ Warning

- 1. Do not drop, bump, or apply excessive impacts (100 m/s²) while handling. Although the body of the sensor may not be damaged, the internal parts of the sensor could be damaged and lead to a malfunction.
- The tensile strength of the cord is 35 N. Applying a greater pulling force on it can cause a malfunction. When handling, hold the body of the sensor—do not dangle it from the cord.
- 3. Do not exceed the screw-in torque of 7 to 9 N·m when connecting the pipe to the switch. Exceeding these values may cause the switch to malfunction.
- 4. Do not use pressure sensors with corrosive and/or flammable gases or liquids.
- Allow a sufficient margin of tube length in piping in order to prevent application of torsional, tensile or moment load to the tubes and fittings.
- 6. When a brand of tubing other than SMC is used, make sure that the tolerance of the tube's O.D. satisfies the following specifications.
 - 1) Nylon tubing: ±0.1 mm or less
 - 2) Soft nylon tubing: ±0.1 mm or less
 - 3) Polyurethane tubing: +0.15 mm or less, -0.2 mm or less
- 7. The applicable fluid is air. Consult SMC if the switch is to be used with other types of fluids.

Connection

- Incorrect wiring can damage the switch and cause a malfunction or erroneous switch output. Connections should be done while the power is turned off.
- 2. Do not attempt to insert or pull the pressure sensor or its connector when the power is on. A switch output malfunction may occur.
- 3. Wire separately from power lines and high voltage lines, avoiding wiring in the same conduit with these lines. Malfunctions may occur due to noise from these other lines.
- 4. If a commercial switching regulator is used, make sure that the F.G. terminal is grounded.

Operating Environment


\land Warning

- 1. This pressure switch is CE marked; however, it is not equipped with surge protection against lightning. Lightning surge countermeasures should be applied directly to system components as necessary.
- 2. This pressure switch does not have an explosion proof rating. Never use in the presence of an explosive gas as this may cause a serious explosion.
- Do not use in an environment where static electricity can cause problems, otherwise system failure or malfunction may result.

Mounting


⚠ Caution

1. Mounting and removing with panel mount adapter



2. Mounting with brackets


 Mount a bracket to the using two M3 x 5L mounting screws and install on piping. The switch can be installed horizontally depending on the installation location.



When using bracket B, take piping dimensions into consideration for installation.

Connection/Removal of Connector


- To connect the connector, insert it straight while pinching the lever, and then push the lever into the jack of the housing and lock it.
- To remove the connector, pull it straight out while applying pressure with your thumb to the lever and unhooking it from the jack.



 Do not attempt to insert or pull the pressure sensor or its connector when the power is on. A switch output malfunction may occur.

Piping

- Cut the tube perpendicularly.
- Hold the tube and insert it into the one-touch fitting carefully and securely all the way to the bottom.



Back page 3





Series ZSE30A(F)/ISE30A Specific Product Precautions 2

Be sure to read this before handling. Refer to the back of pages 1 and 2 for Safety Instructions and "Precautions for Handling Pneumatic Devices" (M-03-E3A) for Pressure Switches Precautions.

Set Pressure Range and Rated Pressure Range


A Caution

Set the pressure within the rated pressure range.

The set pressure range is the range of pressure that is possible in setting.

The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) on the switch.

Although it is possible to set a value outside the rated pressure range, the specifications will not be guaranteed even if the value stays within the set pressure range.



Rated pressure range of switch
Set pressure range of switch

