


AC Line Rated Disc Capacitors
Class X1, 400 VAC/Class Y4, 125 VAC



LO' = 0.110" (2.8) typ

INSULATION RESISTANCE:

min. 1000 ΩF

TOLERANCE ON CAPACITANCE:

± 20 %

DISSIPATION FACTOR:

2.0 % max. at 1 kHz; 1 V

CERAMIC DIELECTRIC:

Y5V (Class 2)

CATEGORY TEMPERATURE RANGE:

(- 25 to + 125) °C

CLIMATIC CATEGORY ACC. TO EN60068-1:

25/125/21

OPERATING TEMPERATURE RANGE:

(- 30 to + 125) °C

FEATURES

- Worldwide Safety Agency Recognition
Underwriters Laboratories - UL1414
Canadian Standards Association - CSA 22.2
European EN132400 to IEC 60384-14 Second Edition
- Complete Range of Capacitance Values



APPLICATIONS

- Required in AC Power Supply and Filter Applications
- Specific Industry Requirements

DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having a diameter of 0.032" (0.81 mm) or 0.025" (0.64 mm). The capacitors may be supplied with radial kinked or straight leads having a lead spacing of 0.375" (9.5 mm) or 0.250" (6.4 mm). The standard tolerance is ± 20 %. Coating is made of flame retardant epoxy resin in accordance with "UL94V-0".

CAPACITANCE RANGE:

1.0 nF to 0.050 μF

RATED VOLTAGE:

IEC 60384-14.2: (Y4) 125 VAC, 50 Hz
IEC 60384-14.2: (X1) 400 VAC, 50 Hz
UL 1414: 250 VAC, 60 Hz
CSA 22.2 No.1: 125/250 VAC, 60 Hz

DIELECTRIC STRENGTH BETWEEN LEADS:

Component test:
2000 VAC, 50 Hz, 2 s
As repeated test admissible only once with:
1800 VAC, 50 Hz, 2 s
Random sampling test (destructive test):
2000 VAC, 50 Hz, 60 s

DIELECTRIC STRENGTH OF BODY INSULATION:

2300 VAC, 50 Hz, 60 s (destructive test)

125L Series



Vishay Cera-Mite

AC Line Rated Disc Capacitors
Class X1, 400 VAC/Class Y4, 125 VAC

ORDERING INFORMATION, CERAMIC X1/Y4 CAPACITORS 125L							
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	WIRE SIZE		LS LEAD SPACE INCH (mm)	ORDERING CODE
				AWG	INCH (mm)		
Y5V							
1000	± 20 %	0.330 (8.4)	0.195 (5.0)	20	0.032 (0.81)	0.250 (6.4)	125LD10-R
1500		0.330 (8.4)	0.195 (5.0)				125LD15-R
2000		0.330 (8.4)	0.185 (4.7)				125LD20-R
2200		0.330 (8.4)	0.180 (4.6)				125LD22-R
3300		0.365 (9.3)	0.195 (5.0)				125LD33-R
4700		0.400 (10.2)	0.185 (4.7)				125LD47-R
5000		0.430 (10.9)	0.195 (5.0)			125LD50-R	
6800		0.490 (12.4)	0.190 (4.8)			125LD68-R	
8200		0.530 (13.5)	0.190 (4.8)			125LD82-R	
0.010 μF		0.560 (14.2)	0.190 (4.8)			125LS10-R	
0.015 μF		0.720 (18.3)	0.205 (5.2)			125LS15-R	
0.018 μF		0.790 (20.1)	0.205 (5.2)			125LS18-R	
0.020 μF		0.620 (15.7)	0.240 (6.1)	22	0.025 (0.64)	125LS20-R	
0.022 μF		0.900 (22.9)	0.185 (4.7)	20	0.032 (0.81)	125LS22-R	
0.030 μF		0.720 (18.3)	0.240 (6.1)	22	0.025 (0.64)	125LS30-R	
0.050 μF		0.900 (22.9)	0.240 (6.1)	22	0.025 (0.64)	125LS50-R	

Note:


1. Alternate lead spacings of 7.5 mm and 10 mm are available bulk or tape and reel on request.
2. European required minimum lead clearance (prevents use of inside crimp) 0.118" (3 mm)

TAPE and REEL OPTIONS







To specify T & R, add two letter suffix to the ordering code (details of the packaging code see general section of the catalog)



LEAKAGE CURRENT VS. VOLTAGE
(TYPICAL)



INSERTION LOSS VS. FREQUENCY
(TYPICAL)





APPROVALS						
IEC 60384 - 14/2nd Issue (1993) incl. Am.1 (1995) - Safety Tests						
EN 132 400 (1994) - Safety Tests						
That approval together with CB Test Certificate substitutes the national approval of the following nations:						
Belgium	France	Italy	Austria	China	Japan	Spain
Denmark	Greece	Luxembourg	Portugal	Singapore	Poland	United Kingdom
Germany	Ireland	Netherlands	Sweden	Slovenia	Hungaria	Czech Republic
Finland	Iceland	Norway	Switzerland	Korea	Israel	
X1 - Capacitor: CB-Test Certificate:	DE 1-19447	1000 pF ... 0.05 µF		400 V _{AC}		
Y4 - Capacitor: CB-Test Certificate:	DE 1-19447	1000 pF ... 0.05 µF		125 V _{AC}		
UNDERWRITERS LABORATORIES INC.						
UL 1414	Line-by-pass component. Agency Files/Licenses	E99264	1000 pF ... 0.05 µF	250 V _{AC}		
CANADIAN STANDARDS ASSOCIATION						
CSA C22.2 Isolation component No. 1	Agency Files/Licenses	LR 62016	1000 pF... 0.05 µF	250 V _{AC}		

Note 1

UL1414 Across-The-Line, Antenna Coupling, and Line-By-Pass Capacitors:

- Across-The-Line - A capacitor connected either across a supply circuit or between one side of a supply circuit and a conductive part that may be connected to earth ground.
- Antenna-Coupling - A capacitor connected from an antenna terminal to circuits within an appliance
- Line-By-Pass - A capacitor connected between one side of a supply circuit and an accessible conductive part

Note 2

IEC 60384-14 Subclass Y Capacitors:

- A capacitor of a type suitable for use in situations where failure of the capacitor could lead to danger of electric shock
- Class Y capacitors are divided into sub- classes based on type of insulation bridged and voltage ranges
- For definitions of basic, supplementary, double and reinforced insulation, see IEC Publication 536
- Subclass Y capacitors may be used in applications which require a Subclass X rating

Note 3

IEC 60384-14 Subclass X Capacitors:

- A capacitor of a type suitable for use in situations where failure of the capacitor would not lead to danger of electric shock.
- Class X capacitors are divided into subclasses according to the peak impulse test voltage superimposed on the main voltage

MARKING	
	<p> Type: 040C085B251AY202MLA010 - R CM PN: 125LD20 - R E3 Qty. : 250 LOT1: 11642584 DC1: 0622 IEC60384 - 14 / 2: LOT2: DC2: Y4 (125~) , X1 (400~) R.C. : 7032 S.L. : 0010 Op.No. : 771 BATCH NO. : 200822CZ LR62016 PN: 125LD20 - R PO: 0011642584 / 0001 RoHS </p>



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.