



6100-3

C13



70° C

F



70° C

C15



120° C

C19



70° C

J



70° C

C6



70° C

C8



70° C

C8 polarized



70° C

C14



70° C

E



70° C

C16



120° C

Description

Appliance Inlet,

Approvals

- VDE Certificate Number: 40015595
- UL File Number: E96454

Other versions on request

- Types for enhanced glow wire test requirements acc. IEC 60695-2-11 to -13 for the use in unattended household equipment acc. IEC 60335-1

References**Weblinks**

[pdf](#), [html](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data


Allowable Operation Temp.	-40 °C to 85 °C
Degree of Protection	from front side IP 40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class acc. to IEC 61140
Panel Thickness s	Screw Mounting screw torque max 0.5Nm Snap-in 1 mm

Packaging unit 50 Pcs**Accessories****Description**

Sealing Kit
Sealing for Appliance Inlets

IP 54

0098.0103



Assorted Covers
Rear Cover