

• Home> 5219327F

Part Number: **5219327F General Description** 

Series 521

Configuration 5 mm Lens

Description Discrete LED Lamp

Package Options Bulk Packaging

Sizes 5mm

Lamp Type Single Color

Lens Color Tinted Diffused

## Absolute Maximum Ratings (Ta = 25°)

Forward Current mA 7mA

Forward Current Pulsed 500mA

Solder Temperature 260° for 5 sec

Operating Temperature -55~+100

Storage Temperature  $-55 \sim +100$ 

## **Operating Characteristics**

Color Green

LED Type Standard Efficiency

Luminous Intensity Min1.2Luminous Intensity Typical1.8Test Current mA2mAPower Dissipation Max24mW

Site Map Contact Us Dialight BLP Ltd Privacy Policy Careers Copyright© 2009, Dialight. All Rights Reserved.






This is a
RoHS Compliant Product
To learn more click here

0500000000000

## 5mm Discrete LED Low Current, 2mA Diffused



521-9320, -9321, -9327



PART NO.	<u>COLOR</u>
521-9320	Red
521-9321	Yellow
521-9327	Green

## MOUNTING CLIP: 515-0004 located on page 6-48

ABSOLUTE MAXIMUM RATINGS (TA=25°C)	Red <b>-9320</b>	Yellow <b>-9321</b>	Green <b>-9327</b>	
Power Dssipation (mW) Derating (mA/°C) From 92°C	27 1	36 1	24 1	
Forward Current (mA)	7	7	7	
Peak Current (mA) Pulse width = 10 µs	500	500	500	
Operating Temperature (°C)	-55/+100	-55/+100	-55/+100	
Storage Temperature (°C)	-55/+100	-55/+100	-55/+100	
Soldering Temperature	260°C, 5 seconds, 1.6 mm from case			

Solder Adherence per MIL-STD-202E, Method 208C

OPERATING CHARACTERISTICS (TA=25°C)		Red <b>-9320</b>	Yellow <b>-9321</b>	Green <b>-9327</b>
Luminous Intensity (mcd) I <sub>F</sub> =2mA	Min. Typical	1.2 2	1.2 1.8	1.2 1.8
Peak Wavelength (nm) λ Peak	Typical	635	583	565
Viewing Angle (2Θ <sup>½</sup> )	Typical	50°	50°	50°
Forward Voltage (V) I <sub>F</sub> =2mA	Typical Max.	1.8 2.2	1.9 2.7	1.8 2.2
Reverse Voltage (V), I <sub>R</sub> =50µA	Min.	5	5	5

 $<sup>\</sup>Theta^{\, |}$  is the off axis angle at which the luminous intensity is half the axial luminous intensity