

Have a Question? Chat with a Product Information Specialist

What can we help you find?

Email

**Products Industries** Resources **About TE My Account Innovation Support Center** 

## 640389-8 Product Details



640389-8

TE Internal Number: 640389-8 Active



#### MTA, CST-100 II, MT-6 and SL Connectors and Headers

(Statement of Compliance)



# **Product Highlights:**

- MTA-156 Product Line
- MTA Series
- Wire-to-Board
- Applies To Printed Circuit Board
- Connector

View all Features

**Quick Links** 

Share

- Pricing & Availability
- Search for Tooling
- View Mating Products (94)

Print

- Product Feature Selector
- ▶ Contact Us About This Product

Add to My Part List Request Sample Find Similar Products

#### **Buy Product**

#### **Documentation & Additional Information**

#### **Product Drawings:**

 MTA-156 HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE,... (PDF, English)

### Catalog Pages/Data Sheets:

MTA, CST-100 II, SL-156 and AMP Economy Power (EP) C... (PDF, English)

# **Product Specifications:**

None Available

## **Application Specifications:**

None Available

# **Instruction Sheets:**

None Available

# CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version AG)
- 3D Model (IGES, Version AG)
- 3D Model (STEP, Version AG)

#### Additional Information:

- Product Information
- Product Line Information

## **Related Products:**

- Tooling
- Mating Products (94)

List all Documents

# Product Features (Please use the Product Drawing for all design activity)

### **Product Type Features:**

- Product Line = MTA-156
- Series = MTA
- Product Type = Connector
- Connector Type = Header
- Termination Method to Wire/Cable = Solder
- Post Size (mm [in]) = 1.14 [.045]
- Termination Method to PC Board = Through Hole -Solder
- PCB Mounting Orientation = Right Angle
- PCB Mount Retention = Without
- PCB Mount Alignment = Without
- Right Angle Bending Side = Front
- Strain Relief = Without
- Sealed = No
- UL File Number = E28476

### **Housing Features:**

- Connector Style = Plug
- Centerline (mm [in]) = 3.96 [0.156]
- Housing Style = Friction Lock
- Housing Material = Polyester PBT GF
- Housing Color = Natural
- Mating Alignment = Without
- UL Flammability Rating = UL 94V-0

# **Configuration Features:**

- Number of Positions = 8
- Post Number(s) Omitted = None
- Backwall/Post Interruption(s) = Without
- Number of Rows = 1

### Industry Standards:

• CSA File Number = LR7189

#### **Mechanical Attachment:**

- Contact Retention = Without
- Mating Retention Type = Friction Lock
- Panel Mount Retention = Without

#### **Electrical Characteristics:**

- Contact Rated Current (A) = 7
- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 600

### **Termination Features:**

• Tail Length (mm [in]) = 3.18 [0.125]

#### **Dimensions:**

- Mating Post Length (mm [in]) = 10.16 [0.400]
- PCB Thickness, Recommended (mm [in]) = 1.60 [0.063]

#### **Body Features:**

- Header Type = Unshrouded
- Mating Retention = With
- Underplate Material Thickness (µm [µin]) = 1.27 [50.000]
- Assembly Integration Feature = Without

#### **Contact Features:**

- Contact Type = Pin
- Contact Shape = Square
- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Tin
- Tail Plating Material = Tin
- Contact Style = Right-Angle
- Contact Layout = In-Line
- Multiple Contact Types = Without
- Contact Plating, Mating Area, Thickness (µm [µin]) = 2.54 [100]
- Tail Plating Thickness (μm [μin]) = 2.54 [100]
- Underplate Material = Nickel

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS
- Agency/Standard = CSA, UL
- UL Rating = Recognized
- CSA Rating = Certified

#### **Environmental:**

• Operating Temperature (°C [°F]) = -55 - +105 [-67 - +221]

#### Conditions for Usage:

- Applies To = Printed Circuit Board
- For Use With = MTA .156 Connector Assembly or SL .156 Connector Assembly

#### Operation/Application:

• Application Use = Wire-to-Board

#### Packaging Features:

- Packaging Method = Package
- Packaging Quantity = 1

#### Other:

Brand = AMP

#### **Corporate Information**

About TE Investors News Room Supplier Portal Careers Terms & Conditions

Privacy Policy

**Quick Links** 

**Distributor Inventory Product Cross Reference** Documents & Drawings **Product Compliance Support Center** 

Site Map

**Customer Support** 

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

## **Keep Me Informed**















