

What can we help you find?

| Products Industries | Resources About TE My Acco | |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 5188834-1 Product De | tails | 😳 Share 🚔 Print 🔤 Email |
| TE Internal Number: 5188834-1 ✓ Active View 3D PDF | 2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM) Always EU RoHS/ELV Compliant (Statement of Compliance) Product Highlights: Connector Assembly Connector Assembly Connector Style = Plug Type = Type A Interface Type = 2mm HM View all Features | Quick Links Pricing & Availability Search for Tooling View Mating Products (1) Product Feature Selector Contact Us About This Product |
| | Add to My Part List Request Samp | ble Find Similar Products |
| | Buy Product | |
| Documentation & Additional I | Information | |
| Product Drawings: • MALE ASSEMBLY, Z-PACK | 2mm HM, TYPE A (PDF, English) | Iditional Information: • Product Line Information |
| Catalog Pages/Data Sheets: • None Available | Re | elated Products: Tooling Mating Products (1) |
| Product Specifications: Z-Pack 2 mm HM CONNEC | TORS (PDF, English) | |
| Application Specifications: • Z-PACK 2mm HM Intercon English) | nection System for Board-to-Bo (PDF, | |
| Instruction Sheets: • None Available | | |
| CAD Files: (CAD Format & Comp. 2D Drawing (DXF, Version 3D Model (IGES, Version C 3D Model (STEP, Version C | O) D) | |
| | List all Documents | |
| Product Features (Please use | the Product Drawing for all design activity) | |
| Product Type Features: Product Type = Connector Connector Type = Connector PCB Mounting Orientation Mechanical Attachment: Board Mount = Fixed Boar Front Mating Level = Leve Termination Features: Interface Type = 2mm HM | tor Assembly = Vertical Mating Alignm Mating Alignm Housing Color Housing Mater I 1 Configuration Feat Number of Rov Number of Pos | ent = With ent Type = Multi-Purpose Center = Gray rial = Polyester - GF ures: ws = 5+2 sitions = 154 |
| • Termination End Plating = Dimensions: | Tin over Nickel • Shielded = Yes • Rows Loaded = | |
| Module Length (mm [in]) | = 50.00 [1.968] Industry Standards | 5: |
| Body Features: | RoHS/ELV Con | npliance = RoHS compliant, ELV |

Have a Question? Chat with a Product Information Specialist


compliant • Type = Type A CompactPCI Designation = P1/P4 Lead Free Solder Processes = Not relevant for lead • ٠ free process RoHS/ELV Compliance History = Always was RoHS **Contact Features:** ٠ • Contact Configuration = Signal compliant • UL Flammability Rating = UL 94V-0 • Feedthrough Post Length (mm [in]) = 3.70 [0.145] • CompactPCI = Yes Other: • Contact Plating, Mating Area, Material = • Brand = AMP Performance-Based • Grounding Contact = Without ٠ Contact Style = Short Tail ٠ Number of Signal Contacts = 110 Contact Base Material = Phosphor Bronze ٠


Corporate Information Quick Links Customer Support Distributor Inventory Email or Chat With Us About TE Investors Product Cross Reference Find a Phone Number News Room Documents & Drawings Knowledge Base Supplier Portal Product Compliance Support Center Manage Your Account Site Map Careers Terms & Conditions **Keep Me Informed Privacy Policy** AODA Accessibility Policy AODA Multi-Year Accessibility Plan

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

in





| | | 2 | | | | | | | | | 1 | | | |
|------------------------------------------------|--------------|---------------------------------|------------------------|----------|--------------------|---------|------------|---------------------|-------------|--------|------------------|------------------|-----|---------|
| | ос Д D | | P | LTR | | | | VISION | | | | DATE | DWN | APVD |
| | | | | A1 | REVISED |) PER E | CO-11- | -00503 | 33 | | | 28MAR11 | RK | HMR |
| | | | | | | | | | | | | | | |
| | | | | | CO | | AC | \top | LA | YС | $) \bigcup \top$ | | | |
| | | | | | | | | | | | | | | |
| | | | | | Z | D | b | С | d | е | f | | | |
| | | | | 1 | C | В | В | В | В | В | С | | | |
| | | | | 2 | С | B | В | В | В | В | С | | | |
| | | | | 3 | C | B | B | <u>B</u> | B | B | C | | | |
| | | | | 4 | C | B | B | B | B | B | C | | | |
| | | | | 6 | C | B | B | B | B | B | C | | | |
| | | | | 7 | С | B | В | В | В | В | С | | | |
| | | | | 8 | С | В | В | В | В | В | С | | | |
| | | | | 9 | C | B | Β | B | Β | Β | С | | | |
| | | | | 10 | C | B | B | <u> </u> | B | B | C | | | |
| | | | | 11 | C | B | В | В | A | B | С | | | |
| | | | | | | N | 1ULTI C | PUF Ente | | E | | | | |
| | | | | | | | 0 | | . 1 X | | | | | |
| | | | | 15 | С | В | В | В | В | В | С | | | |
| | | | | 16 | C | B | Β | B | B | B | С | | | |
| | | | | 17 18 | C | B | B | B | B | B | C | | | |
| | | | | 19 | C | B | B | B | B | B | С | | | |
| | | | | 20 | C | B | B | B | B | B | C | | | |
| | | | | 21 | С | В | В | В | В | В | С | | | |
| | | | | 22 | С | В | В | В | В | В | С | | | |
| | | | | 23 | C | B | B | B | B | B | С | | | |
| | | | | 24 25 | C | B | B | B | B | B | C | | | |
| | | | 2 | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| RS | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | | | | | | | \square | 6 | 14 | | 1-5 | 5188834 | -9 | |
| | | | | | | | 2 | $\sqrt{5}$ | $\sqrt{14}$ | | | 88834- | | |
| | | | | | | | | $\overline{\wedge}$ | 4 | | | 88834- 88834- | | |
| | | | | | | | | <u> </u> | | | | PART | | |
| ONTROLLED DOCUM | 1ENT. | DWN B.CAR | BO | | 15JUL05 | | | | | | | | | |
| TOLERANCES UNLE OTHERWISE SPECIF | ISS FIED: | CHK G.SKIF APVD G.SKIF | PPER PPER | | 15JUL05 15JUL05 | NAME | | | SEMBI | Y 7 | | 2mm HV | | |
| $3 \text{ PLC} \pm -$ | ±0.2 | PRODUCT : | _{SPEC} 3—1 | 908 | 2 | | | | | TYPE | | | | |
| 4 PLC ± - ANGLES ± - FINISH SEE TABLE | | | | 902 | 9 | | cage cod | | •5188 | | | | _ | CTED TO |
| | | CUSTO | MER | DRA | wing | | | | S | cale 4 | :1 SHE | et of 1 2 | PRE | × A1 |

| MATERIAL: CONTACT: PHOSPHOR BRONZE. HOUSING: GLASS-FILLED POLYESTER. |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION PIN: 0.5µm MIN TIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER. |
| CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101 PERFORMANCE LEVEL 2. |
| A CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101 PERFORMANCE LEVEL 1. |
| $\frac{1}{5}$ connector tested and qualified against telcordia gr-1217-core quality level 3, central office applications. |
| 6 connector tested and qualified against telcordia gr-1217-core quality level 3, uncontrolled enviroment applications. |
| CONNECTOR MARKED WITH PART NUMBER AND DATE CODE. ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS, MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION. |
| 8 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID PATTERN DEFINED BY CONTACT LAYOUT. |
| 9 FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT". |
| 10 FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS". |
| A area reserved for keying part (basic P/N 100525) |
| POLARIZATION FEATURE. |
| 13 to be measured at bottom of shroud. |
| 14 CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT. |

6

-5

Δ

14 CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT, TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

8

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

C COPYRIGHT - By -

D

С

В

А

4805 (3/11)

THIS DRAWING IS A CO DIMENSIONS: mm MATERIAL SEE SHEET 1

| | 2 | | | | 1 | | | |
|-----|------|---|-----|-------------|-------------|------|-----|------|
| LOC | DIST | | | | REVISIONS | | | |
| AD | 00 | P | LTR | | DESCRIPTION | DATE | DWN | APVD |
| | • | | _ | SEE SHEET 1 | | - | _ | _ |
| | | | | | | | | |

В

А

D

С

| A CC | NTROLLED DOCUMENT. | DWN 15JUL05 B.CARBO | | _ TE | TE Connectivity | | | | |
|-------|----------------------------------------------------|-----------------------------------------------|-------------------------------|----------------------|-----------------|-------|-------------------|---------------------|--|
| | | CHK 15JUL05 G.SKIPPER | | - TE | | | | | |
| | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD 15JUL05 G.SKIPPER | MALE ASSEMBLY, Z-PACK 2mm HM, | | | | | | |
| | 0 PLC ± = 1 PLC ± 0.1 2 PLC ± = 3 PLC ± = | product spec 108—19082 application spec | - | | TYPE A | | | | |
| 4 PLC | | 114-19029 | SIZE | CAGE CODE DRAWING NO | | | | RESTRICTED TO | |
| | FINISH SEE SHEET 1 | WEIGHT |]A 1 | 00779 C- 51 | 88834 | | | — | |
| | | CUSTOMER DRAWING | | | scale 4:1 | SHEET | 2 ^{OF} 2 | 2 ^{REV} A1 | |