

• Home> 5590303007F

Part Number: **5590303007F** 

**General Description** 

Color Yellow

Series 559

Configuration Snap-In, Integral Resistor PMI

Description Yellow Snap-In LED, .250" Mounting Hole Indicator

Housing Black PBT, UL94V-0

LED Type Snap-In LED

Mounting Method Snap In

Compliancy Front of Panel, UL94V-0
Termination 24 AWG, 14" Wire Lead

Mounting Hole Size .250"

Panel Thickness 0.031" - 0.062"

Diffused Diffused

Luminous Intensity Typical 8

Forward Current mA 13 mA

Voltage 12.0 VDC

Operating Temperature -20 +85

Storage Temperature -55 +100



# 559 Series 5V & 12V - Integral Resistor Snap-in LED - .250" Mounting Hole Panel Mount Indicators



### **FEATURES / BENEFITS**

- ▲ RoHS Compliant
- ▲ Long life typically 100K hours
- ▲ Low power consumption uses up to 90% less energy than an incandescent indicator
- ▲ Front panel snap-in mounting requires no additional hardware
- No heat generated
- ▲ Resistant to shock and vibration
- ▲ Termination straight terminals for wire wrapping or lead wire for soldering or optional terminals
- Colors include red, green, yellow

#### **APPLICATIONS**

Dialight's 559 series LED panel mount indicator is available with a variety of LEDs including AllnGaP and InGaN technology for high brightness applications, bicolor and integral resistors. These indicators are designed for a variety of applications such as:

- · Main and remote power indication
- · Maintenance and warning indication
- Status indication Instrumentation ......and many more!

### **SPECIFICATIONS**

▲ Voltage requirements:

5 & 12 VDC (no resistor required)

▲ Mounting hole size: 0.249 -0.252" (6.32 - 6.40 mm)


▲ Panel thickness: 0.031-0.062" (.787 - 1.57 mm)

▲ Housing: Black housing material meets UL94V-0 and enhances LED contrast

- \*Operating temperature: -20°C to +85°C
- ▲ \*Storage temperature: -55°C to +100°C
- ▲ Electrical connection

Straight terminals for wire wrapping or either

6 or 14 inch 24 AWG lead wire



\* Based on LED color -Contact factory for details

Dialight reserves the right to make changes at any time in order to supply the best product possible.

Please see back of page for part numbers and additional specifications.







# 559 Series5V & 12V - Integral Resistor

## **Snap-in LED - .250" Mounting Hole Panel Mount Indicators**

## **5 VOLT OPERATION**

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	Voltage (VDC)	Current (mA)	Viewing Angle 2Ø 1/2	Maximum DC forward Voltage	Termination	RoHS Complaint
559-0102-001F	Red	635	8	5	10	60	7.5	Straight terminals	~
559-0202-001F	Green	565	8	5	10	60	7.5	Straight terminals	~
559-0302-001F	Yellow	583	8	5	10	60	7.5	Straight terminals	~
559-0102-003F	Red	635	8	5	10	60	7.5	6 inch wire leads	~
559-0202-003F	Green	565	8	5	10	60	7.5	6 inch wire leads	~
559-0302-003F	Yellow	583	8	5	10	60	7.5	6 inch wire leads	~
559-0102-007F	Red	635	8	5	10	60	7.5	14 inch wire leads	~
559-0202-007F	Green	565	8	5	10	60	7.5	14 inch wire leads	~
559-0302-007F	Yellow	583	8	5	10	60	7.5	14 inch wire leads	<b>~</b>

Typical Operating Characteristics (Ta=25°C)

## **12 VOLT OPERATION**

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	Voltage (VDC)	Current (mA)	Viewing Angle 2Ø 1/2	Maximum DC forward Voltage	Termination	RoHS Complaint
559-0103-001F	Red	635	8	12	13	60	15	Straight terminals	>
559-0203-001F	Green	565	8	12	13	60	15	Straight terminals	>
559-0303-001F	Yellow	583	8	12	13	60	15	Straight terminals	>
559-0103-003F	Red	635	8	12	13	60	15	6 inch wire leads	>
559-0203-003F	Green	565	8	12	13	60	15	6 inch wire leads	>
559-0303-003F	Yellow	583	8	12	13	60	15	6 inch wire leads	<b>&gt;</b>
559-0103-007F	Red	635	8	12	13	60	15	14 inch wire leads	>
559-0203-007F	Green	565	8	12	13	60	15	14 inch wire leads	>
559-0303-007F	Yellow	583	8	12	13	60	15	14 inch wire leads	>

Typical Operating Characteristics (Ta=25°C)

## **LED Panel Mount Indicator Selection**

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options.

- ▶ .156" (3.96mm) *558 Series*
- .250" (6.35mm) **559 Series**
- 5mm *605 Series*
- ▶ 6mm 606 Series
- 7mm *607 Series*

- 8mm *608 Series*
- 9mm *609 Series*
- ▶ 10mm *610 Series*
- ▶ 11/16" Watertight *557 Series*
- ▶ 1" Watertight *556 Series*



