

NC6-P107-12 Product Details



NC6-P107-12

TE Internal Number: 1-1437664-7



Barrier Strips

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Barrier Strip
- Barrier Style = Single Row, Dual Barrier
- Block Style = Flat
- 9.53 mm Centerline
- Vertical Mount Angle

Documentation & Additional Information

Product Drawings:

NC6-P107-XX ASSEMBLY (PDF, English)

Catalog Pages/Data Sheets:

- 1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE (PDF, English)
- BUCHANAN TERMINAL BLOCKS CATALOG BARRIER STRIPS (PDF, English)

Product Specifications:

None Available

Application Specifications:

None Available

Instruction Sheets:

None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version O1)
- 3D Model (IGES, Version O1)
- 3D Model (STEP, Version O1)

Additional Information:

• Product Line Information

Related Products:

Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Barrier Strip
- Block Style = Flat
- Mount Angle = Vertical
- Profile = Low
- Mounting Insert = Without

Mechanical Attachment:

- Mounting Options = None
- Mounting Bushing = With
- Mounting Style = Direct (All Positions Filled)
- Mounting Ears = Without

Electrical Characteristics:

• Top Hardware = Binding Combo Head

Termination Features:

Terminal Plating = Bright Tin

Body Features:

- Barrier Style = Single Row, Dual Barrier
- Terminal Style = Printed Circuit Pin 4.60 [.181]
- Screw Material = Steel
- Screw Plating = Zinc Chromate
- Terminal Material = Copper Alloy

Housing Features:

• Centerline (in [mm]) = 0.375 [9.53]

Configuration Features:

- Number of Positions = 12
- Number of Levels = Single
- Screw Head Type = Combo Phil-Slot

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Buchanan
- Comment = Other options available upon request, consult our Product Information Center.

