




Kings Part	Military Part	Gender	Dimensions (in inches)				Cable Group	Cross Reference To:	Cable Procedure	
KTH-2001			0.069		0.213			Connector	NONE	



NOTES:

1. FOR USE WITH RG-55, 58, 141, 142, 223 & ITT BA13077A CABLE GROUPS.
2. MATERIAL: ALLOY STEEL; FINISH: BLACK OXIDE

HEX SIZES (ACROSS FLATS)				DIE WIDTH	WEB WIDTH			
A	B	C	D	F	G	H	I	
.069	—	.213	—	.400	.080	—	—	

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
3 PLACE DECIMALS $\pm .004$
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

REVISIONS

ISSUE	CHANGES
2	CN 27545 C SD 8 NOV 85

REF:

FINISH

SPEC.

MATL.

SPEC.

CRIMP DIE

DRAWN JGL. DATE 15 JUN 72
APPR. DATE

KINGS ELECTRONICS
40 MARBLEDALE ROAD
TUCKAHOE, N. Y. 10707

KTH-2001

CN