


Kings Part	Military Part	Gender	Dimensions (in inches) A B C D				Cable Group	Cross Reference To:	Cable Procedure	
KTH-2002			0.069	0.100	0.255	0.400		Connector	NONE	



NOTES: 1. FOR USE WITH RG-59,62,71 & 210/U CABLE GROUPS. 2. MATERAL: ALLOY STEEL; FINISH: BLACK OXIDE

•	HEX SI	ZES (ACRO	SS FLATS)	 DIE WIDTH WEB WIDTH			
Δ	В	C	D	F	G H	1	
.069	.100	.255		.400	.093 .080		

UNLESS OTHERWISE SPECIFIED:

- 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010 3 PLACE DECIMALS ± .004 ANGLES ± 0° 30'.
 T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
- REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
- 3. NO FILLETS PERMITTED.
- 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.

SPEC. CRIMP DIE DATE 15 JUN 72 DRAWN JGL. DATE KINGS ELECTRONICS 40 MARBLEDALE ROAD TICKAHOE, N. Y. 10707

FINISH

SPEC. MATL.

REVISIONS CHANGES CN 27547 C AJ 2 DEC 85